7000 GreenZone Fridge Freezer 176.9 cm

OSC7C181DF



Cooling that adapts to you. No Frost prevents ice build-up
The 7000 No Frost AI CoolAssist Fridge-Freezer intuitively adapts to your lifestyle adjusting cooling for effortless freshness, whether you're adding groceries or away on holiday. No Frost prevents ice build-up, so you don't have to defrost.

Product Benefits & Features



AI CoolAssist® – advanced cooling that adapts to you
AI CoolAssist® intuitively adapts fridge settings to your daily routine - whether adding groceries or leaving for vacation. AI CoolAssist® learns your habits to optimize cooling temperature, and, during low-use times, can save up to 14% energy.*



TwinTech® No Frost - keeps food juicy and hydrated
TwinTech® No Frost has an advanced dual cooling system for the fridge and freezer. This technology ensures the freezer stays frost-free and the fridge humidity optimal, preventing the food from drying out.

*Energy savings measured on 1780 CB Multichill, 1780 CB Twintech Nofrost and 1225 Freezer NoFrost during activation of Autovacation mode versus factory default settings with AI CoolAssist off and tested with an external temperature of 25°C. Actual energy savings may vary based on usage patterns and



Every corner. Thoroughly chilled. With Cooling 360°
Cooling 360° protects food quality with a steady temperature. Available in metal, glass, or plastic, it prevents ingredients from freezing at the back by circulating cold air through multiple channels for even cooling throughout.*



ExtraChill drawer. For delicate ingredients
An additional pull-out drawer designed for organizing and storing delicate foods such as cheeses and cold cuts. It maintains a lower temperature than the rest of the fridge due to active circulation of cold air.

The Cooling 360° design and materials may vary by market and could include metal, glass, or plastic. Product specifications and materials may vary by region. Please check with your local retailer for more details.



New-era innovation. Unique fridge-freezer with recycled plastic
A new era of cooling is here. Introducing our fridge-freezer with an inner lining made of 70% recycled plastic. Plastic from discarded fridges is used to make new ones, helping reduce waste thorugh circularity.

*Inner liner rHIPS made with up to 70% recycled plastic representing 13% of total fridge plastic"

- TwinTech® NoFrost: Dual cooling keeps humidity in the fridge to prevent food from drying out, while the freezer stays frost-free.
- ExtraChill drawer: A drawer that's cooler than the rest of the fridge—ideal for meat, fish, and cheese.
- Open Door Signal: Visible & audible.
- Flexi-Space: Removable glass shelves in freezer compartment.
- Fixed fittings: Attach a matching cupboard door directly onto the appliance door.
- Designed and manufactured in Europe by AEG.

AEG

7000 GreenZone Fridge Freezer 176.9 cm

OSC7C181DF

Product Specification

Series	7000
Energy Rating	D
Freezer Defrost Type	No Frost
Fridge Capacity (L)	182
Freezer Capacity (L)	62
Main Colour	White
Dimensions (mm) (HxWxD)	1769x557x549
Fridge Light Type	Luna – 1 Top
Number of thermostats	1
Built-in Dimensions (mm) (HxWxD)	1780x560x550
Installation Type	BI DoD
Door Hinge Position	Right & Reversible
Cord Length (m)	2.4
Voltage (V)	220-240
Frequency (Hz)	50
Freezer Light Type	None
Freezer - Number Of Drawers	3 Full Width
Hatch Doors	No
Chiller Compartment	No
Product Number (PNC)	All Open
Minimum Ambient Temperature (°C)	10
Annual Energy Consumption (kWh)	173
Climate Class	SN-N-ST
Freezing Capacity (kg)	7
Noise (dB)	34

Door Colour	White
Noise Rating	B
Egg Trays	None
Plug or Hardwired	Uk Moulded Plug
High-Temp Indicator Type	Display;Sound With Switch Off Function
Holiday Function	No
Fridge Defrost Type	Auto
Fridge - Number of Shelves	3 Full Width
Fridge - Recommended Temp (°C)	4
Freezer - Recommended Temp (°C)	-18
Net weight (kg)	68
Gross weight (kg)	70