Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2014 with regard to energy labelling of household washing machines and household washer-dryers

Supplier's name or trade mark: HOTPOINT

Supplier's address: BEKO EUROPE MANAGEMENT S.R.L., VIA VARESINA, 204 20156 MILANO ITALY

Model identifier: HBWH 93 CARE UK

General product parameters:

Parameter	Value		Parameter	Value	
Rated capacity[(a)] (kg)	9,0		Dimensions in cm	Height	85
				Width	60
				Depth	58
Energy Efficiency Index[(a)] (EEI_W)	36,2		Energy efficiency class[(a)]	A	
Washing efficiency index[(a)]	1,031		Rinsing effectiveness (g/kg)[(a)]	4,9	
Energy consumption in kWh per cycle, based on the eco 40-60 programme at a combination of full and partial loads. Actual energy consumption will depend on how the appliance is used.	0,344		Water consumption in litre per cycle, based on the eco 40-60 programme at a combination of full and partial loads. Actual water consumption will depend on how the appliance is used and on the hardness of the water.	49	
Maximum temperature inside the treated textile[(a)] (°C)	Rated capacity	25	Weighted remaining moisture content[(a)] (%)	53,9	
	Half	26			
	Quarter	22			
Spin speed[(a)] (rpm)	Rated capacity	1 351	Spin-drying efficiency class[(a)]	B	
	Half	1 351			
	Quarter	1 351			
Programme duration[(a)] (h:min)	Rated capacity	3:48	Type	Free-standing	
	Half	2:53			
	Quarter	2:53			
Airborne acoustical noise emissions in the spinning phase[(a)] (dB(A) re 1 pW)	72		Airborne acoustical noise emission class[(a)] (spinning phase)	A	

Off-mode (W) (if applicable)	0,50	Standby mode (W) (if applicable)	0,50
Delay start (W) (if applicable)	4,00	Networked standby (W) (if applicable)	N/A

Minimum duration of the guarantee offered by the supplier: 24 months

This product has been designed to release silver ions during the washing cycle	**NO**

Additional information:

Weblink to the supplier's website, where the information in point 9 of Annex II to Commission Regulation (EU) 2019/2023 is found: https://docs.hotpoint.eu/

(a) for the eco 40-60 programme.

EPREL registration number: 2472009

Model placed on the Union market from 30/10/2025.

https://eprel.ec.europa.eu/qr/2472009

Supplier: BEKO EUROPE MANAGEMENT S.R.L. (Authorised representative) **Website:** www.bekoeurope.com

Customer care service:

Name: BEKO EUROPE MANAGEMENT S.R.L. **Website:**

Email: public_inquiry@europeanappliances.com **Phone:** +39 02 83715807

Address:
VIA VARESINA, 204
20156 MILANO
ITALY