ThinkVision M16 Monitor 64BFUAR1AU

Lenovo

The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- 16-inch WUXGA IPS display with 16:10 aspect ratio
- 970g, 7 mm thickness without stand
- 300 nits brightness, 45% NTSC, 1500:1 contrast ratio
- TÜV-certified Flicker-Free and Hardware Low Blue Light
- Ergonomic stand with 0-90° tilt adjustment and up to 10mm height adjustment
- Dual USB-C®® ports with up to 65W power delivery
- Case color - Eclipse Black
- 3-year limited warranty

Premium Care - Advanced Support from Real People. Real Fast.

REAL PERSON
Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.

REAL FAST
Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.

HASSLE FREE
'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

PC HEALTH CHECK
Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Recommended Accessories United Kingdom

NanoSaver Cable Lock from Lenovo

4XE1L51710

NanoSaver Combination Cable Lock from Lenovo

4XE1F30277

NanoSaver Essential Cable Lock from Lenovo

4XE1F30276

NanoSaver Twin Head Nano/MS 2.0 MasterKey Cable Lock from Lenovo

4XE1B81920

NanoSaver Twin Head Nano/MS 2.0 Cable Lock from Lenovo

4XE1B81919

NanoSaver MasterKey Twin Head Lock Cable Lock from Lenovo

4XE1B81918

>> View More Accessories

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

ThinkVision M16 Monitor 64BFUAR1AU

Lenovo

PERFORMANCE

Display Size
16″

View Area
344.7x215.4 mm

Panel
In-Plane Switching

Backlight
WLED

Aspect Ratio
16:10

Resolution
1920x1200

Pixel Pitch
0.1795x0.1795 mm

Dot / Pixel Per Inch
142 dpi

View Angle (H / V)
178° / 178°

Response Time
6ms (Extreme mode) / 8ms (Typical mode)

Color Support
16.7 Million

Refresh Rate
60Hz

Brightness
300 cd/m²(panel)

Contrast Ratio
1500:1

Color Gamut
45% NTSC

Screen Surface Treatment
Anti-glare

Curvature
None

Camera
None

Microphone
None

Speakers
None

Power Consumption (Typical / Maximum)
4.5W / 5.5W

Touchscreen
None

DESIGN

Stand
Tilt, Height Adjust Stand

Case Color
Eclipse Black

Side Bezel Width
7.1 mm

ThinkCentre M Series Support
None

Pen
None

Dimensions (WxDxH)[1]
- Highest Position | 360.0 x 116.5 x 262.1 mm (14.17 x 4.59 x 10.32 inches)
- Lowest Position | 360.0 x 116.8 x 252.1 mm (14.17 x 4.60 x 9.93 inches)

Packaging Dimensions (WxDxH)
413.0 x 300.0 x 76.0 mm (16.26 x 11.81 x 2.99 inches)

Weight[2]
0.97 kg (2.1 lbs)

Packaging Weight
2.2 kg (4.8 lbs)

CONNECTIVITY

Left Ports
1x USB-C® (Hi-Speed USB / USB 2.0), with USB PD 3.0 and DisplayPort™ 1.2, up to 65w PD

Right Ports
1x USB-C® (Hi-Speed USB / USB 2.0), with USB PD 3.0 and DisplayPort™ 1.2, up to 65w PD

SERVICE

Base Warranty
3-year limited warranty

CERTIFICATIONS

Environmental Certification
ENERGY STAR® Certified, EPEAT Gold, RoHS, EU Energy Efficiency Level (Level-B)

Ergonomic Certification
TÜV Rheinland® Flicker Free, TÜV Low Blue Light (Hardware solution)

Sync Technology
None

SOFTWARE

Operating System
Support Windows® 10, Windows® 11

ACCESSORIES

In the Box
- Monitor with stand
- 1x USB-C® to USB-C® cable (1m)
- 1x Sleeve
- Quick setup guide

MODEL

Region : APS
EAN / UPC / JAN: 0199273686551 / 199273686551 / None
Announce Date : 2026-05-14

Product image is a sample, it may not match the real color of this model

Note:
[1] The system dimensions may vary depending on configurations.
[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

- Please refer to the official Lenovo store website or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.