

Lenovo 500w 2-in-1 Gen 5

Designed for business professionals, this next-generation laptop delivers reliable performance for everyday workflows. Powered by the Intel® Core™ i3 Processor N350, it ensures smooth multitasking, whether you're managing spreadsheets, drafting proposals, or handling virtual meetings. With 128GB of storage, professionals can securely store essential documents and presentations, while support for up to 8GB LPDDR5-4800 memory enables seamless operation across multiple applications. Its lightweight design enhances portability, making it an ideal choice for consultants, sales teams, and remote workers who need efficiency on the go.



Redefining possibilities with powerful performance and groundbreaking on-device AI

Whether you're crunching numbers, analyzing market trends, or collaborating on presentations, these laptops, equipped with the latest-generation processors and ample memory, ensure unparalleled efficiency and reliability.

The 12.2” IPS touch display with 300-nit brightness delivers crisp, vibrant visuals, while Corning® Gorilla® Glass provides superior protection against scratches and cracks. Elevate your video collaboration experience with a 1080p front-facing camera and an AI-accelerated microphone, which enhances audio quality and reduces background noise. The garaged stylus ensures quick access for seamless note-taking, while Lenovo Pencil Touch transforms any No. 2 pencil into a precise digital tool for sketching and annotations.

Lenovo DuraSpec technology ensures exceptional toughness, withstanding spills up to 360ml, desk-height drops onto concrete, and an A-cover force of up to 60kg. Designed for long-term resilience, the device also features hardened ports, anti-peel D-cover rubber feet, and anti-pick keys. Additionally, a copper heat pipe enhances thermal efficiency, keeping the system cool even under heavy workloads.

Stay productive with the 47Wh battery, which supports Rapid Charge, delivering up to 80% power in just one hour. With Intel® Wi-Fi 7 (5 Gig) connectivity, professionals can enjoy seamless collaboration, fast cloud access, and high-speed data transfers anywhere.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Accessories

Lenovo 15.6-inch Laptop Casual Backpack B210 Grey



- Extra cushioning and padding for maximum comfort
- Waterproof fabric to keep your gadgets dry and safe
- Conviniently placed compartments and pockets for easy access.

PN: GX40Q17225

Lenovo Go 130W Multi-Port Charger



- Get the maximum power out of your charger
- On-the-go port expansion & charging
- Power multiple devices through easy interface connection

PN: G0A6130WUS, G0A6130WEU, G0A6130WUK

Lenovo 500w 2-in-1 Gen 5

Performance

Processor
Intel N-series or Intel Core N-series

Operating System*
Windows 11 Pro or Home

Graphics
Intel Graphics (integrated)

Memory
8GB LPDDR5-4800, soldered

Storage
UFS models:
128GB UFS 2.2 on systemboard, one M.2 2242 PCIe 3.0 x2 slot
SSD models:
One drive, 256GB M.2 2242 SSD

Audio*
High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Atmos
Dual-microphone array or single + dual microphones

Camera*
Front HD 720p, with privacy shutter
Front HD 720p, with privacy shutter; rear 5MP
Front FHD 1080p, with privacy shutter
Front FHD 1080p, with privacy shutter; rear 5MP

Battery
47Wh (up to 13 hr) battery, Rapid Charge with 65W AC adapter

Power Adapter*
45W USB-C adapter, PD3.0
65W USB-C adapter, PD3.0

Design

Display
12.2" WUXGA (1920x1200) IPS glossy 16:10, 300nits, 50% NTSC, Corning Gorilla Glass, touch

Multimode
Laptop, tent, stand, and tablet modes supported by 360° hinge

Pen*
Lenovo Integrated Pen*

Keyboard
6-row, Copilot key

Touchpad
Mylar surface touchpad
60.5 x 104 mm (2.38 x 4.09 inches)

Dimensions
287 x 208 x 19.75 mm (11.3 x 8.2 x 0.78 inches)

Weight
Around 1.33 kg (2.92 lbs)

Color
Slate grey

Case material
PC-ABS (top)
PC-ABS (bottom)

Connectivity

WLAN + Bluetooth*
802.11ax (Wi-Fi 6E), Bluetooth 5.3

Ports
1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
1x USB-C (USB 5Gbps / USB 3.2 Gen 1), with USB PD 45-65W
1x USB-C (USB 10Gbps / USB 3.2 Gen 2), with USB PD 45-65W & DP
1x HDMI 1.4
1x Headphone / microphone combo jack (3.5mm)

Docking
Docking support via USB-C

Security & Privacy

Security
Discrete TPM 2.0
Kensington Nano Security Slot
Camera privacy shutter

Environmental

Material
85% recycled ABS C cover frame
50% recycled PC ABS D cover
48% recycled TPU D cover fee
90% recycled PCC plastic
30% recycled magnets
90% recycled PCC plastic
80% recycled FSC Carton
80% recycled FSC accessory tray
90% ocean bound plastic bag
100% recycled dry-pressed pulp cushion

Certifications

Green Certifications
ENERGY STAR 9.0*
EPEAT 1.0 Gold Registered*
ErP Lot 6/26
RoHS compliant

Other Certifications
ASTM F963*
MIL-STD-810H military test passed
TÜV Rheinland Low Blue Light (Hardware Solution)

Items with * are optional and only available on selected models. Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2026 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.