Specifications

Eaton P036-EN4-ARD-6

PDU Power Cord, C19 to P-Lock Lite C20 - 20A, 250V, 12 AWG, 4 ft. (1.2 m), Red, 6 Pack

General specifications

PRODUCT NAME	Eaton Tripp Lite series P-Lock power cord
CATALOG NUMBER	P036-EN4-ARD-6
UPC	037332303318
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	18.11 in
PRODUCT WIDTH	14.17 in
PRODUCT WEIGHT	4.81 lb
WARRANTY	Limited lifetime
COMPLIANCES	REACH RoHS
CERTIFICATIONS	CAN/CSA C22.2 UL Listed cUL Listed CSA C22.2.
GLOBAL CATALOG	P036-EN4-ARD-6
PRODUCT TYPE	P-Lock power cord

Powering Business Worldwide

Product specifications

TYPE	PDU Extension Power Cord
POWER CORD COLOR	Red
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
RELATIVE HUMIDITY	35 TO 85% RH, Non-Condensing
STORAGE TEMPERATURE	23° to 158°F (-5° to 70°C)
DEVICE COMPATIBILITY	Computer Monitor/HDTV PDU Printer Server Tablet UPS
AWG-SIZE	12
CABLE LENGTH	4 Foot
NUMBER OF CONDUCTORS	3
OUTER CABLE DIAMETER	11.2mm
POWER CORD JACKET TYPE	SJT
WIRE SIZE (AWG) - MAX	3.31
COLOR	Red
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Red
PACKAGE CONTENTS	(6) PDU Power Cords, C19 to P-Lock Lite C20, 4 ft. (1.2 m), Red
CONNECTOR COLOR	Red
CONNECTOR TYPE	Power
PRODUCT FEATURES	Locking High Voltage Locking Plug
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PLUG COLOR	Red
SIDEA CONNECTOR1	IEC-320-C20
SIDEB CONNECTOR1	IEC-320-C19
CONNECTOR GROUP	C19 C20
CONNECTOR	IEC 320-C19 IEC 320-C20

Resources

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.