Product Datasheet

PBlaze7 7940 Series 15.36TB U.2-15MM PCIe 5.0



- **Product Code:** MZQL215THBLA-00A07-OS
- **Product EAN:** 5059902200624
- **Warranty:**

Technical Specifications

Operational Conditions

Operating Temperature (T-T):	0 - 77 °C
Minimum Operating Temperature:	0 °C
Maximum Operating Temperature:	77 °C

Features

SSD Capacity:	15 TB
SSD Form Factor:	U.2

Interface:	PCI Express 5.0
NVMe:	Yes
Memory Type:	3D TLC
Component For:	Server
Hardware Encryption:	Yes
Target Workload:	Read Intensive (RI)
Sequential Read Speed (ATTO):	13500 MB/s
Sequential Write Speed (ATTO):	9500 MB/s
Mean Time Between Failures (MTBF):	2500000 h
Drive Writes Per Day (DWPD):	1

Logistics Data

Country Of Origin:	China, Taiwan

Origin Storage Limited

2-4 Rutherford Centre, Rutherford Road, Basingstoke, Hampshire, RG24 8PB UK

Tel: +44 (0)1256 351500 | **E-Mail:** sales@originstorage.com | **Web:** www.originstorage.com

Copyright 2026 - Origin Storage Limited | All trademarks are the property of their respective owners, E&OE.