Legion 32Q-2c Monitor 68F5GACBEU





The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- 31.5" QHD (2560 × 1440) fast VA display, 1500R curvature
- 240Hz refresh rate, 0.5ms MPRT response time
- AMD FreeSync™™ Premium and VESA Adaptive Sync support
- 99% sRGB and 95% DCI-P3 color gamut, 1.07B colors
- 400 nits brightness, VESA DisplayHDR™™ 400
- Natural Low Blue Light with Eyesafe®® 2.0 certification
- Ergonomic stand with lift, tilt, and swivel adjustments
- 2 × HDMI®® 2.1 FRL, 1 × DisplayPort™™ 1.4
- Lenovo®® Accessory Display Manager (LADM) and Legion Space software support
- Case color - Eclipse Black
- 3-year

Premium Care - Advanced Support from Real People. Real Fast.

REAL PERSON
Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.

REAL FAST
Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.

HASSLE FREE
'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

PC HEALTH CHECK
Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Product Illustration









Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Legion 32Q-2c Monitor 68F5GACBEU

PERFORMANCE

Display Size
31.5"

View Area
697.3x392.3 mm

Panel
Vertical Alignment

Backlight
WLED

Aspect Ratio
16:9

Resolution
2560x1440

Pixel Pitch
0.2724x0.2724 mm

Dot / Pixel Per Inch
93 dpi

View Angle (H / V)
178° / 178°

Response Time
0.5 ms (MPRT) / 1 ms (Level 4) / 2 ms (Level 3) / 4 ms (Level 2) / 5 ms (Level 1) / 6 ms (G to G)

Color Support
1.07 Billion

Refresh Rate
240Hz

Brightness
400 cd/m² (Typical) / 410 cd/m² (Peak)

Contrast Ratio
4000:1

Color Gamut
99% sRGB, 95% DCI-P3

Screen Surface Treatment
Anti-glare

Curvature
1500R

Camera
None

Microphone
None

Speakers
None

Power Consumption (Typical / Maximum)
30W / 45W

Power Adapter
Integrated

Touchscreen
None

Smart System
None

DESIGN

Stand
Tilt, Swivel, Height Adjust Stand

Case Color
Eclipse Black

Side Bezel Width
1.8 mm

Mounting
Supports VESA mount 100 x 100 mm

ThinkCentre M Series Support
None

Dimensions (WxDxH)[1]
- Head Only | 714.7 x 102.8 x 423.1 mm (28.14 x 4.05 x 16.66 inches)
- Lowest Position | 714.7 x 230.0 x 459.1 mm (28.14 x 9.05 x 18.07 inches)
- Highest Position | 714.7 x 230.0 x 594.1 mm (28.14 x 9.05 x 23.39 inches)

Packaging Dimensions (WxDxH)
820.0 x 232.0 x 516.0 mm (32.28 x 9.13 x 20.31 inches)

Weight[2]
- Monitor With Stand | 8.5 kg (18.8 lbs)
- Monitor Head Only | 5.2 kg (11.4 lbs)

Packaging Weight
- EPS: 10.9 kg (24 lbs)
- Pulp: 13.5 Kg (29.7 lbs)

CONNECTIVITY

Rear Ports
- 2 x HDMI® 2.1 FRL[3]
- 1x DisplayPort™ 1.4 (HBR3)[4]

SERVICE

Base Warranty
3-year

CERTIFICATIONS

Environmental Certification
RoHS, EU Energy Efficiency Level (Level-F), Volatile Organic Compound Certification

Ergonomic Certification
TÜV Low Blue Light (Hardware solution), Eyesafe® Display 2.0

Sync Technology
AMD FreeSync™ Premium, VESA Adaptive Sync

Special Features
- DisplayHDR™ 400
- AMD FreeSync™ Premium
- VESA Adaptive Sync
- Lenovo® Artery (Lenovo® Accessories and Display Manager)[5]
- Legion Space
- Gaming Console Support: PS4 / SWITCH / PS5 / Xbox One X / Legion Go
- Natural Low Blue Light

SOFTWARE

Operating System
Support Windows® 10, Windows® 11

ACCESSORIES

In the Box
- Monitor with stand
- 1x DP cable (1.8m)
- 1x Power cable (1.8m)
- Quick setup guide
- Warranty booklet

MODEL

Region	: EMEA
EAN / UPC / JAN	: 0199273902835 / 199273902835 / None
Announce Date	: 2026-07-13

Note:
[1] The system dimensions may vary depending on configurations.
[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.
[3] Supports 2560 x 1440@240Hz as specified in HDMI 2.1 FRL.
[4] Supports 2560 x 1440@240Hz bandwidth 32.4Gbps.
[5] Formerly Lenovo Display Control Center. Supports Windows 10 & 11, Mac OS (functions vary across systems).

- Please refer to the official Lenovo store website or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.