ThinkPad E14 Gen 8 (Intel) 21Y6009QMH





The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- Intel Core™ Ultra 5 325, 8C (4P + 4LPE) / 8T, Max Turbo up to 4.5GHz, 12MB Intel® Smart Cache
- 1x 24GB SODIMM DDR5-5600
- 512GB SSD M.2 2242 PCIe® 4.0x4 NVMe® Opal 2.0
- Integrated Intel® Graphics
- Windows® 11 Pro, WE (EN/FR/DE/NL/IT)
- Case color - Black
- 3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in, CO2 Offset 0.2 ton (3rd Gen) TP WHB (CPN)

Premier Support - A direct 24x7x365 line to our most elite technicians.

- Advanced technical support, 24x7x365, in more than 100 markets
- Comprehensive hardware & OEM software support
- Single point of contact for simplified end-to-end case management
- Technical Account Managers for proactive relationship and escalation management
- Priority on service delivery and repair parts
- Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Recommended Accessories

United Kingdom



Lenovo 540 Convertible 16" Tote Backpack (Beige)

GX41X41974



ThinkPad Thunderbolt 4 Dock Gen2 7000-UK/HK/SGP/MYS/SRI

40BG0135UK



Lenovo 900 Multi-Device Wireless Mouse

GY51V37443



Lenovo 1TB Value Gen4 OPAL2 M.2 2242 SSD IV

4XD1V92800



Lenovo 65W Mini USB-C GaN Charger

G0A665WBUK



ThinkPad Dual-Mode Wireless ANC Foldable Headset 8550 (Aura Edition) - USB-A,...

4XD1V23301

>> View More Accessories

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

ThinkPad E14 Gen 8 (Intel) 21Y6009QMH

PERFORMANCE

Processor
Intel Core™ Ultra 5 325, 8C (4P + 4LPE) / 8T, Max Turbo up to 4.5GHz, 12MB Intel® Smart Cache

AI PC Category
Copilot+ PC[1]

NPU
Up to 47 TOPS

Graphics
Integrated Intel® Graphics

Chipset
Intel® SoC Platform

Memory
1x 24GB SODIMM DDR5-5600

Memory Slots
Panther Lake: two DDR5 SODIMM slots, dual-channel capable

Max Memory[2]
Panther Lake: Up to 64GB DDR5-5600

Storage
512GB SSD M.2 2242 PCIe® 4.0x4 NVMe® Opal 2.0

Storage Slot
Panther Lake: two M.2 slots • One M.2 2242 PCIe® 4.0 x4 slot • One M.2 2280 PCIe® 4.0 x4 slot

Max Storage Support[3]
Panther Lake: up to two drives, 2x M.2 SSD • M.2 2242 SSD up to 1TB • M.2 2280 SSD up to 1TB[4]

Card Reader
No card reader

Audio Chip
High Definition (HD) Audio, Senary SN6147 codec

Speakers
Stereo speakers, 2W x2, Dolby Atmos®, audio by HARMAN

Microphone
2x, Array

Camera
FHD 1080p + IR Hybrid with Privacy Shutter

Battery
64Wh

Power Adapter
65W USB-C® (3-pin)

DESIGN

Display
14" WUXGA (1920x1200) IPS 400nits Anti-glare, 45% NTSC, 60Hz[5]

Touchscreen
None

Screen-to-Body Ratio
90%

Pen
Pen Not Supported

Keyboard
Backlit, English (EU)

Dimensions (WxDxH)[6]
313 x 220.3 x 10.1/15.25 (front/rear), 19.7 (maximum) mm; 12.32 x 8.67 x 0.40/0.60 (front/rear), 0.78 (maximum) inches

Weight[7]
Starting at 1.34 kg (2.95 lbs)

Case Color
Black

Case Material
Aluminium (Top), Aluminium (Bottom)

SOFTWARE

Operating System
Windows® 11 Pro, WE (EN/FR/DE/NL/IT)

Bundled Software
Lenovo® AI Now

CONNECTIVITY

WLAN + Bluetooth
Wi-Fi® 7, 802.11be 2x2 + BT5.4

WWAN
WWAN Not Supported

SIM Card
No physical SIM card included

Ethernet
100/1000M (RJ-45)

NFC
No NFC

Standard Ports
- 1x USB-A (USB 5Gbps)
- 1x USB-A (USB 10Gbps), Always On
- 2x Thunderbolt™ 4, with USB PD 15-65W and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)

Docking
Various docking solutions supported via Thunderbolt™ / USB-C®. For more compatible docking solutions, please visit Docking for ThinkPad® E14 Gen 8 (Intel®)

SECURITY & PRIVACY

ThinkShield
ThinkShield is a comprehensive security solution that encompasses hardware, software, and supply chain components. For more detials, visit here

Security Chip
Discrete TPM 2.0 Enabled

Physical Locks
Kensington Nano Security Slot™, 2.5 x 6 mm

Smart Card Reader
No Smart Card Reader

Fingerprint Reader
Touch Style, Match-on-Chip, Integrated in Power Button

Other Security
- Camera privacy shutter
- IR camera for Windows® Hello (facial recognition)

MANAGEABILITY

System Management
Non-vPro®

SERVICE

Base Warranty
1-year, Courier or Carry-in

Included Upgrade
3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in, CO2 Offset 0.2 ton (3rd Gen) TP WHB (CPN)

ACCESSORIES

Bundled Accessories
None

CERTIFICATIONS

Green Certifications
- ENERGY STAR® 9.0
- EPEAT 1.0 Gold Registered[8]
- EPEAT 2.0 Gold Registered[8]
- ErP Lot 6/26
- RoHS compliant
- TCO Certified, generation 10

Mil-Spec Test
MIL-STD-810H military test passed

Other Certifications
TÜV Rheinland® Low Blue Light (Software Solution)

MODEL

TopSeller	: Yes	**EAN / UPC / JAN**	: 0828132277226
Announce Date	: 2026-06-16	**End of Support**	: 2032-11-14

Note:
[1] Copilot+ PCs have at least 16GB RAM, 256GB storage, and a NPU that runs 40+ TOPs to run the latest AI tools build-in latest Windows 11 to accelerate productivity and creativity.
[2] The max memory is based on the test results with current Lenovo memory offerings.
[3] The storage capacity supported is based on the test results with current Lenovo storage offerings.

- Please refer to the official Lenovo store website or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.
- To view full note details, please visit the web page.