Product information according to Commission regulation (EU) No 66/2014

Attribute Name	Position	Symbol	Value	Unit
Model Denomination			NRN84A06XB 949598748	
Type of hob			Built-In Hob	
Number of electric cooking zones			4	
Number of electric cooking areas			Hide	
Heating technology (induction cooking zones and cooking areas, radiant cooking zones, solid plates) per electric cooking zone and/or area			Radiant Heater	
For circular cooking zones or area: diameter of useful surface area per electric heated cooking zone, rounded to the nearest 5 mm	Left Front	Ø	21,0	cm
	Left Rear	Ø	14.5	cm
	Right Front	Ø	14.5	cm
For non-circular cooking zones or areas: length and width of useful surface area per electric heated cooking zone or area, rounded to the nearest 5 mm	Right Rear	L x W	26.5 x 17,0	cm
Energy consumption per cooking zone or area calculated per kg	Left Front	$EC_{electric\ cooking}$	194.9	Wh/kg
	Left Rear	$EC_{electric\ cooking}$	188	Wh/kg
	Right Front	$EC_{electric\ cooking}$	188	Wh/kg
	Right Rear	$EC_{electric\ cooking}$	191.6	Wh/kg
Energy consumption for the hob calculated per kg		$EC_{electric\ hob}$	190.6	Wh/kg

EN 60350-2 - Household electric cooking appliances -- Part 2: Hobs - Methods for measuring performance"

Suggestions for a correct use in order to reduce the environmental impact:
• When you heat up water, use only the amount you need.
• If it is possible, always put the lids on the cookware.
• Before you activate the cooking zone put the cookware on it.
• Put the smaller cookware on the smaller cooking zones.
• Put the cookware directly in the centre of the cooking zone.
• Use the residual heat to keep the food warm or to melt it."