TOUCHSCREENS

## INFORMATION




# 11” PCAP 10pt touchscreen PC with Android, Power over Ethernet Technology, NFC/RFID reader and a RGB LED bar around the screen

The smart and intuitive 11" ProLite TW1125LAS-B3PNR brings intuitive interaction and clear communication to meeting rooms, reception areas and information points. Combining a responsive touchscreen with Android, this compact touch panel PC runs applications directly on the device, supporting a wide range of professional uses—from room reservations and visitor check-in to interactive information and digital signage.


An integrated RGB LED bar makes room availability visible at a glance, while the NFC/RFID reader supports contactless check-in, employee authentication and other app-enabled interactions. Built-in microphones and speakers extend its versatility to voice-enabled applications and interactive services. Power over Ethernet delivers power and data through a single cable, simplifying installation and keeping cabling discreet. Flexible mounting in landscape, portrait or face-up orientation allows the display to fit naturally into a variety of environments.

Additionally, it integrates effortlessly with iiSignage², iiyama’s Content Management System (CMS), giving you full control over your messages and advertising, in landscape portrait and face-up position.




## RGB Led bar

The RGB Led bar will clearly and intuitively indicate the room's availability status and can display a wide range of colors.




## NFC & RFID reader

Thanks to the NFC/RFID reader, the touch panel PC alows to communicate wirelessly with enabled devices or tags within close proximity.



## Connectivity

The RJ45 (LAN) connector supporting Power over Ethernet technology (POE) allows to provide both data connection and power by a single cable, which simplifies installation in areas where many cables would interfere with the environment.



## Android OS

Thanks to Android OS, you can easily customize the display to your needs by installing applications directly to it.

## SPECIFICATION

### 01 DISPLAY CHARACTERISTICS

| | |
|---|---|
| **Design** | Edge to edge glass |
| **Diagonal** | 10.95", 27.81cm |
| **Panel** | IPS Panel Technology, LED |
| **Native resolution** | 1920 x 1200 (2 megapixel HD) |
| **Aspect ratio** | 16:10 |
| **Panel brightness** | 450 cd/m² |
| **Brightness** | 405 cd/m² with touch |
| **Light transmittance** | 90% |
| **Static contrast** | 1500:1 with touch |
| **Response time (GTG)** | 25ms |
| **Viewing zone** | horizontal/vertical: 160°/160°, right/left: 80°/80°, up/down: 80°/80° |
| **Colour support** | 16.7mln |
| **Viewable area W x H** | 147.4 x 235.8mm |
| **Pixel pitch** | 0.1228mm |
| **Bezel colour and finish** | black, matte |

### 02 TOUCH

| | |
|---|---|
| **Touch technology** | projective capacitive |
| **Touch points** | 10 (HID, only with supported OS) |
| **Touch method** | finger, glove (latex), capacitive stylus |
| **Touch interface** | USB |

### 03 INTERFACES / CONNECTORS / CONTROLS

| | |
|---|---|
| **Audio output** | Mini jack x1<br>Speakers 2 x 2W |
| **HDCP** | yes |
| **USB ports** | x3 (1x v. 3.2 (Gen 1, 5Gbit; DC5V, 900mA), 1x 2.0 (DC5V, 500mA), 1 x USB-C (DC5V, 900mA) video output only) |
| **RJ45 (LAN)** | x1 (PoE - IEEE802.3at/max. 24W, 1000M) |
| **Microphone** | x1 (Quad microphone) |

### 04 FEATURES

| | |
|---|---|
| **Integrated software** | GMS, Android 16 |
| **CPU** | Rockchip RK3576 Octa-Core 4x A53 + 4x A72, up to 2.2GHz |
| **GPU** | ARM G52 MC3 |
| **Storage** | 64GB eMMC |
| **Memory** | 4GB LPDDR5X |

| | |
|---|---|
| **WiFi** | IEEE802.11ax/ac/a/b/g/n |
| **Bluetooth** | 5.4 |
| **Hardware** | NFC (NXP 7221), RFID (125kHZ,9600kbit/s) |
| **Extra** | Auto-rotation, SD card slot (microSD), anti-glare coating, PoE, NFC/RFID reader, RGB Led lightbar, slide on wall mount with cable cover |
| **Kiosk mode** | yes |
| **Max. non-stop operating time** | 24/7 |
| **Glass thickness** | 1.1mm |
| **Glass hardness** | 6H |

## 05 GENERAL

| | |
|---|---|
| **Control buttons** | Power switch |
| **Applications** | Applications: Bootup timer, calculator, calendar, Chrome, Alarm / clock / Timer / Stopwatch, orginize albums, Gmail, HDMI in, iiSignage2, iiyama player, maps, play store, PwmLightDemo, settings, sound recorder, systemlock |
| **Flicker free** | yes |

## 06 MECHANICAL

| | |
|---|---|
| **Orientation** | landscape, portrait, face-up |
| **VESA mounting** | 75 x 75mm, 100 x 100mm |
| **Cable management system** | yes |
| **MTBF** | 50000 hours |

## 07 ACCESSORIES INCLUDED

| | |
|---|---|
| **Cables** | power (2.5m) |
| **Guides** | quick start guide, safety guide |
| **Other** | AC adapter, interchangeable plugs (EU/UK), cable cover/wall mount |
| **Cable cover** | yes |

## 08 POWER MANAGEMENT


| | |
|---|---|
| **Power supply unit** | external |
| **Power supply** | DC 12 V |
| **Power usage** | 9W typical, 0.5W stand by, 0.3W off mode |

## 09 SUSTAINABILITY

| | |
|---|---|
| **Regulations** | CE, EAC, RoHS support, ErP, WEEE, REACH, UKCA |
| **REACH SVHC** | above 0.1%: Lead |

## 10 DIMENSIONS / WEIGHT

| | |
|---|---|
| **Product dimensions W x H x D** | 260 x 171 x 23.5mm |
| **Box dimensions W x H x D** | 456 x 394 x 236mm |
| **Weight (without box)** | 1.07kg |
| **Weight (with box)** | 2.2kg |
| **EAN code** | 4948570128440 |



## GALLERY


iiyama
ProLite
TW1125LAS
11" TOUCH
RGB


iiyama
ProLite
TW1125LAS
11" TOUCH
1920x1200
RGB
LED BAR


iiyama
ProLite
TW1125LAS
11" TOUCH
1920x1200
RGB
LED BAR



iiyama
ProLite
TW1125LAS
11" TOUCH
1920x1200
RGB
LED BAR



iiyama
ProLite
TW1125LAS
11" TOUCH
1920x1200
RGB
LED BAR


iiyama
ProLite
TW1125LAS
11" TOUCH
1920x1200
RGB
LED BAR





















All trademarks and registered trademarks acknowledged. E & O E. Specification subject to change without notice. All LCD's comply with ISO-9241-307:2008 in connection with pixel defects. **© IIYAMA CORPORATION. ALL RIGHTS RESERVED**