Streamer 3in1 Wireless Mic Kit

Item no.:

126-63

EAN: 5705730126635

5 Years Warranty













Sandberg Streamer 3in1 Wireless Mic Kit can do three things: Use the microphones as lavalier mics, as a handheld interview mic in the handle, or as a table mic on the included mini tripod. With two microphones, you can interview with one while your guest wears the other on their clothing, attached with a magnet. Plug the USB-C receiver into your device, and you're ready to go—no drivers needed. Noise reduction ensures clear speech, and the handle also serves as a charging case with over 9 hours of recording time.

More information:
www.sandberg.world

Product Sheet 126-63 en - v2.5

Sandberg Streamer 3in1 Wireless Mic Kit

Specifications

Wireless 2 channel microphone system with USB-C receiver
(requires a USB-C port on your device)
Transmission frequency: 2.4 GHz
Number of microphones: 2
Microphone type: Omnidirectional
Sensitivity: -34 dB
Frequency response: 20 Hz – 20 kHz
Sampling rate: 32 kHz / 16-bit
Signal-to-noise ratio: 65 dB
Max. SPL: 120 dB
Latency: Approx. 20 ms
Working distance: Up to 40m (depending on environment)
Switchable noise cancellation
Switchable reverb effect
Mute function
Microphone battery: 60 mAh
Working time: Up to 3 hours per charge, 9+ hours with charging case
Charging case battery: 400 mAh (charges microphones approx. 3 times)
Charge input: USB-C, 5V/1A
Operating temperature: -10 °C to 50 °C

Packaging info

2 Lavalier Microphones with magnets
1 USB-C wireless 2 channel receiver
3 Windshields
1 Table tripod stand
1 Screw mount ball hinge
1 Charge case / interview microphone body
1 USB-C to USB-A charge cable, 30 cm
1 USB-C charge cable, 30 cm
1 USB-C extension cable, 10 cm
1 Quick guide
1 Carry pouch

Dimensions

	Product	Package
Height (cm)	2.00	16.30
Width (cm)	12.80	12.20
Depth (cm)	2.50	4.00
Weight (g)	142.00	215.00

Product:
www.sandberg.world/product/streamer-3in1-wireless-mic-kit

Dealer:

Sandberg®