E2270SWHN

21.5 inch (54.7 cm) LCD MONITOR

Intelligent performance, streamlined design

Three-Year Warranty

AOC stands behind the quality of each and every monitor with a generous three-year warranty starting from the original date of purchase. Within the warranty period, any AOC displays with manufacturing defects or faulty components will be repaired or replaced at no additional charge. Read the complete **AOC warranty** statement for more information.

HDMI input

High Definition Multimedia Interface or HDMI is a global standard for digitally transmitting high-definition video and multichannel audio. This versatile single-cable solution allows you to easily connect your display to devices like computers, laptops, game consoles and media players.

General

CartonDimensions	558x108x394 mm

Screen Details

Color	Black
Resolution	1920x1080 PX
Refresh rate	60Hz
Response time	5 ms
Panel	TN
Backlight	WLED
Aspect ratio	16:9
Brightness (typical)	200 cd/m²
Contrast (dynamic)	20M:1
Contrast (static)	700:1
Pixel Pitch (H) (V)	0.248
Diagonal (inch)	21.5 inch
Active Screen Area (HxW)	476,64x268,11 mm mm
Viewing angle (CR10)	90/65 º
Display Colours	16.7 Million
Scanning Frequency	30-83khz/50-76hz
OSD languages	EN, FR , ES, PT, DE, IT, NL, SE, FI, PL ,CZ, RU, KR, CN (T), CN (S), JP

Connections

Signal Input	HDMI 1.4 x 1, VGA
Audio output	Headphone out (3,5mm)

What's in the box

VGA cable (1,2 m), HDMI cable (1,5 m), Power Cable C7 (1.2 m),

Sustainability

• Environmental and energy: RoHS, Lead-free, Mercury Free

• Recyclable packaging material: 100 %

Ergonomics

Tilt	-5/15 °
Vesa Wallmount	100x100

Power details

Powersupply	Internal
Powersource	100 - 240V 50/60Hz
Power Consumption	On 19 watt, Off 0.5 watt Standby 0.5 watt,

Dimensions

Product Dimensions (incl base)	503,37x375x48 mm
CartonDimensions	558x108x394 mm
Net Weight (excl package)	2.7 Kg
Gross Weight (incl package)	3.45 Kg

Warranty

Warranty Period	3 Years
EAN	4038986125321
MTBF	50.000 hours

Regulations

TUV-GS 1, CE 1, energystar 1, FCC 1, EAC 1, Rohs compliant 1,