Data Sheet

2-Slot USB 3.0 SD Card Reader with UASP - SD 4.0, UHS II

Product ID: 2SD4FCRU3

This USB 3.0 SD™ card reader lets you access two SD cards simultaneously.

You can:

- Download and edit photos and videos
- Back up presentations, documents and spreadsheets
- Distribute content to multiple employees

The card reader transfers files between your USB-A tablet, laptop or desktop computer and the SD card.

Ultra-Fast Read/Write Access

The USB SD card reader features SD 4.0 and UHS-II support. It reads and writes to and from the cards at speeds of up to 312MB/s. The reader also supports USB 3.0 connection speeds of up to 5Gbps between the computer and the reader. For 70% faster performance between the computer and the reader, UASP is also supported when connected to a computer that also supports UASP.

The reader is backward compatible with USB 2.0 and 1.1.

Multi SD Card Reader Supports All SD Card Types

The dual SD card reader supports all SD cards: SD (Secure Digital), SDHC™ (Secure Digital High Capacity) and SDXC™ (Secure Digital Extended Capacity). It also supports UHS cards, and is backward compatible with older SD cards.

The card reader will also support the following card types when connected through an adapter:

- microSD™
- miniSD™
- MMCmobile™
- RS-MMC™
- MMCplus™

Portable Design

The reader has a small footprint design and comes with a wrap-around USB-A cable. It fits nicely inside a carrying case. The reader is USB powered, but you can connect a power source to the Micro-USB power port if you require more power.

2SD4FCRU3 is TAA compliant and comes with a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

RoHS Compliant Available

Applications

- Access multimedia content quickly -- ideal for creative professionals and mobile workers
- Review or edit files on two SD cards simultaneously, out in the field or in the studio

Features

- Save time and access two SD cards simultaneously with this USB 3.0 SD card reader
- Experience fast read/write speeds with USB 3.0 (5Gbps) on each slot
- 70% faster transfer speeds with UASP support, when connected to a UASP compatible host
- Perform high-speed file transfers: card reader supports SD 4.0, UHS-II and bus speeds up to 312MB/s
- Edit your photos, videos and presentations anywhere you go with this dual SD card reader

	Warranty	2 Years
Hardware	Bus Type	USB 3.0
	Chipset ID	Genesys Logic - GL3215 Genesys Logic - GL3522
	Interface	USB 3.0
Performance	General Specifications	Supports SD 4.0 and UHS-II (Ultra High Speed) for high speed file transfers, with bus speed up to 312MB/s
	Maximum Data Transfer Rate	5 Gbps
	Memory Media Type	SD/MMC (Secure Digital/Multimedia Card)
		SDHC (Secure Digital High Capacity)
		SDXC (Secure Digital eXtended Capacity)
	Type and Rate	USB 3.0 - 5 Gbit/s
Connector(s)	Drive Connectors	2 - SD / MMC Slot Female
	Host Connectors	1 - USB Type-A (9 pin) USB 3.0 Receptacle
	Other Interface(s)	1 - USB Micro-B (5 pin) Receptacle
Software	OS Compatibility	OS independent; No software or drivers required
Special Notes / Requirements	**Note**	USB powered. For additional power, connect the USB cable on your power source to the AUX Micro-B power port.
	System and Cable Requirements	Available USB port
Power	Output Current	2000 mA
	Output Voltage	5 DC
	Plug Type	USB Micro-B
	Power Source	Not Included (not required for standard applications)
Environmental	Humidity	5% ~ 90%
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 70°C (-4°F to 158°F)
Physical Characteristics	Color	Black
	Enclosure Type	Plastic
	Product Height	0.5 in [13.5 mm]
	Product Length	4.2 in [106 mm]
	Product Weight	2 oz [57 g]
	Product Width	2.7 in [69.5 mm]

Packaging Information	Shipping (Package) Weight	5 oz [142 g]
What's in the Box	Included in Package	1 - dual-slot SD card reader 1 - quick-start guide
	External Ports	2 - SD / MMC Slot Female

Product appearance and specifications are subject to change without notice.