Specifications

Eaton BPM125DR

Eaton BPM Bypass Power Module, Wall-mount or rackmount, 3U, Black, Yes, Split-phase (L1, L2, N, G), 9PXM, 9170+, 9155, 9PXSP 8-10K, 1, HW (50-125A), (6) 5-20R, (3) L14-30R

General specifications

PRODUCT NAME	Eaton Bypass Power Module (BPM)
CATALOG NUMBER	BPM125DR
UPC	743172090317
PRODUCT LENGTH/DEPTH	26.5 in
PRODUCT HEIGHT	5.1 in
PRODUCT WIDTH	17.3 in
PRODUCT WEIGHT	2 lb
WARRANTY	2 year
COMPLIANCES	TAA Compliant
PRODUCT TYPE	Bypass Power Module

Powering Business Worldwide

Additional specifications

RECEPTACLE	(6) 5-20R, (3) L14-30R
RACK SIZE	3U
COLOR	Black
RACK MOUNTING KIT	Yes
PHASE (INPUT)	Split-phase (L1, L2, N, G)
USED WITH	Eaton 9170+, 9155, 9PXSP 8-10 kVA

Electrical input

INPUT CONNECTION	Hardwired

Electrical output

RECEPTACLE	(6) 5-20R, (3) L14-30R

Resources

BROCHURES	Eaton Bypass Power Module (BPM) product brochure
MANUALS AND USER GUIDES	Eaton Bypass Power Module (BPM) user guide
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BPM125DR

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.