PHILIPS

Wawel Ceiling Light 17 W

Ceiling Lights

4000/6500/2700 K

White

Dimmable; SceneSwitch



31821/31/P5

Quality lighting for a cosy home

The Philips myLiving WAWEL LED ceiling light comes with integrated LED to optimise light output and uniformity. Control its brightness according to your mood with step tunable and memory functions.

Light effect
- Even light distribution

Advanced LED light
- Tunable 2,700-6,500 K

Energy saving
- 80% energy saving, compared to traditional light sources

Highlights

Even light distribution

80% energy saving

Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year. So reduce your energy bill and start saving now.

Tunable

This lamp is tunable. You can tune it to your preferred light colour; from warm white (2,700 K) to cool daylight (6,500 K).

Specifications

Bulb characteristics
- Intended use: Indoor
- Dimmable: Yes

Design and finishing
- Colour: White
- Material: Metal, Plastic

Durability
- Number of switch cycles: 15,000
- Nominal lifetime: 20,000

Environmental
- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics
- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700-4000-6500 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 94 lm/W

Miscellaneous
- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Dimmable, SceneSwitch

Other characteristics
- Lamp current: 130 mA

Product dimensions and weight
- Net weight: 0.64 kg
- Overall height: 66 mm
- Overall length: 350 mm
- Overall width: 350 mm

Service
- Warranty: 5 year(s)

Technical specifications
- Diameter: 350 mm
- Total lumen output fixture: 1600
- Light colour: Tunable white light
- Mains power: AC 220-240
- IP code: IP20 | Finger-protected
- Class of protection: Class I – Earthed

Packaging dimensions and weight
- EAN/UPC - product: 8718696162774
- Net weight: 0.64 kg
- Gross weight: 1.02 kg
- Height: 39.7 cm
- Length: 7 cm
- Width: 39.6 cm

Issue date: 2025-12-06
Version: 0.466

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com