Specifications

Eaton 9SX1000G

Eaton 9SX online, extended runtime UPS, 1000 VA, 900 W, 208V, C14 input, Outputs (6) C13, 9.9"Hx6.3"Wx15.1"D, 30.9 lb., network card optional

General specifications	
PRODUCT NAME	Eaton 9SX UPS
CATALOG NUMBER	9SX1000G
UPC	743172091284
PRODUCT LENGTH/DEPTH	15.1 in
PRODUCT HEIGHT	9.9 in
PRODUCT WIDTH	6.3 in
PRODUCT WEIGHT	30.4 lb
WARRANTY	3 year limited
COMPLIANCES	FCC Compliant CE Marked
CERTIFICATIONS	cULus Listed ICC-ES AC156 OSHPD Seismic certified
GLOBAL CATALOG	9SX1000G
PRODUCT TYPE	UPS

Powering Business Worldwide

Battery

BATTERY MANAGEMENT	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
EXTENDED BATTERY CAPABILITY	Yes

Electrical output

RECEPTACLE	(6) C13
TOPOLOGY	Online/Double-conversion
WATTAGE	900 W
VA RATING	1000 VA
OUTPUT WAVEFORM	True sine wave
VOLTAGE	208 V
OUTPUT POWER FACTOR	0.9
OUTPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240/250V)
OUTPUT FREQUENCY	50/60 Hz
FEED TYPE	1

Electrical input

INPUT CONNECTION	C14
INPUT CORD LENGTH	8 ft
INPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240V)
INPUT FREQUENCY RANGE	60 Hz: 50–70 Hz, 50 Hz: 40–60 Hz
INPUT POWER FACTOR	>.99

Communications

COMMUNICATION	• (1) MiniSlot • (1) USB port • (1) Serial RS-232 port • (1) RPO/ROO/Signal input terminal • (1) mini-terminal block for output relay
EXPANSION SLOTS	• (1) Mini-Slot (MS) expansion port. Optional connectivity cards may be ordered separately. • - Gigabit Web/SNMP card part number: NETWORK-M3 • - Modbus card part number: INDGW-M2 • - Relay card part number: RELAY-MS
USER INTERFACE	5-button graphical user interface
POTENTIAL FREE SWITCH CONTACT	Yes

Environmental

ALTITUDE	3000 m
BTU RATING	Online : 421 BTU/hr, Battery : 777 BTU/hr, High efficiency : 208 BTU/hr
NOISE LEVEL	51 dB at 1m
RELATIVE HUMIDITY	0-96% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)

Additional specifications

CONSTRUCTION TYPE	Free standing model
EFFICIENCY AT MAX. LOAD	89%
PACKAGE CONTENTS	• 9SX1000G Eaton 9SX Double-Conversion UPS • (2) C13-to-C14 adapters, 6 ft. (1.8 m) • USB cable • RS-232 cable • Quick start guide
INTERNAL BYPASS	Yes

Warranty and support

STANDARD FACTORY WARRANTY	• 3-YEAR FACTORY WARRANTY • - 3 years • - Parts, electronics and batteries coverage • - Standard ground shipping • - Technical support
EXTENDED SERVICE PLANS	• ADVANCED DEPOT EXCHANGE • - 5-year depot repair: 9SW5Y-1000UC • - Expedited parts coverage for 5 years • - Parts, electronics and UPS batteries coverage • - Next business day shipping • - Technical support • • 5-YEAR ON-SITE PLAN: WFLN75XX-2509UC • - On-site parts and labor coverage for years 5 • - Parts, electronics and UPS batteries coverage • - 24x7 on-site labor coverage, next-day response • - Next-day shipping • - Technical support

Resources

BROCHURES	Eaton 9SX UPS installation and user manual Eaton 9SX UPS brochure Eaton 9SX UPS visio stencils Eaton 9SX UPS technical specifications
CERTIFICATION REPORTS	EC DoC Eaton 9SX
CHARACTERISTIC CURVE	9SX1000G ups-battery-runtime graph
DRAWINGS	9SX1000G UPS 2D technical drawing 9SX1000G UPS 3D technical drawing
MANUALS AND USER GUIDES	Quick start guide for Eaton 9SX UPS 208V models
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 9SX1000G

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.