PRODUCT CARD

Manufactuer: Lanberg
Z20244

19" WALL-MOUNTED RACK 12U/600X600 DEMOUNTED FLAT PACK BLACK LANBERG

Catalog nr: WF01-6612-10B







Product description

Wall mount, single section Lanberg cabinet WF01-6612-10B is a solution designed to expand networks, installation of cabling and equipment in size 19” with max. 60kg. loading capacity. It can be used in networks, server rooms, small and medium businesses. It can also work in low voltage systems such as cable television networks, alarm systems, fire protection systems and access control systems, CCTV and IP surveillance. Appropriate design allows simple, self-assembly. Cabinet is characterized by IP20 degree of protection, opening front door with possibility of rotate to 180° with lock, removable side panels (locks included). The cabinet has cable entry panel on top and bottom cover. This product is made of high grade cold rolled steel. Cabinet structure for self-assembly is in flat pack which facilitates transport. In addition, parcel includes additional accessories for rail mounts, M6 cage nuts and blank entry panels.

Features:
- Manufactuer: Lanberg,
- Manufactuer code: WF01-6612-10B,
- Cabinet type: Wall mount,
- Body color: Black RAL9004,
- Height: 12U,
- Cabinet dimensions (W x D x H): 600x600x635 mm,
- Packaging dimensions (W x D x H): 62x64.5x22 cm,
- Spacing between rack rails: 450 mm,
- Spacing between holes in rack rails: 475 mm,
- Internal spacing between rack rails: 500 mm,
- Loading capacity: max. 60 KG,
- Degree of protection: IP20,
- Doors type: Temper glass,
- Standard: ANSI/EIA RS-310-D, IEC297-2, DIN41494; PART1 & PART7, ETSI,
- Material: High grade cold rolled steel, powder coated,
- Fan avaliable: Yes, 120mm, 110V or 220V,
- Thickness: Mounting profile - 1,50mm, Others - 1,2mm,
- Cable entry panel: Top, Bottom,
- Included: Accessory bag, earth kit, front door lock, two side panels with locks, 10 cage nuts M6.

Additional accessories:
- AK-1001-B – Lanberg fixed shelf for wall mount Lanberg cabinet
- AK-1004-B – Lanberg front and back fixed shelf for wall mounting and freestanding Lanberg cabinet
- AK-1008-B – Lanberg support board for wall-mount and free-standing Lanberg cabinet
- AK-1101-B – Lanberg brush panel 1U
- AK-1102-B – Lanberg brush panel for cable entry panel
- AK-1201-B – Lanberg cable management type A
- AK-1202-B – Lanberg cable management type B
- AK-1302-S – Lanberg 50 cage nuts M6
- AK-1401-B – Lanberg blank panel 1U
- AK-1402-B – Lanberg blank panel 2U
- AK-1501-B – Lanberg fan 230V for wall-mount Lanberg cabinet

Despite making every effort, we not guarantee, that published technical information does not contain failures or mistakes that can not be legal basis for claims. If you have any questions, please to contact the salesperson before you decide.

Product features

Width [mm]	600,00
Height [mm]	635,00
Type of cabinet	Hanging; One-section; Self-assembly
Height [U]	12,00
Depth [mm]	600,00
Maximale Belastung [kg]	60,00
Weatherproof rating IP	20,00
Profile sheet thickness [mm]	1,50
Other elements sheet thickness [mm]	1,20
Front door types	Glass
Included Accessories	Front lock; Side locks; M6 screws
Weight [kg]	23,00

Logistics data

EAN	5901969403152
Unit width [cm]	62,00
Unit height [cm]	22,00
Unit lenght [cm]	64,50
Unit weight [kg]	23.00000
VAT rate [%]	23,00 %
Guarantee	24
Country of origin	CN

Despite making every effort, we not guarantee, that published technical information does not contain failures or mistakes that can not be legal basis for claims. If you have any questions, please to contact the salesperson before you decide.