Epson **TM-T20III (011A0): USB + Serial, PS, Blk, UK**

DATASHEET / BROCHURE



This entry-level thermal POS receipt printer provides a cost-effective POS solution with fast print speeds and economical features.

The combination of its fast print speeds, high reliability and economical operation, make this printer a must-have for small retail and speciality stores, hospitality venues and grocery stores.

Affordable
This easy-to-use model is our entry-level POS receipt printer and has an 80mm printing width. Its Automatic Paper Reduction feature reduces top and bottom margins, line feed width and barcode height, allowing for flexible receipt printing. This monitors and controls the amount of paper used. Paper costs are minimised by printing the top logo of the next receipt before cutting, so the top margin is further reduced by 12mm.

Reliable
With the mean time between failures (MTBF) of 360,000 hours and a mechanism life of 15 million lines, you can rely on the TM-T20III in high-volume printing environments.

Flexible
The TM-T20III comes with a built-in USB interface. You can select from two models: 1) USB + Serial, 2) Ethernet, making the model a long-term investment as it is possible to switch connectivity at any time.

Fast
Its print speed of 250mm/sec can save you time and its competitive price and running costs can save you money; ideal for when you need to beat queues quickly.

KEY FEATURES

- **Economical**
  Automatic paper reduction function
- **Reliable**
  Mechanism life of 15 million lines
- **Fast print speed**
  Print speed of 250mm/sec
- **Flexible connectivity**
  Two models: 1) USB + Serial 2) Ethernet
- **Peace of mind**
  Epson is Europe's number one POS printer manufacturer[1]

EPSON®

PRODUCT SPECIFICATIONS

INTERFACES	
Interfaces	RS-232, USB 2.0, Drawer kick-out
GENERAL	
Product dimensions	140 x 199 x 146 mm (Width x Depth x Height)
Product weight	1.7 kg
Colour	Black (EBCK)
Noise Level	Operation (Roll):55 dB (A)
Supported Humidity	Operation 10% - 90%, Storage 10% - 90%
Supported Temperature	Operation 5° C - 45° C, Storage -10° C - 50° C

OPTIONAL ACCESSORIES

- OT-BZ20-634: Optional External Buzzer
  C32C890634

LOGISTICS INFORMATION

SKU	C31CH51011A0
EAN code	8715946680453
Dimensions Single Carton	490 x 400 x 295 mm
Carton Weight	0 Kg
Country of Origin	Philippines
Layer	16 Units
Layer Block	24 Units

Epson **TM-T20III (011A0): USB + Serial, PS, Blk, UK**

WHAT'S IN THE BOX

- CD Manual
- Main unit
- Power switch cover
- Roll paper
- Rubber feet
- USB cable
- Wall hanging bracket
- Warranty document
- Paper roll spacer
- Setup guide
- AC adapter, C1
- UK AC cable

For more information please contact:

Home users: 0343 90 37766
Business users*: 0871 42 37766
Republic of Ireland: 01 436 7742
Or visit us at https://www.epson.co.uk/contactus
* 10p per minute plus network extras.

Web: www.epson.co.uk
www.epson.ie

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
Product information is subject to change without prior notice.
Last extracted: 2025-02-26

1. Number one POS printer manufacturer based on shipments for FY17 (IDC 2018)

EPSON®