Печать PDF 100% 100% Отменить

FSP - Power Never Ends

Hyper (500/600/700W)

fsp-europe.com/hyper-500600700w-old-version/

All All

Hyper Front View

Hyper 500 3D View

Hyper 500 Colorbox

Hyper 600 3D View

Hyper 600 Colorbox

Hyper 700 3D View

Hyper 700 Colorbox

Features:

- Complies with ATX 12V v2.31 & EPS 12V v2.92
- Efficiency >85%
- Active PFC, Power Factor ≥99%
- PCI-Express 6+2 Pin Connectors for VGA Card
- SATA Array Cable
- All Sleeved Cables
- 120mm Quiet Fan,
- Complete Protections: OCP, OVP, SCP
- Multiple Safety Approvals

Meet 85 Plus
The efficiency is >85%

SATA Array Cable
- 50mm intervals for 4 SATA device installation
- Optimized the airflow in case
- No-hassle with case side panel

Quiet and durable Cooling
Powered by FDB (Fluid Dynamic Bearing) fan with low noise and long-lasting life span

Active PFC
Power Factor ≥ 99%

Meet ErP/EuP 2013 Standard

Intel® Haswell™ Platform Ready

Connector Table:

Connector Type	Connector Illustration	HP500	HP600	HP700
ATX12V 24 Pin		-	-	-
ATX12V 20+4 Pin		1	1	1
CPU 8 Pin		-	-	-
CPU 4+4 Pin		1	1	1
CPU 4 Pin		-	-	-
PCI-E 2.0 6+2 (8) Pin		2	4	4
PCI-E 2.0 6 Pin		-	-	-
S-ATA		8	8	8
Molex 4 Pin		2	2	2
Floppy 4 Pin		1	1	1
Fan 2 Pin		-	-	-

Specifications:

Model	HP500	HP600	HP700
Effeciency	>85%		
Input Voltage	200 ~ 240Vac		
Frequency	50 ~ 60Hz		
PFC	Active PFC (0.99)		
Power Provided	500W	600W	700W
Over-Current Protection	✓		
Over-Voltage Protection	✓		
Short-Circuit Protection	✓		
Case Color	Black		
Chassis Fan	120mm		
Noise	< 19 dBA at 50% loading		
Form Factor	ATX 12V V2.31 & EPS 12V V2.92		
Safety Approval	CE, CB, TUV, C-tick		
Dimensions (LxWxH) mm	150 x 140 x 86		

Power Output Table:

500W	HP500					
AC Input	200-240Vac ~ 3A 50Hz					
DC Output	+3.3V	+5V	+12V1	+12V2	-12V	+5Vsb
Max Output Current	20A	20A	25A	25A	0.3A	3A
Max Combined Power	120W		456W		18.6W	
Total Power	500W					

600W	HP600					
AC Input	200-240Vac ~ 3.5A 50Hz					
DC Output	+3.3V	+5V	+12V1	+12V2	-12V	+5Vsb
Max Output Current	20A	20A	30A	30A	0.3A	3A
Max Combined Power	140W		540W		18.6W	
Total Power	600W					

700W	HP700					
AC Input	200-240Vac ~ 4A 50Hz					
DC Output	+3.3V	+5V	+12V1	+12V2	-12V	+5Vsb
Max Output Current	20A	20A	35A	35A	0.5A	2.5A
Max Combined Power	150W		636W		18.6W	
Total Power	700W					

Powered by PrintFriendly.com © Privacy