MPN: MMHP219-64GB

64GB Memory Module LOAD REDUCED, DDR4 PC4 19200, 288PINS, DIMM

In CoreParts you will find a wide range of alternative RAM modules all using original chip sets, that match the performance of your original RAM modules with different sizes, and capacities, manufactured by high-end, certified and trusted suppliers.

- High Quality
- Tested and certified
- Matching Performance
- Reliable with 10 years Warranty

Specifications

Features	**CAS latency**	15
	Component for	PC/server
	ECC	Yes
	Internal memory	64 GB
	Internal memory type	DDR4 PC4 19200
	Memory clock speed	2400 MHz
	Memory form factor	288PINS DIMM
	Memory layout (modules x size)	1 x 64 GB
	Memory voltage	1.2 V
	Module configuration	2048M x 4
Other features	**Capacity**	64 GB
	Chips organisation	2048*4
	Number of pins	288
Vendor information	**Brand Name**	CoreParts
	Warranty	10 Year(s)