MPN: POEINJ-25W-USBC

Gigabit PoE to USB-C Converter 25W

POEINJ-25W-USBC is an indoor PoE rated networking converter, special convert power&data from PoE to Type-C devices. It is with 1 PoE port for 802.3bt standard input and 1 Type-C port for power output and 1 RJ45 port for data output. The dataspeed is 10/100/1000Mbps (Gigabit).This converter ouput total 25W for Type-C PDs, and the voltage output from 5V-20V base on the required of your Type-C PDs. It is designed with OVP,OCP, SCP, then worked safty for the Type-C PDs, such as computers, IPad, Macbook, Google Wifi etc.

- Designed with PVP, OCP, SCP
- Designed for Computers, iPads, MacBook, Google Wifi etc.
- Material : Black Metal
- Active

Specifications

Features	**Certification**	CE, FCC, UL & RoHS
	Easy to install	Yes
	LED indicators	Yes
	Maximum operating distance	100 m
	Plug and Play	Yes
	Power protection features	Over current, Under voltage, Short circuit, Under power
	Product colour	Black
	Rack mounting	Yes
	RoHS compliance	Yes
	Surge protection	Yes
	Wall mountable	Yes
Network	**Cable standard**	CAT6
	Cable types supported	Cat5, Cat5e, Cat6, Cat6a
	Cabling technology	10/100/1000Base-T
	Ethernet interface type	Gigabit Ethernet
	Ethernet LAN data rates	1000 Mbit/s
	Networking standards	IEEE 802.3, IEEE 802.3ab, IEEE 802.3u
	Power over Ethernet (PoE)	Yes
Operational conditions	**Operating relative humidity (H-H)**	20 - 80 %
	Storage temperature (T-T)	-20 - 70 °C
Packaging content	**Number of products included**	1 pc(s)
Ports & interfaces	**DC-in jack**	Yes
	Ethernet LAN (RJ-45) ports	2
	Other connection	USB Type C
Power	**AC adapter input voltage**	100 - 240 V
	Output current	3 A
	Output power	25 W

Power	**Power plug type**	Type F
	Total Power over Ethernet (PoE) budget	25 W
Vendor information	**Brand Name**	MicroConnect
	Warranty	2 Year(s)

Other images