LogiLink®
manufactured by
CANOVATE®





Wallmount cabinet with openable side panels, assembled

Technical Features

Material:	1 / 1.2 / 1.5 mm steel
Max. Static Load:	Up to 50 kg
Finish:	Electrostatic Powder Paint
Color:	RAL 7035 or RAL 9005

- » Steel frame
- » Glass door with cylindrical lock
- » Openable side panels from outside
- » 1 Pair of 19" Mounting Rails
- » RoHS compliant, UL Certificated
- » Delivered fully assembled



Wallmount Cabinet - RAL 7035 Light Grey / RAL 9005 Black

Height U	Outer width (W) mm	Outer depth (D) mm	Outer height (H) mm	Inner width (W1) mm	Inner depth (D1) mm	Inner height (H1) mm	19" rails adjustable depth range (C)	Weight kg	Part No. X=B (Black) X=G (Grey)
6	540	550	323	498	530	283	100–495	15	W06B54X
9	540	550	456	498	530	416	100–495	17	W09B54X
12	540	550	589	498	530	549	100–495	19	W12B54X
15	540	550	723	498	530	683	100–495	21	W15B54X

* The specifications and pictures are subject to change without notice.
*All trade names referenced are the registered namework of their respective owners.

RoHS compliant