MPN: LVN122112

305m Cat6 U-UTP cable 4x2xAWG23 LSZH white

Used in structured cabling systems. For transmission of telecommunications and high speed data.



Lanview Cat6 Unshielded LSZH cables are manufactured and tested to the ISO/IEC 11801, EIA/TIA 568B and EN50173-2 standards. Each cable consists of 4x2 color coded PE insulated conductors.

- Reaction-to-fire class: Dca
- AWG 23 solid copper
- EMC Class: B
- 305 m REELEX box
- Meter marked cable
- NVP Value: 69%

Specifications

Features	**AWG wire size**	23
	Cable class	Dca
	Cable fire class	Dca
	Cable length	305 m
	Cable shape	Round
	Cable shielding	U/UTP (UTP)
	Cable standard	Cat6
	Conductor material	Copper
	Conductor type	Solid
	Connector 1	Open end
	Connector 2	Open end
	Data transfer rate	10000 Mbit/s
	Ethernet interface type	10 Gigabit Ethernet
	Frequency	250 MHz
	Halogen-free	Yes
	Jacket material	Low smoke zero halogen (LSZH)
	Power over Ethernet (PoE)	Yes
	Power over Ethernet (PoE) type supported	PoE++ (4PPoE)
	Product colour	White
	RoHS compliance	Yes
Legal Information	**ADR Information**	No restrictions
	Country of Origin	China
	Tariff No.	8544421000

Legal Information	**UNSPSC Code**	26121609
Logistics data	**Products per pallet (sea)**	50 pc(s)
Package dimensions	**Depth (package,cm)**	39.5 cm
	Gross Weight (Package, kg)	13 kg
	Height (package,cm)	39.5 cm
	Width (package,cm)	23 cm
Packaging data	**Package type**	Box
	Quantity per pack	1 pc(s)
Product dimensions	**Net Weight (Product, kg)**	12 kg
	Product Depth	39.5 cm
	Product Height	39.5 cm
	Product Width	23 cm
Vendor information	**Brand Name**	Lanview
	Warranty	25 Year(s)
Weight & dimensions	**Outer diameter**	6.3 mm

Other images

