MOTHERBOARDS

MEG Z590 UNIFY-X

PURE BLACK, PURE PERFORMANCE



SPECIFICATIONS

Model Name	MEG Z590 UNIFY-X
CPU Support	Supports 10th Gen Intel® Core™ Processors, 11th Gen Intel® Core™ Processors, Pentium® Gold and Celeron® Processors
CPU Socket	LGA 1200
Chipset	Intel® Z590 Chipset
Graphics Interface	1x PCIe 4.0 x16 slot, 1x PCIe 3.0 x4 slot Support 2-way AMD® CrossFire™ Technology
Display Interface	Support 4K@60Hz as specified in HDMI 2.0b – Requires Processor Graphics
Memory Support	2 DIMMs, Dual Channel DDR4-5600MHz(OC)
Expansion Slots	2x PCIe 3.0 x1 slots
Storage	3x M.2 Gen4 x4 64Gb/s slots, 1x M.2 Gen3 x4 32Gb/s slot, supports Intel® Optane™ Technology 6x SATA 6Gb/s ports
USB ports	1x USB 3.2 Gen 2x2 20Gbps (1 Type-C), 2x USB 3.2 Gen 2 10Gbps (1 Type-A + 1 Type-C), 10x USB 3.2 Gen 1 5Gbps (10 Type-A), 6x USB 2.0
LAN	Intel® I225-V 2.5G LAN
Wireless / Bluetooth	Intel® Wi-Fi 6E AX210, Bluetooth 5.2
Audio	8-Channel (7.1) HD Audio with Audio Boost 5

FEATURES

Dedicated for Extreme OC

The top-notch R&D design and exclusive 2 DIMM solution deliver the world class memory performance.

Extreme Power Design

INTERSIL digital PWM, 16+2+1 phases with 90A SPS, Mirrored Power Arrangement and dual CPU power connectors to unleash the maximum performance.

Quadruple M.2 Connectors

Onboard quadruple M.2 connectors for the maximum storage performance with three Lightning Gen 4 solution.

Triple Lightning Gen4 M.2

Maximum onboard triple Gen4 M.2 solution provides multiple configurations for demanding gamers and power users.

Outstanding Cooling Solution

Aluminum Cover design, VRM Heat-pipe, 7W/mK thermal pads, M.2 Shield Frozr and MOSFET Baseplate to ensure the extreme performance with low temp.

2.5G LAN

Onboard 2.5G LAN with LAN manager, delivering the best online gaming experience.

Wi-Fi 6E

The latest wireless solution supports 6GHz spectrum, MU-MIMO and BSS color technology, delivering speeds up to 2400Mbps.

Lightning USB 20G

Built-in USB 3.2 Gen 2x2 port, offers 20Gbps transmission speed, 4X faster than USB 3.2 Gen 1.

Smart Button

Reset Computer, Safe Boot, Turbo Fan and EZ LED control functions with just one click.

8 Layer PCB with 2oz Thickened Copper

An Enhanced PCB design provides higher performance and long-lasting system stability without any compromise.

CONNECTIONS



1. Clear CMOS Button
2. USB 2.0
3. USB 3.2 Gen 1 5Gbps (Type-A)
4. USB 3.2 Gen 1 5Gbps (Type-A)
5. 2.5G LAN
6. Wi-Fi / Bluetooth
7. HD Audio Connectors
8. Flash BIOS Button
9. HDMI
10. USB 3.2 Gen 2 10Gbps (Type-A)
11. USB 3.2 Gen 2x2 20Gbps (Type-C)
12. Optical S/PDIF-Out

Generated 2021-10-05, check for the latest version www.msi.com/datasheet. The information provided in this document is intended for informational purposes only and is subject to change without notice.

TRUE GAMING © 2021 Micro-Star Int'l Co.Ltd. MSI is a registered trademark of Micro-Star Int'l Co.Ltd. All rights reserved.Intel, the Intel logo, the Intel Inside logo and Intel Core are trademarks of Intel Corporation or its subsidiaries in the U.S. and/or other countries.