Data sheet

HP LaserJet Pro 3002dn Printer

Get fast printing speeds and easy management tools with LaserJet Pro.

This printer is built for powerful productivity with fast speeds and reliable hardware, delivering effortless everyday use from wherever work happens so you can focus more on your business.

This printer uses dynamic security, which may be updated periodically by firmware updates. The printer is intended to be used solely with cartridges using an original HP chip. Cartridges using a non-HP chip may not function or may cease to function. More at: www.hp.com/learn/ds

Highlights

- Instant Ink for Laser available
- Fast print speed (33 ppm A4)
- High monthly duty cycle (50,000 pages)
- Automatic two-sided printing standard
- HP Smart app
- HP Wolf Pro security

Powerful productivity.

- Support your small workteams with this smart printer, designed for up to 7 users.
- Print more efficiently. Save time, paper, and costs with fast print speed and auto two-sided printing.
- Do more in fewer steps. Simple shortcuts allow your employees to complete common tasks with just a touch.
- Get productivity in the palm of your hand. Print, scan and get time-saving Shortcuts with HP Smart app.[1]

Seamless management.

- Centralise print management for your enterprise. HP Web Jetadmin makes it easy with its suite of features.[2]
- Set up your printers quickly wherever work happens. Cloud connectivity makes it easy for your IT team.
- Access your printers from a single dashboard. Smart Admin guides you through setup and gives IT visibility.[3]

HP Wolf Pro Security.

- Get printer security out of the box. Preconfigured settings mean it's ready when you are.
- Set up and manage your printers from a single dashboard. Smart Admin makes the experience seamless.[3]
- Add a layer of security. PIN/pull option authenticates your print jobs only when you're present.
- Set configuration policies and validate settings universally with HP JetAdvantage Security Manager.[4]

Hassle-free supplies management with Instant Ink.

- Enroll to save on Original HP Toner with Instant Ink. Get toner, delivery and recycling. [5,6,7]
- Never run out of toner with Instant Ink for laser. [8]
- With Instant Ink, get toner automatically delivered to workers or offices all on one consolidated bill.[7]
- With Instant Ink, you get to select the right plans for each of your printers. Change or cancel at any time.[9]

Product walkaround

HP LaserJet Pro 3002dn Printer shown

1. Fast printing, up to 33 ppm, 250-sheet standard paper capacity
2. Built for the small workteams of up to 7 users
3. Automatic 2-sided printing
4. Pre-configured security settings
5. High-speed USB ports, built-in fast Ethernet
6. Cassette type input tray



Accessories, Supplies and Support

Supplies	**W1390A** HP 139A Black Original LaserJet Toner Cartridge (Average cartridge yields 1,500 standard pages. Declared yield value in accordance with ISO/IEC 19752.)
	W1390X HP 139X High Yield Black Original LaserJet Toner Cartridge (Average cartridge yields 4,000 standard pages. Declared yield value in accordance with ISO/IEC 19752.)
Accessories	
Service and Support	**UH761E** 3 years Advanced Exchange (All EMEA countries Except Adriatic, Africa, CIS, EEM, Israel, Middle East, Russia, South Africa, Turkey) **UH757E** 3 years Next Business Day exchange (available in Austria, Belgium, Czech Republic, Denmark, Finland, France, Germany, Greece, Ireland, Italy, Netherlands, Norway, Poland, Portugal, Romania, Slovakia, Spain, Sweden, Switzerland, UK) **UH764E** 3 years Return to Depot (available in Adriatic, Africa, CIS, EEM, Israel, Middle East, Russia, South Africa, Turkey)

Technical specifications

Model	HP LaserJet Pro 3002dn Printer
Product number	3G651F
Functions	Print
Control panel	3 Buttons (ON, Info, Cancel/Resume); 3 Indicator LEDs (Paper, Attention, Toner).
Print	
Print technology	Laser
Print speed[1]	Black (A4, normal): Up to 33 ppm ; Black (A4, duplex): Up to 20 ipm
First page out[2]	Black (A4, ready): As fast as 7.0 sec ; Black (A4, sleep): As fast as 8.7 sec
Print resolution	Black (best): Up to 1200 x 1200 dpi ; Technology: 600dpi with Resolution Enhancement technology (REt); HP ProRes 1200
Monthly duty cycle	Up to 50,000 A4; Recommended monthly page volume: 350 to 2500 pages
Printer smart software features	Automatic duplex, Easy OOBE, Smart security, Print always work, Print anywhere
Standard print languages	PCL5c; PCL6; PS; PCLmS; PDF; URF; PWG; PCLm
Fonts and typefaces	84 scalable TrueType fonts
Print area	Print margins Top: 4.23 mm, Bottom: 4.23 mm, Left: 4.23 mm, Right: 4.23 mm; Maximum print area : 207 x 348 mm
Duplex printing	Automatic (standard)
Processor speed	800 MHz
Connectivity	
Standard	Hi-Speed USB device (compatible with USB 2.0 specifications); 10/100Mbps Ethernet.
Mobile printing capability	HP Smart App; Apple AirPrint™; Mopria™ Certified
Supported network protocols	TCP/IP: IPv4; IPv6; IP Direct Mode; LPD; SLP; Bonjour; WS-Discovery; BOOTP/ DHCP/ AutoIP; WINS; SNMP v 1/2/3; and HTTP/HTTPS
Network capabilities	10/100Mbps Ethernet.
Memory	Standard: 256 MB ;Maximum: 256 MB
Media handling	
Number of paper trays	Standard: 1 ;Maximum: 1 Main Tray
Media types	Paper (Cut sheets, plain, glossy film, labels), envelopes, card stock, postcards
Media size	Custom (metric): Width 76 to 216 mm ; Length 127 to 356mm Supported (metric): A4, A5, A5-R, A6, B5(JIS); B6(JIS); Oficio (216x340); 16K (195 x 270 mm); 16K (195 x 270 mm); 16K (197 x 273 mm); L 9x13 cm; 10x15cm; Japanese Postcard; Double Japan Postcard Rotated; Japanese Envelope Chou #3; Japanese Envelope Chou #4; Envelope B5; Envelope C5; Envelope C6; Envelope DL
Media handling	Standard input: 1 main tray; 250 sheets or 10 envelopes Standard output: 150-sheet output tray
Media weight	60 to 163 g/m²
Input capacity	Tray 1: Sheets: up to 250; Envelopes: up to 10 Maximum: Up to 250 sheets
Output capacity	Standard: Up to 150 sheets Envelopes: Up to 10 Maximum: Up to 150 sheets
Compatible operating systems	Microsoft® Windows® 11, 10, 7 SP1: 32-bit or 64-bit, 2 GB available hard disk space, Internet connection, Microsoft® Internet Explorer or Edge. Apple® macOS v10.15 Catalina, macOS v11 Big Sur, macOS v12 Monterey,; 2 GB HD; Internet required; Linux (For more information, see https://developers.hp.com/hp-linux-imaging-and-printing)
Compatible network operating systems	Windows Server 2008 R2 64-bit, Windows Server 2008 R2 64-bit (SP1), Windows Server 2012 64-bit, Windows Server 2012 R2 64-bit, Windows Server 2016 64-bit, Linux- For more information see http://developers.hp.com/hp-linux-imaging-and-printing,
Minimum system requirements	Windows: Microsoft® Windows® 11, 10, 7 SP1: 32-bit or 64-bit, 2 GB available hard disk space, Internet connection, Microsoft® Internet Explorer or Edge. Mac: Apple® macOS v10.15 Catalina, macOS v11 Big Sur, macOS v12 Monterey; 2 GB HD; Internet required
Software included	No CD in box; Downloadable Software from http://www.hp.com, http://www.hpsmart.com/setup, in-OS app stores.
Security management	Password-protected network embedded Web server; enable/disable Network ports; SNMPv1 community password change; 802.1x authentication
Printer management	HP Smart, HPSM, Web JetAdmin, admin.hpsmart.com
Dimensions and weight	
Printer dimensions (W x D x H)	Minimum 367.0 x 398.2 x 216.2 mm; Maximum: 367.0 × 758.8 × 366.1 mm
Printer weight	7.5 Kg
Operating environment	Temperature: 15 to 32.5°C Humidity: 30 to 70% RH
Storage conditions	Temperature: -20 to 60ºC
Acoustics	Acoustic power emissions: 6.5 B(A) (printing at 33ppm) Acoustic pressure emissions: 53 dB(A)
Power	Requirements: 110-volt input voltage: 110 to 127 VAC (+/- 10%), 60 Hz/50 Hz;220-volt input voltage: 220 to 240 VAC (+/- 10%), 60 Hz/50 Hz; Consumption: 484 watts (active printing), 2.93 watts (ready), 1.06 watts (sleep), 0.06 watts (Manual off), 0.06 watts (Auto Off/Manual On), 0.9 watts (Auto Off/Wake on LAN);; Typical Electricity Consumption (TEC): Energy Star: 0.387kWh/week;; Power supply type: Internal (Built-in) power supply
Certifications	RCM (Australia), TUV and GS Mark (Germany), BSMI (Taiwan), CCC (China), BIS (India), KC (South Korea), SIRIM (Malaysia), Cambodia, Ukraine, EAC, Eastern European approvals, CE Marking, FCC, Energy Star, UL, Paraguay, Chile, Argentina, Indonesia, Singapore, Philippines, etc. Electromagnetic emission standard: CISPR32:2012 & CISPR32:2015 /EN55032:2012 & EN55032:2015+AC:2016 - Class B; EN 61000-3-2:2014; EN 61000-3-3:2013; EN 55035:2017; FCC Title 47 CFR, Part 15 Class B/ICES-003, Issue 6 Blue Angel Blue Angel compliant Yes, Blue Angel DE-UZ 205 Telecom compliance: NA, without wireless module.
Sustainable impact specifications	Mercury free
Country of origin	Made in Vietnam
What's in the box[3]	3G651F HP LaserJet Pro 3002dn Printer; HP Black LaserJet Toner Introductory Cartridge (yield ~1000 pages); Setup Guide; Reference Guide; Regulatory Flyer; Warranty Guide; Power cord
Warranty	One year limited warranty. Warranty and support options vary by product, country and local legal requirements.

Footnotes

[1] Requires the HP Smart app download. For details on local printing requirements see http://www.hp.com/go/mobileprinting. Certain features/software are available in English language only, and differ between desktop and mobile applications. Subscription may be required. Internet access required and must be purchased separately. HP account required for full functionality. List of supported operating systems available in app stores. Fax capabilities are for sending a fax only. After 3 months, a monthly fee applies to continue advanced features with HP Smart Pro. For more information, see http://www.hpsmart.com.
[2] HP Web Jetadmin is available for download at no additional charge at http://www.hp.com/go/webjetadmin.
[3] Easy setup and manage - Requires use of Smart Admin Dashboard for printer setup and onboarding of users.
[4] HP JetAdvantage Security Manager must be purchased separately. To learn more, please visit http://www.hp.com/go/securitymanager.
[5] Recycling: Program availability varies. Original HP cartridge return and recycling is currently available in more than 60 countries, territories and regions in Asia, Africa, Europe, and North and South America through the HP Planet Partners program. For details, see http://www.hp.com/recycle.
[6] Save up to 50% on toner (mono) – Based on monthly subscription cost of HP Instant Ink monochrome toner service 1,500-page plan without purchase of additional sets of pages compared to cost per page to print ISO/IEC 24711 pages on most in-class, traditional A4 monochrome toner cartridge printers <€494 and MFPs priced and <€672 using original standard-capacity integrated cartridges (toner and drum in one cartridge). Average CPP per country used to determine percent savings claim versus CPP for HP Instant Ink. Sale prices not considered for this study. Printers which only use XL cartridges excluded due to non-standard hardware & supplies model. Keypoint Intelligence September 2021 study commissioned by HP, based on publicly available information as of August 18, 2021. Printers selected by market share in IDC Quarterly Hardcopy Peripherals Tracker – Final Historical 2021Q2. For details: www.keypointintelligence.com/HPInstantInk.
[7] Automatic delivery and consolidated bill: Printers require direct connection to the Internet for program participation. Internet access sold separately.
[8] Never run out: Based on plan usage, Internet connection to eligible HP printer, valid credit/debit card, email address, and delivery service in your geographic area.
[9] Change or cancel: Change or cancel your plan at any time online. If you decide to cancel your HP Instant Ink you can go back to using HP original Standard or XL cartridges. Plan upgrades are effective immediately and the charges will be applied retrospectively or in the next billing cycle, depending on user choice. Plan downgrades and cancellations are effective after the last day of the current billing period. For full details go to http://www.hpinstantink.com/terms.

Technical specifications disclaimers

[1] Measured using ISO/IEC 24734, excludes first set of test documents. For more information see http://www.hp.com/go/printerclaims. Exact speed varies depending on the system configuration, software application, driver, and document complexity.
[2] Measured using ISO/IEC 17629. For more information see http://www.hp.com/go/printerclaims. Exact speed varies depending on the system configuration, software application, driver, and document complexity.
[3] For yield information on the cartridge included with your printer, see http://www.hp.com/go/toneryield. Yield values measured in accordance with ISO/IEC 19752 and continuous printing. Actual yields vary considerably based on images printed and other factors.

www.blauer-engel.de/uz219

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

gb-en April 2023