UNIFIED COMMUNICATIONS



INFORMATION



Speakerphone for meeting rooms

The omnidirectional audio pickup from up to 3 meters with intelligent noise reduction and echo cancellation algorithms make the UC SPK01M the perfect choice for medium meeting rooms. Guaranteeing seamless connection, a USB cable or an audio cable this elegant speaker can be paired with up to 3 devices at the same.

FEATURES



Omnidirectional

The UC SPK01M supports 360-degree omnidirectional audio pickup ensuring every voice in your meeting room is transmitted to the participants joining remotely.



High-quality voice experience

This performance speaker with intelligent noise reduction and echo cancellation algorithms guarantees crystal clear sound for your calls.



Easy set up

Seamless connection via Bluetooth, a USB cable or an audio cable. The speaker is instantly operational after connection.



Multiple device connectivity

Connect up to 3 devices at the same time via Bluetooth, a USB cable and an audio cable.

SPECIFICATION

01 SPEAKER

Maximum sound pressure level	85dB
Distortion	≦1%
Signal to noise ratio	75dB
Frequency range	150Hz ~ 16kHz

02 MICROPHONE

Number of microphone arrays	x3
Voice pickup range	3m (radius)
Frequency range	150Hz ~ 7.5kHz

03 CONNECTIVITY & BUTTON OPERATIONS

USB Type C	x1 (Audio In/Out, Charge 5V/2A)
AUX	x1 (In/Out, 3.5mm)
Buttons	Power, Volume, Blutooth, Mute, Answer/Hang up

04 ACCESSORIES & BATTERY

USB (type A to C) cable	yes
Audio cable	yes
Battery capacity	7.4V/2200mAh
Charging	wired 5V/2A
Battery life on a single charge	8 hours

05 SUSTAINABILITY

Regulations	CE, RoHS support, ErP, WEEE, REACH

06 DIMENSIONS / WEIGHT

Weight (without box)	0.39kg
EAN code	4948570033034

GALLERY







All trademarks and registered trademarks acknowledged. E & O E. Specification subject to change without notice. All LCD's comply with ISO-9241-307:2008 in connection with pixel defects. **© IIYAMA CORPORATION. ALL RIGHTS RESERVED**