

# Technical Accessory Guides (TAGs)

For Associates, Resellers, ISVs and Alliance Partners

Global



Version: Active-Only

Will only show products that are known to be available for sale

Need to provide an update or change?

Contact <mailto:ns9759@zebra.com>



For Internal Use by  
**PartnerConnect Members Only**



## TC501 Series Technical Accessory Guide






Does not include TC51/TC52/TC52x/TC52ax/TC53/TC56/TC57/TC57x/TC58 accessories. See separate guide for these TC5X series accessories.  
Does not include TC55 accessories. See separate guide for TC55 accessories.

**NOTE:** This document is only for general reference. Solutions Pathway and related PMBs should be used for product availability, pricing, and final solution selection.





\* Zebra does not endorse or specifically recommend any **third-party products, accessories, or hardware**. ZEBRA DISCLAIMS ANY AND ALL LIABILITY, INCLUDING ANY EXPRESS OR IMPLIED WARRANTIES, WHETHER ORAL OR WRITTEN, FOR SUCH THIRD PARTY PRODUCTS, ACCESSORIES, OR HARDWARE. THE CUSTOMER ACKNOWLEDGES THAT NO REPRESENTATION HAS BEEN MADE BY ZEBRA AS TO THE FITNESS OF THE THIRD-PARTY PRODUCTS, ACCESSORIES, OR HARDWARE FOR THE CUSTOMER'S INTENDED PURPOSE.





### Cradles and Charging



#### Single Device Charge + Communication Cradles

Part Number	Picture	Description	Notes	Required Items
CRD-TC5A-1SE-B (for use with rugged boot)  CRD-TC5A-1SE (for use without rugged boot)		Single-Slot TC501 Charger w/ Ethernet ShareCradle Base	<ul style="list-style-type: none"> <li>▶ Device with standard battery charges from 0–90% in about 1.5 hours</li> <li>▶ Connects to charge contacts and USB-C port on bottom of device.</li> <li>▶ Allows network speeds up to 1Gb/s via ethernet connection in back of base.</li> <li>▶ Compatible with device units with hand strap, Rugged Boot (only CRD-TC5A-1SC-B-01), Trigger Handle attached.</li> <li>▶ Includes:               <ul style="list-style-type: none"> <li>- CRDCUP-TC5A-1DF-B or CRDCUP-TC5A-1DF</li> <li>- CRD-ETHSNGLBASE-01</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>▶ USB-C Cable (CBL-EC5X-USBC3A-01)</li> <li>▶ Power Supply (PWR-WUA5V45W1US or country specific version)</li> <li>▶ Rugged Boot (SG-TC5AEXC01) required for use with CRD-TC5A-1SC-B-01</li> </ul>
CRD-TC5A-2SE1B-B (for use with rugged boot)  CRD-TC5A-2SE1B (for use without rugged boot)		Single-Slot TC501 and Spare Battery Charger w/ Ethernet ShareCradle Base	<ul style="list-style-type: none"> <li>▶ Device with standard battery charges from 0–90% in about 1.5 hours</li> <li>▶ Connects to charge contacts and USB-C port on bottom of device.</li> <li>▶ Allows network speeds up to 1Gb/s via ethernet connection in back of base.</li> <li>▶ Compatible with device units with hand strap, Rugged Boot (only CRD-TC5A-2SE1B-B), Trigger Handle attached.</li> </ul>	<ul style="list-style-type: none"> <li>▶ USB-C Cable (CBL-EC5X-USBC3A-01)</li> <li>▶ Power Supply (PWR-WUA5V45W1US or country specific version)</li> <li>▶ Rugged Boot (SG-TC5AEXC01) required for use with CRD-TC5A-2SE1B-B</li> </ul>
CRDCUP-TC5A-1DF-B (for use with rugged boot)  CRDCUP-TC5A-1DF (for use without rugged boot)		Single-Slot TC501 Charger ShareCradle Cup	<ul style="list-style-type: none"> <li>▶ Device with standard battery charges from 0–70% in about 45 minutes.</li> <li>▶ Can be paired with ShareCradle Ethernet Base (CRD-ETHSNGLBASE-01) to enable ethernet connectivity.</li> <li>▶ Connects to charge contacts and USB-C port on bottom of device.</li> <li>▶ Also serves as replacement cradle cup for the single-slot and five-slot ShareCradle bases.</li> <li>▶ Compatible with device units with hand strap, Rugged Boot (only CRDCUP-TC5A-1DF-B), Trigger Handle attached.</li> </ul>	<ul style="list-style-type: none"> <li>▶ USB-C Cable (CBL-EC5X-USBC3A-01)</li> <li>▶ Power Supply (PWR-WUA5V45W1US or country specific version)</li> <li>▶ Rugged Boot (SG-TC5AEXC01) required for use with CRDCUP-TC5A-1DF-B</li> </ul>



CRD-ETHSNGLBASE-01		Single-Slot Ethernet ShareCradle Base	<ul style="list-style-type: none"> <li>▶ Standalone Base to pair with cradle cups chargers for adding ethernet connectivity.</li> <li>▶ Allows network speeds up to 1Gb/s via ethernet connection in back of base.</li> <li>▶ Included in all single-slot Ethernet ShareCradle Configurations.</li> </ul>	<ul style="list-style-type: none"> <li>▶ USB-C Cable (CBL-EC5X-USBC3A-01)</li> <li>▶ Power Supply (PWR-WUA5V45W1US or country specific version)</li> </ul>
Single Device Charge-Only Cradles				
CRD-TC5A-2SC1B-B (for use with rugged boot)  CRD-TC5A-2SC1B (for use without rugged boot)		Single-Slot TC501 and Spare Battery Charge-Only ShareCradle Cup	<ul style="list-style-type: none"> <li>▶ Device with standard battery charges from 0–90% in about 1.5 hours.</li> <li>▶ Connects to charge contacts on bottom of device.</li> <li>▶ Also serves as replacement cradle cup for the five-slot TC501 and Spare Battery Charge-Only ShareCradles.</li> <li>- Note: This unit lacks USB-C port connection and cannot be paired with the ethernet bases.</li> <li>▶ Compatible with device units with hand strap, Rugged Boot (only CRD-TC5A-2SC1B-B), Trigger Handle attached.</li> </ul>	<ul style="list-style-type: none"> <li>▶ USB-C Cable (CBL-EC5X-USBC3A-01)</li> <li>▶ Power Supply (PWR-WUA5V45W1US or country specific version)</li> <li>▶ Rugged Boot (SG-TC5AEXC01) required for use with CRD-TC5A-2SC1B-B</li> </ul>
Multi-Device Cradles				
Part Number	Picture	Description	Notes	Required Items
CRDCUP-TC5A-2D-B (for use with rugged boot)  CRDCUP-TC5A-2D (for use without rugged boot)		2-Slot TC501 Charger ShareCradle Cup	<ul style="list-style-type: none"> <li>▶ Device with standard battery charges from 0–90% in about 1.5 hours.</li> <li>▶ Connects to charge contacts on bottom of device.</li> <li>▶ Also serves as replacement cradle cup for the single-slot and five-slot ShareCradle bases.</li> <li>▶ Compatible with device units with Rugged Boot (only CRDCUP-TC5A-2D-B) and hand strap; Trigger Handle can remain attached on back cup only.</li> </ul>	<ul style="list-style-type: none"> <li>▶ USB-C Cable (CBL-EC5X-USBC3A-01)</li> <li>▶ Power Supply (PWR-WUA5V45W1US or country specific version)</li> <li>▶ Rugged Boot (SG-TC5AEXC01) required for use with CRDCUP-TC5A-2D-B</li> </ul>
CRD-TC5AB-5SC5DF-1 (for use with rugged boot)  CRD-TC5A-5SC5DF-1 (for use without rugged boot)		5-Slot TC501 Fast-Charging ShareCradle Kit	<ul style="list-style-type: none"> <li>▶ Device with standard battery charges from 0–70% in about 45 minutes.</li> <li>▶ Connects to charge contacts and USB-C port on bottom of device.</li> <li>▶ Compatible with device units with hand strap, Rugged Boot (only CRD-TC5AB-5SC5DF-1), Trigger Handle attached.</li> <li>▶ Can be racked/ mounted in a standard 19 inch rack system via the mounting accessory (BRKT-SCRD-SMRK-01)</li> <li>▶ Kit Includes:               <ul style="list-style-type: none"> <li>- Power Supply: PWR-BGA12V150W1WW</li> <li>- Single-Slot TC501 Charger Cup - QTY 5: CRDCUP-TC5A-1DF-B or CRDCUP-TC5A-1D</li> <li>- 5-Slot Fast Charger Base: CRD-FCBASE-01</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>▶ AC Line Cord (23844-00-00F or country specific version)</li> <li>▶ Rugged Boot (SG-TC5AEXC01) required for use with CRD-TC5AB-5SC5DF-1</li> </ul>

<p>CRD-TC5A-5SC5DF-B (for use with rugged boot)</p> <p>CRD-TC5A-5SC5DF (for use without rugged boot)</p>		<p>5-Slot TC501 Fast-Charging ShareCradle</p>	<ul style="list-style-type: none"> <li>▶ Device with standard battery charges from 0–70% in about 45 minutes.</li> <li>▶ Connects to charge contacts and USB-C port on bottom of device.</li> <li>▶ Compatible with device units with hand strap, Rugged Boot (only CRD-TC5A-5SC5DF-B), Trigger Handle attached.</li> <li>▶ Can be racked/ mounted in a standard 19 inch rack system via the mounting accessory (BRKT-SCRD-SMRK-01)</li> <li>▶ Includes: <ul style="list-style-type: none"> <li>- Single-Slot TC501 Charger Cup - QTY 5: CRDCUP-TC5A-1DF-B or CRDCUP-TC5A-1D</li> <li>- 5-Slot Fast Charger Base: CRD-FCBASE-01</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>▶ Power Supply (PWR-BGA12V150W1WW)</li> <li>▶ AC Line Cord (23844-00-00F or country specific version)</li> <li>▶ Rugged Boot (SG-TC5AEXC01) required for use with CRD-TC5A-5SC5DF-B</li> </ul>
<p>CRD-TC5AB-5SE5D-1 (for use with rugged boot)</p> <p>CRD-TC5A-5SE5D-1 (for use without rugged boot)</p>		<p>5-Slot TC501 Charger w/ Ethernet ShareCradle Kit</p>	<ul style="list-style-type: none"> <li>▶ Device with standard battery charges from 0–90% in about 1.5 hours.</li> <li>▶ Connects to charge contacts and USB-C port on bottom of device.</li> <li>▶ Allows network speeds up to 1Gb/s via ethernet connection in back of base.</li> <li>▶ Compatible with device units with hand strap, Rugged Boot (only CRD-TC5AB-5SE5D-1), Trigger Handle attached.</li> <li>▶ Can be racked/ mounted in a standard 19 inch rack system via the mounting accessory (BRKT-SCRD-SMRK-01)</li> <li>▶ Kit Includes: <ul style="list-style-type: none"> <li>- Power Supply: PWR-BGA12V150W1WW</li> <li>- Single-Slot TC501 Charger Cup - QTY 5: CRDCUP-TC5A-1DF-B or CRDCUP-TC5A-1D</li> <li>- 5-Slot Ethernet Base: CRD-ETHBASE-01</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>▶ AC Line Cord (23844-00-00F or country specific version)</li> <li>▶ Rugged Boot (SG-TC5AEXC01) required for use with CRD-TC5AB-5SE5D-1</li> </ul>
<p>CRD-TC5A-5SE5D-B (for use with rugged boot)</p> <p>CRD-TC5A-5SE5D (for use without rugged boot)</p>		<p>5-Slot TC501 Charger w/ Ethernet ShareCradle</p>	<ul style="list-style-type: none"> <li>▶ Device with standard battery charges from 0–90% in about 1.5 hours.</li> <li>▶ Connects to charge contacts and USB-C port on bottom of device.</li> <li>▶ Allows network speeds up to 1Gb/s via ethernet connection in back of base.</li> <li>▶ Compatible with device units with hand strap, Rugged Boot (only CRD-TC5A-5SE5D-B), Trigger Handle attached.</li> <li>▶ Can be racked/ mounted in a standard 19 inch rack system via the mounting accessory (BRKT-SCRD-SMRK-01)</li> <li>▶ Includes: <ul style="list-style-type: none"> <li>- 1-Slot TC501 Charger Cup - QTY 5: CRDCUP-TC5A-1DF-B or CRDCUP-TC5A-1D</li> <li>- 5-Slot Ethernet Base: CRD-ETHBASE-01</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>▶ Power Supply (PWR-BGA12V150W1WW)</li> <li>▶ AC Line Cord (23844-00-00F or country specific version)</li> <li>▶ Rugged Boot (SG-TC5AEXC01) required for use with CRD-TC5A-5SE5D-B</li> </ul>
<p>CRD-TC5AB-5SC5D5B-1 (for use with rugged boot)</p> <p>CRD-TC5A-5SC5D5B-1 (for use without rugged boot)</p>		<p>5-Slot TC501 and Spare Battery Charge-Only ShareCradle Kit</p>	<ul style="list-style-type: none"> <li>▶ Device with standard battery charges from 0–90% in about 1.5 hours.</li> <li>▶ Connects to charge contacts on bottom of device.</li> <li>▶ Compatible with device units with hand strap, Rugged Boot (only CRD-TC5AB-5SC5D5B-1), Trigger Handle attached.</li> <li>▶ Can be racked/ mounted in a standard 19 inch rack system via the mounting accessory (BRKT-SCRD-SMRK-01)</li> <li>▶ Kit Includes: <ul style="list-style-type: none"> <li>- Power Supply: PWR-BGA12V150W1WW</li> <li>- Single-Slot TC501 and Spare Battery Charge-Only Cup - QTY 5: CRD-TC5A-2SC1B-B or CRD-TC5A-2SC1B</li> <li>- 5-Slot Fast Charger Base: CRD-FCBASE-01</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>▶ AC Line Cord (23844-00-00F or country specific version)</li> <li>▶ Rugged Boot (SG-TC5AEXC01) required for use with CRD-TC5AB-5SC5D5B-1</li> </ul>


<p>CRD-TC5A-5SC5D5B-B (for use with rugged boot)</p> <p>CRD-TC5A-5SC5D5B (for use without rugged boot)</p>		<p>5-Slot TC501 and Spare Battery Charge-Only ShareCradle</p>	<ul style="list-style-type: none"> <li>▶ Device with standard battery charges from 0–90% in about 45 minutes.</li> <li>▶ Connects to charge contacts on bottom of device.</li> <li>▶ Compatible with device units with hand strap, Rugged Boot (only CRD-TC5AB-5SC5D5B-1), Trigger Handle attached.</li> <li>▶ Can be racked/ mounted in a standard 19 inch rack system via the mounting accessory (BRKT-SCRD-SMRK-01)</li> <li>▶ Includes: <ul style="list-style-type: none"> <li>- Single-Slot TC501 and Spare Battery Charge-Only Cup - QTY 5: CRD-TC5A-2SC1B-B or CRD-TC5A-2SC1B</li> <li>- 5-Slot Fast Charger Base: CRD-FCBASE-01</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>▶ Power Supply (PWR-BGA12V150W1WW)</li> <li>▶ AC Line Cord (23844-00-00F or country specific version)</li> <li>▶ Rugged Boot (SG-TC5AEXC01) required for use with CRD-TC5A-5SC5D5B-B</li> </ul>
<p>CRD-TC5AB-5SC10D-1 (for use with rugged boot)</p> <p>CRD-TC5A-5SC10D-1 (for use without rugged boot)</p>		<p>10-Slot TC501 Charger ShareCradle Kit</p>	<ul style="list-style-type: none"> <li>▶ Device with standard battery charges from 0–90% in about 1.5 hours.</li> <li>▶ Connects to charge contacts and USB-C port on bottom of device.</li> <li>▶ Compatible with device units with hand strap, Rugged Boot (only CRD-TC5AB-5SC10D-1), Trigger Handle attached.</li> <li>▶ Can be racked/ mounted in a standard 19 inch rack system via the mounting accessory (BRKT-SCRD-SMRK-01)</li> <li>▶ Kit Includes: <ul style="list-style-type: none"> <li>- Power Supply: PWR-BGA12V150W1WW</li> <li>- 2-Slot TC501 Charger Cup - QTY 5: CRDCUP-TC5A-2D-B or CRDCUP-TC5A-2D</li> <li>- 5-Slot Fast Charger Base: CRD-FCBASE-01</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>▶ AC Line Cord (23844-00-00F or country specific version)</li> <li>▶ Rugged Boot (SG-TC5AEXC01) required for use with CRD-TC5AB-5SC10D-1</li> </ul>
<p>CRD-TC5A-5SC10D-B (for use with rugged boot)</p> <p>CRD-TC5A-5SC10D (for use without rugged boot)</p>		<p>10-Slot TC501 Charger ShareCradle</p>	<ul style="list-style-type: none"> <li>▶ Device with standard battery charges from 0–90% in about 1.5 hours.</li> <li>▶ Connects to charge contacts and USB-C port on bottom of device.</li> <li>▶ Compatible with device units with hand strap, Rugged Boot (only CRD-TC5A-5SC10D-B), Trigger Handle attached.</li> <li>▶ Can be racked/ mounted in a standard 19 inch rack system via the mounting accessory (BRKT-SCRD-SMRK-01)</li> <li>▶ Includes: <ul style="list-style-type: none"> <li>- 2-Slot TC501 Charger Cup - QTY 5: CRDCUP-TC5A-2D-B or CRDCUP-TC5A-2D</li> <li>- 5-Slot Fast Charger Base: CRD-FCBASE-01</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>▶ Power Supply (PWR-BGA12V150W1WW)</li> <li>▶ AC Line Cord (23844-00-00F or country specific version)</li> <li>▶ Rugged Boot (SG-TC5AEXC01) required for use with CRD-TC5A-5SC10D-B</li> </ul>
<p>CRD-FCBASE-01</p>		<p>5-Slot Fast-Charging ShareCradle Base</p>	<ul style="list-style-type: none"> <li>▶ Included in all multi-slot ShareCradles except for the Ethernet models.</li> <li>▶ Modular system allows each base to handle various combination of Handheld, Tablet, and Wearable mobile computers on one base.</li> <li>▶ Can be racked/ mounted in a standard 19 inch rack system via the mounting accessory (BRKT-SCRD-SMRK-01)</li> </ul>	<ul style="list-style-type: none"> <li>▶ Power Supply (PWR-BGA12V150W1WW)</li> <li>▶ AC Line Cord (23844-00-00F or country specific version)</li> </ul>






CRD-ETHBASE-01		5-Slot Charger w/ Ethernet ShareCradle Base	<ul style="list-style-type: none"> <li>▶ Included in the multi-slot Ethernet ShareCradle configuration.</li> <li>▶ Allows network speeds up to 1Gb/s.</li> <li>▶ Modular system allows each base to handle various combination of Handheld, Tablet, and Wearable mobile computers on one base.</li> <li>▶ Can be racked/ mounted in a standard 19 inch rack system via the mounting accessory (BRKT-SCRD-SMRK-01)</li> </ul>	<ul style="list-style-type: none"> <li>▶ Power Supply (PWR-BGA12V150W1 WW)</li> <li>▶ AC Line Cord (23844-00-00F or country specific version)</li> </ul>
BRKT-SCRD-SMRK-01		5-Slot ShareCradle Mounting Bracket	<ul style="list-style-type: none"> <li>▶ Allows for rack and wall mounting of one 5-Slot ShareCradle, up to four Single-Slot ShareCradles, or up to four 4-Slot Battery Chargers.</li> <li>▶ Bracket can be mounted on standard 19" network rack or on a wall.</li> <li>▶ Has cable routing slots and removable power supply tray that stores and conceals power supplies.</li> <li>▶ Adjustable tabs &amp; screw mounts for easy hanging/installation.</li> <li>▶ Adjustable orientations: <ul style="list-style-type: none"> <li>- 25° High Density (5-Slot Charge Only Cradle)</li> <li>- Horizontal (Single Slot Cradle or 4-Slot Battery Chargers).</li> </ul> </li> <li>▶ See the Bluetooth-Generic Accessories TAG for info on 3rd party Network Racks that can be used for mounting this bracket.</li> </ul>	




**Misc. Cradle Accessories**

Part Number	Picture	Description	Notes	Required Items
HLD-TC5AB-01 (for use with rugged boot)		TC501 w/ Rugged Boot Holder for ShareCradle	<ul style="list-style-type: none"> <li>▶ Replacement cradle inserts/shims that are typically included with each TC501 ShareCradle.</li> <li>▶ "TC501" with Rugged Boot symbol shim used when device has boot/exoskeleton installed.</li> <li>▶ Compatible with device units with hand strap, Rugged Boot, Trigger Handle attached.</li> <li>▶ Typically ordered to replace lost/damaged shims.</li> <li>▶ Note: As of February 2026, picture does not represent final design</li> </ul>	▶ Rugged Boot (SG-TC5AEXC01) required for use
HLD-TC5A-01 (for use without rugged boot)		TC501 Holder for ShareCradle	<ul style="list-style-type: none"> <li>▶ Replacement cradle inserts/shims that are typically included with each TC501 ShareCradle.</li> <li>▶ "TC501" shim used when TC501 not equipped with rugged boot.</li> <li>▶ Compatible with device units with hand strap or Trigger Handle attached.</li> <li>▶ Typically ordered to replace lost/damaged shims.</li> <li>▶ Note: As of February 2026, picture does not represent final design</li> </ul>	

**Legacy ShareCradle Cups and Components**

Part Number	Picture	Description	Notes	Required Items
CRDCUP-NGTC5AB-01 (for use with rugged boot)  CRDCUP-NGTC5ANB-01 (for use without rugged boot)		TC501 Replacement Charge-Only Device Cup for One Device  (Legacy ShareCradle)	<ul style="list-style-type: none"> <li>▶ Only for use with legacy ShareCradle</li> <li>▶ Enables the use of TC501 devices with legacy ShareCradle setups.</li> <li>▶ Includes: <ul style="list-style-type: none"> <li>- Legacy ShareCradle Cup: CRDCUP-NGTC5TC7</li> <li>- TC501 Shim: SHIM-CRD-TC5AB (for use with rugged boot) or SHIM-CRD-TC5A (for use without rugged boot)</li> </ul> </li> </ul>	▶ Rugged Boot (SG-TC5AEXC01) required for use with CRDCUP-NGTC5AB-01






<p>CRDCUP-NGTC5AB-05 (for use with rugged boot)</p> <p>CRDCUP-NGTC5ANB-05 (for use without rugged boot)</p>		<p>TC501 Replacement Charge-Only Device Cup for Five Devices</p>	<ul style="list-style-type: none"> <li>▶ Only for use with legacy ShareCradle</li> <li>▶ Enables the use of TC501 devices with legacy ShareCradle setups.</li> <li>▶ Includes: <ul style="list-style-type: none"> <li>- Legacy ShareCradle Cup - QTY 5: CRDCUP-NGTC5TC7</li> <li>- TC501 Shim - QTY 5: SHIM-CRD-TC5AB (for use with rugged boot) or SHIM-CRD-TC5A (for use without rugged boot)</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>▶ Rugged Boot (SG-TC5AEXO01) required for use with CRDCUP-NGTC5AB-05</li> </ul>
<p>CRDCUP-NGTC5AEB-01 (for use with rugged boot)</p> <p>CRDCUP-NGTC5AEN-01 (for use without rugged boot)</p>		<p>TC501 Replacement Ethernet Device Cup for One Device</p>	<ul style="list-style-type: none"> <li>▶ Only for use with legacy ShareCradle</li> <li>▶ Enables the use of TC501 devices with legacy ShareCradle setups.</li> <li>▶ Includes: <ul style="list-style-type: none"> <li>- Legacy ShareCradle w/ Ethernet Cup: CRDCUP-NGTC5TC7ETH</li> <li>- TC501 Shim: SHIM-CRD-TC5AB (for use with rugged boot) or SHIM-CRD-TC5A (for use without rugged boot)</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>▶ Rugged Boot (SG-TC5AEXO01) required for use with CRDCUP-NGTC5AEB-01</li> </ul>
<p>CRDCUP-NGTC5AEB-05 (for use with rugged boot)</p> <p>CRDCUP-NGTC5AEN-05 (for use without rugged boot)</p>		<p>TC501 Replacement Ethernet Device Cup for Five Devices</p>	<ul style="list-style-type: none"> <li>▶ Only for use with legacy ShareCradle</li> <li>▶ Enables the use of TC501 devices with legacy ShareCradle setups.</li> <li>▶ Includes: <ul style="list-style-type: none"> <li>- Legacy ShareCradle w/ Ethernet Cup - QTY 5: CRDCUP-NGTC5TC7ETH</li> <li>- TC501 Shim - QTY 5: SHIM-CRD-TC5AB (for use with rugged boot) or SHIM-CRD-TC5A (for use without rugged boot)</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>▶ Rugged Boot (SG-TC5AEXO01) required for use with CRDCUP-NGTC5AEB-05</li> </ul>
<p>SHIM-CRD-TC5AB (for use with rugged boot)</p> <p>SHIM-CRD-TC5A (for use without rugged boot)</p>		<p>TC501 Replacement Shim for Legacy ShareCradle Cups</p>	<ul style="list-style-type: none"> <li>▶ Replaces the TC53x / TC58x shim to make Legacy ShareCradles compatible with TC501 devices</li> <li>▶ Only for use with legacy ShareCradle</li> <li>▶ ShareCradle cup configuration dependent on use of Rugged Boot(SG-TC5AEXO-01)</li> </ul>	<ul style="list-style-type: none"> <li>▶ Rugged Boot (SG-TC5AEXO01) required for use with SHIM-CRD-TC5AB</li> </ul>
<b>Battery Charging</b>				
<b>Part Number</b>	<b>Picture</b>	<b>Description</b>	<b>Notes</b>	<b>Required Items</b>
<p>CRDCUP-TC5A7A-4B</p>		<p>4-Slot Battery Charger</p>	<ul style="list-style-type: none"> <li>▶ Charges up to four spare Standard capacity, Wireless charging, or Extended capacity batteries.</li> <li>▶ Can be used standalone or up to 4 Chargers can be mounted on Mounting Bracket (BRKT-SCRD-SMRK-01)</li> </ul>	<ul style="list-style-type: none"> <li>▶ USB-C Cable (CBL-EC5X-USBC3A-01)</li> <li>▶ Power Supply (PWR-WUA5V45W1US or country specific version)</li> </ul>






Direct to Device Charging and Communication				
Part Number	Picture	Description	Notes	Required Items
CBL-EC5X-USBC3A-01		USB-C to USB-C cable	<ul style="list-style-type: none"> <li>▶ USB-C to USB-C cable</li> <li>▶ Supports 3.0 Communications and Fast Charge Speeds</li> <li>- NOTE: Must use fast charge capable USB-C power adapter (PWR-WUA5V45W1 US) to achieve fast charge speeds with compatible ShareCradles</li> <li>▶ Attaches to USB-C port on bottom of device or into back of compatible next-generation ShareCradles and battery charger</li> <li>▶ Cable length is 1M (~3.25 ft.)</li> </ul>	
Snap-On Accessories				
Part Number	Picture	Description	Notes	Required Items
TRG-TC5AB-ELEC-01 (for use with rugged boot)		Electronic Trigger Handle	<ul style="list-style-type: none"> <li>▶ Drop spec of device is 7 feet to concrete</li> <li>▶ Uses electrical trigger via contacts on back side of TC501</li> <li>▶ Trigger Handle accessory offers customers the option of using the product in a gun form factor, ideal for scan-intensive situations.</li> <li>▶ Trigger Handle attaches to the mounts on the Rugged Boot (required) and device.</li> <li>▶ Does not block access to rear facing camera and flash allowing camera to be used while using the trigger handle.</li> <li>▶ Compatible with both Standard and Extended capacity batteries.</li> <li>▶ Optional Wrist Strap (SG-PD40-WLD1-01) also available.</li> </ul>	▶ Rugged Boot/Exoskeleton (SG-TC5AEXO-01)
TRG-TC5A-ELEC-01 (for use without rugged boot)		Electronic Trigger Handle	<ul style="list-style-type: none"> <li>▶ Drop spec of device is 6 feet to tile</li> <li>▶ Uses electrical trigger via contacts on back side of TC501</li> <li>▶ Trigger Handle accessory offers customers the option of using the product in a gun form factor, ideal for scan-intensive situations.</li> <li>▶ Trigger Handle attaches to the mounts on the device.</li> <li>▶ Does not block access to rear facing camera and flash allowing camera to be used while using the trigger handle.</li> <li>▶ Compatible with both Standard and Extended capacity batteries.</li> <li>▶ Optional Wrist Strap (SG-PD40-WLD1-01) also available.</li> </ul>	

Soft Goods - Cases/Holsters

Part Number	Picture	Description	Notes	Required Items
SG-TC5AEXO-01		Rugged Boot/Exoskeleton	<ul style="list-style-type: none"> <li>▶ Boot increases drop spec of device to 9 ft. to concrete.</li> <li>▶ Two piece design provides for an easier installation and snaps together to form boot.</li> </ul>	
SG-NGTC5TC7-HLSTR-01		Soft Holster	<ul style="list-style-type: none"> <li>▶ Vertical orientation with Open Bucket design to accommodate TC501, device with optional Rugged Boot/Exoskeleton installed or device with optional Trigger Handle.</li> <li>▶ Strap on rear of holster allows adjustment for use with the accessory options mentioned above.</li> <li>▶ Leather material.</li> <li>▶ Includes Loop for storage of optional stylus.</li> <li>▶ Non rotating for maximum durability.</li> <li>▶ Holster includes cut-out for speaker output.</li> </ul>	



<p>3PTY-MOB-031009</p> <p>NOTE: Products sold that do not bear the Zebra brand name are serviced and supported exclusively by their manufacturers in accordance with terms and conditions packaged with the products. Zebra's Limited Warranty does not apply to products that are not Zebra branded, even if packaged or sold with Zebra products. Please contact the manufacturer directly for technical support and customer service. See PMB 11136 for more info.</p>		<p>Mobilis Basic Holster with Belt</p>	<ul style="list-style-type: none"> <li>▶ Textile holster is compatible with medium size devices.</li> <li>▶ Can be mounted to belt, forklift, etc.</li> <li>▶ Includes loop for stylus storage.</li> <li>▶ Belt included</li> </ul>	
<p>3PTY-MOB-031002</p> <p>NOTE: Products sold that do not bear the Zebra brand name are serviced and supported exclusively by their manufacturers in accordance with terms and conditions packaged with the products. Zebra's Limited Warranty does not apply to products that are not Zebra branded, even if packaged or sold with Zebra products. Please contact the manufacturer directly for technical support and customer service. See PMB 11136 for more info.</p>		<p>Mobilis Premium Holster with Belt</p>	<ul style="list-style-type: none"> <li>▶ Textile holster is compatible with medium size devices.</li> <li>▶ Can be mounted to belt, forklift, etc.</li> <li>▶ Includes pockets for stylus storage and spare battery.</li> <li>▶ Includes top D-ring loops for attaching optional shoulder strap and elastic closure strap for keeping device secure in holster.</li> <li>▶ Belt included</li> </ul>	
<p>SG-TC5A-WMADP1-01</p>		<p>Arm/Wrist Mount (Standard length Strap)</p>	<ul style="list-style-type: none"> <li>▶ Allows device to be worn as a wearable device.</li> <li>▶ Wearable design allows the user to have easy access to the device while having the ability to use both hands.</li> <li>▶ Swivel design allows device to be viewed in Portrait or Landscape mode.</li> <li>▶ Use of a Bluetooth Ring Scanner like the RS5100 is recommended. Allows for occasional use of device's built-in scanner while in mount.</li> <li>▶ Also provides access to device's USB-C port for use with RS5100/RS6100 Corded Scanner adapter cable.</li> <li>▶ Uses BOA dial-to-fit design which is strong, durable, and easy to use.</li> <li>▶ Velcro free design uses non-absorbent materials that can be wiped down.</li> <li>▶ Includes Carrier, Comfort Pad, and Small/Medium size Double BOA wrist strap (SG-WT5X6-WSTDS-01).</li> <li>▶ White Dial and accent color on strap identify size as Standard (small-medium).</li> <li>▶ Strap length can be adjusted between 128 to 191 mm (approx 5.0 to 7.5")</li> <li>▶ It is typical for each user to have their own wrist mount (for hygiene).</li> <li>▶ Same design and materials as WT6000 series wrist mounts.</li> <li>▶ Must be used with Rugged Boot/Exoskeleton installed on device</li> <li>▶ Compatible with Standard and Extended Capacity Battery</li> </ul>	<p>▶ Rugged Boot/Exoskeleton (SG-TC5AEXO1-01)</p>
<p>SG-TC5A-WMADP2-01</p>		<p>Arm/Wrist Mount (Extended length Strap)</p>	<ul style="list-style-type: none"> <li>▶ Allows device to be worn as a wearable device.</li> <li>▶ Wearable design allows the user to have easy access to the device while having the ability to use both hands.</li> <li>▶ Swivel design allows device to be viewed in Portrait or Landscape mode.</li> <li>▶ Use of a Bluetooth Ring Scanner like the RS5100 is recommended. Allows for occasional use of device's built-in scanner while in mount.</li> <li>▶ Also provides access to device's USB-C port for use with RS5100/RS6100 Corded Scanner adapter cable.</li> <li>▶ Uses BOA dial-to-fit design which is strong, durable, and easy to use.</li> <li>▶ Velcro free design uses non-absorbent materials that can be wiped down.</li> <li>▶ Includes Carrier, Comfort Pad, and Medium/Large size Double BOA Wrist Strap (SG-WT5X6-WSTDL-01).</li> <li>▶ Black Dial and accent color on strap identify size as Extended (medium-large).</li> <li>▶ Strap length can be adjusted between 164 to 265 mm (approx 6.5 to 10.5")</li> <li>▶ It is typical for each user to have their own wrist mount (for hygiene).</li> <li>▶ Same design and materials as WT6000 series wrist mounts.</li> <li>▶ Must be used with Rugged Boot/Exoskeleton installed on device</li> <li>▶ Compatible with Standard and Extended Capacity Battery</li> </ul>	<p>▶ Rugged Boot/Exoskeleton (SG-TC5AEXO1-01)</p>
<p>SG-WT5X6-WSTDS-01</p>		<p>Replacement Arm/Wrist Strap (standard size)</p>	<ul style="list-style-type: none"> <li>▶ White Dial and accent color on strap identify size as Standard (small/medium)</li> <li>▶ Strap length can be adjusted between 128 to 191 mm (approx 5.0 to 7.5")</li> </ul>	

SG-WT5X6-WSTD1-01		Replacement Arm/Wrist Strap (extended size)	<ul style="list-style-type: none"> <li>▶ Black Dial and accent color on strap identify size as Extended (medium/large)</li> <li>▶ Strap length can be adjusted between 164 to 265 mm (approx 6.5 to 10.5")</li> </ul>	
SG-WT5X6-WSTD1-01		Replacement Wrist Strap (extra-large size)	<ul style="list-style-type: none"> <li>▶ Blue Dial and accent color on strap identify size as extra-large.</li> <li>▶ Strap length can be adjusted between 218 to 375 mm (approx 8.5 to 14.75")</li> </ul>	
SG-NGWT-WSTPST-01		Replacement Arm/Wrist Strap (standard size)	<ul style="list-style-type: none"> <li>▶ White Dial and accent color on strap identify size as Standard (small/medium)</li> <li>▶ Strap length can be adjusted between 128 to 191 mm (approx 5.0 to 7.5")</li> </ul>	
SG-NGWT-WSTPLN-01		Replacement Arm/Wrist Strap (extended size)	<ul style="list-style-type: none"> <li>▶ Black Dial and accent color on strap identify size as Extended (medium/large)</li> <li>▶ Strap length can be adjusted between 164 to 265 mm (approx 6.5 to 10.5")</li> </ul>	
SG-NGWT-WSTPXL-01		Replacement Wrist Strap (extra-large size)	<ul style="list-style-type: none"> <li>▶ Blue Dial and accent color on strap identify size as extra-large.</li> <li>▶ Strap length can be adjusted between 218 to 375 mm (approx 8.5 to 14.75")</li> </ul>	


<p>3PTY-MOB-030004</p> <p>NOTE: Products sold that do not bear the Zebra brand name are serviced and supported exclusively by their manufacturers in accordance with terms and conditions packaged with the products. Zebra's Limited Warranty does not apply to products that are not Zebra branded, even if packaged or sold with Zebra products. Please contact the manufacturer directly for technical support and customer service. See PMB 11136 for more info.</p>		<p>Mobilis Universal Wrist Mount/Arm Band</p>	<ul style="list-style-type: none"> <li>▶ Universal: fit all handheld devices from 5" to 7"</li> <li>▶ Includes 360° rotating holder to use device vertically or horizontally.</li> </ul>	
<p>SG-WT4027050-01R</p>		<p>Arm Sleeve (pack of 5)</p>	<ul style="list-style-type: none"> <li>▶ Worn under wrist mount strap if worker is in short-sleeved shirt and wants: <ul style="list-style-type: none"> <li>- Extra sweat wicking/ personal layer</li> <li>- Extra comfort</li> <li>- Extra slip-resistance</li> </ul> </li> <li>▶ Material will not snag</li> <li>▶ One size fits all</li> <li>▶ Washable in mild detergent. Should be air dried.</li> <li>▶ Pack of 5 Arm Sleeves</li> </ul>	
<p>SG-TC5A7A-HDSTP-01 (single strap)</p> <p>SG-TC5A7AHDSTP-03 (pack of 3)</p>		<p>Hand Strap</p>	<ul style="list-style-type: none"> <li>▶ Allows device to be easily held in palm of hand.</li> <li>▶ Can be attached to device, even with rugged boot installed.</li> <li>▶ Includes loop for holding optional stylus.</li> <li>▶ Hand strap supports wireless charging feature (device dependent).</li> </ul>	
<p>50-12500-066</p>		<p>Wrist Strap for Trigger Handle</p>	<ul style="list-style-type: none"> <li>▶ Attaches to bottom of Trigger Handle (TRG-TC5AB-ELEC-01, TRG-TC5A-ELEC-01)</li> </ul>	

## Vehicle Cradles and Holders

### Powered Cradles and Holders (provides device charging and/or communication)

Part Number	Picture	Description	Notes	Required Items
3PTY-RAM-HOL-ZE41-2U (non-locking version)  3PTY-RAM-HOL-ZE41L-2U (locking version)  <small>NOTE: Products sold that do not bear the Zebra brand name are serviced and supported exclusively by their manufacturers in accordance with terms and conditions packaged with the products. Zebra's Limited Warranty does not apply to products that are not Zebra branded, even if packaged or sold with Zebra products. Please contact the manufacturer directly for technical support and customer service. See PMB 11136 for more info.</small>		RAM Pogo Pin Charge-Only Vehicle Cradle	<ul style="list-style-type: none"> <li>▶ Spring-loaded cradle allows easy one handed insertion and removal.</li> <li>▶ Compatible with RAM two-hole AMPS pattern diamond bases that will connect to B and C size ball mounts, allowing for a wide variety of mounting options.</li> <li>▶ Included shims allows cradle to be compatible with devices with and without Rugged Boot/Exoskeleton attached. Also compatible with devices with handstrap attached.</li> <li>▶ Power delivered through two integrated pogo pins via 5.5mm DC barrel connector</li> <li>▶ Includes stylus holder (stylus not included) which is fixed mounted on left side of cradle. Optional Stylus (SG-STYLUS-TCX-MTL-03) will fit into holder.</li> </ul>	<b>For Charging:</b> RAM GDS Modular Charger, see In-Vehicle Power Supplies section below  <b>For Mounting:</b> Windshield Suction Mount (RAM-B-166U) OR Vehicle Cradle RAM mount ball (RAM-B-238U) and additional RAM mount hardware - See mounting bracket options in the <b>Common Mounting Systems</b> Technical Accessory Guide (TAG).
3PTY-RAM-HOL-ZE41C-2U (non-locking version)  3PTY-RAM-HOL-ZE41KL-C-2U (locking version)  <small>NOTE: Products sold that do not bear the Zebra brand name are serviced and supported exclusively by their manufacturers in accordance with terms and conditions packaged with the products. Zebra's Limited Warranty does not apply to products that are not Zebra branded, even if packaged or sold with Zebra products. Please contact the manufacturer directly for technical support and customer service. See PMB 11136 for more info.</small>		RAM USB-C Charge-Only Vehicle Cradle	<ul style="list-style-type: none"> <li>▶ Spring-loaded cradle allows easy one handed insertion and removal.</li> <li>▶ Compatible with RAM two-hole AMPS pattern diamond bases that will connect to B and C size ball mounts, allowing for a wide variety of mounting options.</li> <li>▶ Included shims allows cradle to be compatible with devices with and without Rugged Boot/Exoskeleton attached. Also compatible with devices with handstrap attached.</li> <li>▶ Power and data transferred via USB-C connector</li> <li>▶ Includes stylus holder (stylus not included) which is fixed mounted on left side of cradle. Optional Stylus (SG-STYLUS-TCX-MTL-03) will fit into holder.</li> </ul>	<b>For Charging:</b> RAM GDS Modular Charger, see In-Vehicle Power Supplies section below  <b>For Mounting:</b> Windshield Suction Mount (RAM-B-166U) OR Vehicle Cradle RAM mount ball (RAM-B-238U) and additional RAM mount hardware - See mounting bracket options in the <b>Common Mounting Systems</b> Technical Accessory Guide (TAG).

### Un-Powered Cradles and Holders (passive holders, no charging support)





Part Number	Picture	Description	Notes	Required Items
3PTY-RAM-HOL-ZE41-NPU (non-locking version)  3PTY-RAM-HOL-ZE41KL-NPU (locking version)  <small>NOTE: Products sold that do not bear the Zebra brand name are serviced and supported exclusively by their manufacturers in accordance with terms and conditions packaged with the products. Zebra's Limited Warranty does not apply to products that are not Zebra branded, even if packaged or sold with Zebra products. Please contact the manufacturer directly for technical support and customer service. See PMB 11136 for more info.</small>		RAM Vehicle Holder	<ul style="list-style-type: none"> <li>▶ Spring-loaded cradle for TC501/701 allows easy one handed insertion and removal.</li> <li>▶ Compatible with RAM two-hole AMPS pattern diamond bases that will connect to B and C size ball mounts, allowing for a wide variety of mounting options.</li> <li>▶ Included shims allows cradle to be compatible with devices with and without Rugged Boot/Exoskeleton attached. Also compatible with devices with handstrap attached.</li> <li>▶ Includes stylus holder (stylus not included) which is fixed mounted on left side of cradle. Optional Stylus (SG-STYLUS-TCX-MTL-03) will fit into holder.</li> <li>▶ Holder is compatible with RAM Qi2 Wireless Charger sold separately (RAM-GDS-CHARGE-W2M)</li> </ul>	<b>For Mounting</b> ▶ see RAM website for options

Vehicle Mounting Hardware

Refer to the Common Mounting Systems Technical Accessory Guide (TAG) for mounting options



Misc

Part Number	Picture	Description	Notes	Required Items
SG-STYLUS-TCX-MTL-03 (pack of 3)		Fiber Tipped Stylus	<ul style="list-style-type: none"> <li>▶ Black Passive Stylus with Zebra logo</li> <li>▶ 5" length</li> <li>▶ Heavy duty - made from stainless steel and brass. No plastic parts - real pen feel.</li> <li>▶ Can be used in rain.</li> <li>▶ Micro-Knit Hybrid Mesh Fiber Tip provides silent, smooth gliding use.</li> <li>▶ Big improvement over rubber tipped or plastic tipped stylus.</li> <li>▶ Compatible with all capacitive touch screen devices.</li> <li>▶ Can be tethered to device using SG-TC5NGTC7NG-TETHER-03.</li> </ul>	
3PTY-MOB-001054  NOTE: Products sold that do not bear the Zebra brand name are serviced and supported exclusively by their manufacturers in accordance with terms and conditions packaged with the products. Zebra's Limited Warranty does not apply to products that are not Zebra branded, even if packaged or sold with Zebra products. Please contact the manufacturer directly for technical support and customer service. See PMB 11135 for more info.		Mobilis Capacitive Stylus with Coiled Tether Cord (pack of 10)	<ul style="list-style-type: none"> <li>▶ Black Passive Stylus with Mobilis logo</li> <li>▶ Compatible with all capacitive touch screen devices.</li> </ul>	
SG-TC5NGTC7NG-TETHER-03 (pack of 3)		Tether for Stylus	<ul style="list-style-type: none"> <li>▶ String type tether prevents loss of stylus</li> <li>▶ NOTE: Other Zebra coiled tethers are not recommended for use with TC53/TC58 as they may interfere with other accessories.</li> <li>▶ NOTE: This tether is recommended when using Fiber Tipped Stylus (SG-STYLUS-TCX-MTL-03). Other tethers may not fit easily through the tether loop hole on the stylus.</li> </ul>	
SG-TC5A7A-SCRNP-01 (single)  SGTC5A7A-SCRNP-03 (pack of 3)		Screen Protectors	<ul style="list-style-type: none"> <li>▶ Tempered glass</li> <li>▶ Includes alcohol wipes, cleaning cloth, and instructions needed for screen protector installation.</li> </ul>	





**Headset/Audio Accessories**





**Wired Headsets and Audio Accessories**  
 NOTE: Wired headsets with 2.5mm or 3.5mm jacks are not supported on TC53e, TC58 or TC58e devices since they do not include a headset jack.  
 Only TC53 units include a headset jack.

Part Number	Picture	Description	Notes	Required Items
HDST-USBC-PTT1-01		PTT Headset (USB-C connector)	<ul style="list-style-type: none"> <li>▶ For Push-To-Talk (PTT) applications.</li> <li>▶ Compatible with Zebra PTT Express and PTT Pro.</li> <li>▶ Connects to USB-C port on device.</li> <li>▶ Rotating earpiece allows for right or left ear configuration.</li> <li>▶ Provides PTT button, volume up/volume down buttons.</li> <li>▶ Cable length is 32 in. (81 cm)</li> <li>▶ mono with microphone</li> <li>▶ includes clip for attaching PTT button to clothing.</li> </ul>	


**Bluetooth Headsets and Audio Accessories**  
 NOTE: Bluetooth headsets with PTT function not supported by Zebra PTT Express application. Check Zebra WFC Central Client app Release Notes to verify compatibility.

Part Number	Picture	Description	Notes	Required Items
See HS2100-HS3100 Accessories Document		HS3100 Rugged Bluetooth Headset for VDP applications	<ul style="list-style-type: none"> <li>▶ HD Voice, also known as Wide Band Audio, brings incredible audio clarity</li> <li>▶ Built to handle the everyday inevitable drops</li> <li>▶ Dustproof, sprayproof and waterproof</li> <li>▶ Ready for the freezer and outdoor subzero temperatures</li> <li>▶ Feather-light for extraordinary comfort</li> <li>▶ Noise cancellation tuned for VDP (voice directed picking) applications.</li> <li>▶ Not designed for the aggressive noise cancellation required for VoIP or voice calls. Headset's send level is not tuned to satisfy VoIP or voice standards and will result with audio being quieter at the far end and delivering more noise.</li> <li>▶ Swap batteries on the fly — without losing the Bluetooth connection</li> <li>▶ Split-second tap-to-pair simplicity using NFC.</li> <li>▶ Detachable swivel boom minimizes costs.</li> <li>▶ Swivelling boom mutes microphone allowing users to prevent voice pick applications from recognizing non-voice pick conversations.</li> <li>▶ User-replaceable pads and windscreens maximize comfort and hygiene</li> <li>▶ 15 hours of battery power</li> </ul>	See HS2100/HS3100 Accessories Document for headset accessories
various Bluetooth models B550-XT B350-XT C400-XT C300-XT  (3rd party) *  <a href="http://www.blueparrott.com">http://www.blueparrott.com</a>		BlueParrott Bluetooth Headsets	<ul style="list-style-type: none"> <li>▶ Various Bluetooth models available with options that include:                             <ul style="list-style-type: none"> <li>- Blocking out 96% of background noise</li> <li>- Over 24 hours of talk time</li> <li>- NFC Tap to Pair capable</li> <li>- Bluetooth wireless range capable up to 300 ft.</li> <li>- Convertible wearing options: over the head, behind the neck.</li> </ul> </li> </ul> See BlueParrott site for model specific options.	







<p>APTT1 or APTT2 (3rd party) *</p> <p><a href="https://www.aina-wireless.com/">https://www.aina-wireless.com/</a></p>		<p>Aina Push-To-Talk (PTT) Bluetooth Voice Responder Remote Speaker/Mic (RSM)</p>	<ul style="list-style-type: none"> <li>▶ Bluetooth speaker-microphone designed to work with different walkie talkie style Push-to-Talk applications, including Zebra PTT Pro (check with Zebra PTT Pro engineering team for current device/OS support).</li> <li>▶ Includes clip for attaching device to clothing for lapel speaker/mic usage.</li> <li>▶ Features several buttons which the application developers can assign to different functions.</li> <li>▶ Users can remotely control functions such as push-to-talk, phone calls, channel switching and emergency alerts.</li> <li>▶ Device is ruggedized, MIL-STD 810G and IP67.</li> <li>▶ Long lasting battery designed for 24 hour approx battery life. Can be recharged via micro-USB port.</li> <li>▶ Includes 3.5mm headset jack allowing headphones to be connected for keeping conversations more private.</li> <li>▶ Can be easily paired to mobile computer using NFC tap-to-pair.</li> </ul>	
<p>H3-B-1 (3rd party) *</p> <p><a href="https://www.dellking.com">https://www.dellking.com</a></p>		<p>Wandfu H3 Push-To-Talk (PTT) Bluetooth Remote Speaker/Mic (RSM)</p>	<ul style="list-style-type: none"> <li>▶ Bluetooth speaker-microphone designed to work with different walkie talkie style Push-to-Talk applications, including Zebra PTT Pro (check with Zebra PTT Pro engineering team for current device/OS support).</li> <li>▶ Includes clip for attaching device to clothing for lapel speaker/mic usage.</li> <li>▶ Includes 3.5mm headset jack allowing headphones to be connected for keeping conversations more private.</li> </ul>	
<p>BTR-155 (3rd party) *</p> <p><a href="https://www.savoxaccessories.com">https://www.savoxaccessories.com</a></p>		<p>Savox BTR-155 Bluetooth Remote Speaker/Mic (RSM)</p>	<ul style="list-style-type: none"> <li>▶ Bluetooth speaker-microphone designed to work with different walkie talkie style Push-to-Talk applications, including Zebra PTT Pro (check with Zebra PTT Pro engineering team for current device/OS support).</li> <li>▶ Includes clip for attaching device to clothing for lapel speaker/mic usage.</li> <li>▶ Rugged wireless speaker microphone, IP55.</li> <li>▶ Allows cable-free movement</li> <li>▶ Familiar speaker microphone functions; PTT and volume buttons</li> <li>▶ Includes 2.5mm headset jack allowing headphones to be connected for keeping conversations more private.</li> <li>▶ LED status indication</li> <li>▶ High speaker volume</li> <li>▶ Includes: <ul style="list-style-type: none"> <li>- Savox RSM</li> <li>- Modular Wired earpiece</li> <li>- Wall Charger</li> <li>- USB Cable</li> <li>- Quick Start Guide</li> <li>- Carrying Strap</li> </ul> </li> </ul>	
<p>BTH-101 (3rd party) *</p> <p><a href="https://www.savoxaccessories.com">https://www.savoxaccessories.com</a></p>		<p>Savox Push-To-Talk (PTT) Bluetooth Headset</p>	<ul style="list-style-type: none"> <li>▶ Bluetooth headset designed to work with different walkie talkie style Push-to-Talk applications, including Zebra PTT Pro (check with Zebra PTT Pro engineering team for current device/OS support).</li> <li>▶ Also operates as standard Bluetooth headset for taking phone calls.</li> <li>▶ Device is lightweight and ruggedized, IP55.</li> </ul>	

<p>various (3rd party) *</p> <p><a href="http://stonemountainfd.com">http://stonemountainfd.com</a></p>		<p>Stone Mountain BluSkye Bluetooth Remote Speaker Mic (RSM)</p>	<ul style="list-style-type: none"> <li>▶ Bluetooth speaker-microphone designed to work with different walkie talkie style Push-to-Talk applications, including Zebra PTT Pro (check with Zebra PTT Pro engineering team for current device/OS support).</li> <li>▶ Device is ruggedized, MIL-STD 810G and IP68.</li> </ul>	
<p><b>Power Cords/Power Supplies</b></p>				
<p><b>AC Cords and Power Supplies</b></p>				
Part Number	Picture	Description	Notes	Required Items
<p>PWR-BGA12V150W1WW</p>		<p>Power Supply with integrated DC Cord</p>	<ul style="list-style-type: none"> <li>▶ Used to power 5 and 10-slot next-generation ShareCradle bases</li> <li>▶ 100-240 VAC, 12VDC, 12.5A</li> <li>▶ Level VI Efficiency rated</li> <li>▶ 1.2 meter (~4 ft) integrated DC cord</li> <li>▶ NOTE: The older 50W (BGA-12V50W0WW) does not adequately power redesigned ShareCradles</li> </ul>	<ul style="list-style-type: none"> <li>▶ AC Line Cord (23844-00-00R or country specific version)</li> </ul>
<p>23844-00-00R</p>		<p>AC Line Cord, Grounded 3-Prong</p>	<ul style="list-style-type: none"> <li>▶ Used to power Cradles</li> <li>▶ 7.5 feet cord length</li> <li>▶ This AC Line Cord is for use in North America. See the <b>AC Line Cords by Country TAG</b> for comparable line cords to use in other countries.</li> </ul>	
<p>PWR-WUA5V45W1US (US plug style) PWR-WUA5V45W1GB (UK plug style) PWR-WUA5V45W1EU (EU plug style) PWR-WUA5V45W1AU (Australia plug style) PWR-WUA5V45W1CN (China plug style) PWR-WUA5V45W1IN (India plug style) PWR-WUA5V45W1KR (Korea plug style) PWR-WUA5V45W1BR (Brazil plug style) PWR-WUA5V45W1AR (Argentina/Chile/Mexico plug styles)</p>		<p>USB-C Power Supply</p>	<ul style="list-style-type: none"> <li>▶ Provides up to 45W power for faster charging</li> <li>▶ 100-240 VAC</li> </ul>	

**In-Vehicle Power Supplies**

Part Number	Picture	Description	Notes	Required Items
various SKUs (3rd party) *  <a href="https://www.rammount.com">https://www.rammount.com</a>		RAM GDS Modular Chargers	<ul style="list-style-type: none"> <li>▶ Used to power RAM Vehicle Cradles</li> <li>▶ Charger versions includes:                             <ul style="list-style-type: none"> <li>- USB Type-C male connection to 5.5mm DC connector adapter cable</li> <li>- Hard wired power adapter, USB Type-C female connector; 10-30V or 30V-64V input range, 5V output</li> <li>- NOTE: USB Type-A version must be used with Pogo Pin cradles</li> </ul> </li> <li>▶ When upgrading devices, avoid rewiring by unplugging power connector and attaching new charger components</li> </ul>	

**Batteries**

Part Number	Picture	Description	Notes	Required Items
BTRY-TC5A7A-SC-01 (single)		Spare 1X Standard Capacity Battery with PowerPrecision Plus (5000 mAh) 	<ul style="list-style-type: none"> <li>▶ Designed, manufactured &amp; tested to meet rigorous controls &amp; standards</li> <li>▶ Premium-grade cells with higher capacity &amp; longer life cycle</li> <li>▶ Designed to help prevent overcharging &amp; electrical shock</li> <li>▶ Strong &amp; robust housing for optimal performance &amp; durability</li> <li>▶ Information available:                             <ul style="list-style-type: none"> <li>- Advanced state of Charge (shows the remaining battery power based on two factors: present charge and present real-time usage patterns of the device.</li> <li>- Advanced State of Health (highly accurate end-of-life prediction)</li> <li>- Dynamic usage patterns are constantly calculated, factoring in criteria such as the applications that are in use and scanning frequency).</li> </ul> </li> </ul>	
BTRY-TC5A7A-EC-01 (single)		Spare Extended Capacity Battery with PowerPrecision Plus (7240 mAh) 	<ul style="list-style-type: none"> <li>▶ Designed, manufactured &amp; tested to meet rigorous controls &amp; standards</li> <li>▶ Premium-grade cells with higher capacity &amp; longer life cycle</li> <li>▶ Designed to help prevent overcharging &amp; electrical shock</li> <li>▶ Strong &amp; robust housing for optimal performance &amp; durability</li> <li>▶ Information available:                             <ul style="list-style-type: none"> <li>- Advanced state of Charge (shows the remaining battery power based on two factors: present charge and present real-time usage patterns of the device.</li> <li>- Advanced State of Health (highly accurate end-of-life prediction)</li> <li>- Dynamic usage patterns are constantly calculated, factoring in criteria such as the applications that are in use and scanning frequency).</li> </ul> </li> </ul>	
BTRY-TC5A7A-WC-01 (single)		Spare 1X Standard Capacity Battery with PowerPrecision Plus (5000 mAh) and <b>Wireless Charging</b> 	<ul style="list-style-type: none"> <li>▶ Designed, manufactured &amp; tested to meet rigorous controls &amp; standards</li> <li>▶ Premium-grade cells with higher capacity &amp; longer life cycle</li> <li>▶ Designed to help prevent overcharging &amp; electrical shock</li> <li>▶ Strong &amp; robust housing for optimal performance &amp; durability</li> <li>▶ Information available:                             <ul style="list-style-type: none"> <li>- Advanced state of Charge (shows the remaining battery power based on two factors: present charge and present real-time usage patterns of the device.</li> <li>- Advanced State of Health (highly accurate end-of-life prediction)</li> <li>- Dynamic usage patterns are constantly calculated, factoring in criteria such as the applications that are in use and scanning frequency).</li> </ul> </li> <li>▶ Includes support for wireless charging</li> </ul>	