

Real Bosch!

Woodworking tools with a system



Range for 2011/2012

Professional blue woodworking tools with a system:
For trade and industry.



BOSCH
Invented for life

Woodworking tools with a system:

For trade and industry.



* For all professional blue power tools when registered within four weeks of purchase at www.bosch-professional.com/warranty

Robert Bosch Ltd (Blue Power Tools)

PO Box 98

Uxbridge

Middlesex

UB9 5HJ

Tel. 0844 736 0107

(4 pence per minute from a BT landline, call charges from other networks will vary and mobiles may be significantly more)

www.bosch-professional.co.uk



BOSCH
Invented for life

Precision with a system – Professional power tools for woodworking.

For 125 years, the name “Bosch” has stood for innovative technology and for masterful tools and accessories. Engineers in four European Bosch woodworking competence centres always consider the needs of professionals in the woodworking trade when developing our professional blue products.

This results in a fully harmonised range comprising tools and accessories that are designed to suit each other and be combined with each other perfectly.

We therefore offer not only leading machines in terms of technical features, we also offer complete solutions for woodworking.





Saws	4
▶ Jigsaws	6
▶ Hand-held circular saws	10
▶ Plunge circular saw	12
▶ Sabre saws	14
▶ Multicutters	16
▶ Overview of saw blades	18
Benchtop saws	20
▶ Gliding mitre saw	22
▶ Mitre saw	23
▶ Combination saw	23
▶ Table saws	26
Routers, planers, sanders	28
▶ Routers	30
▶ Planers	34
▶ Orbital sanders	35
▶ Random orbit sanders	36
▶ Overview of abrasives	40
Pneumatic nailers	42
▶ Framing nailers	44
▶ Finishing nailers	45
▶ Brad nailer	46
▶ Stapler	46
▶ Coil nailer	47
Cordless screwdrivers, cordless drill/drivers and drywall screwdrivers	48
▶ Cordless screwdrivers	50
▶ Cordless drill/drivers	51
▶ Drywall screwdrivers	52
Mobile working	54
▶ L-BOXX	54
▶ Stands for benchtop saws	55





Professional saws from Bosch – the highest standard in power and precision.

Cutting filigree mouldings to size, trimming resilient worktops, cutting boards to length, mounting windproof roof panels, installing load-bearing beams – these are just some of the challenges that you master on a daily basis. And with the help of the precise and reliable professional saws from Bosch, you will achieve unparalleled quality.

-
- ▶ Jigsaws P.6
 - ▶ Hand-held circular saws P.10
 - ▶ Plunge circular saw P.12
 - ▶ Sabre saws P.14
 - ▶ Multicutters P.16
 - ▶ Overview of saw blades P.18

Power and precision from the inventor of the jigsaw.

More innovation, more precision, more flexibility, more power, longer lifetime.
You shouldn't expect anything less.



The golden double roller guarantees maximum precision.

The new GST 140 CE and BCE Professional jigsaws offer a new standard for precision work. The patented double roller aligns with the actual position of the saw blade to enable optimum, high-precision guidance of the saw blade. The saw blade is also prevented from bending or wobbling – for perfect work results.

NEW! GST 140 CE and BCE Professional jigsaws

The new standard in precision

- ▶ High-precision saw blade guidance due to patented double roller reduces saw blade bending – for excellent cut precision
- ▶ Tool-free, secure-fitting saw blade changing system (SDS) prevents the saw blade from wobbling to ensure maximum surface quality
- ▶ Compact, lightweight design with small grip circumference enables optimum control when sawing



	NEW! GST 140 CE Professional	NEW! GST 140 BCE Professional
Rated power input (W)	720	720
Cutting depth in wood (mm)	140	140
Cutting depth in aluminium (mm)	20	20
Cutting depth in unalloyed steel (mm)	10	10
Part number with L-BOXX 110V	–	0 601 515 060
Part number with L-BOXX 240V	0 601 514 070	0 601 515 070
SSP Ex Vat with L-BOXX	£206.00	£206.00




GST 150 CE and BCE Professional jigsaws

The most powerful tools in their price class

- ▶ High power reserves, even in hard and thick beams, due to powerful and overload-capable 780-watt motor
- ▶ Extremely robust and bend-resistant base plate for the toughest jobs
- ▶ High cutting precision due to new saw blade clamping system

Bend resistance of the base plate in comparison to other jigsaws



Bend-resistant base plate for the toughest jobs.

The base plate of the GST 150 Professional is extremely robust and bend-resistant. It is considerably sturdier than those on comparable tools. The base plate does not bend until the force of over 130 kg is applied to it.

	GST 150 CE Professional	GST 150 BCE Professional	NEW! GST 90 BE Professional
Rated power input (W)	780	780	650
Cutting depth in wood (mm)	150	150	90
Cutting depth in aluminium (mm)	20	20	20
Cutting depth in unalloyed steel (mm)	10	10	10
Part number 110V	0 601 512 060	0 601 513 060	0 601 58F 060
Part number 240V	0 601 512 070	0 601 513 070	0 601 58F 070
SSP Ex Vat	£133.00	£133.00	£113.00

The Bosch system for professional jigsaws.

The optimum solution for woodworking tasks is systematic: cleverly coordinated tools and matching consumable and system accessories. Always one idea ahead and perfectly combinable.

Bosch is the inventor of the jigsaw, and the reinventor, because since building the GEB 1 more than 60 years ago, we have continually enhanced the principle. Today you have the choice between different models that are designed to perfectly suit all application ranges and that have one thing above all in common with the original jigsaw: they truly enrich your everyday work.

For example, the **new GST 140 CE and BCE Professional jigsaws** set an impressive new standard for precise work: the patented double roller reduces saw blade bending and straying to ensure excellent cut precision.

“Extra-Clean for Wood” saw blades – a Bosch innovation – ensure tear-free cut edges and impressive cut quality.

The Bosch circle cutter/guide rail adapter is the perfect addition to all jigsaws. You can use it both to cut circular holes and – in combination with an FSN Professional guide rail – to make clean straight cuts with absolute precision.

A powerful and flexible dust extraction system guarantees clean working. The hose and adapter are rotatable and can be fitted to the tool in a way that does not restrict the work area. The entire device is also very quick and easy to fit.

To also ensure that you always have everything under control when you are on the move, we offer you the **L-BOXX**, which is an intelligent solution for the transport and storage of your tools and accessories. The L-BOXX is available in four sizes, it is made of impact-resistant plastic, has a load-bearing capacity of up to 100 kg, is splash-protected, and it is equipped with Easy Click system and an individually configurable interior.



“We are constantly in contact with various different user groups, in order to meet their requirements. When developing the new ‘Extra-Clean for Wood’ line, we spoke to numerous joiners and incorporated their impressions and their suggestions for improvement. We merged these inputs with our sophisticated manufacturing process to develop a unique saw blade line. In the end, we have launched a product onto the market that sets a new standard with regards to cut quality and tear-free edges.”

Marzell Chanton – plant manager for jigsaw blades, St. Niklaus, Switzerland

The Bosch system for professional jigsaws.



1. Jigsaw blades



2. Circle cutter / guide rail adapter



3. Dust extraction adapter



4. L-BOXX



1. Jigsaw blades	Part number	SSP Ex Vat
Precision for Wood T144DP*	2 608 633 A35	£9.50
Precision for Wood T301BCP*	2 608 633 A37	£13.61
Extra-Clean for Wood T308B*	2 608 663 751	£11.93
Extra-Clean for Wood T308BO*	2 608 663 868	£11.93

*Part numbers and price are each for a set of 5

2. Circle cutter / guide rail adapter	Part number	SSP Ex Vat
Circle cutter / guide rail adapter	2 608 040 292	£11.56

3. Dust extraction adapter	Part number	SSP Ex Vat
Dust extraction adapter for GST 140 Professional	2 605 510 301	£7.65

4. L-BOXX	Part number	SSP Ex Vat
L-BOXX 136	2 608 438 692	£45.43

Powerful and comfortable even in continuous use – the Bosch hand-held circular saw G-models.

Optimised for guide rails, specially developed for the building trade and tough in use: professional Bosch hand-held circular saws. Their robustness, compact dimensions and low weight with high performance set standards in their segment.



NEW! GKS 55 GCE and 85 G Professional hand-held circular saws


The powerhouses – optimised for guide rails

- ▶ Exact interplay with the new Bosch FSN Professional guide rail system and with rails from other suppliers
- ▶ Mitre cuts with the guide rail are possible without an adapter
- ▶ Fast sawing progress due to powerful motors

	NEW! GKS 55 GCE Professional	NEW! GKS 85 G Professional
Rated power input (W)	1350	2200
Cutting depth at 90° (mm)	55	85
Saw blade diameter (mm)	160	235
Weight (kg)	3.9	7.8
Part number with L-BOXX 110V	–	0 601 57A 961
Part number with L-BOXX 240V	0 601 664 971	0 601 57A 971
SSP Ex Vat with L-BOXX	£228.00	£249.00

The fast way to achieve a straight cut.

A good example of system strength and perfect interaction between tool and accessory: the new Bosch hand-held circular saw G-models have been specially optimised for use with guide rails. The guide rail system enables rapid completion of precise, straight cuts. The FSN VEL Professional connecting piece can be used to connect rails of different lengths precisely, sturdily and quickly. The FSN WAN Professional angle guide helps to align the guide rails precisely and at accurate angles on the workpiece.



NEW! FSN 800, FSN 1100, FSN 1600, FSN 2100 and FSN 3100 Professional guide rails

Rail technology for exact guidance

- The rails remain exactly straight, even when using an extended rail, due to the self-aligning connecting piece
- VEL connecting piece for quick and sturdy connection of guide rails
- Anti-splinter guard for clean cut edges and non-slip strips for secure handling

	NEW! FSN 800 Professional	NEW! FSN 1100 Professional	NEW! FSN 1600 Professional	NEW! FSN 2100 Professional	NEW! FSN 3100 Professional	NEW! FSN VEL Professional (connecting piece)
Part number	1 600 Z00 005	1 600 Z00 006	1 600 Z00 00F	1 600 Z00 007	1 600 Z00 008	1 600 Z00 009
SSP Ex Vat	£61.00	£77.00	£93.00	£144.00	£187.00	£51.00

	NEW! FSN WAN Professional (angle guide)	NEW! FSN SZW Professional (G-clamps)	NEW! FSN KK Professional (plastic caps)	NEW! FSN SS Professional (anti-splinter guard)	NEW! FSN HB Professional (non-slip strip)
Part number	1 600 Z00 00A	1 600 Z00 00B	1 600 Z00 00C	1 600 Z00 00D	1 600 Z00 00E
SSP Ex Vat	£100.00	£41.00	£10.00	£19.00	£19.00

Precision and power – the new plunge circular saw for a clean cut.

The Bosch plunge circular saw – the expert for cutting panel materials and wooden materials. The high-quality components of this saw and the optimum coordination with the new Bosch guide rail system ensure excellent cut quality.

NEW! GKT 55 GCE Professional plunge circular saw

Delivers power and precision to give you a clean cut

- Clean, precise cuts due to high-quality machine components, precision saw blade and matching guide rail system
- Comfortable working, especially indoors, due to highly efficient dust extraction and noise-reducing saw blade
- Adjustable speed, powerful 1400-watt motor and Constant Electronic for cutting different materials such as wood, panel materials, aluminium and acrylic glass



	NEW! GKT 55 GCE Professional
Rated power input (W)	1400
Cutting depth at 90° (mm)	57
Saw blade diameter (mm)	165
Weight (kg)	4.7
Part number with L-BOXX 110V	0 601 675 061
Part number with L-BOXX 240V	0 601 675 071
Part number with L-BOXX and FSN 1600 Professional guide rail	0 601 675 061/71 & 1 600 Z00 00F
SSP Ex Vat	£338.00
Price with L-BOXX and guide rail FSN 1600 Professional	£373.00

The Bosch system for the professional plunge circular saw.

Precise work results with the new Bosch plunge circular saw and the matching system accessories.

The **Top Precision Best for Wood saw blades** are optimised for the highest demands. They are laser-cut from premium steel (up to HRC 46) – so they stand for high precision and no blade warping.

Special carbide teeth made of MicroteQ, a carbide powder with microfine grains, minimise wear on the cutting edges – for the best cut quality and extremely long lifetime. **CleanteQ** is a special chrome coating that reduces the adhesion of residues. It therefore protects the blade against corrosion and also keeps it cool.

StabilteQ is a technology that uses polyurethane-filled damping slots to reduce vibration. For you this means increased precision and more comfort. Noise development is also reduced. Laser-cut expansion slots additionally ensure high blade stability and accuracy.

The **FSN guide rail system** is the perfect addition for maximum precision, enabling you to make exact cuts of any length. When your work is done, you can store and transport your saw quickly and safely in the matching **L-BOXX**.


The Bosch system for the professional plunge circular saw.



1. Saw blades



2. Guide rails



3. L-BOXX



Accessories for a clean cut

1. Saw blades	Part number	SSP Ex Vat
Top Precision Best for Wood circular saw blade 165x20x48T	2 608 642 384	£73.41
Top Precision Best for Wood circular saw blade 165x20x20T	2 608 642 385	£51.90
Top Precision Best for Wood circular saw blade 165x20x32T	2 608 642 386	£59.02
Top Precision Best for Multi Material circular saw blade 165x20x56T	2 608 642 387	£111.89
Top Precision Best for Multi Material circular saw blade 165x20x48T	2 608 642 388	£111.89
2. Guide rails	Part number	SSP Ex Vat
FSN 800 Professional (800 mm)	1 600 Z00 005	£61.00
FSN 1100 Professional (1,100 mm)	1 600 Z00 006	£77.00
FSN 1600 Professional (1,600 mm)	1 600 Z00 00F	£93.00
FSN 2100 Professional (2,100 mm)	1 600 Z00 007	£144.00
FSN 3100 Professional (3,100 mm)	1 600 Z00 008	£187.00
3. L-BOXX	Part number	SSP Ex Vat
L-BOXX 374	2 608 438 694	£66.75

Powerful, ergonomic and robust – the new Bosch sabre saws.

Bosch sabre saws impress with their powerful motors and ergonomic design. This enables them to master every task quickly and reliably.

Bosch sabre saw blades for every material.

Brick, metal, iron, aluminium, wood and plastic – Bosch's sabre saw blades make better cuts in every material. The SDS system on Bosch sabre saws makes it possible to change the saw blade in seconds.



NEW! GSA 1100 E Professional sabre saw

Optimum visibility in any work situation

- ▶ Integrated LEDs for a better view of the workpiece
- ▶ Powerful 1100-watt motor for fast sawing progress
- ▶ Metal hook for hanging up the tool during a work break





High performance with anti-vibration system.

The new GSA 1300 PCE Professional offers a powerful 1300 watts – and the lowest vibration in its class. This is made possible by the anti-vibration system, which consists of an anti-vibration handle and mass balance in the tool. For you this means low-fatigue working, even in continuous use.



NEW! GSA 1300 PCE Professional sabre saw

Lowest vibration in its class – and a powerful 1300 watts



- For low-fatigue working: anti-vibration handle and mass balance
- 1300-watt high-performance motor with Constant Electronic for the toughest applications
- Pendulum stroke for fast sawing progress

	NEW! GSA 1100 E Professional	NEW! GSA 1300 PCE Professional
Rated power input (W)	1100	1300
Saw, stroke length (mm)	28	28
No-load stroke rate (spm)	2,700	2,900
Weight (kg)	3.9	4.1
Part number 110V	0 601 64C 860	0 601 64E 260
Part number 240V	0 601 64C 870	0 601 64E 270
SSP Ex Vat	£134.00	£197.00

Unlimited applications – Bosch multicutters. The blue problem solvers.

The name says it all: Bosch multicutters stand for perfect trimming, adjusting and repairing. Comprehensive accessories enable countless possible applications and are fitted in just a few moves.

“Developing new accessories for our oscillating multitools (OMT) is as versatile as the applications themselves. I’m constantly in contact with our product marketing, multicutter engineering, quality control and production, in order to develop a perfectly coordinated system for our professional customers. There’s no better feeling than hearing the customer say that the tool and accessory worked together impeccably.”

Daniel Grolimund, head of OMT accessories development, Solothurn, Switzerland



GOP 10,8 V-Li Professional cordless multicutter

Perfect trimming, adjusting, repairing

- ▶ Wide range of applications such as plunge cuts, flush sawing and sanding due to comprehensive range of accessories
- ▶ Excellent handling due to compact design and weight of only 1.0 kg
- ▶ Up to 20,000 oscillations per minute for the same professional performance as comparable mains-powered tools



















































NEW! GOP 300 SCE Professional multicutter

Accessory changes in no time

- ▶ SDS system for fast, tool-free changing of accessories with maximum convenience
- ▶ Powerful 300-watt motor with Constant Electronic for constant work progress in every application
- ▶ Slim grip circumference for more comfortable working in precision applications and in continuous use


	GOP 10,8 V-Li Professional	GOP 250 CE Professional	NEW! GOP 300 SCE Professional
Battery voltage (V)	10.8	–	–
Battery capacity (Ah Premium)	1.3	–	–
Rated power input (W)	–	250	300
No-load speed (rpm)	5,000 – 20,000	8,000 – 20,000	8,000 – 20,000
Weight (kg)	1.0 (including battery)	1.3	1.7
Part number 110V with L-BOXX & 8 accessories	0 601 858 00C (Body Only, w/o charger or batteries. Carton with L-BOXX inlay)	0 601 230 060 (Carton with L-BOXX inlay)	0 601 230 561
Part number 240V with L-BOXX & 8 accessories	0 601 858 077 (2 x 1.3 Ah batteries)	0 601 230 070 (Carton with L-BOXX inlay)	0 601 230 571
Part number 110V with L-BOXX & 48 accessories	0 601 858 078 (2 x 1.3 Ah batteries + 36 accessories)	0 601 230 061	0 601 230 562
Part number 240V with L-BOXX & 48 accessories TBC	–	0 601 230 071	0 601 230 572
SSP Ex Vat	£146.00	£116.00	£197.00
with L-BOXX and 8 accessories	£206.00	£169.00	£228.00
with L-BOXX and 48 accessories	£104.00	–	–
Body Only	£99.00	–	–

Accessories for Bosch multicutters.

				
Tile and bathroom renovation	Flooring work	Trimming and adjustment work	For all work with insulation materials and sealants	Automobile and ship building
 2 608 661 757 HM-RIFF, 70 mm  2 608 661 689 Diamond-RIFF, 85 mm	 2 608 661 633 BIM, 100 mm  2 608 661 636 BIM-TiN, 85 mm	 2 608 661 781 BIM, 65x40 mm  2 608 661 644 BIM, 28x50 mm	 2 608 661 693 BIM, 100 mm  2 608 661 691 HCS, 28x50 mm	 2 608 661 758 BIM-TiN, 85 mm  2 608 661 759 BIM-TiN, 65 mm
 2 608 661 642 HM-RIFF, 85 mm  2 608 661 692 HM-RIFF, 65 mm	 2 608 661 643 HCS, 85 mm  2 608 661 781 BIM, 65x40 mm	 2 608 661 645 BIM, 32x40 mm  2 608 661 637 HCS, 32x40 mm	 2 608 661 647 HCS, 52x38 mm	 2 608 661 760 BIM-TiN, 85 mm  2 608 661 761 BIM-TiN, 65 mm
 2 608 661 648 HM-RIFF, 78 mm  2 608 661 644 BIM, 28x50 mm	 2 608 661 760 BIM-TiN, 85 mm  2 608 661 693 BIM, 100 mm	 2 608 661 638 HCS, 20x30 mm  2 608 661 639 HCS, 10x30 mm		 2 608 661 689 Diamond-RIFF, 85 mm  2 608 661 692 HM-RIFF, 65 mm
 2 608 661 688 BIM, 32x30 mm  2 608 661 640 BIM, 20x20 mm	 2 608 661 647 HCS, 52x38 mm  2 608 661 646 HCS	 2 608 661 688 BIM, 32x30 mm  2 608 661 640 BIM, 20x20 mm		 2 608 607 542 93 mm  2 608 604 494 2 608 604 495
	 2 608 607 540 93 mm	 2 608 661 641 BIM, 10x20 mm  2 608 661 758 BIM-TiN, 85 mm		 2 608 604 496  2 608 613 016
		 2 608 661 759 BIM-TiN, 65 mm  2 608 661 636 BIM-TiN, 85 mm		
 OIS applies to all accessories shown		 2 608 607 541 93 mm  2 608 607 543 93 mm		


Overview – professional saws and matching accessories from Bosch.


The professional range offers the matching accessory for every application – for tear-free curved cuts in wood, for cutting thick wooden beams to length and for fast work progress when cutting metal.

Which power tool?	Your requirement?	Which material?	Our recommendation	Product example
	Tear-free straight cuts	Hardwood	Extra-Clean for Hard Wood	T 308 BF
	Tear-free curved cuts	Hardwood	Extra-Clean for Hard Wood	T 308 BOF
	Highest possible precision	Hardwood	Precision for Wood	T 301 BCP
	Fastest possible work progress	Hardwood	Speed for Hard Wood	T 144 DF
	Tear-free straight cuts	Softwood	Extra-Clean for Wood	T 308 B
	Tear-free curved cuts	Softwood	Extra-Clean for Wood	T 308 BO
	Highest possible precision	Softwood	Precision for Wood	T 301 BCP
	Fastest possible work progress	Softwood	Speed for Wood	T 144 D
	Clean cuts	Synthetics – CORIAN, VARIOCOR	Special for Synthetics	T 301 CHM
	Clean cuts	Synthetics – GRP/EPOXY	Special for Synthetics	T 301 CHM
	Highest possible precision	Synthetics – GRP/EPOXY	Special for Fibre and Plaster	T 141 HM
	Fastest possible work progress	Synthetics – GRP/EPOXY	Special for Fibre and Plaster	T 141 HM
	Highest possible precision	Composite – Countertop	Precision for Wood	T 301 BCP
	Highest possible precision	Composite – Sandwich material	Flexible for Metal-Sandwich	T 718 BF
	Highest possible precision	Composite – Insulation materials	Special for Soft-Material	T 313 AW
	Fastest possible work progress	Metal	Speed for Metal	T 121 AF
	Fastest possible work progress	Aluminium	Special for Alu	T 127 D
	Fastest possible work progress	Stainless steel	Special for Inox	T 118 EHM
	Fastest possible work progress	Multi Material	Progressor for Wood and Metal	T 345 XF





Which power tool?	Your requirement?	Which material?	Our recommendation	Product example
Sabre saws 	Smallest possible cutting depth	Metal	Flexible for Metal	S 522 BF
	Sawing flush to the wall	Metal	Flexible for Metal	S 1122 BF
	Smooth, low-vibration sawing	Metal	Heavy for Metal	S 1125 VF
	Demolition	Metal	Heavy for Metal	S 1120 CF
	Fastest possible work progress	Metal	Progressor for Metal	S 123 XF
	Highest possible precision	Metal	Endurance for HeavyMetal	S 1136 BEF
	Smallest possible cutting depth	Wood with metal	Flexible for Wood and Metal	S 511 DF
	Sawing flush to the wall	Wood with metal	Flexible for Wood and Metal	S 1122 HF
	Smooth, low-vibration sawing	Wood with metal	Flexible for Wood and Metal	S 1122 VF
	Demolition	Wood with metal	Heavy for Wood and Metal	S 1110 VF
	Fastest possible work progress	Wood with metal	Progressor for Wood and Metal	S 3456 XF
	Longest possible lifetime	Wood with metal	Heavy for Wood and Metal	S 1110 VF
	Cutting firewood	Wood	Top for Wood	S 1542 K
	Clean cuts	Wood	Top for Wood	S 644 D
	Smooth, low-vibration sawing	Wood	Progressor for Wood	S 2345 X

Plunge circular saw 	High precision	Wood and wooden materials	Top Precision Best for Wood 165x20x48T	2 608 642 384
	Fast rip and cross cuts in wood	Wood and wooden materials	Top Precision Best for Wood 165x20x32T	2 608 642 386
	Fast rip cuts in wood	Wood and wooden materials	Top Precision Best for Wood 165x20x20T	2 608 642 385
	Cutting aluminium	Multi Material	Top Precision Best for Multi Material 165x20x56T	2 608 642 387
	Cutting laminate, plastics, acrylic	Multi Material	Top Precision Best for Multi Material 165x20x48T	2 608 642 388

Hand-held circular saws 	Good quality in standard applications in wood	Wood	Optiline Wood 160x20x24T	2 608 641 171
			Optiline Wood 190x30x24T	2 608 641 185
			Optiline Wood 230x30x36T	2 608 640 628
	Fast rip and cross cuts	Wood	Speedline Wood 160x20x18T	2 608 640 787
			Speedline Wood 190x30x24T	2 608 640 801
			Speedline Wood 235x30x30T	2 608 640 807
	Applications in various materials	Multi Material	Multi Material 160x20x42T	2 608 640 503
			Multi Material 190x30x54T	2 608 640 509
	Coarse cuts through construction site timber	Wood	Construct Wood 235x30x16T	2 608 640 636



A close-up photograph of a Bosch benchtop saw, showing its grey metal frame, red adjustment knobs, and a portion of the blade. The saw is mounted on a wooden workbench in a workshop environment. The background is slightly blurred, showing other workshop elements.

Bosch benchtop saws – master every requirement.

Bosch benchtop saws combine high power with exceptional precision. With their high-torque motors and high-quality features – e.g. integrated laser – they enable fast, precise work in every type of wood. This is why they are used wherever powerful, accurate and high-quality work is required.

-
- ▶ Gliding mitre saw P. 22
 - ▶ Mitre saw P. 23
 - ▶ Combination saw P. 23
 - ▶ Table saws P. 26

Maximum efficiency in every job – powerful professional benchtop saws.

Sawing panels, planks and boards, and cutting bevels and angles is no problem for the Bosch benchtop saw range. They work quickly and extremely precisely thanks to their powerful motors and integrated laser guide (on the GCM 12 GDL Professional and GTM 12 Professional).



A WORLD FIRST! GCM 12 GDL Professional double bevel gliding mitre saw

Sawing like never before: extremely smooth with lasting precision

- ▶ Lasting precision due to innovative, maintenance-free and extremely robust guide arm
- ▶ Frictionless slide mechanism ensures very easy sawing without loss of power
- ▶ Accurate cuts and maximum cut quality due to integrated double line laser and “Top Precision Best for Wood” saw blade

	A WORLD FIRST! GCM 12 GDL Professional
Rated power input (W)	2000
Saw blade diameter (mm)	305
Mitre setting (°L/°R)	52/60
Bevel setting (°L/°R)	47
Max. cutting capacity at 0° (mm)	104x341 (110 mm with spacer)
Weight (kg)	32.1
Part number 110V	0 601 B23 660
Part number 240V	0 601 B23 670
SSP Ex Vat	£799.00



NEW! GCM 10 J Professional mitre saw

Powerful and compact

- ▶ Powerful 2000-watt motor – for precise work in a wide variety of materials
- ▶ Very compact design, low weight (14.5 kg) and integrated handle for easy transport
- ▶ Extremely long lifetime due to robust construction and dust-resistant motor technology



GTM 12 Professional combination saw

Multi-talented tool with 100% precision

- ▶ Table saw and mitre saw in one tool
- ▶ Precise work with integrated laser
- ▶ Powerful 1800-watt motor for fast work progress up to 95 mm cutting depth in hardwood*

*in the mitre saw function



GCM 12 GDL Professional: extremely smooth due to innovative guide arm.

The innovative slide mechanism, which is operated by a robust die-cast aluminium glide arm, ensures extremely smooth movement and lasting precision. The glide arm is ball bearing mounted, absolutely maintenance-free and ensures smooth sawing comfort from the first to the last minute the tool is used.

	NEW! GCM 10 J Professional	GTM 12 Professional
Rated power input (W)	2000	1800
Saw blade diameter (mm)	254	305
Mitre setting (°L/°R)	47 / 47	48 / 48
Bevel setting (°L/°R)	47 / 2	47 / 2
Max. cutting capacity at 0° (mm)	89 x 130	95 x 151 (in mitre saw function)
Weight (kg)	14.5	22.0
Part number 110V	0 601 B20 260	0 601 B15 060
Part number 240V	0 601 B20 270	0 601 B15 070
SSP Ex Vat	£279.00	£490.00

The Bosch system for professional blue benchtop saws.

You can complete any task with the right blade. Optimum dust removal perfects the professional workplace.

Excellent cut quality and a clean workplace: it especially depends on the saw blades. And on reliable dust extraction.

Top Precision saw blades – Top results in every cut and blade longevity are a must for every saw blade. The quality of the carbide used to produce the teeth of a saw blade is an essential success factor for a very high-quality product. Bosch is the only manufacturer to produce its own carbide powder. Using precise mixture of cobalt (for its extreme robustness), titanium (for its anticorrosive properties) and tungsten (for its hardness), we create different blends specifically optimised for the applications. This enables maximum lifetime and optimum cut quality to be achieved.

Top Precision Best for Wood: Perfect, clean cuts in all wooden materials. Ideal for table saws, mitre saws and sliding mitre saws. Particularly smooth running, considerably less noise, noticeably reduced vibration – and extremely long life.

Best for Laminate: For the perfect cut in all laminate floorings, with or without sound-dampening layer.

Best for Multi Material: A most versatile blade thanks to a particularly thin kerf for easier sawing and less wastage. A special tooth geometry with negative hook angle ensures perfect cuts.

The GAS 50 M Professional wood extractor ensures ideal dust removal at the workplace around your benchtop saw. The Plus-Clean electromagnetic filter cleaning system guarantees permanent suction power. Its remote automatic switching also provides you with additional convenience.

GTA 3800 Professional, the flexible saw stand for long workpieces, enables precise work with long workpieces and fits all Bosch mitre saws and combination saws.



The Bosch system for professional blue benchtop saws.



1. Saw blades



2. GAS 50 M Professional wood extractor



3. GTA 3800 Professional saw stand



Accessories for excellent cut quality

1. Saw blades	Part number	SSP Ex Vat
Expert for Wood (mitre saws)		
216 mm, 30 mm, 2.3/1.8 mm, 48 teeth	2 608 642 101	£N/A
254 mm, 30 mm, 2.3/1.8 mm, 60 teeth	2 608 642 102	£N/A
305 mm, 30 mm, 2.3/1.8 mm, 72 teeth	2 608 642 103	£97.23
Top Precision Best for Wood (table saws)		
250 mm, 30 mm, 3.2/2.2 mm, 60 teeth	2 608 642 112	£N/A
Best for Laminate (mitre saws)		
216 mm, 30 mm, 2.5/1.8 mm, 60 teeth	2 608 642 133	£112.55
254 mm, 30 mm, 2.5/1.8 mm, 84 teeth	2 608 642 135	£138.22
305 mm, 30 mm, 2.5/1.8 mm, 96 teeth	2 608 642 137	£164.89
Expert for Multi Material		
216 mm, 30 mm, 2.3/1.8 mm, 64 teeth	2 608 642 097	£N/A
254 mm, 30 mm, 2.3/1.8 mm, 80 teeth	2 608 642 098	£N/A
305 mm, 30 mm, 2.3/1.8 mm, 96 teeth	2 608 642 099	£135.17
2. Wood extractor*	Part number	SSP Ex Vat
GAS 50 M Professional	0 601 988 103	£N/A
*GAS 50 M is not available in the UK		
3. Saw stand	Part number	SSP Ex Vat
GTA 3800 Professional	0 601 B24 000	£199.00

Sawing large work materials isn't even a small problem.

The table widener and extension (on the right and on the back) enable stable sawing of even large workpieces with the GTS 10 XC Professional. Large support surfaces ensure safe and comfortable sawing. The 2100-watt powerful motor is additionally protected by an electronics package and has the required power reserves to also saw boards up to 79 mm thick.



NEW! GTS 10 XC Professional table saw

The versatile tool with a powerful 2100 watts

- Powerful 2100-watt motor with motor brake, starting current limitation, overload protection and Constant Electronic for the toughest applications
- Versatile due to integrated slide carriage as well as table widener and table extension
- Tool-free lowering of the riving knife



	NEW! GTS 10 XC Professional
Rated power input (W)	2100
Saw blade diameter (mm)	254
Table size (mm)	584 x 759
Bevel setting (°L / °R)	47 / 1
Max. cutting capacity at 0° (mm)	635 (right) / 250 (left)
Weight (kg)	35
Part number 110V	0 601 B30 460
Part number 240V	0 601 B30 470
SSP Ex Vat	£669.00

	GTA 6000 Professional saw stand suitable for GTS 10 XC Professional
Table size (mm)	750 x 670
Weight with/without accessories (kg)	–
Weight (kg)	12.5
Length of saw stand with extension (mm)	–
Height of saw stand (mm)	602
Part number	0 601 B24 100
SSP Ex Vat	£119.00

NEW! GTS 10 J Professional table saw

Extremely compact and powerful

- ▶ Powerful 1800-watt motor with starting current limitation and overload protection for fast work progress
- ▶ Compact design and many grip areas for optimum transport
- ▶ Tool-free lowering of the riving knife


**Fast transport – fast cutting.**

Due to its compact frame design and low weight, the GTS 10 J Professional is extremely handy and easy to transport. All necessary accessories, e.g. the protective guard and the parallel guide, are securely stored on the machine. The GTS 10 J Professional is therefore the ideal tool for quick cuts on the jobsite.

	NEW! GTS 10 J Professional
Rated power input (W)	1800
Saw blade diameter (mm)	254
Table size (mm)	642x572
Bevel setting (°L/°R)	47 / 2
Max. cutting capacity at 0° (mm)	460 (right) / 210 (left)
Weight (kg)	26
Part number 110V	0 601 B30 560
Part number 240V	0 601 B30 570
SSP Ex Vat	£499.00

	GTA 600 Professional saw stand suitable for GTS 10 J Professional
Table size (mm)	450x520
Weight with/without accessories (kg)	–
Weight (kg)	6.3
Length of saw stand with extension (mm)	–
Height of saw stand (mm)	602
Part number	0 601 B22 001
SSP Ex Vat	£99.00





Routers, planers and sanders – for visibly good results.

There is no room for tolerance when working on surfaces. Maximum precision is required when routing. Material removal accurate to the millimetre when planing. Perfect surfaces when sanding. When it comes to this kind of work, Bosch power tools again guarantee first-class results without compromises.

-
- ▶ Routers P.30
 - ▶ Planers P.34
 - ▶ Orbital sanders P.35
 - ▶ Random orbit sanders P.36
 - ▶ Overview of abrasives P.40

Bosch routers – precise in all application ranges.

Whether you are routing profiles on solid wood or panel materials, rounding off edges, or flush-routing veneers and laminates – the unique Bosch routing depth fine adjustment guarantees the best results.



GKF 600 Professional palm router

The handy specialist for edges

- ▶ Very compact design and ergonomic grip area allow for one-handed guidance, especially for working on edges
- ▶ Continuously variable routing depth adjustment using the setting wheel and secure fitting of the motor enable exact setting and repeatable precision
- ▶ Comprehensive accessories in a sturdy transport system for the many requirements of working on edges



NEW! GMF 1600 CE Professional multifunction router

The powerful plunge and fixed-base router with Trigger Control

- ▶ Patented switch system in the handle (Trigger Control) for optimum control from the beginning
- ▶ Powerful 1600-watt motor with Constant Electronic and Softstart for material-specific working
- ▶ SDS quick-change system: for secure fitting of the separate motor block, either in the plunge or fixed-base unit

	GKF 600 Professional	GOF 900 CE Professional	NEW! GMF 1600 CE Professional	NEW! GOF 1600 CE Professional
Rated power input (W)	600	900	1600	1600
No-load speed (rpm)	33,000	12,000 – 24,000	10,000 – 25,000	10,000 – 25,000
Toolholder (mm)	6.0–8.0	6.0–8.0	8.0–12.7	8.0–12.7
Max. router cage stroke (mm)	–	50	73	73
Part number 110V	0 601 60A 160	0 601 614 641	–	–
Part number 240V	0 601 60A 170	0 601 614 642	0 601 624 072	0 601 624 070
Part number with L-BOXX 110V	0 601 619 742	–	0 601 624 062	0 601 624 060
Part number with L-BOXX 240V	–	–	0 601 624 072	0 601 624 070
SSP Ex Vat	£152.00	£227.00	£TBC	£TBC
SSP Ex Vat with L-BOXX	–	–	£TBC	£TBC



Complete control when working on edges.

The slim grip circumference of the GKF 600 Professional palm router and the low centre of gravity of the GMF 1600 CE multifunction router's fixed-base unit make both tools perfect to handle and control – especially when working on edges or with templates.



GOF 2000 CE Professional router

The robust precision plunge router

- ▶ Robust 2000-watt motor, which has sufficient power reserves for large routing diameters with its Constant Electronic
- ▶ Lockable setting wheels and clamp levers guarantee repeatable precision up to 1/10 mm accuracy
- ▶ The suspension of the plunge function can be switched off for more convenient working at large routing depths and in bench-mounted use



GFF 22 A Professional biscuit jointer

The precise specialist for wood joints

- ▶ Robust metal angle guides with embossed scales and lock-in points enable precise settings for accurate joints
- ▶ 670 watts provide optimum power for making frame, corner, longitudinal and cross joints
- ▶ Tool-free routing depth adjustment for fast work progress

	GOF 2000 CE Professional
Rated power input (W)	2000
No-load speed (rpm)	8,000–21,000
Toolholder (mm)	8.0–12.7
Max. router cage stroke (mm)	65
Part number 110V	0 601 619 741
Part number 240V	0 601 619 742
SSP Ex Vat	£430.00

	GFF 22 A Professional
Rated power input (W)	670
Max. cutting depth (mm)	22
Blade cutter diameter (mm)	105
Blade cutter diameter, bore (mm)	22
Part number 110V	0 601 620 041
Part number 240V	0 601 620 042
SSP Ex Vat	£280.00

The Bosch system for professional routers.

Our tools have an exceptionally precise system. So whether you are doing constructive trimming work, working with templates, routing grooves or working on edges – Bosch always has precisely the right solution for you.

The **SDS template guides** are designed to suit the Bosch routers perfectly, and they enable exact template routing and tool-free mounting – for efficient working.

The **FSN Professional guide rails and the matching FSN OFA Professional guide rail adapter** form a system for enabling easy alignment and precise routing with fine adjustment. The **parallel guide with fine adjustment** does a perfect job of parallel-guiding all Bosch routers. It is also available with extra-long bars.

The **GAS 50 M Professional** is the ideal special extractor for dust-free working with Bosch hand-held circular saws, jigsaws, routers and sanders. As a dust category M certified wood extractor, it is also suitable for extracting liquids. The Plus-Clean electromagnetic filter cleaning system guarantees permanent suction power.

The **intelligent L-BOXX transport and storage system** ensures safe transport and optimum storage of your router and its accessories. The L-BOXX is fully compatible with the German TÜV-tested in-vehicle equipment system from Sortimo.



	GAS 50 M Professional*
Rated power input (W)	1200
Capacity (l)	50
Weight (kg)	15.8
Max. vacuum pressure (mbar)	225
Filter surface area (cm²)	8,600
Part number	0 601 988 103
SSP Ex Vat	£N/A

*GAS 50 M is not available in the UK

The Bosch system for professional routers.



1. SDS template guides



2. Guide rail and adapter / Parallel guide



3. L-BOXX



4. GAS 50 M Professional wood extractor



1. SDS template guide diameter	Part number	SSP Ex Vat
13 mm	2 609 200 138	£15.45
16 mm	2 609 000 471	£N/A
17 mm	2 609 200 139	£13.46
24 mm	2 609 200 140	£18.27
27 mm	2 609 200 141	£18.27
30 mm	2 609 200 142	£15.91
40 mm	2 609 200 312	£22.96
2. Guide rail and adapter / Parallel guide	Part number	SSP Ex Vat
FSN 1100 Professional	1 600 200 006	£74.00
FSN OFA Professional	1 600 200 00G	£TBC
Parallel guide with fine adjustment	2 607 001 387	£72.28
3. L-BOXX	Part number	SSP Ex Vat
L-BOXX 374	2 608 438 694	£66.75
L-BOXX 136	2 608 438 692	£45.43
4. Wood extractor*	Part number	SSP Ex Vat
GAS 50 M Professional	0 601 988 103	£N/A

*GAS 50 M is not available in the UK

Noticeably the best results – professional planers and sanders.

Working on and finishing surfaces – quickly, comfortably and effectively. To enable you to do this, Bosch planers not only have a powerful drive, they also have the unique Woodrazor system. The Bosch orbital sander impresses with the finest surface finish and its excellent handling.

The 1-blade Woodrazor system for perfect surfaces.

The patented Bosch Woodrazor system has only one planer blade, so you no longer have to go to the trouble of aligning a second blade, and optimum results are guaranteed. The Bosch Woodrazor reversible blades are hard-wearing, ultra-sharp and durable for perfect surfaces without the need for subsequent finishing work.



GHO 26-82 Professional planer

The handy planer with lots of power

- ▶ Small, handy machine with powerful 710-watt motor, ideal for all on-site fitting work
- ▶ The fastest and least expensive blade changes on the market due to durable Woodrazor reversible blades and the easiest possible adjustment
- ▶ Comfortable working because chip clearance can be set to either the right or left



GHO 40-82 C Professional planer

The planer for the highest surface quality

- ▶ The highest surface quality due to ultra-sharp blades and constant speed, even when working in hardwood
- ▶ The fastest and least expensive blade changes on the market due to durable Woodrazor reversible blades and the easiest possible adjustment
- ▶ The longest lifetime due to precise aluminium bearing seat and thermodynamic motor protection

	GHO 26-82 Professional	GHO 40-82 C Professional
Rated power input (W)	710	850
Planing width (mm)	82	82
Adjustable depth of cut (mm)	0–2.6	0–4.0
Adjustable rebating depth (mm)	0–9	0–24
Weight (kg)	2.6	3.2
Part number 110V	0 601 594 341	0 601 59A 764
Part number 240V	0 601 594 342	0 601 59A 762
SSP Ex Vat	£134.00	£215.00



Putting an end to fine dust.

Bosch is the only manufacturer with a certification for air purity. The Bosch micro-filters collect 90% of dusts, even particles 100 times finer than a human hair. Another advantage is the collection box, which removes the need for expensive filter bags.



GSS 140 A Professional orbital sander

Every type of sanding sheet sits perfectly with Easy-Fit

- ▶ A perfect hold of the paper without creasing and tearing due to Bosch Easy-Fit System – for Velcro-type paper and rolls of paper
- ▶ Bosch micro-filter system: perfect, efficient dust extraction
- ▶ Ergonomic design with two softgrip surfaces for two grip positions



GSS 280 AE Professional orbital sander

The sander for the highest surface quality

- ▶ High-quality sanding plates for the best surface quality and five times longer lifetime than rubber sanding plates
- ▶ Quiet and low-vibration for more comfortable working
- ▶ Best bearing seal and high-quality aluminium bearing flange for smooth running and long lifetime of the motor

	GSS 140 A Professional	GSS 230 AE Professional	GSS 280 AE Professional
Rated power input (W)	180	300	330
Orbit diameter (mm)	1.6	2.4	2.4
Sanding plate width (mm)	113	92	114
Sanding plate length (mm)	105	182	226
Part number 110V	0 601 297 088	0 601 292 662	0 601 293 662
Part number 240V	0 601 297 090	0 601 292 663	0 601 293 663
SSP Ex Vat	£69.00	£158.00	£191.00

The freehand experts – professional blue random orbit sanders.

Bosch random orbit sanders ensure perfect surface results – even on curved and shaped workpieces. Smooth running and freewheel brakes guarantee a surface finish free of scores and an optimum material removal rate.



GEX 125-1 AE Professional random orbit sander

Comfortable sanding in any work position

- Compact, ergonomic design with large softgrip surfaces for variable grip positions and outstanding comfort
- Bosch micro-filter system: perfect, efficient dust extraction
- Speed preselection for material-specific working



GEX 150 Turbo Professional random orbit sander

Three tools in one

- Just one click: switch from fine sanding to coarse sanding or polishing
- Five times more material removal in turbo operation (coarse sanding); the time-saving means that the tool pays for itself after a few working hours
- Longest lifetime thanks to perfect bearing seal, overload protection and a robust turbo switch

	GEX 125-1 AE Professional
Rated power input (W)	250
Sanding pad diameter (mm)	125
Orbit diameter (mm)	2.5
No-load speed (rpm)	7,500 – 12,000
Part number 110V	0 601 387 561
Part number 240V	0 601 387 571
SSP Ex Vat	£93.00

	GEX 150 Turbo Professional
Rated power input (W)	600
Sanding pad diameter (mm)	150
Orbit diameter (mm)	4.5
No-load speed (rpm)	3,100 – 6,650
Part number 110V	0 601 250 782
Part number 240V	0 601 250 783
SSP Ex Vat	£269.00



NEW! GEX 125-150 AVE Professional random orbit sander

Minimal vibration: no more tingling in your hands

- ▶ Unique vibration damping: the lowest vibration even in continuous use
- ▶ The highest surface quality: sanding unit is decoupled from housing to ensure consistent contact pressure
- ▶ Flexibility for every application range due to the choice of using 150 mm or 125 mm sanding pad diameter



Faster results – less strain.

Extended periods of sanding work usually used to lead to numbness in your hands that could last for days. This is now a thing of the past. The new GEX 125-150 AVE Professional random orbit sander offers the lowest vibration on the market. Its vibration level is less than the critical limit of 2.5 m/s^2 . This is achieved by completely decoupling the grip surfaces from the motor housing using polymer elements. It also has the best material removal rate in its class. The sanding pad rests perfectly flat, so it delivers the best surface results even when the contact pressure is unevenly distributed.

	NEW! GEX 125-150 AVE Professional
Rated power input (W)	400
Sanding pad diameter (mm)	125/150
Orbit diameter (mm)	4
No-load speed (rpm)	5,500–12,000
Part number with L-BOXX 110V	0 601 37B 160
Part number with L-BOXX 240V	0 601 37B 170
SSP Ex Vat with L-BOXX	£207.00

The Bosch system for professional sanders.

Matching abrasives and reliable dust extraction expand the application range of sanders. We pursue a strategy of innovation for this, especially when it comes to abrasives.

The **new abrasives range** offers **the right abrasive for virtually every requirement and application**. For outstanding results on the most common materials from belt sanding through to hand sanding. Different paper colours help you to choose the right sanding paper/material combination. Red is our Best for Wood, whilst white is Best for Paint.

When making abrasives, Bosch uses the many years of experience of sia Abrasives, a company which recently became part of Bosch. sia Abrasives is known as one of the world's leading manufacturers of innovative abrasives. The flexible abrasives are all produced at top quality in Switzerland. This ensures that, even when working on demanding surfaces and valuable materials, the desired sanding results can be achieved and additional costs incurred by damaging workpieces are eliminated. From abrasives for hand sanding through to the appropriate abrasive for all conventional hand-held power tools: Bosch offers the professional and complete range of abrasives that professional trades people demand.

Sanding pads from Bosch are available in extra-soft, soft and hard foams for every application.

Sanding plates from Bosch increase the functionality of orbital sanders. There are sanding plates with a delta tip, extended sanding plates, sanding plates with and without Velcro-type fastening – and guaranteed the right plate for every application.

Dust-free working with the GAS 50 M Professional: this special extractor for wood is the ideal addition for clean, dust-free working. It reliably collects even the finest particles, and it is even suitable for extracting liquids.

The L-BOXX is the convenient, stackable transport system for Bosch sanders. Thanks to a wide range of accessories, it is individually configurable for power tools, accessories and consumables.



“When manufacturing rotor blades for wind turbines, the interaction between sander and abrasive is a significant efficiency multiplier. Dialogue with professional tradespeople resulted in the combination of the GEX 125-150 AVE Professional with the Bosch ‘Best for Paint’ abrasive. Thanks to our many years of expertise, we have succeeded in offering a convincing solution where the crucial factors are material removal rate, surface quality and efficiency.”

Jürg Schnyder, sia applications specialist, abrasives competence centre, Frauenfeld

The Bosch system for professional sanders.



1. Sanding pads



2. Sanding plates



3. GAS 50 M Professional wood extractor















4. L-BOXX



1. Sanding pads*	Part number	SSP Ex Vat
8+1 150 mm pad	2 608 601 185	£N/A
150 mm pad, soft	2 608 601 051	£16.21
150 mm pad, medium-hard	2 608 601 052	£16.21
150 mm pad, hard	2 608 601 053	£16.21
*For GEX 125-150 AVE Professional, GEX 150 AC Professional and GEX 125 AC Professional		
2. Sanding plates*	Part number	SSP Ex Vat
Delta-shaped for GSS 230 Professional	2 608 000 189	£21.61
Extension for GSS 230 and GSS 280 Professional	2 608 000 190	£21.61
Adapter, 8 holes, 80 mm width	2 608 000071	£12.43
Adapter, 8 holes, 93 mm width	2 608 000072	£14.96
Adapter, 14 holes, 115 mm width	2 608 601 130	£N/A
*For GSS 230 AE Professional and GSS 280 AE Professional		
3. Wood extractor**	Part number	SSP Ex Vat
GAS 50 M Professional	0 601 988 103	£N/A
**GAS 50 M is not available in the UK		
4. L-BOXX	Part number	SSP Ex Vat
L-BOXX 136	2 608 438 692	£45.43
L-BOXX 236	2 608 438 693	£55.63
















Overview – the right abrasive for every application.


Finishing on curved surfaces, removing material on large surfaces or working in tight spaces – Bosch offers relevant accessories for every application, and for every sander.

	Surface quality	Material removal rate	Suitable for shapes and radii	Suitable for corners and edges	Paint
Machines	Application				best  previously: White Paint
 <p>Random orbit sanders for fine sanding on flat and curved surfaces</p>	100%				 K 40 – 400
 <p>Delta sanders for perfect sanding into the smallest corners</p>	100%				 K 40 – 320  K 40 – 180
 <p>Orbital sanders for large and perfect surfaces and the finest finishing into corners</p>	100%				 K 40 – 320
 <p>Belt sanders for the highest material removal rate on large surfaces</p>	100%				
 <p>Orbital sanders and hand sanding</p>	100%				 K 40 – 320  K 40 – 320





Wood		
best  Wood previously: Red Wood-top	expert  Wood previously: Red Wood	professional  Wood previously: Red Wood-eco
 K 40 – 400	 K 40 – 240	
 K 40 – 400	 K 40–240	 K 40–180
 K 40 – 400	 K 40 – 240	
 K 40 – 400		
 K 40–400		 K 40–320
 K 40–400		 K 40–240



*Sanding performance = material removal rate and lifetime





A direct hit every time – Bosch nailers and staplers.

Power, precision and robustness – From framing nailer for frame construction to a finishing nailer for interior fitting work or brad nailer and stapler for furniture construction: these tools guarantee you a fast work progress and neat and efficient working thanks to the innovative Bosch Full Force Technology or the Wood Protection System.

-
- ▶ Framing nailers P.44
 - ▶ Finishing nailers P.45
 - ▶ Brad nailer P.46
 - ▶ Stapler P.46
 - ▶ Coil nailer P.47

Hard on the nail, soft on the wood – innovative Bosch pneumatic nailers.

Bosch pneumatic nailers feature powerful drives for optimum work progress and compactness for working in any position. Thanks to the unique Wood Protection System, they are also gentle on the workpiece.



GSN 90-21 RK Professional, GSN 90-34 DK Professional and **NEW!** GSN 100-34 DK Professional framing nailers

The powerful tools for optimum work progress

- ▶ Full power, even at high firing frequency, due to innovative Full Force Technology
- ▶ Fast work progress due to tool-free release of the magazine when nails are jammed in the firing channel
- ▶ Compact design for more comfortable working, even in continuous use



	GSN 90-21 RK Professional	GSN 90-34 DK Professional	NEW! GSN 100-34 DK Professional
Application	Roof and frame construction	Roof and frame construction	Roof and frame construction
Angle	21°	34°	34°
Nail type	Full head strip nail	Strip nail with D head	D head
Nail diameter (mm)	2.8–3.8	2.8–3.8	2.8–3.3
Nail length (mm)	50–90	50–90	60–100
Operating pressure (bar)	5–8	5–8	5–8
Weight (kg)	3.9	3.8	4.0
Part number	0 601 491 001	0 601 491 301	0 601 491 501
SSP Ex Vat	£311.00	£311.00	£311.00



GSK 64 Professional and **NEW!** GSK 64-34 Professional finishing nailers

The compact tools for every work position

- Very compact tool design also enables work in hard-to-reach areas
- Quick and easy drive-depth adjustment by means of tool-free setting on the tool
- Wood Protection System means no blank firing, thus preventing damage to the workpiece

Optimum workpiece protection: Wood Protection System.



The Wood Protection System from Bosch protects the wood by disabling the triggering mechanism when the magazine is empty (on GSK 64 Professional, GSK 50 Professional and GTK 40 Professional). Your advantage: the workpiece cannot be damaged by the striking pin and the tool components are not strained by blank firing. In addition to this, all muzzles on these Bosch pneumatic nailers are equipped with a detachable rubber tip – for optimum workpiece protection.



	GSK 64 Professional	NEW! GSK 64-34 Professional
Application	Fastening	Interior fitting work
Angle	0°	34°
Nail type	Finish nail	Brad nail
Nail diameter (mm)	1.6	1.8
Nail length (mm)	25–64	32–64
Operating pressure (bar)	5–8	5–8
Weight (kg)	1.6	1.6
Part number	0 601 491 901	0 601 491 903
SSP Ex Vat	£176.00	£176.00




GSK 50 Professional brad nailer and GTK 40 Professional stapler

The precise tools for flawless finishing

- ▶ Slim design for precise positioning at the fastening point
- ▶ Wood Protection System means no blank firing, thus preventing damage to the workpiece
- ▶ Rubber-coated tip prevents damage to valuable surfaces

	GSK 50 Professional	GTK 40 Professional
Application	Fastening	Fastening
Angle	0°	0°
Nail type	Brad	Narrow crown staple
Nail diameter (mm)	1.2	1.2
Nail length (mm)	15–50	15–40
Operating pressure (bar)	5–8	5–8
Weight (kg)	1.1	1.1
Part number	0 601 491 D01	0 601 491 G01
SSP Ex Vat	£103.00	£103.00



**Every second counts, every nail is driven perfectly:
Bosch Full Force Technology.**



The Full Force Technology (standard on all Bosch pneumatic nailers) has been developed and patented by Bosch. It has a new type of valve system that reduces the size of the pressure chamber without sacrificing impact energy. This makes the tool more compact and accelerates the build-up of pressure in the tool. It therefore enables you to drive nails in flush even at high firing frequency – for less reworking and higher productivity.



NEW! GCN 45-15 Professional coil nailer

The robust tool for exact positioning

- ▶ Robust construction with additional protectors for high reliability and perfect protection of the tool
- ▶ Carbide-reinforced muzzle for a long lifetime
- ▶ Tool-free adjustable stop for perfect positioning on roof shingles of different sizes

	NEW! GCN 45-15 Professional
Application	Roof construction
Angle	15°
Nail type	Wire-collated coil nails
Nail diameter (mm)	3
Nail length (mm)	19–45
Operating pressure (bar)	5–8
Weight (kg)	2.4
Part number	0 601 491 C01
SSP Ex Vat	£269.00







Bosch cordless screwdrivers and drywall screwdrivers – the right tool for every job.

Bosch lithium-ion cordless tools for professionals from 3.6 to 36 volts impress with their extremely long battery runtime, optimum weight and extreme durability. With more than 50 lithium-ion products, Bosch has a comprehensive range of cordless tools – also especially for woodworking, such as cordless jigsaws, circular saws and sabre saws.

Bosch drywall screwdrivers are ideal for driving rows of screws and for comfortable continuous use. Due to their versatility and comprehensive accessories, Bosch cordless and drywall screwdrivers ensure that you have the right tool for every job.

-
- ▶ Cordless screwdrivers P.50
 - ▶ Cordless drill/drivers P.51
 - ▶ Drywall screwdrivers P.52

Compact. Powerful. Cordless.

A selection of our cordless screwdrivers.

Cordless screwdrivers with Bosch lithium-ion technology set new standards in compact size, capability and reliability. These tools impress with their extremely long battery runtime, optimum weight and durability.

More cordless tools at: www.bosch-professional.com/gb/en



NEW! GSR Mx2Drive Professional cordless screwdriver

Maximum power in trouser-pocket size

- ▶ Maximum power: innovative 2-speed gearbox allows for the gear to be changed without interruption by the on/off switch, and provides a powerful 10 Nm
- ▶ Fast and precise due to optimum gear ratio: fast driving in 2nd gear (580 rpm) – precise and flush driving in 1st gear (150 rpm)
- ▶ Extremely compact: very short head length (only 158 mm) and low weight (only 0.5 kg) – fits in any trouser pocket

	NEW! GSR Mx2Drive Professional
Weight including battery (kg)	0.5
Battery capacity (Ah)	1.3
Max. screw diameter (mm)	5
Max. torque (hard screwdriving applications) (Nm)	10
Speed in 1st gear/2nd gear (rpm)	150/0–580
Part number (1 x 1.3 Ah battery, carton)	0 601 9A2 170
Part number (2 x 1.3 Ah batteries, plastic box)	0 601 9A2 171
SSP Ex Vat Carton	£56.00
SSP Ex Vat (Plastic box)	£72.00



NEW! GSR 10,8-2-LI Professional cordless screwdriver

The shortest high-power tool in its class

- ▶ At 169 mm it has the shortest design in its class for optimum handling, especially when performing drilling and screwdriving applications overhead and in tight spaces
- ▶ Professional performance: 2-speed gearbox ensures a powerful 30 Nm when drilling (up to 19 mm) and screwdriving (up to 7 mm)
- ▶ Professional quality 10 mm Auto-Lock drill chuck

	NEW! GSR 10,8-2-LI Professional
Weight including battery (kg)	0.95
Battery capacity (Ah)	1.3
Max. screw diameter (mm)	7
Toolholder	10 mm Auto-Lock
Max. drilling diameter in wood (mm)	19
Speed in 1st gear/2nd gear (rpm)	0–350/1,300
Max. torque (hard screwdriving applications) (Nm)	30
Part number Body only	0 601 868 101
Part number with Carton	0 601 868 170
Part number with L-BOXX ready	0 601 868 171
SSP Ex Vat Body Only	£73.00
SSP Ex Vat Carton	£148.00
SSP Ex Vat with L-BOXX ready	£171.00

Bosch cordless tools – the right tool for every job.

With more than 50 lithium-ion products, Bosch has a comprehensive range of cordless tools – also especially for woodworking, such as cordless jigsaws, circular saws and sabre saws.

More information can be found in the current cordless catalogue or at www.bosch-professional.com/gb/en

**GSR 14,4-2-Li and GSR 18-2-Li Professional cordless drill/drivers**

The lightest tools in their class

- ▶ Lowest weight at only 1.3 kg (14.4 Volt)
- ▶ Perfect handling due to very short design (head length of only 196 mm) and slim, ergonomic grip circumference
- ▶ Newly developed 2-speed planetary gearbox for a powerful and versatile range of applications when screwdriving and drilling

GSR 14,4 V-Li and 18 V-Li Professional cordless drill/drivers

The shortest endurance runners

- ▶ Extremely compact due to shortest design (only 185 mm) in their class and low weight (only 1.7 kg, 14.4 Volt/3.0 Ah) for perfect handling
- ▶ Up to 500 screws (6 x 60 mm in softwood) with only one battery charge (18 Volt/3.0 Ah)
- ▶ Powerful 67 Nm (18 Volt) due to newly developed gearbox design and new 4-pole Bosch high-performance motor

	GSR 14,4-2-Li Professional	GSR 18-2-Li Professional	GSR 14,4 V-Li Professional	GSR 18 V-Li Professional
Weight including battery (kg)	1.3	1.4	1.7	1.8
Battery capacity (Ah)	1.3 (Compact)	1.3 (Compact)	3.0 (Premium)	3.0 (Premium)
Max. screw diameter (mm)	7	8	7	8
Max. drilling diameter in wood (mm)	25	29	32	35
Speed in 1st gear/2nd gear (rpm)	0–400/1,250	0–400/1,300	0–500/1,600	0–500/1,700
Max. torque (hard screwdriving applications) (Nm)	38	45	60	67
Part number				
Body only	–	–	0 601 866 001	0 601 866 101
with Carton	0 601 9A4 475	0 601 9A4 375	0 601 866 071	0 601 866 171
with L-BOXX ready	0 601 9A4 470	0 601 9A4 370	0 601 866 070	0 601 866 170
SSP Ex Vat Body only	–	–	£83.00	£92.00
SSP Ex Vat with Carton	£177.00	£197.00	£170.00	£179.00
SSP Ex Vat with L-BOXX ready	£198.00	£223.00	£223.00	£231.00

From powerful to fast – the new drywall screwdrivers.

The drywall screwdrivers are designed for quick and efficient screwdriving, driving rows of screws, and for comfortable continuous use. All of the tools have an ergonomic design, a lock-on button for continuous operation, and they can be comfortably operated with only one hand.



NEW! GSR 6-25 TE Professional drywall screwdriver

The powerful drywall screwdriver

- ▶ High torque enables powerful screwdriving
- ▶ Comfortable working due to ergonomic design and depth stop that can be operated with one hand
- ▶ Precise screwdriving to a constant depth due to exact shut-off clutch



NEW! GSR 6-45 TE Professional drywall screwdriver

The universal drywall screwdriver

- ▶ Optimum coordination of torque and speed enables a wide range of applications
- ▶ Comfortable working due to ergonomic design and depth stop that can be operated with one hand
- ▶ Precise screwdriving to a constant depth due to exact shut-off clutch

	NEW! GSR 6-25 TE Professional	NEW! GSR 6-45 TE Professional
Rated power input (W)	701	701
Max. torque (soft screwdriving applications) (Nm)	20	12
Toolholder	1/4" internal hexagon	1/4" internal hexagon
No-load speed (rpm)	0–2,500	0–4,500
Weight without cable (kg)	1.5	1.4
Self-drilling screw diameter (mm)	6	6
Part number 110V	0 601 445 060	0 601 445 160
Part number 240V	0 601 445 0P0	0 601 445 1P0
SSP Ex Vat	£171.00	£145.00



Efficiency added on: the collated screwgun attachment for Bosch drywall screwdrivers.

The MA 55 Professional collated screwgun attachment is available as a system accessory (Part no.: 1 600 Z00 00Y) that can be added on to the GSR 6-25 TE and GSR 6-45 TE Professional. It can be mounted, dismantled and adjusted without the need for additional tools. Designed for high RPMs, it enables you to precisely drive rows of screws at top speed.



NEW! GSR 6-45 TE drywall screwdriver + MA 55 Professional

The efficient drywall solution

- Enables precise driving of rows of screws at top speed
- Tool-free adjustment and mounting/dismantling of the collated screwgun attachment
- Comfortable working due to ergonomic design and low weight



NEW! GSR 6-60 TE Professional drywall screwdriver

The extremely fast drywall screwdriver

- High speed enables very fast fixing of plasterboards
- Comfortable working due to ergonomic design and depth stop that can be operated with one hand
- Precise screwdriving to a constant depth due to exact shut-off clutch

	NEW! GSR 6-45 TE + MA 55 Professional	NEW! GSR 6-60 TE Professional
Rated power input (W)	701	701
Max. torque (soft screwdriving applications) (Nm)	12	12
Toolholder	1/4" internal hexagon	1/4" internal hexagon
No-load speed (rpm)	0–4,500	0–6,000
Weight without cable (kg)	1.8	1.4
Self-drilling screw diameter (mm)	6	6
Part number 110V	0 601 445 161 (with L-BOXX)	0 601 445 260
Part number 240V	0 601 445 1P0 (with L-BOXX)	0 601 445 2P0
SSP Ex Vat	£280.00	£171.00

Mobile working – clever solutions for safe tool storage and easy transport.

The Bosch LBOXX is the intelligent, modular transport and storage system for power tools, accessories and consumables.

The LBOXX – space for tools and more.
Anybody who has to transport multiple tools and accessories is almost certainly going to need the L-BOXX. The blue boxes are available in 4 sizes, they are easily clicked together, and they can carry up to 40 kg in total when stacked together. Each L-BOXX can hold up to 25 kg and can be individually configured as required.



L-BOXX

The intelligent transport and storage system

- ▶ Unbeatably easy system of clicking together and separating the different L-BOXXes for transporting multiple power tools and accessories
- ▶ Exclusive compatibility with the German TÜV-tested in-vehicle equipment system from Sortimo
- ▶ Flexible options for storing power tools, accessories and consumables due to Sortimo’s wide range of accessories
- ▶ Very robust lid: fully splash-protected and a load bearing capacity of up to 100 kg

	L-BOXX 102	L-BOXX 136	L-BOXX 238	L-BOXX 374
Outer dimensions (LxWxH) (mm)	442 x 357 x 117	442 x 357 x 151	442x357x253	442x357x389
Inner dimensions (LxWxH) (mm)	378 x 313 x 71	378 x 311 x 107	378 x 306 x 209	378 x 296 x 345
Weight (kg)	2.1	2.2	2.8	3.4
Part number	2 608 438 691	2 608 438 692	2 608 438 693	2 608 438 694
SSP Ex Vat	£42.18	£45.43	£55.63	£66.75

Bosch saw stands for benchtop tools are assembled in seconds and are also convenient to transport on uneven construction site terrain.



**Unlimited flexibility –
the mobility concept for benchtop saws.**

The GTA 2500 W Professional and GTA 60 W Professional saw stands are a means of transport and a work bench in one. They fit all Bosch mitre saws, sliding mitre saws, gliding mitre saws and tables saws. They are assembled and dismantled with only one lever movement, without having to remove the benchtop saw.



GTA 60 W Professional and GTA 2500 W Professional saw stands

For table saws or for mitre saws and sliding mitre saws

- Double the benefit: a means of transport and a work bench in one
- Easy to assemble and dismantle with only one lever movement, without having to remove the benchtop saw

	GTA 60 W Professional (for table saws)	GTA 2500 W Professional (for mitre saws)
Length of saw stand unfolded (mm)	1220	1220
Height of saw stand unfolded (mm)	622	864
Weight (kg)	24	35
Part number	0 601 B12 000	0 601 B12 100
SSP Ex Vat	£183.00	£280.00