

USER MANUAL **G-MASTER**

LCD Monitor

ENGLISH

G-MASTER G4380UHSU

Thank you very much for choosing the iiyama LCD monitor.

We recommend that you take a few minutes to read carefully through this brief but comprehensive manual before installing and switching on the monitor. Please keep this manual in a safe place for your future reference.

iiyama | Servicecard





Dear user, we congratulate you on the purchase of your iiyama LCD.

For details on warranty and locally used pixel policies that apply directly after installation of your product please check the iiyama website.

To report a fault, please contact your local support centre found at www.iiyama.com/service

Things to check before you call the iiyama information line

- if the power cable is connected securely and turned on?
- | if the display has been turned on?
- | if the signal cable is connected securely and the correct input selected?
- | if the computer has been restarted with the display connected?
- | if the graphics card is correctly installed with the latest drivers possible?
- | if the correct native resolution has been selected via 'Display Properties'?
- If the R/G/B signal configuration is correct?
- | if the displays On Screen Menu is shown?
- | if the correct brightness and contrast settings have been set?
- | if given display tolerances and compatibility have been considered?
- | if via the On Screen Menu you have performed a Factory Reset/Recall?

Before reporting the screen defect, please prepare the following information/evidence:

model number *

purchase receipt and serial number *

name and address for collection

telephone/fax number, for availability during the day

- convenient collection date (date, time)
- short description of the defect

Important Note:

If there is no fault found in the collected equipment after inspection, the transferring party shall incur charges for transport and administration.

If you have checked all of the above and there is still no picture, call our information line for assistance in your country.





CE MARKING DECLARATION OF CONFORMITY

This LCD monitor complies with the requirements of the EC/EU Directive 2014/30/EU "EMC Directive", 2014/35/EU "Low Voltage Directive", 2009/125/EC "ErP Directive" and 2011/65/EU "RoHS Directive".

The electro-magnetic susceptibility has been chosen at a level that gives correct operation in residential areas, business and light industrial premises and small-scale enterprises, inside as well as outside of the buildings. All places of operation are characterised by their connection to the public low voltage power supply system.

IIYAMA CORPORATION: Wijkermeerstraat 8, 2131 HA Hoofddorp, The Netherlands

Model No. : PL4380UH



We recommend recycling of used product. Please contact your dealer or iiyama service center. Recycle information is obtained via the Internet, using the address: http://www.iiyama.com You can access the Web page of different countries from there.

- We reserve the right to change specifications without notice.
- All trademarks used in this user manual are the property of their respective owners.
- Eprel registration number G4380UHSU-B1 : 1064183

TABLE OF CONTENTS

FOR YOUR SAFETY	1
SAFETY PRECAUTIONS	1
SPECIAL NOTES ON LCD MONITORS	3
CUSTOMER SERVICE	3
CLEANING	3
BEFORE YOU OPERATE THE MONITOR	4
FEATURES	4
CHECKING THE CONTENTS OF THE PACKAGE	4
INSTALLATION	5
FITTING AND REMOVAL OF BASE	6
CONTROLS AND CONNECTORS	7
FUNCTIONS OF THE REMOTE CONTROL	8
PREPARING THE REMOTE CONTROL	9
BASIC OPERATION	10
BASIC OPERATION CONNECTING YOUR MONITOR	
	13
CONNECTING YOUR MONITOR	13 14
CONNECTING YOUR MONITOR	13 14 14
CONNECTING YOUR MONITOR COMPUTER SETTING ADJUSTING THE VIEWING ANGLE	13 14 14 15
CONNECTING YOUR MONITOR COMPUTER SETTING ADJUSTING THE VIEWING ANGLE OPERATING THE MONITOR	13 14 14 15 17
CONNECTING YOUR MONITOR COMPUTER SETTING ADJUSTING THE VIEWING ANGLE OPERATING THE MONITOR ADJUSTMENT MENU CONTENTS	13 14 14 15 17 30
CONNECTING YOUR MONITOR COMPUTER SETTING ADJUSTING THE VIEWING ANGLE OPERATING THE MONITOR ADJUSTMENT MENU CONTENTS STANDBY FEATURE	13 14 14 15 17 30 31
CONNECTING YOUR MONITOR COMPUTER SETTING ADJUSTING THE VIEWING ANGLE OPERATING THE MONITOR ADJUSTMENT MENU CONTENTS STANDBY FEATURE TROUBLE SHOOTING	13 14 15 17 30 31 32
CONNECTING YOUR MONITOR COMPUTER SETTING ADJUSTING THE VIEWING ANGLE OPERATING THE MONITOR ADJUSTMENT MENU CONTENTS STANDBY FEATURE TROUBLE SHOOTING RECYCLING INFORMATION	13 14 15 17 30 31 32 33
CONNECTING YOUR MONITOR COMPUTER SETTING ADJUSTING THE VIEWING ANGLE OPERATING THE MONITOR ADJUSTMENT MENU CONTENTS STANDBY FEATURE TROUBLE SHOOTING RECYCLING INFORMATION APPENDIX	13 14 15 17 30 31 32 33 33

ENGLISH

FOR YOUR SAFETY

SAFETY PRECAUTIONS

WARNING

STOP OPERATING THE MONITOR WHEN YOU SENSE TROUBLE

If you notice any abnormal phenomena such as smoke, strange sounds or fumes, unplug the monitor and contact your dealer or iiyama service center immediately. Further use may be dangerous and can cause fire or electric shock.

NEVER REMOVE THE CABINET

High voltage circuits are inside the monitor. Removing the cabinet may expose you to the danger of fire or electric shock.

DO NOT PUT ANY OBJECT INTO THE MONITOR

Do not put any solid objects or liquids such as water into the monitor. In case of an accident, unplug your monitor immediately and contact your dealer or iiyama service center. Using the monitor with any object inside may cause fire, electric shock or damage.

INSTALL THE MONITOR ON A FLAT, STABLE SURFACE

The monitor may cause an injury if it falls or is dropped.

DO NOT USE THE MONITOR NEAR WATER

Do not use where water may be splashed or spilt onto the monitor as it may cause fire or electric shock.

OPERATE UNDER THE SPECIFIED POWER SUPPLY

Be sure to operate the monitor only with the specified power supply. Use of an incorrect voltage will cause malfunction and may cause fire or electric shock.

PROTECT THE CABLES

Do not pull or bend the power cable and signal cable. Do not place the monitor or any other heavy objects on the cables. If damaged, the cables may cause fire or electric shock.

ADVERSE WEATHER CONDITIONS

It is advisable not to operate the monitor during a heavy thunder storm as the continual breaks in power may cause malfunction. It is also advised not to touch the plug in these circumstances as it may cause electric shock.

CAUTION

INSTALLATION LOCATION

Do not install the monitor where sudden temperature changes may occur, or in humid, dusty or smoky areas as it may cause fire, electric shock or damage. You should also avoid areas where the sun shines directly on the monitor.

DO NOT PLACE THE MONITOR IN A HAZARDOUS POSITION

The monitor may topple and cause injury if not suitably located. Please also ensure that you do not place any heavy objects on the monitor, and that all cables are routed such that children may not pull the cables and possibly cause injury.

MAINTAIN GOOD VENTILATION

Ventilation slots are provided to keep the monitor from overheating. Covering the slots may cause fire. To allow adequate air circulation, place the monitor at least 10cm (or 4 inches) from any walls. When removing the tilt stand, the ventilation slots on the back side of the monitor can be blocked. This may overheat the monitor and may cause fire or damage. Make sure to allow enough ventilation when removing the tilt stand. Operating the monitor on its back, side, upside down or on a carpet or any other soft material may also cause damage.

DISCONNECT THE CABLES WHEN YOU MOVE THE MONITOR

When you move the monitor, turn off the power switch, unplug the monitor and be sure the signal cable is disconnected. If you do not disconnect them, it may cause fire or electric shock.

UNPLUG THE MONITOR

If the monitor is not in use for a long period of time it is recommended that it is left unplugged to avoid accidents.

HOLD THE PLUG WHEN DISCONNECTING

To disconnect the power cable or signal cable, always pull it by the plug. Never pull on the cable itself as this may cause fire or electric shock.

DO NOT TOUCH THE PLUG WITH WET HANDS

Pulling or inserting the plug with wet hands may cause electric shock.

WHEN YOU INSTALL THE MONITOR ON YOUR COMPUTER

Be sure the computer is strong enough to hold the weight of the monitor, otherwise, you may damage your computer.

CAREFUL! PROTECT YOUR HANDS AND FINGERS

Be careful not to hurt your fingers or hands when you change the angle.

REMARK FOR 24/7 USAGE

This product is not specifically designed for 24/7 usage in all environments.

FOR SINGLE USERS

This product is primarily intended for close viewing by a single user.

OTHERS

ERGONOMIC RECOMMENDATIONS

To eliminate eye fatigue, do not operate the monitor against a bright background or in a dark room. For optimal viewing comfort, the monitor should be just below eye level and 40-60 cm (16-24 inches) away from your eyes. When using the monitor over a prolonged time, a ten minute break every hour is recommended as looking at the screen continuously can cause eye strain.

ENGLISH

SPECIAL NOTES ON LCD MONITORS

The following symptoms are normal with LCD monitors and do not indicate a problem.

- **NOTE** When you first turn on the LCD monitor, the picture may not fit in the monitor area because of the type of computer that is used. In this case, adjust the picture position to the correct position.
 - You may find slightly uneven brightness on the screen depending on the desktop pattern you use.
 - Due to the nature of the LCD screen, an afterimage of the previous screen may remain after switching the image, when the same image is displayed for hours. In this case, the screen can be recovered slowly by changing the image or turning off the Power Switch for some hours.

CUSTOMER SERVICE

NOTE If you have to return your unit for service and the original packaging has been discarded, please contact your dealer or iiyama service center for advice or replacement packaging.

CLEANING

NOTE

- **WARNING** If you drop any materials or liquids such as water into the monitor when cleaning, unplug the power cable immediately and contact your dealer or iiyama service center.
- **CAUTION** For safety reasons, turn off the power switch and unplug the monitor before you clean it.
 - To protect the LCD panel, do not scratch or rub the screen with a hard object.
 - Never use any of the following strong solvents. These will damage the cabinet and the LCD screen.

Thinner	Spray-type cleaner
Benzine	Wax
Abrasive cleaner	Acid or Alkaline solvent

- Touching the cabinet with any product made from rubber or plastic for a long time may cause degeneration or loss of paint on the cabinet.
- **CABINET** Stains can be removed with a cloth lightly moistened with a mild detergent solvent. Then wipe the cabinet with a soft dry cloth.
- LCD Periodic cleaning with a soft dry cloth is recommended.
- **SCREEN** Don't use tissue paper etc. because these will damage the LCD screen.

BEFORE YOU OPERATE THE MONITOR

FEATURES

- Supports Resolutions up to 3840 × 2160
- High Contrast 4000:1 (Typical), Advanced Contrast Function Available, Brightness 550cd/m² (Typical)
- Moving Picture Response Time 0.4ms
- Supports AMD FreeSync[™] Premium Technology (through DisplayPort input)
- Supports HDR400
- Flicker Free
- Blue Light Reducer
- Digital Character Smoothing
- 2 × 7W Stereo Speakers
- Standby Feature
- VESA Mounting Standard (200mm×100mm) Compliant
- Keyhole for Security Lock

CHECKING THE CONTENTS OF THE PACKAGE

The following accessories are included in your package. Check to see if they are enclosed with the monitor. If anything is missing or damaged, please contact your local iiyama dealer or regional iiyama office.

- Power Cable*
- USB Cable
- Headphone Hook
- Quick Start Guide
- CAUTION The rating of the Power Cable enclosed in 120V area is 10A/125V. If you are using a power supply higher than this rating, then a power cable with a rating of 10A/ 250V must be used. However, all guarantees and warranties are void for any problems or damage caused by a power cable not supplied by iiyama.

An approved power cable greater or equal to H05VVF, 3G, 0.75mm² must be used.

ENGLISH

4 BEFORE YOU OPERATE THE MONITOR

- Remote Control
- DisplayPort Cable
- Batteries (2pcs)
- Stand-Base with a screw Safety Guide

- HDMI Cable

INSTALLATION

CAUTION ■ Before installation, make sure the wall, ceiling or desktop arm is strong enough to hold the necessary weight of the monitor and the mount.

< WALL MOUNTING >

CAUTION When you use with the wall mounting, in consideration of thickness of the mounting stage, tighten the M4 Screw (4pcs) which "L" length is 10mm to fasten the monitor. Using the screw longer than this may cause electric shock or damage because it may contact with the electrical parts inside the monitor.



< LANDSCAPE MODE >

It is designed to be compatible in landscape mode.



FITTING AND REMOVAL OF BASE

- **CAUTION** Put the monitor on a stable surface. The monitor may cause injury or damage if it falls or is dropped.
 - Do not give a strong impact to the monitor. It may cause damage.
 - Unplug the monitor before removal or installation to avoid an electric shock or a damage.

<Installation>

- ① Put a piece of soft cloth on the table beforehand to prevent the monitor from being scratched.
 - Lay the monitor flat on a table with front face down.
- 2 Install the Stand-Base as shown on below picture.
- ③ Tighten the 'thumb screw' to secure the Stand-Base to the monitor.



Thumb screw for Stand-Base

<Removal>

- (1) Put a piece of soft cloth on the table beforehand to prevent the monitor from being scratched. Lay the monitor flat on a table with front face down.
- (2) Loosen the 'thumb screw' to remove the Stand-Base from the monitor.

CONTROLS AND CONNECTORS

<Front>

<Back>



- Power Indicator
 NOTE Blue: Normal operation
 Orange: Standby mode
- 2 Remote Sensor
- ③ Input Select Button (INPUT)
- ④ + / Volume Button (+)
- ⑤ / i-Style Color Button (-)
- 6 Menu Button (MENU)
- ⑦ Power Button (🕁)
- (8) AC Connector (\sim : Alternating current)
- 9 Speakers
- 1 Headphone Hook Hole *
- USB 2.0 Downstream Connector (↔ 5V, 500mA)
- ⑦ USB 2.0 Downstream Connector (∽↔ 5V, 500mA)
- (i) USB 3.0 Downstream Connector (∽⇔ 5V, 900mA) Blue
- (USB 3.0 Downstream Connector (∽ 5V, 1.5A) Yellow
- (15) USB 3.0 Upstream Connector (∞↔)
- 16 Keyhole for Security Lock
 - NOTE You can fasten a security lock and cable to prevent the monitor from being removed without your permission.

- 1 Headphone Connector (\bigcap)
- 18 DisplayPort Connector (DP2)
- (19) DisplayPort Connector (DP1)
- (1) HDMI Connector (HDMI2)
- 1 HDMI Connector (HDMI1)
- 2 Cable Holder

* If necessary, attach the included Headphone Hook and turn to secure it.

FUNCTIONS OF THE REMOTE CONTROL



1		Turns the monitor ON and OFF.
2	∢ ► ► ► ■ ■ ■ ■ ■ ■ ■ ■ ■ ■ ■ ■ ■ ■ ■ ■	Not available on this model.
3	- SOURCE	Selects the source. Press → or → button to select from DP1, DP2, HDMI1 or HDMI2. Press [OK] button to confirm and exit.
4	f [HOME]	Opens the monitor's on-screen menu systems.
5		Not available on this model.
6		Navigates through submenus and settings. I : Up Button : Down Button : Left Button : Right Button
	ОК	Confirms your selection or save changes.
\bigcirc	tt ADJUST	Not available on this model.
8	INUTE]	Turns on or off the mute function when the Menu is not displayed.
9		Not available on this model.
10	[NUMBER] / ID SET / ENTER	Not available on this model.
1	NORMAL / ID	Not available on this model.
12	FORMAT	Open the Video Mode Adjust.
13	➡ [BACK]	Returns to a previous menu or closes the OSD Menu.
14	i INFO	Provides resolution information.
15	OPTIONS	Not available on this model.
16	VOL + / -	+: Increases the sound volume. -: Decreases the sound volume.

ENGLISH

PREPARING THE REMOTE CONTROL

To use the remote control, insert the two dry batteries.

CAUTION

Do not use any other batteries other than those specified in this manual for the Remote Control. Do not insert old and new batteries together in the Remote Control. Make sure that the terminals match the "+" and "--" indications in the battery compartment. Remove dead batteries immediately to prevent them from leaking into the battery compartment. Burst batteries or the electrolyte from these batteries may cause stains, fire or injury.

① Open the battery cover.



② Align and insert two AAA batteries according to their plus and minus ports (as indicated in the compartment).
Batteries 2



③ Close the battery cover.



Refer to the above instructions when taking out the batteries.

- Replace with new batteries when the Remote Control does not work close to the monitor. Use AAA dry batteries. Risk of explosion if battery is replaced by an incorrect type.
- Operate the Remote Control by pointing it toward the Remote Sensor on the monitor.
- Other manufacturers remote control will not work with this monitor. Use the provided Remote Control ONLY.
- Used batteries needed to follow the local rules to be discarded. (Suggestion: to dispose of used batteries please follow correct policy as per your local regulations.)
- Batteries shall not be exposed to excessive heat such as sunshine, fire or the like.
- If you do not intend to use the remote control for a long period, remove the batteries.

BASIC OPERATION

Turning the monitor ON

The monitor is turned On and the Power Indicator turns to Blue when you press the \bigcirc Button on the remote control or the monitor. The monitor is turned Off and the Power Indicator turns to Orange when you press the \bigcirc Button on the remote control or the monitor. Press again to turn On the monitor.

NOTE

Even when using the standby mode or turning Off the Button, the monitor will consume a small amount of electricity. Disconnect the Power Cable from the power supply whenever the monitor is not in use or during the night, to avoid unnecessary power consumption.



INPUT

MENU ம

Display the adjustment menu page

The menu page appears on the screen when you press the Button on the remote control or the MENU Button on the monitor.

The menu page disappears when you press the \neg / \checkmark Button on the remote control or the INPUT Button on the monitor.



[Remote Control]



[Remote Control]



Move the cursor vertically

Select adjustment by pressing the \downarrow / \downarrow Buttons on the remote control or the + / – Buttons on the monitor while the menu page is displayed on the screen.





ENGLISH

■ Move the cursor horizontally

Select menu or setting, or perform the adjustment by pressing the -/- Buttons on the remote control or the + / – Buttons on the monitor while the menu page is displayed on the screen.



[Remote Control]



Adjust the volume of sound

Press the VOL+ / VOL- Buttons on the remote control or the + / - Buttons on the monitor to adjust the volume of sound when the menu page is not displayed on the screen.



NOTE

ENGLISH

For the monitor, press the + Button first and then adjust the volume with the + / – Buttons.

[Remote Control]



Switch the input signal

Press the **D** SOURCE Button on the remote control or the INPUT Button on the Monitor when the menu is not displayed, it shows Signal Select menu.



[Remote Control]



CONNECTING YOUR MONITOR

- ① Ensure that both the computer and the monitor are switched off.
- ② Connect the computer to the monitor with the signal cable.
- ③ Connect the computer to the monitor with the USB Cable.
- ④ Connect the Power Cable to the monitor first and then to the power source.
- (5) Turn on your monitor and computer.
- NOTE Make sure that the building installation has a circuit breaker of 120/240V, 20A (maximum).
 - The signal cables used for connecting the computer and monitor may vary with the type of computer used. An incorrect connection may cause serious damage to both the monitor and the computer. The cable supplied with the monitor is for a standard connector. If a special cable is required please contact your local iiyama dealer or regional iiyama office.
 - The Class I pluggable equipment Type A must be connected to protective earth.
 - The socket-outlet shall be installed near the equipment and shall be easily accessible.
 - Excessive sound pressure from ear-/headphones can cause hearing damage/hearing loss.



[Example of Connection]

Signal Timing

Change to the desired signal timing listed on page 34: COMPLIANT TIMING.

ADJUSTING THE VIEWING ANGLE

- For optimal viewing it is recommended to look at the full face of the monitor.
- Hold the stand so that the monitor does not topple when you change the monitor's angle.
- You are able to adjust the monitor's angle up to 10° upward, 2° downward.
- **NOTE** Do not touch the LCD screen when you change the angle. It may cause damage or break the LCD screen.
 - Careful attention is required not to pinch your fingers or hands into the moving part of the stand when you change the angle.



ENGLISH

OPERATING THE MONITOR

To create the best picture, your iiyama LCD monitor has been preset at the factory with the COMPLIANT TIMING shown on page 34. You are also able to adjust the picture by following the button operation shown below.



- ② Select the Menu item which contains the adjustment icon relating to the adjustment you want to make. Press the OK Button on the remote control or the MENU Button on the monitor. Then, use the 1/1 Buttons on the remote control or the + / Buttons on the monitor to highlight the desired adjustment icon.
- ③ Press the OK Button on the remote control or the MENU Button on the monitor again. Use the → / → Buttons on the remote control or the + / Buttons on the monitor to make the appropriate adjustment or setting.
- ④ Press the OK Button on the remote control or the MENU Button on the monitor, then the -/ → Button on the remote control or the INPUT Button on the monitor to leave the menu, and the settings you just made would be automatically saved.

For example, to correct for OSD vertical position, select Menu item of Setup Menu and then press the OK Button on the remote control or the MENU Button on the monitor. Then, select OSD Vertical Position by using the ||/| Buttons on the remote control or the + / – Buttons on the monitor.

An adjustment scale becomes active after you press the OK Button on the remote control or the MENU Button on the monitor. Then, use the -/ - Buttons on the remote control or the + / – Buttons on the monitor to change the OSD vertical position settings. The OSD vertical position of the overall display should be changing accordingly while you are doing this.



Press the OK Button on the remote control or the MENU Button on the monitor and finally the -/ - Button on the remote control or the INPUT Button on the monitor to close the On Screen Display feature. All changes are saved in the memory.



- When Button operations are aborted during adjustment, On-Screen Display disappears when the time set for the OSD Time has passed. Also, the -/ Button on the remote control or the INPUT Button on the monitor can be used to return previous menu and turn off the On-Screen Display.
- Any changes are automatically saved in the memory when the On Screen Display disappears. Turning off the power should be avoided while using the Menu.

ADJUSTMENT MENU CONTENTS

Г

Picture Adjust *1	wortheast wortheast wortheast worksong worksong	B ANDITES CHARMAN R ALVAT C CONSULT C CONSULT C C CONSULT C C C C C C C C C C C C C C C C C C C
Adjustment Item	Problem	/ Option Button to Press
Contrast	Too dark Too bright	RC Monitor
Brightness *2	Too dull Too intense	e
Overdrive		ye the gray level response time of the LCD panel.
Adv. Contrast	On	Increased Contrast Ratio
Auv. Contrast	Off	Typical Contrast Ratio
	Off	Normal
Eco	Mode1	Brightness of back-light is reduced.
	Mode2	Brightness of back-light is reduced more than Mode1.
	Mode3	Brightness of back-light is reduced more than Mode2.
	Off	Typical
Blue Light Reducer Direct	Mode1	Blue light is reduced.
	Mode2	Blue light is reduced more than Mode1.
	Mode3	Blue light is reduced more than Mode2.
Black Tuner	From -5 to You can ac	+5 djust Dark shades. + 1 2/3/4/5/6/7 + 1
	Off / 0 / 1 /	2/3/4/5/6/7
MBR * ³	Improve the panel.	e moving picture response time of the LCD
	Gamma1	
Gamma	Gamma2	
	Gamma3	

*1 The availability of each item depends on which item is activated. See the Function Correlation Matrix on page 29 for more details.

*² Adjust the Brightness when you are using the monitor in a dark room and feel the screen is too bright.

*³ MBR is available only when the refresh rate is 75Hz or more.



You can skip the Menu items and directly display an option setting screen by using the following button operations.

• Blue Light Reducer: Keep pressing the – Button on the monitor for 3 seconds when the Menu is not displayed.

Input Select	C-MASTER Fritaria	411 8471 50462 7 A45 11 MAUL 12 MAUL 13 92 14 9 92 14 9 92 15 92 16 91 16 92 16 92	CMATTR GAMBOND WRAC KARFT KARFT KARFT
Adjustment Item			Option
	Auto		Search for an available input source and select automatically.
		DP2	Select the Digital (DisplayPort2) input.
Input Source	Manual	DP1	Select the Digital (DisplayPort1) input.
	Ivialiual	HDMI2	Select the Digital (HDMI2) input.
		HDMI1	Select the Digital (HDMI1) input.
NOTE Input source is fix selected.	ked, not sele	cted automati	ically when HDMI and DisplayPort which are

Direct

You can skip the Menu items and directly display an option setting screen by using the following button operations.

• Input Select: Press the - SOURCE Button on the remote control or the INPUT Button on the monitor when the Menu is not displayed, it shows following Menu.



Audio Adjust	G: MARCE USAR Image: Notation of the second of the	CALUTE SOLICIU	
Adjustment Item	Problem /	Option	Button to Press
Volume Direct	Too soft Too loud		
Mute Direct	On	Turn off the sour	nd temporarily.
Mute Direct	Off	Return the soun	d volume to the previous level.
	witched as foll on \longrightarrow Off —	ows by pressing t	the / Buttons

Direct

ENGLISH

You can skip the Menu items and directly display an adjustment scale or an option setting screen by using the following button operations.

- Volume: Press the VOL + / Buttons on the remote control or the + Button on the monitor when the Menu is not displayed.
- Mute: Press the **I** Sutton on the remote control or keep pressing the + Button on the monitor for 3 seconds when the Menu is not displayed.

Store User Setting	CHALLENEE	
Adjustment Item		Option
	User Mode 1	Save the settings of the screen adjustment.
User Modes	User Mode 2	Save the settings of the screen adjustment.
	User Mode 3	Save the settings of the screen adjustment.
from "i-Style Color" mer	u of "Image Adj verdrive, Adv. Co	ontrast, Eco, Black Tuner, MBR, Gamma, Volume,

Color Settings *		EMPENTURE CCCL NORMAL		
Adjustment Item	Problem	n / Option		Button to Press
	Cool	Cool color		
Color Temperature	Normal	Normal color		
	Warm	Warm color		
		Red		
		Yellow		
	Hue	Green	Too weak	+
		Cyan	Too strong	
		Blue		
6-Axis		Magenta		
07000		Red		
		Yellow		
	Saturation	Green	Too weak	🔶 🔶 +
		Cyan	Too strong	
		Blue		
		Magenta		
	Red	Too weak		* * +
User Preset	Green	Too strong		
	Blue	loo caong		-

* Disabled when Blue Light Reducer or HDR is active.

E Image Adjust	swytheret sources and the second se	C MASTER GODDADD PANOT FINIT COLOR
Adjustment Item	Option	Button to Press
	Off	Return to a state set by color adjustment except i-Style Color.
	Standard *1	For general windows environment and monitor default setting
	Sport Game *1	For Sports game environment
i Style Color Direct	FPS Game *1	For FPS game environment
i-Style Color Direct	Strategy Game *1	For Strategy game environment
	Text *1	For text editing and viewing in a word processing environment
	User Mode 1	Applies customized monitor settings.
	User Mode 2	Applies customized monitor settings.
	User Mode 3	Applies customized monitor settings.
	Off	Normal
V Dee Teebreleeu * ¹	Soft	Enhance the picture edge.
X-Res Technology *1	Middle	Enhance the picture edge more than the Soft option.
	Hard	Enhance the picture edge more than the Middle option.
	123456	
Sharp and Soft	Press the ► / + B	The picture quality from 1 to 6 (sharp to soft). \clubsuit attach to change the picture quality in the picture \checkmark / – Button to change the picture \clubsuit + numerical order.
11D111 D +2	Full	For full-range color scale signal
HDMI Range * ²	Limited	For limited color scale signal
	On	Reduce the input-lag.
Direct Drive Mode *3	Off	Typical
NOTE Changing Resol		ate or turning Power Off/On might disable the Direct

Drive Mode function.

*1 Disabled when HDR is active.

*² Available for HDMI input only.

*³ The availability of each item depends on which item is activated. See the Function Correlation Matrix on page 29 for more details.

Direct

You can skip the Menu items and directly display an option setting screen by using the following button operations.

• i-Style Color: Press the – Button on the monitor when the Menu is not displayed.

ENGLISH

E Image Adjust	Contraction Contracti	
Adjustment Item		Option
	Full	Expansion display
	Aspect *4	Expansion display of Aspect
	Dot by dot *5	Display the picture dot by dot.
	17inch	Display the picture as 17 inch screen (5 : 4).
	19inch	Display the picture as 19 inch screen (5 : 4).
	19.5inch	Display the picture as 19.5 inch screen (16 : 9).
X	21.5inch	Display the picture as 21.5 inch screen (16 : 9).
Video Mode Adjust *3	23inch	Display the picture as 23 inch screen (16 : 9).
	23.8inch	Display the picture as 23.8 inch screen (16 : 9).
	24inch	Display the picture as 24 inch screen (16 : 9).
	24.5inch	Display the picture as 24.5 inch screen (16 : 9).
	27inch	Display the picture as 27 inch screen (16 : 9).
	31.5inch	Display the picture as 31.5 inch screen (16 : 9).
	34inch	Display the picture as 34 inch screen (16 : 9).

*³ The availability of each item depends on which item is activated. See the Function Correlation Matrix on page 29 for more details.

^{*4} Available only with 16:10, 5:4 and 4:3 resoluctions.
 ^{*5} Available only at resolutions 2560 × 1440 or less.

Language	CHASTER Translater Mr State Mr St	OWATER GLIBOREU Kers Prigde BI Vers Prigde BI Con Prigde Con P		
Adjustment Item		Ор	tion	
	English	English	Nederlands	Dutch
	Deutsch	German	Polski	Polish
Language	Español	Spanish	Português	Portuguese
Language	Français	French	Русский	Russian
	Italiano	Italian	Ĉesky	Czech
	日本語	Japanese		

Setup Menu		G-MASTE	ER G4380UHSU
	- MCTURE ADJUST	SETUP MENU	
	INPUT SELECT		_
	C) AUDIO ADJUST		 ▶
	TORE USER SETTING		•
	COLOR SETTINGS		077
	IMAGE ADJUST	HDR ×CR CN	011
		Fredlync Premium ON	011
	COR SETUP MENU		017
			011
	RESET	USB STANDBY MODE ON	011

Adjustment Item		Problem / Option	Button to Press		
OSD Horizontal Position	1) is too left) is too right			
OSD Vertical Position		OSD is too low OSD is too high			
OSD Time	11	You can set the OSD display duration time between 5 and 30 seconds.			
	On	G-MASTER Logo is displayed wh	nen the monitor is turned on.		
Opening Logo	Off	G-MASTER Logo is not displayed turned on.	d when the monitor is		
HDR *1	On	For HDR (High Dynamic Range)	signal		
אטח	Off	For normal signal			
FreeSupe Dramium * ^{1,2}	On	Enable the FreeSync function.			
FreeSync Premium * ^{1,2}	Off	The FreeSync function is turned	Off.		
LED	On	The Power Indicator is turned On).		
	Off	The Power Indicator is turned Of	f.		
NOTE Turn Off the Power Indicator when you are bothered by the light.					
	On	DDC/CI is On.			
DDC/CI	Off	DDC/CI is Off.			
	On	The USB hub enters into the stand with the monitor	dby mode in synchronization		

USB Stanby mode The USB hub remains activated if the monitor enters into the Off standby mode. *1 The availability of each item depends on which item is activated. See the Function Correlation

with the monitor.

Matrix on page 29 for more details.

*² Available for DisplayPort input only.

Display Information	CMASTER Menne Menne	GANGTER GLEBOHRD BOLLF WORKERCK HIGT THE BIN OF	
	CON SETUP MEAU ESPLAY INFORMATION ESPLAY INFORMATION ESPLAY]	
Displays information regarding t computer.	the current	input signal coming fr	om the graphic card in your

NOTE See your graphic card user guide for more information about changing the resolution and refresh.

Reset Direct	C + MARENTRA C + MARTIN de CASANDIO Image: Construction of the constr
Adjustment Item	Option
Yes	Factory-preset data is restored.

Direct

You can skip the Menu items and directly perform "Reset" by using the following button operations.

• Reset: While the monitor is turned Off, press the () Button and the INPUT Button on the monitor at the same time.

• Lock Mode:

<OSD>

If you turn on the monitor with holding down the MENU Button on the monitor while the monitor is off, the OSD button operations will be locked / unlocked.

<Power / OSD>

If you keep pressing the MENU Button on the monitor for 10 seconds when the Menu is not displayed, the Power / OSD button operations will be locked / unlocked.

Function Correlation Matrix

\square	Selected item Picture Adjust						Image A	Adjust	Set	up Menu						
					A du c		Blue	Black			Direct			1 1	FrooSync	
Active	Active item			Brightness	Overdrive	Adv. Contrast	Eco	Light Reducer	Tuner	MBR	Gamma	Drive Mode	Full / Aspect	Dot by dot / 17-34inch	HDR	FreeSync Premium
<u> </u>	Adv. Co	ontrast	_	_	✓		_	_	~	-	~	~	~	~	-	_
Adju	Eco		~	_	~	_	$\overline{\ }$	-	~	-	~	~	✓	~	-	✓
Picture Adjust	Blue Lig	ght Reducer	~	~	~	_	_	\square	~	-	~	~	~	~	-	✓
Ë	MBR		✓	_	_	_	_	-	_		✓	~	~	~	-	_
	i-Style Color	Standard / Sport Game / FPS Game / Strategy Game / Text	_	_	_	_	_	-	_	_	~	_	~	~	-	-
ljust	00101	User Mode 1/2/3	~	✓	~	~	~	✓	~	~	~	~	~	✓	~	✓
Image Adjust	Direct Drive	On	~	✓	~	~	~	✓	~	~	~		~	- 1	~	✓
mag	Mode	Off	~	~	-	~	~	 ✓ 	~	-	~	~	~	 ✓ 	 ✓ 	-
	Video Mode	Full / Aspect	~	~	~	~	✓	 ✓ 	~	✓	~	~		✓	 ✓ 	✓
	Adjust	Dot by dot / 17-34inch	~	~	_	~	~	 ✓ 	~	-	~	_	✓	\square	 ✓ 	-
Setup Menu	HDR		_	_	✓	_	✓	-	_	_	_	~	✓	-	\square	✓
Se	FreeSy	nc Premium	✓	✓	✓	-	\checkmark	✓	✓	-	✓	\checkmark	✓	-	✓	

✓ : Available

-: Not available

STANDBY FEATURE

This product features the standby function. When activated, it automatically reduces unnecessary power consumption of the monitor when your computer is not in use.

There is a standby step the monitor takes as described below. The standby function, including any timer settings is configured by the operating system. Check your operating system manual for information on how this can be configured.

Standby Mode

When the video signal from the computer is off, the monitor enters into Standby Mode which reduces the power consumption to 0.5W or less*. The screen becomes dark, and the power indicator turns to orange. From Standby Mode, the image reappears in several seconds when either the keyboard or the mouse are touched again.



* When the "USB Standby mode" of "Setup Menu" is On.

TROUBLE SHOOTING

If the monitor fails to operate correctly, please follow the steps below for a possible solution.

- 1. Perform the adjustments described in OPERATING THE MONITOR, depending on the problem you have. If the monitor does not get a picture, skip to 2.
- 2. Consult the following items if you cannot find an appropriate adjustment item in OPERATING THE MONITOR or if the problem persists.
- If you are experiencing a problem which is not described below or you cannot correct the problem, discontinue using the monitor and contact your dealer or iiyama service center for further assistance.

Problem

.

Check

IJ	not appear.	
	(Power indicator does not light up.)	 The Power Cable is firmly seated in the socket. The Power Switch is turned ON. The AC socket is live. Please check with another piece of equipment.
	(Power indicator is blue.)	 If the blank screen saver is in active mode, touch the keyboard or the mouse. Increase the Contrast and/or Brightness. The computer is ON. The Signal Cable is properly connected. The signal timing of the computer is within the specification of the monitor.
	(Power indicator is orange.)	 If the monitor is in standby mode, touch the keyboard or the mouse. The computer is ON. The Signal Cable is properly connected. The signal timing of the computer is within the specification of the monitor.
2	The screen is not synchronized.	 The Signal Cable is properly connected. The signal timing of the computer is within the specification of the monitor.
3	The screen position is not in the center.	□ The signal timing of the computer is within the specification of the monitor.

④ The screen is too □ The video output level of the computer is within the specification of the bright or too dark. monitor.

Problem Check (5) The screen is shaking. The power voltage is within the specification of the monitor. The signal timing of the computer is within the specification of the monitor. (6) No sound. The audio equipment (computer etc.) is ON. The Volume is turned up. The Mute is OFF. The audio output level of the audio equipment is within the specification of the monitor.

The sound is too □ The audio output level of the audio equipment is within the specification loud or too quiet.
 of the monitor.

RECYCLING INFORMATION

For better environment protection please don't dispose your monitor. Please visit our web site: www.iiyama.com for monitor recycling.

APPENDIX

Design and specifications are subject to change without prior notice.

SPECIFICATIONS

Size Category		43"					
	Panel technology	VA					
	Size	Diagonal: 42.5" (108cm)					
1.05	Pixel pitch	0.245mm H × 0.245mm V					
LCD Panel	Brightness	550cd/m ² (Typical)					
	Contrast ratio	4000 : 1 (Typical), Advanced Contrast Function Available					
	Viewable angle	Right / Left: 89° each, Up / Down: 89° each (Typical)					
	MPRT	0.4ms					
Display C	Colors	Approx. 1.07 Billion					
Sync Fre	quency	HDMI: Horizontal: 30.0-135.0kHz, Vertical: 30-120Hz DisplayPort (FreeSync: Off): Horizontal: 30.0-330.0kHz, Vertical: 48-144Hz DisplayPort (FreeSync: On): Horizontal: 30.0-275.0kHz, Vertical: 48-120Hz					
Native R	esolution	3840 × 2160, 8.2 MegaPixels					
Support r	Support max. resolution HDMI: 3840 × 2160 60Hz 2560 × 1440 120Hz DisplayPort (FreeSync: Off): 3840 × 2160 144Hz DisplayPort (FreeSync: On): 3840 × 2160 120Hz						
Input Cor	nnector	HDMI × 2, DisplayPort × 2					
Input Vid	Input Video Signal HDMI, DisplayPort						
USB Star	ndard	USB3.0 (DC5V, 900mA) × 1, USB3.0 (DC5V, 1.5A) × 1, USB2.0 (DC5V, 500mA) × 2					
	of USB Ports	1 Upstream: Series B					
Connecto		4 Downstream: Series A					
· ·	ne Connector	ø 3.5mm mini jack (Stereo)					
Speakers		7W × 2 (Stereo speakers)					
Power So	n Screen Size	941.18mm W × 529.42mm H / 37.1" W × 20.8" H					
	onsumption * ¹	100-240VAC, 50/60Hz, 1.5A 85W typical (45W typical in factory configuration) Standby mode: 0.5W maximum, Off mode: 0.3W maximum					
Dimensio Net Weig		977.5 × 621.5 × 251.0mm / 38.5 × 24.5 × 9.9" (W×H×D) 14.9kg / 32.8lbs					
Tilt Angle	•	Upward: 10°, Downward: 2°					
Environm Consider		Operating:Temperature Humidity5 to 35°C / 41 to 95°F 10 to 80% (No condensation)Storage:Temperature Humidity-20 to 60°C / -4 to 140°F 5 to 85% (No condensation)					
Approval	s	CE, UKCA, TÜV-Bauart, EAC, VCCI, PSE					

NOTE *¹ When the "USB Standby mode" of "Setup Menu" is On.

*² Protruding portions are not included.

DIMENSIONS



COMPLIANT TIMING

Video Mode	Horizontal Frequency	Vertical Frequency	Dot Clock	
800 × 600	37.879kHz	60.317Hz	40.000MHz	
000 × 000	46.875kHz	75.000Hz	49.500MHz	
1024 × 768	48.363kHz	60.004Hz	65.000MHz	
1024 × 700	60.023kHz	75.029Hz	78.750MHz	
1280 × 1024	63.981kHz	60.020Hz	108.000MHz	
1200 * 1024	79.976kHz	75.025Hz	135.000MHz	
1680 × 1050	65.290kHz	60.000Hz	146.250MHz	
1920 × 1080	67.500kHz	60.000Hz	148.500MHz	
1920 × 1060	137.280kHz	120.000Hz	285.542MHz	
2560 × 1440	183.000kHz	120.000Hz	497.760MHz	
	67.500kHz	30.000Hz	297.000MHz	*1
	135.000kHz	60.000Hz	594.000MHz	
2940×2160	179.440kHz	80.000Hz	703.405MHz	*2
3840 × 2160	226.500kHz	100.000Hz	887.880MHz	*2
	274.440kHz	120.000Hz	1075.805MHz	*2
	329.330kHz	144.000Hz	1290.966MHz	*2,3

NOTE *¹ Available for HDMI input only.

*² Available for DisplayPort input only.

*³ Available only when the FreeSync function is Off.

Console	1080p (1920×1080)	1440p (2560×1440)	2160p (3840×2160)
PS5	60 / 120Hz	_	60Hz
Xbox Series X/S	60 / 120Hz	120Hz	60Hz