FUJITSU

Data Sheet FUJITSU Server PRIMERGY TX1330 M4 Tower Server

Highly expandable advanced server for typical SME business requirements

FUJITSU Server PRIMERGY will give you the servers you need to power any workload and changing business requirements. As business processes expand so does the need for applications. Each has its own resource footprint, so you need a way to optimize your computing to better serve your users. PRIMERGY systems will help you match your computing capabilities to your business priorities with our complete portfolio of expandable PRIMERGY tower servers for remote and branch offices, versatile rack-mount servers as well as hyper-converged multi-node servers. They convince by business proven quality with a wide range of innovations, highest efficiency cutting operational cost and complexity, provide more agility in daily operations, and integrate seamlessly to let help you concentrate on core business functions.

Perfect for small and medium businesses as well as branch offices, FUJITSU Server PRIMERGY TX tower systems are robust and cost-efficient servers by providing rock solid reliability. Additionally they are characterized by simple IT operations, low power consumption and quiet operation so that they can be handled by non-technically trained staff and can be used in standard office environments. By the way: Almost all PRIMERGY TX servers can be rack-mounted to offer best flexibility.

PRIMERGY TX1330 M4

The FUJITSU Server PRIMERGY TX1330 M4 is an advanced technology, highly expandable and robust mono-socket server versatile enough for use across multiple industries plus classic small and medium-sized enterprise requirements. It features the latest in processing and memory for appropriately sized workloads such as file/ print, web, ERP/CRM, email, business specific applications plus use cases with high storage requirement such as centralized storage and databases. The mono-socket tower system features

the latest powerful Intel® Xeon® E-2100 product family processors with up to 64 GB DDR4 memory at 2,666 MT/s, to boost application performance. The server is designed for high levels of secure expandability with up to 24x 2.5-inch hot-plug storage devices (3.5-inch drive configurations are also available) along with 4x ultra-fast NVMe devices (up to 16x 2.5-inch devices can be fielded alongside), advanced RAID controllers (up to 4/8GB cache) and data back-up options, making it ideal for consolidating and managing large datasets. Up to 4 PCIe slots are available to add both RAID cards as well as networking options (such as 10/25 Gb controllers). High availability features such as the optional Fujitsu Battery Backup Unit, high-efficiency (94%), redundant power supplies or redundant fans ease operator concerns and provide investment protection. The aesthetic design makes it suitable for deployment in public areas such as showrooms, retail premises or offices. New generation technologies include M.2 modules for efficient OS installation along with Dual microSD capability for VMware ESXi, plus the latest USB 3.1 Gen 2 ports. Furthermore, advanced server management is available via the iRMC S5, which allows remote management capabilities, and the Fujitsu ServerView[®] Suite, which provides administrators with comprehensive support during server installation, deployment and administration.











Features & Benefits

Main Features

Advanced technology for workload-versatile performance

■ Workload versatile with the combination of the latest Intel® Xeon® E-2100 processors, and up to 64GB DDR4 memory (4 DIMMs) at 2,666 MT/s. Affordable Core™ i3 and Pentium® processors are also available.

High storage and networking expandability

Server supports up to 4x NVMe devices plus either 8x3.5-inch storage devices or 16x2.5-inch devices. Maximal capacity with standard drives is up to 12x3.5-inch devices, or up to 24x2.5-inch devices. It also supports Fujitsu's powerful RAID controllers (including SAS 3.0, 4/8 GB cache). Backup options include LTO and RDX. Security optimization includes TPM 2.0 support plus Fujitsu's secure 3-way lock for server access. Server also features redundant (2x1GbE) LAN as standard plus advanced networking options (10/25Gb Ethernet, Fiber Channel controllers).

Future ready, today

4x PCIe Gen3 slots for expansion and deployment flexibility via rack upgrade capability.

Technology update for enhanced utilization

Support of 2x M.2 modules: 1x SATA; 1x NVMe/SATA and Dual micro-SD modules for efficient boot requirements. New 3.1 Gen2 USB ports (2x 3.1 Gen2 plus 2x 3.1 Gen1, 4x 2.0, Internal 2x 3.1 Gen1) for enhanced connectivity.

High reliability for investment protection

High efficiency 450W power supplies (94% efficiency) are available with both hot-plug capability and redundancy. Fujitsu Battery Backup Unit an optional Internal UPS in modular PSU form-factor, 5 years lifetime, fully integrated.

Expanded deployment capability

Optimized air flow and Fujitsu's Cool-safe

 Advanced Thermal Design technology.

Full server management features and easy serviceability

Comprehensive software management suite and easy to service design to reduce your IT administrator's burden.

Benefits

- The server compute and memory can be optimized for most appropriately sized standard workloads across industries. Intel® Xeon® E-2100 processors offer higher performance for more demanding compute needs. The workloads can range from appropriately sized, individual to virtualized multi-app environments including workloads such as File/Print, Email, ERP/ CRM, Messaging, Centralized data storage and industry specific applications.
- NVMe drives offer ultra-fast storage for low-latency applications, while the server's huge storage capacity offers secure, costeffective capability to consolidate and manage large datasets, combined with growth potential. Redundant LAN offers reliable data connectivity out of the box. Advanced options such as 10/25 GbE or Fiber Channel networking cards offer high data transfer for demanding environments, e.g. virtualized environments or centralized storage.
- PCI expansion slots permit timely, cost-effective upgrades in line with your business growth. Upgrade the server with a graphics card, or Fujitsu RAID controllers for reliable data storage or advanced networking options for seamless data transmission. Similarly, a rack kit provides investment protection. As their business grows, customers can deploy multiple PRIMERGY TX1330 M4 servers in a rack.
- For effective boot options choose from amongst cost-effective and reliable mirrored SATA modules or deploy high-speed NVMe devices, while Dual microSD modules support mirrored VMware ESXi boot. Technology update with new high data rate USB is good for latest generation peripheral devices.
- Good for the environment, and your business the high efficiency, redundant power supplies offer enhanced reliability and lower energy expenditure. The Battery Backup Unit protects your valuable investment by supporting safe power down and expanded server operation time in case of power loss.
- Expanded range of operation (5 °C to 45 °C) and also reduces noise emissions, making the server suitable for deployment in public areas.
- Simplified server management via a comprehensive software suite which can include the iRMC S5 and the Fujitsu ServerView suite, which includes tools for installation and deployment, permanent status monitoring and control. Server also features a screw-less chassis with hot-plug 2.5-inch devices, hot-plug PSUs and "Easy Rails" for 3.5-inch storage disks for efficient access to critical components.

Technical details

PRIMERGY TX1330 M4			
Base unit	PRIMERGY TX1330 M4	PRIMERGY TX1330 M4	PRIMERGY TX1330 M4
Housing types	Tower	Tower	Rack
Power supply	Standard	Hot-plug	Hot-plug
Product Type	Mono Socket Tower Server	Mono Socket Tower Server	Mono Socket Tower Server
Mainboard			
Mainboard type	D3673		
Chipset	Intel® C246		
Processor quantity and type	1 x Intel® Xeon® E-2100 processor family / Intel® Pentium® processor / Intel® Core™ i3 processor		
Processor	Intel® Xeon® processor E-2186G (6C/12T, 3.80 GHz, up to 4.3 GHz, 2,666 MHz)		
	Intel® Xeon® processor E-2176G (6C/12T, 3.70 GHz, up to 4.3 GHz, 2,666 MHz)		
	Intel® Xeon® processor E-2174G (4C/8T, 3.80 GHz, up to 4.3 GHz, 2,666 MHz)		
	Intel® Xeon® processor E-2146G (6C/12T, 3.50 GHz, up to 4.2 GHz, 2,666 MHz)		
	Intel [®] Xeon [®] processor E-2144G	(4C/8T, 3.60 GHz, up to 4.2 GHz, 2,666 I	MHz)
	•	6C/12T, 3.30 GHz, up to 4.2 GHz, 2,666 M	
	Intel® Xeon® processor E-2134 (4C/8T, 3.50 GHz, up to 4.2 GHz, 2,666 MHz)		
	Intel® Xeon® processor E-2126G (6C/6T, 3.30 GHz, up to 4.1 GHz, 2,666 MHz)		
	Intel® Xeon® processor E-2124G (4C/4T, 3.40 GHz, up to 4.1 GHz, 2,666 MHz)		
	Intel® Xeon® processor E-2124 (4C/4T, 3.30 GHz, up to 3.9 GHz, 2,666 MHz)		
	Intel® Pentium® processor G5400 (2C/4T, 3.70 GHz, 2,666 MHz)		
	Intel® Core™ i3-8100 processor (4C/4T, 3.60 GHz, 2,400 MHz)		
Memory slots	4		
Memory slot type	DIMM (DDR4)		
Memory capacity (min max.)	4 GB - 64 GB		
Memory protection	ECC		
Memory notes	Mix and match possible; with dual channel operation better performance (2 modules with equal capacity necessa Single channel (1 module) configuration possible.		
Memory options	A GB (1 module(s) 4 GB) DDR4, unbuffered, ECC, 2,666 MHz, PC4-2666, DIMM, 1Rx8		DIMM, 1Rx8
	8 GB (1 module(s) 8 GB) DDR4, unbuffered, ECC, 2,666 MHz, PC4-2666, DIMM, 1Rx8		
	16 GB (1 module(s) 16 GB) DDR4, unbuffered, ECC, 2,666 MHz, PC4-2666, DIMM, 2Rx8		
nterfaces			
USB 2.0 ports	4 (4x external rear)		
USB 3.0 ports	4 (2x internal, 2x external front, Gen 2 ports	USB 3.0 is now known as USB 3.1 Gen 1). Server also has 2x external rear USB 3.1
Graphics (15-pin)	1 analog graphics interface derived from iRMC (up to 1600x1200 or 1920x1080 at 16bpp)		
Serial connection	1 x serial RS-232-C		
LAN / Ethernet	2 x1 Gb/s Ethernet; RJ45		
Management LAN (RJ45)	1 x dedicated management LAN port for iRMC S5 (10/100/1000 Mbit/s) Management LAN traffic can be switched to shared onboard Gbit LAN port		
Onboard or integrated Controller			
RAID controller	Optionally integrated RAID 0/1 or RAID 5/6 controller for SAS base units (occupies one PCIe slot). All hardware storage controller options are described under Components		
SATA Controller	Intel [®] C246, 2 ports used for accessible drives		
SATA controller type notes	4 port for internal SATA HDDs with RAID 0, 1, 10 for Windows and Linux;		
LAN Controller	Intel® i210 onboard 2 x 10/100/1000 Mbit/s Ethernet		
	iSCSI, PXE-Boot and WoL are sup		

Onboard or integrated Controller			
Remote management controller	Integrated Remote Management Controller (iRMC S5, 512 MB attached memory incl. graphics controller) IPMI 2.0 compatible		
Trusted Platform Module (TPM)	TPM 2.0 module (option)		
Slots			
PCI-Express 3.0 x1 (mech. x4)	1 x Full height, up to 168 mm length		
PCI-Express 3.0 x4	1 x Full height, up to 168 mm length		
PCI-Express 3.0 x8	2 x Full height, up to 240 mm length r	notched	
Slot Notes	Optional PCIe to legacy PCI adapter available. In SAS configuration 1x PCI-Express occupied by modular RAID controller.		
PCI-Express 3.0 x4	1 x notched	1 x notched	1 x notched
PCI-Express 3.0 x8	2 x notched	2 x notched	2 x notched
Drive bays			
Storage drive bays	3.5-inch or 2.5-inch hot-plug SAS/SATA		
Accessible drive bays	3 x 5.25/1.6-inch		
Notes accessible drives	all possible options described in releva	ant system configura	ator
Drive bays			
Storage drive bays	Max. 4x 3.5-inch or 8x 2.5-inch		Max. 12x 3.5-inch or 24x 2.5-inch
Accessible drive bays	3 x 5.25/1.6-inch for 1 x backup drive -	+ 1 x ODD	Accessible drive bays are not available in case of max storage drive configuration
Fan Configuration			
Number of fans	1		2
Fan configuration	1 standard fan		redundant fans
Fan notes	non redundant / non hot-plug		non hot-plug
Operating panel			
Operating buttons	On/off switch NMI button Reset button		
Status LEDs	System status (orange / yellow) Identification (blue) Hard disks access (green) Power (orange / green) At system rear side: System status (orange / yellow) Identification (blue) LAN connection (green) LAN speed (green / yellow) CSS (yellow)		
BIOS			
BIOS features	ROM based setup utility Recovery BIOS BIOS settings save and restore Local BIOS update from USB device Online update tools for main Linux ver Local and remote update via ServerVie Remote PXE boot support Remote iSCSI boot support		

Operating Systems and Virtualization S	Software	
ertified or supported operating	Windows Server 2019 Datacenter	
systems and virtualization software	Windows Server 2019 Standard	
	Windows Server 2019 Essentials	
	Windows Server Datacenter, version 1809	
	Windows Server Standard, version 1809	
	Hyper-V Server 2016 Windows Server 2016 Datacenter Windows Server 2016 Standard Windows Server 2016 Essentials Windows Storage Server 2016 Standard Windows Storage Server 2016 Standard Windows Server Datacenter, version 1709 VMware vSphere™ 6.5	
	VMware vSphere™ 6.7	
	SUSE® Linux Enterprise Server 12	
	Red Hat® Enterprise Linux 7	
	Univention Corporate Server 4	
perating system release link	http://docs.ts.fujitsu.com/dl.aspx?id=d4ebd846-aa0c-478b-8f58-4cfbf3230473	
)perating system notes	Support of other Linux derivatives on demand	
erver Management tandard	ServerView Suite (Deploy)	
	ServerView Installation Manager ServerView Scripting Toolkit ServerView Suite (Control) ServerView Operations Manager (incl. PDA and ASR & R) ServerView Agents and CIM provider ServerView Agentless Management ServerView System Monitor SVOM- Event Manager ServerView RAID Manager ServerView RAID Manager Power Monitor (monitoring the Power Consumption) Power Monitor (monitoring the Power Consumption) Power Management (iRMC) Storage Management (iRMC) Storage Management (server) with SVOM/SV-RAID ServerView Suite (Maintain) iRMC S5 (Remote Management) System Update Manager (BIOS, Firmware, Windows Drives and SV Agents) Performance management (SVOM) Asset Management Primecollect Customer Self Service Online Diagnostics ServerView Suite - Integrate Integration packs for Microsoft System Center, VMware vCenter, VMware vRealize, Nagios, and HP SIM	
Option	ServerView Suite (Maintain) ServerView eLCM iRMC Advanced Pack incl. Advanced Video Redirection (AVR), video capturing and Virtual Media	
imensions / Weight		
oor-stand (W x D x H)	177 x 560 x 455 mm	
ack (W x D x H)	483 x 495 x 175 mm	
imension notes	Floorstand Width 306 mm with tilt protection; depth measured excludes handles on redundant PSU. Rack depth excludes handles of redundant PSU and rack front.	
Iounting Depth Rack	543 mm	
leight Unit Rack	4 U	
Veight	Rack: 13 kg - 25 kg; Tower: 15kg - 28 kg	
Veight notes	Actual weight may vary depending on configuration	

Dimensions / Weight		
Rack integration kit	Rack integration kit can be ordered as option	
Environment		
Operating ambient temperature	5 - 45 °C (41 - 113 °F)	
Operating temperature note	Cool-safe® Advanced Thermal Design (above 35 °C or below 10 °C) depending on configuration. For detailed information see relevant system configurator.	
Operating relative humidity	10 - 85 % (non condensing)	
Operating environment	FTS 04230 – Guideline for Data Center (installation specification)	
Operating environment link	http://docs.ts.fujitsu.com/dl.aspx?id=e4813edf-4a27-461a-8184-983092c12dbe	
Sound pressure (LpAm)	SATA: 23 dB(A) idle mode/ 23 dB(A) operation mode; SAS: 33 dB(A) idle mode/ 37 dB(A) operation mode	
ound power (LWAd; 1B = 10dB)	SATA: 4.1 B idle mode/ 4.1 B operation mode ; SAS: 4.8 B idle mode/ 5.2 B operation mode	
Noise notes	Noise emissions depend on operation modes, system configuration and ambient temperature.	
Electrical values		
Power supply configuration	1 x standard, 1 x hot-plug, 2 x hot-plug redundant, 1 x hot-plug + 1 x Fujitsu FJBU internal battery backup unit (depending on Model)	
Hot-plug power supply redundancy	Optional	
Active power (max. configuration)	231 W	
Apparent power (max. configuration)	235 VA	
leat emission (max. configuration)	831.6 kJ/h (788.2 BTU/h)	
lated current max.	5 A (100 V) / 2.5 A (240 V)	
Active power note	To estimate the power consumption of different configurations use the Power Calculator of the System Architect: http://configurator.ts.fujitsu.com/public/	
Power supply	300W standard, 90% (Gold efficiency), 100-240V, 50 / 60Hz 450W hot-plug, 94% (Platinum efficiency), 100-240V, 50 / 60Hz	
Power supply notes	Power Safeguard adapts system performance in case the power requirements exceeds supply limits.	
Battery backup	Fujitsu Battery Unit 380W, 12V (as option)	
Compliance		
Global	CB RoHS (Substance limitations in accordance with global RoHS regulations) WEEE (Waste electrical and electronical equipment)	
Germany	2D	
Europe	CE	
USA/Canada	CSA us ULc/us FCC Class A	
apan	VCCI:V3 Class A + JIS 61000-3-2	
lussia	GOST-R	
outh Korea	KC	
hina	(((
Australia/New Zealand	C-Tick	
Faiwan 🛛	BSMI	
Compliance link	https://sp.ts.fujitsu.com/sites/certificates	
Compliance notes	* Warning: This is a class A product. In a domestic environment this product may cause radio interference in which case the u may be required to take adequate measures.	

Components

Backup Drives	LTO6HH Ultrium, 2,500 GB, 160 MB/s, half height, SAS 6Gb/s
	LTO7HH Ultrium, 2,500 GB, 300 MB/s, half height, SAS 6Gb/s
	RDX Drive, 320 GB, 500 GB, 1 TB , 25 MB/s, half height, USB 3.0

Optical drives	Blu-ray Disc™ Triple Writer, (6x BD-RW, 8x DVD, 24x CD), ultraslim, SATA I	
	DVD-ROM, (16xDVD; 48xCD), half height, SATA I	
	DVD Super Multi, (16xDVD, 8xDVD+RW 6xDVD-RW, 12xDVD-RAM; 48xCD, 32xCD-RW), half height, SATA I	
	DVD Super Multi ultra slim , (8x DVD; 24x CD), ultraslim, SATA I	
Hard disk drives	HDD SATA, 6 Gb/s, 500 GB, 7,200 rpm, 512e, hot-plug, 3.5-inch, economic	
	HDD SATA, 6 Gb/s, 12 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical	
	HDD SATA, 6 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical	
	HDD SATA, 6 Gb/s, 4 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical	
	HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical	
	HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical	
	HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical	
	HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical	
	HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical	
	HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, economic	
	HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical	
Hard disk drives	HDD SAS, 12 Gb/s, 900 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise	
	HDD SAS, 12 Gb/s, 900 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise	
	HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise	
	HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise	
	HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise	
	HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise	
	HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise	
	HDD SAS, 12 Gb/s, 600 GB , 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED	
	HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise	
	HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise	
	HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise	
	HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED	
	HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise	
	HDD SAS, 12 Gb/s, 12 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED	
	HDD SAS, 12 Gb/s, 12 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical	
	HDD SAS, 12 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED	
	HDD SAS, 12 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical	
	HDD SAS, 12 Gb/s, 4 TB, 7,200 rpm, hot-plug, 3.5-inch, business critical	
	HDD SAS, 12 Gb/s, 2.4 TB, 10,000 rpm, 512e, hot-plug, 3.5-inch, enterprise	
	HDD SAS, 12 Gb/s, 2.4 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise, SED	
	HDD SAS, 12 Gb/s, 2.4 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise	
	HDD SAS, 12 Gb/s, 2 TB, 7,200 rpm, hot-plug, 3.5-inch, business critical	
	HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 3.5-inch, enterprise	
	HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise, SED	
	HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise	
	HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, hot-plug, 2.5-inch, enterprise	
	HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise	
	HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise	
	HDD SAS, 12 Gb/s, 1.2 TB , 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED	

Solid-State-Drive	SSD SATA, 6 Gb/s, 960 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 960 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)		
	SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)		
	SSD SATA, 6 Gb/s, 480 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 480 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)		
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.3 DWPD (Drive Writes Per Day for 5 years)		
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)		
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3.3 DWPD (Drive Writes Per Day for 5 years)		
	SSD SATA, 6 Gb/s, 240 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1.4 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 240 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1.4 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)		
	SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.1 DWPD (Drive Writes Per Day for 5 years)		
	SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)		
	SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3.1 DWPD (Drive Writes Per Day for 5 years)		
	SSD SATA, 6 Gb/s, 7.68 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.5 DWPD (Drive Writes Per Day for 5 years)		
	SSD SATA, 6 Gb/s, 7.68 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.5 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 3.84 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1.0 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 3.84 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1.0 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 3.84 TB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)		
	SSD SATA, 6 Gb/s, 3.84 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)		
	SSD SATA, 6 Gb/s, 1.92 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)		
	SSD SATA, 6 Gb/s, 1.92 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)		
	SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)		
	SSD M.2 SATA, 6 Gb/s, 480 GB, non hot plug, enterprise, 1.4 DWPD (Drive Writes Per Day for 5 years) SSD M.2 SATA, 6 Gb/s, 240 GB, non hot plug, enterprise, 1.4 DWPD (Drive Writes Per Day for 5 years)		
PCIe SSD & SATA DOM SSD	PCle-SSD SFF, 4 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 0.6 DWPD (Drive Writes Per Day for 5 years)		
	PCIe-SSD SFF, 2 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 0.6 DWPD (Drive Writes Per Day for 5 years)		
	PCIe-SSD SFF, 1 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 1 DWPD (Drive Writes Per Day for 5 years)		
	Dual microSD 64GB Enterprise		
CSI / SAS Controller	Fujitsu PSAS CP400i SAS Ctrl. 12 Gbit/s 8 ports int. PCle 3.0 x8		
RAID Controller	Fujitsu PRAID EP580i FH, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, NVMe-PCIe 8 Gbit/s, 16 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 8 GB, Optional FBU based on LSI SAS3516		
	Fujitsu PRAID EP540i FH, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, NVMe-PCIe 8 Gbit/s, 16 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 4 GB, Optional FBU based on LSI SAS3516		
	Fujitsu PRAID EP520i FH, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, NVMe-PCIe 8 Gbit/s, 8 Gbit/s 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3516		
	Fujitsu PRAID EP420i, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3108		
	Fujitsu PRAID EP420i for SafeStore, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3108		
	Fujitsu PRAID EP400i, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 1 GB, Optional FBU based on LSI SAS3108		
	Fujitsu PRAID CP400i, RAID Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 1E, 10, 5, 50, No FBU support		

Fibre Channel controller	Fibre Channel Host Bus Adapter 1 x 32 Gbit/s Cavium QLE2740 MMF LC-style		
	Fibre Channel Host Bus Adapter 2 x 32 Gbit/s Cavium QLE2742 MMF LC-style		
	Fibre Channel Host Bus Adapter 1 x 32 Gbit/s Emulex LPe32000-M6-F MMF LC-style		
	Fibre Channel Host Bus Adapter 2 x 32 Gbit/s Emulex LPe32002-M6-F MMF LC-style		
	Fibre Channel Host Bus Adapter 1 x 16 Gbit/s Qlogic QLE2690 LC-style		
	Fibre Channel Host Bus Adapter 2 x 16 Gbit/s Qlogic QLE2692 LC-style		
	Fibre Channel Host Bus Adapter 1 x 16 Gbit/s Emulex LPe31000-M6-F MMF LC-style		
	Fibre Channel Host Bus Adapter 2 x 16 Gbit/s Emulex LPe31002-M6-F MMF LC-style		
Communication, Network	Converged Network Adapter 2 x 10 Gbit/s / 25 Gbit/s PCIe 3.0 x8 SFP28 (Cavium)		
	Ethernet Ctrl. 2 x 10 Gbit/s ; 1 Gbit/s PCIe 3.0 x8 RJ45 (Cavium)		
	Ethernet Ctrl. 2 x 10 Gbit/s ; 1 Gbit/s PCIe 3.0 x8 RJ45 (Intel®)		
	Ethernet Ctrl. 2 x 10 Gbit/s ; 1 Gbit/s PCIe 3.0 x8 SFP+ (Cavium)		
	Ethernet Ctrl. 2 x 10 Gbit/s / 25 Gbit/s PCIe 3.0 x8 SFP28 (Cavium)		
	Ethernet Ctrl. 2 x 10 Gbit/s / 25 Gbit/s PCIe 3.0 x8 SFP28 (Intel®)		
	Ethernet Ctrl. 2 x 10 Gbit/s / 25 Gbit/s PCIe 3.0 x8 SFP28 (Mellanox)		
	Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 SFP+ (Intel®)		
	Ethernet Ctrl. 2 x 1 Gbit/s PCIe 2.1 x4 RJ45 (Intel®)		
	Ethernet Ctrl. 4 x 10 Gbit/s ; 1 Gbit/s PCIe 3.0 x8 RJ45 (Intel®)		
	Ethernet Ctrl. 4 x 10 Gbit/s PCIe 3.0 x8 SFP+ (Intel®)		
	Ethernet Ctrl. 4 x 1 Gbit/s PCIe 2.1 x4 RJ45 (Intel®)		
Graphics	NVIDIA® Quadro® P400 , 2 GB, PCIe x16, 3 x miniDP		
Rack infrastructure	Rack Mount Kit		
	Cable Management for 19-inch DataCenter / PRIMECENTER Racks		
	Cable Arm 2U for PRIMECENTER- and 3rd-party racks		
Warranty			
Warranty period	1 year		
Warranty type	Onsite warranty		
Warranty Terms & Conditions Product Related Services - the per	http://support.ts.fujitsu.com/warranty/Index.asp?LNG=COM r <mark>fect extension</mark>		
Support Pack Options	Globally available in major business areas: 9x5, Next Business Day Onsite Response Time 9x5, 4h Onsite Response Time (depending on country)		
	24x7, 4h Onsite Response Time (depending on country)		
Recommended Service	24x7, Onsite Response Time: 4h - For locations outside of EMEIA please contact your local Fujitsu partner.		
Service Lifecycle	5 years after end of product life		
Service Weblink	http://www.fujitsu.com/fts/services		

More information

Fujitsu products, solutions & services

In addition to FUJITSU Server PRIMERGY TX1330 M4, Fujitsu provides a range of platform solutions. They combine reliable Fujitsu products with the best in services, know-how and worldwide partnerships.

Fujitsu Portfolio

Built on industry standards, Fujitsu offers a full portfolio of IT hardware and software products, services, solutions and cloud offering, ranging from clients to datacenter solutions and includes the broad stack of Business Solutions, as well as the full stack of Cloud offerings. This allows customers to select from alternative sourcing and delivery models to increase their business agility and to improve their IT operation's reliability.

Computing Products

www.fujitsu.com/global/products/computing/

Software

www.fujitsu.com/software/

More information

Learn more about FUJITSU Server PRIMERGY TX1330 M4, please contact your Fujitsu sales representative or Fujitsu Business partner, or visit our website.

http://www.fujitsu.com/primergy

Fujitsu green policy innovation

Fujitsu Green Policy Innovation is our worldwide project for reducing burdens on the environment.

Using our global know-how, we aim to contribute to the creation of a sustainable environment for future generations through IT. Please find further information at http://www. fujitsu.com/global/about/environment



Copyrights

All rights reserved, including intellectual property rights. Designations may be trademarks and/or copyrights of the respective owner, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see http:// www.fujitsu.com/fts/resources/navigation/ terms-of-use.html Copyright 2019 FUJITSU LIMITED

Disclaimer

Technical data is subject to modification and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective owner, the use of which by third parties for their own purposes may infringe the rights of such owner.

Contact FUJITSU LIMITED

Website: www.fujitsu.com 2019-02-21 WW-EN All rights reserved, including intellectual property rights. Designations may be trademarks and/or copyrights of the respective owner, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see http://www.fujitsu.com/fts/resources/navigation/terms-of-use.html Copyright 2019 FUJITSU LIMITED