Insight Managed Gigabit Ethernet Smart Cloud FlexPoE Switches

Data Sheet

GC108P, GC108PP



Experience the most versatile and easy to manage Advanced Smart switches in the market

As a leading provider of network equipment for SMBs, NETGEAR® understands the importance of reliable and high performance networks. With the growth of virtualization, cloud-based services and applications like VoIP, video streaming and IP surveillance, SMB networks need to extend beyond simple reliability to simpler management and remote monitoring to ensure your network is "always up". NETGEAR also understands that small business owners shouldn't have to understand networking and IT; they need a network that's easy-to-setup and is reliable, so they can focus on their business, not their network. To that end, NETGEAR is introducing our most versatile and easy-to-manage switches ever, NETGEAR Insight Managed Smart Cloud switches, now with NETGEAR's exclusive FlexPoE.

Insight Managed Smart Cloud Switches are the first switches from NETGEAR with anywhere configuration and management. Using either the NETGEAR Insight app on your mobile device or tablet, or the Insight Cloud Portal from your PC, Mac, or tablet, you can quickly discover, setup, monitor and manage your Smart Cloud Switches from anywhere in the world! With their remote cloud manageability, sleek design silent or whisper-quiet operation, they are the most versatile switches in the market for any environment. Whether at home, out of the office or on a business trip, you can still manage and monitor your network as if you were right there.

Outstanding power flexibility with NETGEAR's exclusive FlexPoE



Powered by the industry's first flexible PoE+ integrated technology, you can increase or decrease the PoE budget by simply purchasing a new NETGEAR FlexPoE power supply, effectively future proofing small business networks and budgets. With NETGEAR's exclusive FlexPoE, these two switches help businesses cost effectively increase their power budget to expand their network as needed.

All ports support PoE/PoE+ up to 30W per port, which makes them the perfect switches for deploying Wireless APs, Pan/Tilt/Zoom and fixed IP Cameras, VoIP Phones, access-limited security door locks or any other IoT PoE-powered devices. And with Insight remote/cloud management, you can enable/ disable/reboot PoE on a per port basis or setup PoE schedules for the most efficient energy usage as needed.

Both models have 8 copper Gigabit Ethernet PoE+ ports featuring NETGEAR FlexPoE power. The GC108P ships with a strong 64Ws of PoE budget, while the GC108PP features an astounding 126W of PoE power budget. Should you need more power in the future, rather than replace the entire switch, with NETGEAR FlexPoE you can just purchase the optional NETGEAR FlexPoE EPS130W Power Adapter, which will boost the PoE budget of your GC108P to the same 126W as the GC108PP model.

Innovative features for the most versatile and easy-to-manage switches in the market

Your network. Anytime. Anywhere.

The NETGEAR Inisght Managed Smart Cloud Switches fundamentally change the way you think of networks and IT. Using the NETGEAR Insight app with Insight Managed Smart Cloud Switches and Wireless Access Points provides:

- Instant in-app discovery & set-up
- · Local or remote configuration and monitoring from your mobile device. PC. Mac or tablet
- · Centralized network configuration polices with auto-join and configure (zero-touch provisioning)
- · Multi-site/remote network management and monitoring with single pane-of-glass view
- · Multi-switch/multi-port concurrent configuration using the Port Config Wizard

Remote monitoring and management from the palm of your hand!

With the NETGEAR Insight app, you can setup, manage, and monitor your networks from anywhere, anytime, from the palm of your hand on your phone or tablet! Or, for a larger screen experience, you can use the Insight Cloud Portal from your PC, Mac, or tablet web browser.

Network-centric configuration and management

NETGEAR Insight Managed Switches and Wireless Access Points using the NETGEAR Insight app allow for cross-device automated configuration of VLANs, QoS, ACLs, and LAGs. Auto-join and configure (zero-touch privisioning) allows for additional devices added

Fully-integrated cloud-manageable devices

NETGEAR Insight Managed switches are fully-integrated, cloudmanageable, plug-and-play devices. Just connect to your network and without any setup, they're passing traffic. For configuration setup, management, and monitoring, you can use the Insight mobile app on your mobile device or the Insight Cloud Portal from your PC, Mac, or tablet web browser. No additional cloud controller, appliance, network manager, or on-premise cloud server necessary.

Clean, sleek silent (or whisper-quiet) designs

Insight Managed switches have a modern, clean design, with at-aglance power/cloud and and PoE max LEDs for quick status monitoring. Additionally, on-port LEDs for link/activity and PoE power allow for port-specific connectivity monitoring. Both models are fanless for silent, anywhere deployment in noise-sensitive environments, and include a wall-mount kit for flexible placement.

Build a future-proof network with NETGEAR Insight Managed Switches

- · Extensive L2+/L3 Lite switching features including static routing
- Comprehensive IPv6 management, QoS and ACL support, ensuring investment protection and a smooth migration to IPv6based networking
- · Advanced QoS with IPv4/IPv6 ingress traffic filtering (ACLs) and

- · Dynamic VLAN assignment for easy user authentication and location-independent access to network
- Up to 126W PoE power, with the flexibility to supply power-hungry devices such as 11ac and 11ax Wireless APs, VoIP voice and video phones, security/surveillance cameras including PTZ, and other IoT devices
- · Advanced per-port PoE controls (set specific power budget per port in addition to automatic class-defined) and PoE scheduling
- · Interchangeable external power adapter allows you to increase (or decrease) your PoE Budget as needed with NETGEAR FlexPoE power

NETGEAR quality and reliability

- Industry-leading 5-year Limited Hardware Warranty*
- · Minimal down-time with Next-Business-Day Replacement Warranty
- · Get deployment assistance with 90-days Free Advanced Technical Support**







[§] NETGEAR FlexPoE power – interchangable external power adapter allows for increasing or decreasing your PoE budget at any time with optional NETGEAR FlexPoE power adapters.

Insight Managed Gigabit Ethernet Smart Cloud FlexPoE Switches

Data Sheet

GC108P, GC108PP

Hardware at a Glance

| | FRONT | | | | | REAR | | |
|---------------|------------------------------------|-------------------------|------------------------------|------------------------------------|--------------------------------------|--|---------------------------------|---------------------|
| Model Name | Form- Factor | LEDs (System) | LEDs (Per Port) | 100M/1G Copper (RJ-45) Ports | PoE/PoE+ 802.3af/802.3at Ports | PoE Budget/PA (external PA) | PA Supported & PoE Budget | Power Supply |
| GC108P | Desktop, Wallmount (fanless) | Power/Cloud, PoE Max | Speed/Link/ Activity, PoE | 8 | 8 PoE+ | PoE Budget: 64W [§] PA: 67.5W | PA: 67.5W/130W PoE: 64W/126W | External Adapter |
| GC108PP | Desktop, Wallmount (fanless) | Power/Cloud, PoE Max | Speed/Link/ Activity, PoE | 8 | 8 PoE+ | PoE Budget: 126W PA: 130W | PA 67.5W/130W PoE: 64W/126W | External Adapter |



NETGEAR

O/A

GC108PP

1 2 3 4 5 6 7 8

GC108P: 8-Port Gigabit Ethernet PoE+ Insight Managed Smart Cloud Switch w/FlexPoE Power

- 8 x 1000BASE-T Copper PoE+ ports supporting 1G/100M speeds
- 64W§ FlexPoE power budget budget (fanless, OdB)
- Fanless (OdB), wall-mountable, Kensington lock slot

GC108P: 8-Port Gigabit Ethernet Hi-Power PoE+ Insight Managed Smart Cloud Switch w/FlexPoE Power

- 8 x 1000BASE-T Copper PoE+ ports supporting 1G/100M speeds
- 126W FlexPoE power budget budget (fanless, OdB)
- · Fanless (OdB), wall-mountable, Kensington lock slot

Software at a Glance

| MANAGEMENT | | | | LAY | ER 2+ / LAYE | R 3 LITE FEATU | RES | | |
|--|--|-----------------------------|-------------------------------------|--|--------------------------|--------------------------------|--|--|---------------------------|
| Device Management | Network-wide Management | IPv4/IPv6 ACL and QoS | IPv4/IPv6 Multicast Filtering | VLANs | Auto-VoIP, Auto-Video | Convergence | Link Aggregation/ Port Trunking | Jumbo Frame Support | IPv4 Static Routing |
| NETGEAR Insight mobile app or Insight Cloud Portal for local/remote/ anywhere management from your mobile device, PC, Mac, or tablet Local web browser-based management GUI IPv4 & IPv6 management | Centralized net- work configura- tion (policies) Auto-join & configure (zero-touch provisioning) Mulit-site, multi-network single pane-of- glass view Multi-switch/ multi-port concurrent configuration | L2, L3, L4 Ingress | IGMP and MLD Snooping | Static, Dynamic, Voice, Video, MAC, Protocol- based, and Private | Yes | LLDP-MED, RADIUS, 802.1X | LACP and Manual Static LAGs (up to 8 LAGs with max 8 members) | Yes (up to 10,000 packet size) | Yes |

Performance at a Glance

| Model Name | CPU & Memory | Fabric (Full- duplex) | Latency (64-byte Packet) | Packet Buffer | Packet Forwarding Rate (64-byte) | ACLs | MAC Address Table ARP/NDP Table VLANs | Static Routes (IPv4) | Priority Queues | Multicast IGMP Groups |
|-------------------|--|-----------------------------|--------------------------------|------------------|--|-----------------|--|-------------------------|--------------------|-----------------------------|
| GC108P GC108PP | 500MHz Single Core, 128MB RAM, 32MB SPI FLASH | 16Gbps line-rate | 3.460 µs | 512 KB | 11.9 Mfps | 100 (shared) | 8K MAC (dynamic) 512 ARP / 512 NDP 64 VLANs | 32 | 8 (WRR) | 256 |

[§] NETGEAR FlexPoE power - interchangable external power adapter allows for increasing or decreasing your PoE budget at any time with optional NETGEAR FlexPoE power adapters.

Insight Managed Gigabit Ethernet Smart Cloud FlexPoE Switches

Data Sheet

GC108P, GC108PP

Features and Benefits

| Hardware Features | Benefits |
|--|--|
| Fully-integrated Cloud-manageable Devices | Require no additional hardware (cloud keys, network portals, local servers, VPN or proxy appliances etc) to directly connect to the cloud and allow remote management. No additional hardware, no software or server to setup; nothing. Just connect and go. |
| 1000BASE-T Copper Ethernet PoE+ ports | Support high-density VoIP, Surveillance and Wi-Fi AP deployments, scalable for future growth. Never face the risk of running out of PoE ports or PoE power budget. |
| NETGEAR FlexPoE Power | Interchangeable external power adapter allows you to increase (or decrease) your PoE budget as needed by purchasing an optional NETGEAR FlexPoE power adapter. |
| Power/Cloud LED | Quickly confirm switch has power and is connected to the cloud/internet. |
| Fanless & Silent | Fanless design for silent operation; great for deployment in noise-sensitive environments. |
| Energy Efficient Ethernet (IEEE 802.3az) | Maximum power reduction for ongoing operation cost savings. |
| Desktop or Wall-mount | Flexible deployment on desktop, wall or other location using 75mm VESA-compliant mounts, and the included wall-mount kit. |
| Kensington Lock Slot | Prevent theft, removal, or tampering when used for desktop deployment. |

| Software Features | Benefits |
|---|--|
| Remote setup, management, and monitoring anywhere, anytime, from your mobile device, PC, Mac, or tablet | Locally or remotely setup, configure, manage, monitor or even troubleshoot your network from anywhere, anytime. Check network status, view dashboards for network health and activity, power cycle PoE ports, etc, and update firmware remotely. No need to be on-site, open up ports to your network, or VPN into it. |
| Auto-join and Configure (Zero-Touch Provisioning) | Additional Insight Managed devices added to the network automatically inherit settings and configuration. |
| Multi-site, Multi-network Single Pane-of-Glass View | View and configure multiple networks across multiple sites, all from one single app; NETGEAR Insight. |
| Comprehensive IPv6 Support for Management, ACLs and QoS | Build current network with future in mind. Ensure investment protection and a smooth migration to an IPv6-based network without switch replacement. |
| IPv4 Static Routing | A simple way to provide segmentation of the network with internal routing through the switch – reserving the router for external traffic routing only, making the entire network more efficient. |
| Robust security features: • 802.1x authentication (EAP) | Build a secured, converged network with all types of traffic by preventing external attacks and blocking malware while allowing secure access for authorized users. |
| Port-based security by locked MAC | |
| ACL filtering to permit or deny traffic based on MAC and IP addresses | |
| Comprehensive QoS features: Port-based or VLAN 802.1p-based prioritization | Advanced controls for optimized network performance and better delivery of mission-critical traffic such as voice and video. |
| Layer 3-based (DSCP) prioritization | |
| Port-based egress rate limiting | |

Insight Managed Gigabit Ethernet Smart Cloud FlexPoE Switches

Data Sheet

GC108P, GC108PP

| Software Features (con't) | Benefits |
|--|---|
| Auto-VoIP, Auto-Voice VLAN, and Auto-Video VLAN | Automatic Voice over IP prioritization (Auto-VoIP) simplifies most complex multi-vendor IP telephone deployments either based on protocols (SIP, H.323 and SCCP) or on OUI bytes (default database and user-based OUIs) in the phone source MAC address, providing the best class of service to VoIP streams (both data and signaling) over other ordinary traffic by classifying traffic, and enabling correct egress queue configuration. Similarly, Auto-Video VLAN enables IGMP snooping to minimize broadcast streams. |
| IGMP Snooping and MLD Snooping | Facilitate fast receiver joins and leaves for multicast streams. Save cost and improve network efficiency by ensuring multicast traffic only reaches designated receivers without the need of an extra multicast router. |
| Protected Ports | Ensure no exchange of unicast, broadcast, or multicast traffic between the protected ports on the switch, thereby improving the security of your converged network. This allows your sensitive phone phone conversations to stay private and your surveillance video clips can be forwarded to their designated storage device without leakage or alteration. |
| DHCP Snooping | Ensure IP address allocation integrity by only allowing DHCP messages from trusted DHCP servers and dropping malformed DHCP messages with a port or MAC address mismatch. |
| Dynamic VLAN Assignment (RADIUS) | IP phones and PCs can authenticate on the same port but under different VLAN assignment policies. Users are free to move around and enjoy the same level of network access regardless of their physical location on the network. |
| Private VLAN | Private VLANs help reduce broadcast with added security. |
| Port Trunking/Link Aggregation (LACP) | Build up bigger bandwidth to support aggregated uplink/downlink traffic or to provide redundant link(s). Aggregate up to 8 ports for 8Gbps connections. |
| Loop Prevention and Auto-DoS Prevention | Detect and prevent (auto port shutdown) accidental network loops and protect against DoS attacks. |
| PoE Timer and Scheduling | Allows IT administrators to increase network security, better utilize network resources and conserve energy by scheduling or remotely controlling on/off of PoE ports. |
| Port Mirroring and Cable Test | Many-to-one port mirroring for better and quicker network diagnostics and troubleshooting. Cable test easily identifies bad Ethernet cables. |
| Firmware Updates from Cloud | Direct cloud-to-device firmware updates, initiated and/or scheduled using the Insight app, all from the palm of your hand, anytime, anywhere! |
| Multiple Language Local GUI | Product documentation and local-only web user interfaces are translated, giving you the ability to select your preferred language [‡] . |

Why Insight Managed Smart Cloud Switches?

NETGEAR is revolutionizing unified, centralized network management with it's new line of Insight Managed Smart Cloud Switches and Wireless Access Points, all managed from the palm of your hand, anytime, anywhere, on your phone or tablet using the NETGEAR Insight mobile app. Or, for a larger screen experience, from your PC, Mac, or tablet web browser using the Insight Cloud Portal.

- Ideal for SMBs, offices, retail stores, education, healthcare, owner-operated businesses, etc.
- IT expert or no networking experience at all: Insight Managed Smart Cloud Switches let you focus on your business, not maintaining your network.
- Know immediately if and when your network is not running perfectly; not after you've already lost business or suffered significant down-time.
- Advanced L2+/L3 Lite network features such as IPv4/IPv6 management, VLANs, DiffServ QoS, LACP Link Aggregation, Spanning Tree, Static Routing, advanced per-port PoE controls and PoE scheduling will satisfy even the most advanced small business networks.
- · Fundamentally change and simplify network usability for easier and smoother deployment of voice, video, and WLAN on the same converged platform.
- Industry-leading 5-year warranty on switches, 5-year Next-Business-Day (NBD) replacement, and 90-days free technical support** for peace-of-mind.

Within small and medium-sized organizations, there is growing adoption of PoE devices such as VoIP phones, IP security cameras, wireless access points, proximity sensors, LED lighting, door locks, and other IoT devices that require network switches capable of supporting dense PoE installations. Wireless access points and pan-tilt-zoom HD cameras using Wave 2 802.11ac Wi-Fi also require PoE+ power (802.3at), increasing the power demands on PoE switches. NETGEAR's exclusive FlexPoE power also provides additional flexibility and future-proofing for PoE budgets to meet the current and future needs of converged networks.

[†] English, German, and Japanese are the current supported languages in the local-only web GUI. The Insight mobile app and Insight Cloud Portal support local languages per the device used (phone or computer prowser)


Insight Managed Gigabit Ethernet Smart Cloud FlexPoE Switches

Data Sheet


GC108P, GC108PP

Example Application

In a Business Environment



In a Security and Surveillance



Insight Managed Gigabit Ethernet Smart Cloud FlexPoE Switches

Data Sheet

GC108P, GC108PP

PoE/PoE+ Classes and Power

The following table describes the PoE classes and switch allocations

| DEVICE CLASS | STANDARD | CLASS DESCRIPTION | MINIMUM POWER ALLOCATED TO THE POWERED DEVICE | RANGE OF POWER DELIVERED TO THE POWERED DEVICE |
|-----------------|--------------|---------------------------------|---|---|
| 0 | PoE and PoE+ | Default Power (full 802.3af) | 0.44 W | 0.44 - 12.95 W |
| 1 | PoE and PoE+ | Very low power | 4.0 W | 0.44 - 3.84 W |
| 2 | PoE and PoE+ | Low power | 7.0 W | 3.84 - 6.49 W |
| 3 | PoE and PoE+ | Mid Power | 15.4 W | 6.49 - 12.95 W |
| 4 | PoE+ only | High Power (full 802.3at) | 30.0 W | 12.95 - 25.5 W |



Large screen access via Insight Cloud Portal









Network dashboard



Single pane-of-glass view of multiple networks/locations

Insight Managed Gigabit Ethernet Smart Cloud FlexPoE Switches

Data Sheet

GC108P, GC108PP

| PRODUCT | GC108P | GC108PP | | |
|--|--|---|--|--|
| | NETGEAR OC. 10 | NETGEAR GO = | | |
| Gigabit Ethernet RJ-45 Copper ports (10M/100M/1G) - 1000BASE-T | 8 | 8 | | |
| PoE/PoE+ ports | 8 PoE+ (64W§ FlexPoE budget) | 8 PoE+ (126W§ FlexPoE budget) | | |
| Gigabit SFP (fiber) ports (100M/1G) - 1000BASE-X | N/A | N/A | | |
| Power Supply | External Input: 54V/1.25A | External Input: 54V/2.4A | | |
| Kensington Lock | Yes (| (rear) | | |
| LEDs | | | | |
| Front (per device) | Power/Cloud/Internet | t Connection, PoE Max | | |
| Front (per port) | Speed/Link/Activity (| left), PoE Power (right) | | |
| UNIFIED NETWORK MANAGEMENT (DISCOV | /ERY, SETUP, MONITORING, AND MANAGEMENT | .) | | |
| Discovery, setup, monitoring and management | NETGEAR Insight mobile app on phone or tablet; Insig | ght Cloud Portal from PC, Mac, or tablet web browser | | |
| Remote/Cloud management | Anywhere, anytime, from the palm of your hand using Insight mobile app or from any PC, Mac, or tablet web browser using the Insight Cloud Portal | | | |
| Centralized network configuration (policies) | Centralized network configuration (policies) across Insight Managed Switches, Wireless Access Points, and Business-class ReadyNAS Storage for VLANs, ACLs, QoS, and LAGs | | | |
| Device auto-join and configure (zero-touch provisioning) | Additional Insight Managed devices added to the network automatically inherit the network configuration | | | |
| Multi-site, multi-network single pane-of-glass view | Manage multiple sites, locations, and networks in a single view using the Insight mobile app or Insight Cloud Portal | | | |
| Multi-switch, multi-port concurrent configuration for ACLs, VLANs, QoS, PoE, etc | | tiple ports across multiple switches ng the Port Config Wizard | | |
| PERFORMANCE SPECIFICATION | | | | |
| CPU | | ore, 128MB RAM, PI FLASH | | |
| Packet buffer memory (Dynamically shared across only used ports) | 51 | 2KB | | |
| Forwarding modes | Store-and-forward | | | |
| Bandwidth (non-blocking, full duplex) | 16Gbps | | | |
| Priority queues | 8 | | | |
| Priority queuing | Weighted Round Robin (WRR) and Strict Priority | | | |
| MAC Address database size (48-bit MAC addresses) | 8K (dynamic) | | | |
| Multicast groups | 256 | | | |
| Number of IPv4 static routes | 32 | | | |
| Number of IPv6 static routes | N/A | | | |

Insight Managed Gigabit Ethernet Smart Cloud FlexPoE Switches

Data Sheet

GC108P, GC108PP

| PRODUCT | GC108P | GC108PP | | |
|---|--|--|--|--|
| Number of ARP/NDP cache entries | 512 ARP / 512 NDP | | | |
| Number of VLANs | 64 | | | |
| Number of DHCP snooping bindings | 256 | | | |
| Access Control Lists (ACLs) | 100 shared for MAC, IP and IPv6 ACLs | | | |
| Packet forwarding rate (64 byte packet size) (Mfps or Mpps) | 11 | .9 | | |
| 1G Copper latency (µsec) (64-byte; 1518-byte; 9216-byte frames) | 64-byte: 3 1518-bye: 9216-byte: | 3.360 µsec | | |
| 1G SFP Fiber latency (µsec) (64-byte; 1518-byte; 9216-byte frames) | N ₂ | 'A | | |
| Jumbo frame support | Up to 10,000 |) packet size | | |
| Acoustic noise level @ 25° C (dBA) (ANSI-S10.12) | O dBA (| fanless) | | |
| Mean Time Between Failures (MTBF) @ 25° C | 2,635,395 h | rs (301 yrs) | | |
| POE CONFIGURATION | | | | |
| Number of PoE (802.3af) / PoE+ (802.3at) ports | 8 Pc | DE+ | | |
| Total PoE power budget (watts) - NETGEAR FlexPoE | 64W§ FlexPoE 126W§ FlexPoE | | | |
| Advanced per-port PoE controls (enable/disable/power limit) | Ye | es | | |
| Advanced per-port PoE scheduling/timers | Ye | es . | | |
| L2 SERVICES - VLANS | | | | |
| IEEE 802.1Q VLAN Tagging | Ye | es . | | |
| IP-based VLANs | Ye | es | | |
| MAC-based VLANs | Ye | es | | |
| Auto-VoIP VLAN / Auto-Voice VLAN | Yes, based on OUI bytes (default database and use | er-based OUIs) in the phone source MAC address | | |
| Auto-VoIP | Yes, based on protocols (SIP, H.323 and S | CCP). Prioritzes traffic to a higher queue. | | |
| Voice VLAN | Yes, based on either VLAN ID or passed onto the connecting \ | | | |
| Auto-Video VLAN | Ye | es | | |
| Private VLAN | Ye | es | | |
| L2 SERVICES - AVAILABILITY | | | | |
| Broadcast, multicast, unknown unicast storm control | Yes | | | |
| IEEE 802.3ad - LAGs (LACP) | Yes | | | |
| IEEE 802.3x (full duplex and flow control) | Ye | es | | |
| IEEE 802.1D Spanning Tree Protocol | Ye | es | | |
| IEEE 802.1w Rapid Spanning Tree Protocol | Yes | | | |

Insight Managed Gigabit Ethernet Smart Cloud FlexPoE Switches

Data Sheet

GC108P, GC108PP

| PRODUCT | GC108P | GC108PP |
|--|---------------------|---------------------|
| IEEE 802.1s Multiple Spanning Tree Protocol | Y | es |
| Layer 2 DHCP Relay | N | lo |
| L2 SERVICES - MULTICAST FILTERING | | |
| IGMP snooping (v1, v2 and v3) | Yes | |
| MLD snooping support (v1 and v2) | Y | es |
| IGMP snooping queries | Y | es |
| Block unknown multicast | N | lo |
| Multicast VLAN Registration (MVR) | Y | es |
| Multicast groups | 2! | 56 |
| L3 SERVICES - DHCP | | |
| DHCP client | Y | es |
| DHCP snooping | Y | es |
| Number of DHCP snooping bindings | 2! | 56 |
| L3 SERVICES - ROUTING | | |
| IPv4 static routes | 32 | |
| IPv6 static routes | N/A | |
| VLAN routing | Yes | |
| Host ARP table / NDP cache (number of entries) | 512 ARP , | / 512 NDP |
| ICMP Router Discovery Protocol (IRDP) | Y | es |
| Number of IP VLAN interfaces (routed VLANs) | 1 | 5 |
| LINK AGGREGATION | | |
| IEEE 802.3ad - LAGs (LACP) | Y | es |
| Manual Static LAG | Y | es |
| # of Static or LACP LAGs # of members in each LAG | 8 LAGs with max 8 r | nembers in each LAG |
| NETWORK MONITORING AND DISCOVERY S | ERVICES | |
| 802.1ab LLDP | Y | es |
| LLDP-MED | Y | es |
| SNMP | v1, v. | 2c, v3 |
| RMON group 1,2,3,9 | Y | es |
| NETWORK SECURITY | | |
| IEEE 802.1x | Yes | |
| Guest VLAN | Yes | |
| RADIUS-based VLAN assignment via .1x | Yes | |
| MAC-based .1x | Yes | |
| RADIUS accounting | Y | es |
| Access Control Lists (ACLs) | L2 / L | 3 / L4 |

Insight Managed Gigabit Ethernet Smart Cloud FlexPoE Switches

Data Sheet

GC108P, GC108PP

| PRODUCT | GC108P | GC108PP | | |
|---|--|--|--|--|
| IP-based ACLs (IPv4 and IPv6) | Ye | 25 | | |
| MAC-based ACLs | Yes | | | |
| TCP/UPD-based ACLs | Yes | | | |
| MAC lockdown | Ye | 25 | | |
| MAC lockdown by the number of MACs | Ye | 25 | | |
| Control MAC # Dynamic learned entries (per port) | 40 | 96 | | |
| Control MAC # static entries (per port) | 4 | 8 | | |
| IEEE 802.1x RADIUS port access authentication/type | Yes (| EAP) | | |
| Port-based security by locked MAC addresses | Ye | es | | |
| Dynamic ARP inspection | N | 0 | | |
| Broadcast, multicast, unknown unicast storm control | Ye | 28 | | |
| DoS attacks prevention | Ye | es | | |
| Protected ports | Ye | es | | |
| QUALITY OF SERVICE (QOS) | | | | |
| Port-based rate limiting | Yes, e | gress | | |
| Port-based QoS | Ye | es | | |
| Support for IPv6 fields | Ye | es | | |
| DiffServ QoS | Yes, in | ngress | | |
| IEEE 802.1p COS | Ye | es | | |
| Destination MAC and IP | Ye | es | | |
| IPv4 and v6 DSCP | Ye | es | | |
| IPv4 and IPv6 ToS | IPv4 | only | | |
| TCP/UDP-based | Ye | es | | |
| Weighted Round Robin (WRR) | Ye | es | | |
| Strict priority queue technology | Ye | es | | |
| Auto-VolP VLAN / Auto-Voice VLAN | Yes, based on OUI bytes (default database and use | er-based OUIs) in the phone source MAC address | | |
| Auto-VoIP | Yes, based on protocols (SIP, H.323 and S | SCCP). Prioritzes traffic to a higher queue. | | |
| Voice VLAN | Yes, based on either VLAN ID or 802.1p priority, packets are passed onto the connecting VoIP phone using LLDP-MED. | | | |
| Auto-Video VLAN | Yes | | | |
| OTHER FEATURES | | | | |
| Advanced per-port PoE controls (enable/disable/power limit) | Yes | | | |
| Advanced per-port PoE scheduling/timers | Yes | | | |
| Loop detection & prevention | Yes (t | both) | | |
| DNS Client | Ye | es . | | |

Insight Managed Gigabit Ethernet Smart Cloud FlexPoE Switches

Data Sheet

GC108P, GC108PP

| PRODUCT | GC108P | GC108PP | | |
|--|---|---------|--|--|
| Option to enable/disable BPDU flooding when STP is disabled | Yes | | | |
| Option to enable/disable the flooding of EAPOL when 802.1x is disabled | Yes | | | |
| IEEE NETWORK PROTOCOLS | | | | |
| • IEEE 802.3 Ethernet • IEEE 802.3u 100BASE-T • IEEE 802.3ab 1000BASE-T • IEEE 802.3af PoE • IEEE 802.3at PoE+ • IEEE 802.3ad Trunking (LACP) • IEEE 802.3az Energy Efficient Ethernet (EEE) | IEEE 802.3x Full-Duplex Flow Control IEEE 802.1Q VLAN Tagging IEEE 802.1AB LLDP with ANSI/TIA-1057 (LLDP-MED) IEEE 802.1p Class of Service IEEE 802.1D Spanning Tree (STP) IEEE 802.1s Multiple Spanning Tree (MSTP) IEEE 802.1w Rapid Spanning Tree (RSTP) IEEE 802.1x RADIUS Network Access Control | | | |
| MANAGEMENT, MONITORING & TROUBLESHOOTING Cloud/Remote management Yes | | | | |
| Insight mobile app & Insight Cloud Portal management | Yes | | | |
| uPnP Discovery | Yes | | | |
| Bonjour Discovery | | Yes | | |
| Networking monitoring | | Yes | | |
| Data/performance logs | | Yes | | |
| Centralized network configuration/policies (network-centric management) | Yes | | | |
| Device auto-join and configure (zero-touch provisioning) | | Yes | | |
| Multi-site, multi-network single pane-of-glass view | | Yes | | |
| Multi-switch, multi-port concurrent configuration | | Yes | | |
| Network/global password (for all Insight Managed devices on a network) | Yes (per network/subnet via NETGEAR Insight mobile app and Insight Cloud Portal) | | | |
| Password management | | Yes | | |
| IP Access List | Yes | | | |
| Configurable management VLAN | Yes | | | |
| Admin access control via RADIUS and TACACS+ | | Yes | | |
| IPv6 management | | Yes | | |
| SNTP client over UDP port 123 | | Yes | | |
| Firmware upgrade direct from Cloud (via mobile device or Insight Cloud portal) | Yes | | | |
| SNMP v1/v2c | Yes | | | |
| SNMP v3 with multiple IP addresses | | Yes | | |
| RMON group 1,2,3,9 | Yes | | | |

Insight Managed Gigabit Ethernet Smart Cloud FlexPoE Switches

Data Sheet

GC108P, GC108PP

| PRODUCT | GC108P | GC108PP |
|---|--|---|
| Port mirroring | Yes | |
| Many-to-one port mirroring | Yes | |
| Cable test utility | Yes | |
| Ping and tracerout client | Yes | |
| Local-only web browser-based management GUI with multiple language support* | Yes | |
| SSL/HTTPS Web-based access (version) | No | |
| TLS Web-based access (version) | Yes (v1.0) | |
| TFTP/HTTP firmware upload/download | Yes | |
| Dual software (firmware) image | Yes | |
| Memory and flash log | Yes | |
| Syslog (RFC 3164) | Yes | |
| POWER CONSUMPTION | | |
| Max power (worst case, all ports used, full PoE, line-rate traffic) (Watts) | 4.9 W | 4.9 W |
| Max power (worst case, all ports used, full PoE, line-rate traffic) (Watts) | 66.7 W | 128.4 W |
| Min power (link-down standby) (Watts) | 3.1 W | 3.1 W |
| Heat Dissipation (min w/o PoE and max with full PoE) (BTU/hr) | Min: 10.70 BTU/hr Max: 228.11 BTU/hr | Min: 10.70 BTU/hr Max: 439.13 BTU/hr |
| Energy Efficient Ethernet (EEE) IEEE 802.3az | Yes (deactivated by default) | |
| Auto power down | Yes (deactivated by default) | |
| PHYSICAL SPECIFICATIONS | | |
| Dimensions (W x D x H) | 188 x 110 x 27 mm (7.4 x 4.3 x 1.1 in) | |
| Weight | 0.52 kg (1.14 lb) | |
| Mounting options | Desktop, wall-mount, VESA-standard (75mm) | |
| ENVIRONMENTAL SPECIFICATIONS | | |
| Operating | | |
| Operating Temperature | -0° to 45°C (32° to 113°F) | |
| Humidity | 90% maximum relative humidity (RH), non-condensing | |
| Altitude | 10,000 ft (3,000 m) maximum | |
| Storage | | |
| Storage Temperature | -20° to 70°C (- 4° to 158°F) | |
| Humidity (relative) | 95% maximum relative humidity (RH), non-condensing | |
| Altitude | 10,000 ft (3,000 m) maximum | |

Insight Managed Gigabit Ethernet Smart Cloud FlexPoE Switches

Data Sheet

GC108P, GC108PP

| PRODUCT | GC108P | GC108PP | |
|--|---|-----------------------------|--|
| ELECTROMAGNETIC EMISSIONS AND IMMUI | NITY CERTIFICATIONS | | |
| Certifications | CE Mark, Commercial | | |
| | EN55032:2015+AC:2016, Class A | | |
| | CISPR 32:2015, Class A | | |
| | EN55024:2010+A1:2015 | | |
| | EN61000-3-2:2014, Class A | | |
| | EN61000-3-3:2013 | | |
| | VCCI-CISPR 32:2016, Class A | | |
| | RCM, AS/NZS CISPR 32:2015 Class A | | |
| | 47 CFR FCC Part 15, Subpart B, Class A | | |
| | ANSI C63.4:2014 | | |
| | ICES-003:2016 Issue 6, Class A | | |
| | BSMI CNS 13438, Class A | | |
| | KCC KN32 / KN35 | | |
| SAFETY CERTIFICATIONS | GB4943.1-2011, YD/1993-19 | 998, GB/T9254-2008, Class A | |
| Certifications | CP Mark | Commercial | |
| | CB Mark, Commercial IEC 60950-1:2005 (ed.2) + Am 1:2009 + Am 2:2013 | | |
| | UL 60950-1, 2nd, 2014 and CAN/CSA C22.2 No. 60950-1-07, 2nd, 2014 | | |
| | EN 60950-1; 2006 + A11:2009 + A1:2010 + A12:2011 + A2:2013 | | |
| | RCM, AS/NZS 60950.1:2015 | | |
| | BSMI CNS14336-1 | | |
| | GB4943.1-2011, YD/T993-1998, GB/T9254-2008, Class A | | |
| WARRANTY AND SUPPORT | | | |
| Hardware Limited* Warranty | | (switch) | |
| | 2 years (power adapter) | | |
| Next-Business-Day (NBD) Replacement | 5 years | | |
| Technical support (online, phone) | 90 days free from date of purchase* | | |
| ProSUPPORT OnCall 24x7 Service Packs** | PMBOS1 PMBOS3 PMBOS5 | 2 (3 yrs.) | |

[§] NETGEAR FlexPoE power - interchangable external power adapter allows for increasing or decreasing your PoE budget at any time with optional NETGEAR FlexPoE power adapters.

[†] English, German, and Japanese are the current supported languages in the local-only web GUI. The Insight mobile app and Insight Cloud Portal support local languages per the device used (phone or computer browser).

^{*} This product comes with a limited warranty that is valid only if purchased from a NETGEAR authorized reseller, and covers unmodified hardware, fans and internal power supplies – not software or external power supplies, and requires product registration using the Insight mobile app or Insight Cloud portal within 90 days of purchase; see https://www.netgear.com/about/warranty for details. Intended for indoor use only.

^{**} The NETGEAR OnCall 24x7 contract provides unlimited phone, chat and email technical support for your networking product.

Insight Managed Gigabit Ethernet Smart Cloud FlexPoE Switches

Data Sheet

GC108P, GC108PP

Ordering Information

| PACKAGE CONTENTS | |
|----------------------------|--|
| All models | NETGEAR Insight Managed 8-Port Gigabit Ethernet PoE+ Smart Cloud Switch with FlexPoE Power Rubber footpads for tabletop installation Wall-mount kit (with 75mm VESA standard pattern) Category 5e flat Ethernet cable Quick install guide DC power adapter (power cord localized to country of sale) |
| ORDERING INFORMATION | The state of the s |
| GC108P-100NAS | North America and Latin America |
| GC108P-100PES | Europe |
| GC108P-100UKS | United Kingdom |
| GC108P-100AUS | Australia |
| GC108P-100JPS | Japan and Asia Pacific |
| GC108P-100PRS | China |
| GC108PP-100NAS | North America and Latin America |
| GC108PP-100PES | Europe |
| GC108PP-100UKS | United Kingdom |
| GC108PP-100AUS | Australia |
| GC108PP-100JPS | Japan and Asia Pacific |
| GC108PP-100PRS | China |
| OPTIONAL ACCESSORIES | |
| EPS130W-100xxx | 130W FlexPoE External Power Adapter (power cable localized to country of sale) |
| EXTENDED SUPPORT CONTRACTS | |
| PMBOS12-10000S | 1-Year OnCall 24x7 Service Pack** |
| PMB0S32-10000S | 3-Year OnCall 24x7 Service Pack** |
| PMB0S52-10000S | 5-Year OnCall 24x7 Service Pack** |

Accessory Power Adapters

With NETGEAR's exclusive FlexPoE Power, you can increase (or decrease) your PoE budget anytime by simply upgrading your switch's power adapter, without having to purchase a new switch.

If you only need a lower power budget now, you can use the GC108P with it's strong 64W[§] of future-proof PoE budget. And then if you need more power later, just upgrade your power adapter with a new EPS130W FlexPoE power adapter from NETGEAR. Your switch will then have the same 126W of PoE power budget at the GC108PP.

If you have many power-hungry devices and need a high PoE budget now, you can choose the GC108PP with it's astounding 126W of PoE power. This unique combination from NETGEAR Business makes these switches the most adaptive and flexible PoE switches anywhere.

NETGEAR, the NETGEAR Logo, and NETGEAR Insight are trademarks of NETGEAR, Inc. in the United States and/or other countries. Other brand names mentioned herein are for identification purposes only and may be trademarks of their respective holder(s). Information is subject to change without notice. © NETGEAR, Inc. All Rights reserved.

[§] NETGEAR FlexPoE power - interchangable external power adapter allows for increasing or decreasing your PoE budget at any time with optional NETGEAR FlexPoE power adapters.

[†] English, German, and Japanese are the current supported languages in the local-only web GUI. The Insight mobile app and Insight Cloud Portal support local languages per the device used (phone or computer browser).

^{*}This product comes with a limited warranty that is valid only if purchased from a NETGEAR authorized reseller, and covers unmodified hardware, fans and internal power supplies – not software or external power supplies, and requires product registration using the Insight mobile app or Insight Cloud portal within 90 days of purchase; see https://www.netgear.com/about/warranty for details. Intended for indoor use only.

^{**} The NETGEAR OnCall 24x7 contract provides unlimited phone, chat and email technical support for your networking product.