FUJITSU

Data Sheet
FUJITSU Server PRIMERGY RX2530 M5 Rack Server

Maximum productivity in a 1U housing

FUJITSU Server PRIMERGY will give you the servers you need to power any workload and changing business requirements. As business processes expand so does the need for applications. Each has its own resource footprint, so you need a way to optimize your computing to better serve your users. PRIMERGY systems will help you match your computing capabilities to your business priorities with our complete portfolio of expandable PRIMERGY tower servers for remote and branch offices, versatile rack-mount servers as well as hyper-converged multi-node servers. They convince by business proven quality with a wide range of innovations, highest efficiency cutting operational cost and complexity, provide more agility in daily operations, and integrate seamlessly to let help you concentrate on core business functions.

FUJITSU Server PRIMERGY RX rack systems are versatile rack-optimized servers providing best-in-class performance and energy efficiency, and thus form the "standard" in each data center. PRIMERGY RX servers deliver more than 20 years of development and production know-how resulting in extremely low failure rates below market average, and lead to continuous operations and outstanding hardware availability.

PRIMERGY RX2530 M5
The FUJITSU Server PRIMERGY RX2530 M5 is a rack server that provides high performance, expandability and energy efficiency in a 1U space-saving housing. The PRIMERGY RX2530 M5 is ideal for virtualization, scale-out scenarios, and small databases as well as for high performance computing thanks to the high performance of the new Intel® Xeon® Processor Scalable Family CPUs with up to 28 cores and the latest DDR4 memory technology. Moreover, the RX2530 M5 delivers a great expandability by supporting up to 3,072 GB of main memory and the capability to use up to 12x Intel® Optane™ DC Persistent

Memory NV-DIMM modules. It is future-proof with M.2 device support and the latest iRMC S5 for server management of the next generation. Up to 10 hard disk drives or optionally high-speed PCIe SSDs offer a flexible storage configuration option. A variety of onboard DynamicLoM options, plus its dual-port embedded LAN meet future requirements, cost-optimized. The limited space of a 1U chassis offers highly efficient power supply units and their redundancy on demand. The optional Cool-safe® Advanced Thermal Design this will result in lower operational costs.

http://www.fujitsu.com/global/products/computing/servers/primergy/rack/rx2530m5/

Features & Benefits

Main Features	Benefits
Innovation meets Performance ■ Wide choice of different types of Intel® Xeon® Scalable Processor Family. Each processor offers up to 28 cores, up to 56 threads, 12 memory channels enabling a significantly higher performance and efficiency. They rely on Intel® UltraPath Interconnect for an increased data rate between the CPUs. Intel® Optane™ DC persistent memory is an innovative memory technology that delivers a unique combination of affordable large capacity and persistence (non-volatility). It revolutionizes the data center memory-storage hierarchy of the past and brings massive data sets closer to the CPU for faster time to insight. In total, up to 7,680 GB main memory in a mixed mode (non-volatile memory + DDR4 @ 2,933 MT/s) are available.	■ Ready for the future and data growth scenarios with the performance of two processors – marking the standard of tomorrow with an increase in computing power. Several innovations make this new CPU generation (code-named "Cascade Lake") even more powerful than the current-generation Intel® Xeon® Scalable processors, enabling robust compute capability and increased memory bandwidth for demanding workloads. Intel® Optane™ DC persistent memory technology will transform critical data workloads – from cloud and databases, to in-memory analytics, and content delivery networks.
Enhanced Features for enhanced Computing ■ The RX2530 M5 comes with onboard LAN for basic LAN, DynamicLoM via OCP slot for extended requirements. A mix&match storage drive bay configuration offers the choice of either up to 8x 2.5-inch HDD/SSD + 1x ODD or up to 10x 2.5-inch, thereof optionally max. 10x PCIe 2.5-inch SSD SFF, complemented by internal M.2 devices for hypervisor installations. Our power supply units with up to 96% energy efficiency and Fujitsu's Cool-safe® Advanced Thermal Design for higher ambient temperatures in the data center are available for this server.	■ The right Ethernet connection for all: Basic via onboard LAN, extended with DynamicLoM via OCP guarantees the highest flexibility to integrate the server into existing infrastructures – now and in future without overhauling the existing infrastructure. Flexible expandability and diverse options for storage devices permits for the integration of existing and new SSD and HDD as needed. Less today, more in future – or vice versa. On top of that, this server is not only "greener", but also less expensive over time. Cool-safe® ATD and highly efficient hot-plug power supplies save energy costs.
Foundation for Trust and Security ■ Fujitsu ServerView Suite including tools for installation and deployment, permanent status monitoring and control, free-of-charge BIOS, firmware and selected software updates plus TPM2.0 modules and latest operating system support are a great addition.	■ These features ensure lifecycle investment protection while the comprehensive tools of the Fujitsu ServerView Suite ease the administrators' life. Moreover, hardware and software security features are very important in a fast-paced world, especially considering cybercrime.
Revolutionize data center management ■ Fujitsu ServerView Suite is a free-of-charge management software including tools for installation and deployment, permanent status monitoring and control as well as BIOS, firmware and selected software updates. In addition FUJITSU Software Infrastructure Manager (ISM) provides converged management across multiple data centers. The new ISM Essential license, available free-of-charge provides essential server management and converged monitoring functions.	■ Fujitsu offers comprehensive infrastructure management and server management solutions which is key to efficient data center operations. They provides all the functions for flexible and automated 24x7 IT operations and improves end-user productivity via intelligent and innovative system management solutions. ISM helps improve data center efficiency and overall IT Productivity with converged infrastructure management, paving the path to software-defined data center.

Technical details

PRIMERGY RX2530 M5					
Base unit	PRIMERGY RX2530 M5 LFF	PRIMERGY RX2530 M5 SFF	PRIMERGY RX2530 M5 SFF	PRIMERGY RX2530 M5 SFF	PRIMERGY RX2530 M5 SFF
Housing types	Rack	Rack	Rack	Rack	Rack
Storage drive architecture	4x 3.5-inch SAS/SATA	4x 2.5-inch SAS/SATA	8x 2.5-inch SAS/SATA	10x 2.5-inch SAS/SATA/ PCIe	10x 2.5-inch SATA/ NVMe
Power supply	Hot-plug	Hot-plug	Hot-plug	Hot-plug	Hot-plug
Product Type	Dual Socket Rack Server	Dual Socket Rack Server	Dual Socket Rack Server	Dual Socket Rack Server	Dual Socket Rack Server
Mainboard					
Mainboard type	D3383-B	D3383-B	D3383-B	D3483-B	D3483-B
Chipset	Intel® C624				
Processor quantity and type	1 - 2 x Intel® Xeon® Processor Scalable Family				
Intel® Xeon® Bronze Processor	Intel® Xeon® Bronze 3204 (6C, 1.90 GHz, TLC: 8.25 MB, Turbo: 1.90 GHz, 9.6 GT/s, Mem bus: 2,133 MHz, 85 W, AVX Base 1.50 GHz, AVX Turbo 1.50 GHz)				
Intel® Xeon® Silver Processor	Intel® Xeon® Silver 4208 (8C, 2.10 GHz, TLC: 11 MB, Turbo: 2.50 GHz, 9.6 GT/s, Mem bus: 2,400 MHz, 85 W, AVX Base 1.60 GHz, AVX Turbo 2.00 GHz)				
	Intel® Xeon® Silver 4210 (10C, 2.20 GHz, TLC: 13.75 MB, Turbo: 2.70 GHz, 9.6 GT/s, Mem bus: 2,400 MHz, 85 W, AVX Base 1.90 GHz, AVX Turbo 2.30 GHz)				
	Intel® Xeon® Silver 4214 (12C, 2.20 GHz, TLC: 16.5 MB, Turbo: 2.70 GHz, 9.6 GT/s, Mem bus: 2,400 MHz, 85 W, AVX Base 1.80 GHz, AVX Turbo 2.40 GHz)				
	Intel® Xeon® Silver 4214Y (12C, 2.20 GHz, TLC: 16.5 MB, Turbo: 2.70 GHz, 9.6 GT/s, Mem bus: 2,400 MHz, 85 W, AVX Base 1.80 GHz, AVX Turbo 2.40 GHz)				
	Intel® Xeon® Silver 4215 (8C, 2.50 GHz, TLC: 11 MB, Turbo: 3.00 GHz, 9.6 GT/s, Mem bus: 2,400 MHz, 85 W, AVX Base 2.00 GHz, AVX Turbo 2.60 GHz)				
	Intel® Xeon® Silver 4216 (16C, 2.10 GHz, TLC: 22 MB, Turbo: 2.70 GHz, 9.6 GT/s, Mem bus: 2,400 MHz, 100 W, AVX Base 1.40 GHz, AVX Turbo 2.30 GHz)				

http://www.fujitsu.com/global/products/computing/servers/primergy/rack/rx2530m5/

Intel® Xeon® Gold Processor	Intel® Xeon® Gold processor 5215 (10C, 2.50 GHz, up to 3.0 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 5215L (10C, 2.50 GHz, up to 3.0 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 5215M (10C, 2.50 GHz, up to 3.0 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 5217 (8C, 3.00 GHz, up to 3.4 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 5218 (16C, 2.30 GHz, up to 2.8 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 5218B (16C, 2.30 GHz, up to 2.8 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 5220 (18C, 2.20 GHz, up to 2.7 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 5220S (18C, 2.70 GHz, up to 2.7 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 5222 (4C, 3.80 GHz, up to 3.9 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6209U (20C, 2.10 GHz, up to 2.8 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6210U (20C, 2.50 GHz, up to 3.2 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6212U (24C, 2.40 GHz, up to 3.1 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6222V (20C, 1.80 GHz, up to 2.4 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6226 (12C, 2.70 GHz, up to 3.5 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6230 (20C, 2.10 GHz, up to 2.8 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6230T (20C, 2.10 GHz, up to 2.8 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6234 (8C, 3.30 GHz, up to 4.0 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6238 (22C, 2.10 GHz, up to 2.8 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6238L (22C, 2.10 GHz, up to 3.7 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6238M (22C, 2.10 GHz, up to 3.7 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6240 (18C, 2.60 GHz, up to 3.3 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6240L (18C, 2.60 GHz, up to 3.3 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6240M (18C, 2.60 GHz, up to 3.3 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6240Y (18C, 2.60 GHz, up to 3.3 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6242 (16C, 2.80 GHz, up to 3.5 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6244 (8C, 3.60 GHz, up to 4.3 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6246 (12C, 3.30 GHz, up to 4.1 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6248 (20C, 2.50 GHz, up to 3.2 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6252 (24C, 2.10 GHz, up to 2.8 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6254 (18C, 3.10 GHz, up to 3.9 GHz, 10.4 GT/s)
	Intel® Xeon® Gold processor 6262V (24C, 1.90 GHz, up to 2.5 GHz, 10.4 GT/s)

Intel® Xeon® Platinum Processor	Intel® Xeon® Platinum 8260 (24C, 2.40 GHz, TLC: 35.75 MB, Turbo: 3.10 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 165 W, AVX Base 1.90 GHz, AVX Turbo 2.60 GHz)
	Intel® Xeon® Platinum 8260L (24C, 2.40 GHz, TLC: 35.75 MB, Turbo: 3.10 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 165 W, AVX Base 1.90 GHz, AVX Turbo 2.60 GHz)
	Intel® Xeon® Platinum 8260M (24C, 2.40 GHz, TLC: 35.75 MB, Turbo: 3.10 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 165 W, AVX Base 1.90 GHz, AVX Turbo 2.60 GHz)
	Intel® Xeon® Platinum 8260Y (24C, 2.40 GHz, TLC: 35.75 MB, Turbo: 3.10 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 165 W, AVX Base 1.80 GHz, AVX Turbo 2.50 GHz)
	Intel® Xeon® Platinum 8268 (24C, 2.90 GHz, TLC: 35.75 MB, Turbo: 3.50 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 205 W, AVX Base 2.40 GHz, AVX Turbo 3.00 GHz)
	Intel® Xeon® Platinum 8270 (26C, 2.70 GHz, TLC: 35.75 MB, Turbo: 3.40 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 205 W, AVX Base 2.20 GHz, AVX Turbo 2.90 GHz)
	Intel® Xeon® Platinum 8276 (28C, 2.20 GHz, TLC: 38.5 MB, Turbo: 3.00 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 165 W, AVX Base 1.70 GHz, AVX Turbo 2.60 GHz)
	Intel® Xeon® Platinum 8276L (28C, 2.20 GHz, TLC: 38.5 MB, Turbo: 3.00 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 165 W, AVX Base 1.70 GHz, AVX Turbo 2.60 GHz)
	Intel® Xeon® Platinum 8276M (28C, 2.20 GHz, TLC: 38.5 MB, Turbo: 3.00 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 165 W, AVX Base 1.70 GHz, AVX Turbo 2.60 GHz)
	Intel® Xeon® Platinum 8280 (28C, 2.70 GHz, TLC: 38.5 MB, Turbo: 3.30 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 205 W, AVX Base 2.20 GHz, AVX Turbo 2.90 GHz)
	Intel® Xeon® Platinum 8280L (28C, 2.70 GHz, TLC: 38.5 MB, Turbo: 3.30 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 205 W, AVX Base 2.20 GHz, AVX Turbo 2.90 GHz)
	Intel® Xeon® Platinum 8280M (28C, 2.70 GHz, TLC: 38.5 MB, Turbo: 3.30 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 205 W, AVX Base 2.20 GHz, AVX Turbo 2.90 GHz)
Memory slots	24 (12 DIMMs per CPU, 6 channels with 2 slots per channel)
Memory slot type	DIMM (DDR4 / DDR-T for non-volatile memory modules)
Memory capacity (min. - max.)	8 GB - 7.5 TB
Memory protection	Advanced ECC Memory Scrubbing SDDC Rank sparing memory support Memory Mirroring support
Memory notes	Max. 6 slots populated with DCPMM modules per CPU, please see relevant system configurator for details. Memory Mirroring Mode with identical modules in both channel pairs of a bank (4 or 6 modules per bank) per CPU. Rank Sparing Mode with minimum of 2 modules single ranked (1R) or dual ranked (2R) or 1 module quad ranked (4R) per CPU.
Standard memory modules	8 GB (1 module(s) 8 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, DIMM, 1Rx8
	16 GB (1 module(s) 16 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, DIMM, 2Rx8
	16 GB (1 module(s) 16 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, DIMM, 1Rx4
	32 GB (1 module(s) 32 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, DIMM, 2Rx4
	64 GB (1 module(s) 64 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, DIMM, 2Rx4
	128 GB (1 module(s) 128 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, LRDIMM, 4Rx4
	64 GB (1 module(s) 64 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, LRDIMM, 4Rx4
Standard memory modules (for use in combination with non-volatile memory modules)	96 GB (6 module(s) 16 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, DIMM, 1Rx4
	64 GB (4 module(s) 16 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, DIMM, 1Rx4
	128 GB (8 module(s) 16 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, DIMM, 1Rx4
	192 GB (6 module(s) 32 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, DIMM, 2Rx4
	128 GB (4 module(s) 32 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, DIMM, 2Rx4
	256 GB (8 module(s) 32 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, DIMM, 2Rx4
	768 GB (6 module(s) 128 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, LRDIMM, 4Rx4
	384 GB (6 module(s) 64 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, LRDIMM, 4Rx4
	256 GB (4 module(s) 64 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, LRDIMM, 4Rx4
	512 GB (8 module(s) 64 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, LRDIMM, 4Rx4

Non-volatile memory modules	256 GB (2 module(s) 128 GB) DDR-T, registered, ECC, 2,666 MT/s, NVM, DCPMM, 1Rx4
	512 GB (2 module(s) 256 GB) DDR-T, registered, ECC, 2,666 MT/s, NVM, DCPMM, 2Rx4
	512 GB (4 module(s) 128 GB) DDR-T, registered, ECC, 2,666 MT/s, NVM, DCPMM, 1Rx4
	1024 GB (4 module(s) 256 GB) DDR-T, registered, ECC, 2,666 MT/s, NVM, DCPMM, 2Rx4
	768 GB (6 module(s) 128 GB) DDR-T, registered, ECC, 2,666 MT/s, NVM, DCPMM, 1Rx4
	1536 GB (6 module(s) 256 GB) DDR-T, registered, ECC, 2,666 MT/s, NVM, DCPMM, 2Rx4
	3072 GB (6 module(s) 512 GB) DDR-T, registered, ECC, 2,666 MT/s, NVM, DCPMM, 4Rx4

Interfaces

USB 3.0 ports	5 x USB 3.0 (2x front, 2x rear, 1x internal) - for base unit with 10x 2.5" drives 1x USB 2.0 front only
Graphics (15-pin)	2 x VGA (thereof 1x front optional - not for base unit with 10x 2.5" drives)
Serial 1 (9-pin)	1 x optional (occupies PCIe slot)
Management LAN (RJ45)	1 x dedicated management LAN port for iRMC S5 (10/100/1000 Mbit/s) Management LAN traffic can be switched to shared onboard LAN controller port, speed and connector is related to installed interface card.

Onboard or integrated Controller

RAID controller	All hardware storage controller options are described under Components
SATA Controller	Intel® C624, 1 x SATA channel for ODD

LAN Controller	Intel® C624
	2 x 1 Gbit/s onboard
	Optional DynamicLoM OCP adaptors:
	    4 x 1 Gbit/s Ethernet (RJ45)
	    2 x 10 Gbit/s Ethernet (RJ45)
	    2 x 10 Gbit/s SFP+
	    4 x 10 Gbit/s SFP+
	    2 x 25 Gbit/s SFP28 (only for 10x HDD/SSD base unit)
	All supported features are described in relevant system configurator.
	Wake-on-LAN supported on onboard Port 1 and 2.
	Extra LAN controller(PCIe Cards) are listed below. (i210 LAN card via project release possible)

Remote management controller	Integrated Remote Management Controller (iRMC S5, 512 MB attached memory incl. graphics controller) IPMI 2.0 compatible
Onboard controller notes	Onboard 8x S-ATA 6Gbit/s RAID Controller (RAID 0,1) for up to 8x S-ATA drives available.
Trusted Platform Module (TPM)	Infineon / TPM 1.2 or TPM 2.0 module; TCG compliant (option)

Slots

PCI-Express 3.0 x8	1 x Low profile (2nd processor required for slot 4)
PCI-Express 3.0 x16	3 x Low profile (2nd processor required for slot 4); 1x16 if fh slot selected
Slot Notes	Slot 1 (internal): PCIe Gen3 x8 @CPU1 is dedicated for the modular RAID Controller. Slot 2: PCIe Gen3 x16 @CPU1 for low profile cards with up to 167mm length Slot 3: PCIe Gen3 x16 @CPU1 for low profile cards with up to 167mm length Slot 4 standard: PCIe Gen3 x16 @CPU2 for low profile cards with up to 167mm length Slot 4 option: PCIe Gen3 x16 @CPU2 for full height cards with up to 167mm length (in this case, slot 3 is not available) Slot availability and population depending on selected base unit. Please see relevant configurator for details.

Drive bays (Base unit specific)

Storage drive bays	up to 8 x 2.5-inch, 10 x 2.5-inch or 4 x 3.5-inch baseunit
Accessible drive bays	1 x 5.25/0.4-inch for CD-RW/DVD
Notes accessible drives	Not for 10 x 2.5-inch base unit. All possible options described in relevant system configurator.

Drive bays (Base unit specific)

Storage drive bays	up to 4x 3.5" (LFF) hot plug drives (SAS/SATA)	up to 4x 2.5" (SFF) hot plug drives (SAS/SATA); option for upgrade to 8x 2.5" (SFF) hot plug drives	up to 8x 2.5" (SFF) hot plug drives (SAS/SATA)	up to 10x 2.5" (SFF) hot plug drives (SAS/SATA); thereof up to 4x bays prepared for 2.5" PCIe SSD	up to 10x 2.5" (SFF) hot plug drives (SATA or PCIe SSD)
Optional accessible drives	Ultra slim 9.5mm optical drive (optional)	Ultra slim 9.5mm optical drive (optional)	Ultra slim 9.5mm optical drive (optional)	n/a	n/a

     http://www.fujitsu.com/global/products/computing/servers/primergy/rack/rx2530m5/

General system information

Number of fans	8
Fan configuration	redundant / hot-plug
Fan notes	3+1 fan modules for 1 CPU configuration; 7+1 fan modules for 2 CPU configuration

Operating panel

Operating buttons	On/off switch Reset button NMI button ID button
Status LEDs	System status (orange / yellow) Identification (blue) Hard disks access (green) Power (amber / green) At system rear side: System status (orange / yellow) Identification (blue) LAN connection (green) LAN speed (green / yellow)

BIOS

BIOS features	UEFI compliant Legacy BIOS compatibility customer configuration option Secure boot support ROM based setup utility GPT support for boot drives larger than 2.2 TB Memory Redundancy support (Mirroring, Sparing) IPMI support Recovery BIOS BIOS settings save and restore Local BIOS update from USB device Online update tools for main Linux versions Local and remote update via ServerView Update Manager IPv4/IPv6 remote PXE & iSCSI boot support Cryptographically Signed BIOS Firmware Update HTTP and HTTPS Boot PCIe Bifurcation configurable

Operating Systems and Virtualization Software

Certified or supported operating systems and virtualization software	Windows Server 2019 Datacenter
	Windows Server 2019 Standard
	Windows Server 2019 Essentials
	Windows Server Datacenter, version 1809
	Windows Server Standard, version 1809
	Hyper-V Server 2016
	Windows Server 2016 Datacenter
	Windows Server 2016 Standard
	Windows Server 2016 Essentials
	Windows Storage Server 2016 Standard
	Windows Server Datacenter, version 1709
	VMware vSphere™ 6.5
	VMware vSphere™ 6.7
	SUSE® Linux Enterprise Server 12
	Red Hat® Enterprise Linux 7
Operating system release link	http://docs.ts.fujitsu.com/dl.aspx?id=d4ebd846-aa0c-478b-8f58-4cfbf3230473
Operating system notes	Support of other Linux derivatives on demand

Server Management and Infrastructure Management

Standard	Infrastructure Manager (ISM) Essential
	Node Management
	Health status Monitoring and Control
	Capacity/Threshold Management
	Power Management
	Converged Management
	Auto Discovery
	Remote Management
	Update Management
	Logging and Auditing
	ServerView Suite (Deploy)
	ServerView Installation Manager
	ServerView Scripting Toolkit
	ServerView Suite (Control)
	ServerView Operations Manager (incl. PDA and ASR & R)
	ServerView Agents and CIM provider
	ServerView Agentless Management
	ServerView System Monitor
	SVOM- Event Manager
	ServerView RAID Manager
	SVOM- Threshold Manager
	Power Monitor (monitoring the Power Consumption)
	Power Management (iRMC)
	Storage Management (server) with SVOM/SV-RAID
	ServerView Suite (Maintain)
	iRMC S5 (Remote Management)
	System Update Manager (BIOS, Firmware, Windows Drives and SV Agents)
	Performance management (SVOM)
	Asset Management
	Primecollect
	Customer Self Service
	Online Diagnostics
	ServerView Suite (Integrate)
	ServerView Integration packs for MS System Center, VMware vCenter, VMware vRealize, Nagios, and HP SIM
Option	ServerView Suite (Maintain)
	ServerView eLCM
	iRMC Advanced Pack incl. Advanced Video Redirection (AVR), video capturing and Virtual Media
	ServerView Suite (Dynamize)
	ServerView Virtual IO Manager (SVIOM)
	Infrastructure Manager (ISM)
	Automate device configuration
	Mass OS installation
	Node Management
	Health status Monitoring and Control
	Capacity/Threshold Management
	Power Management
	Converged Management
	Auto Discovery
	Virtual-IO Management
	Network topology Management
	Remote Management
	Update Management
	Logging and Auditing
	Integrate in to
	Enterprise Management
	Vendor specific Management
	Monitor 3rd party platforms
Server Management notes	Regarding dependencies for ServerView Suite software products see dedicated product data sheets.

Dimensions / Weight

Rack (W x D x H)	483 mm (Bezel) / 435mm (Body) x 770.7 x 43 mm
Mounting Depth Rack	748.2 mm
Height Unit Rack	1 U

        http://www.fujitsu.com/global/products/computing/servers/primergy/rack/rx2530m5/

Dimensions / Weight

19" rackmount	Yes
Mounting Cable depth rack	200 mm (1,000 mm Rack recommended)
Weight	up to 16 kg
Weight notes	Actual weight may vary depending on configuration
Rack integration kit	Rack integration kit as option

Environment

Operating ambient temperature	5 - 45 °C (41 - 113 °F)
Operating temperature note	Cool-safe® Advanced Thermal Design (above 35 °C or below 10 °C) depending on configuration. For detailed information see relevant system configurator.
Operating relative humidity	10 - 85 % (non condensing)
Operating environment	FTS 04230 – Guideline for Data Center (installation specification)
Operating environment link	http://docs.ts.fujitsu.com/dl.aspx?id=e4813edf-4a27-461a-8184-983092c12dbe
Noise emission	Measured according to ISO 7779 and declared according to ISO 9296
Sound pressure (LpAm)	Noise typical configuration: 24 dB(A) (idle) / 39 dB(A) (operating)
Sound power (LWAd; 1B = 10dB)	Noise minimum configuration: 4.1 B (idle) / 5.6 B (operating) Noise typical configuration: 5.4 B (idle) / 6.2 B (operating)
Noise notes	Noise emissions depends on operation modes, system configuration and ambient temperature. Typical hardware configuration which is the base for measurement according to ISO 7779: 2x PSU 450W. 2x CPU Xeon 85W, 4x RAM 16GB, 2x HDD 500GB SATA, 6x LAN 1 Gbit/s

Electrical values

Power supply configuration	1 x hot-plug power supply or 2 x hot-plug power supply for redundancy
Hot-plug power supply redundancy	Optional
Active power (max. configuration)	883 W
Apparent power (max. configuration)	892 VA
Heat emission (max. configuration)	3178.8 kJ/h (3012.9 BTU/h)
Rated current max.	10.5 A (100 V) / 5.0 A (240 V)
Active power note	To estimate the power consumption of different configurations use the Power Calculator of the System Architect: http://configurator.ts.fujitsu.com/public/
Power supply	450W hot-plug, 94% (Platinum efficiency), 100-240V, 50 / 60Hz 800W hot-plug, 94% (Platinum efficiency), 100-240V, 50 / 60Hz 800W hot-plug, 96% (Titanium efficiency), 200-240V, 50 / 60Hz 1200W hot-plug, 94% (Platinum efficiency), 100-240V, 50 / 60Hz; 110V range: 1000W, less than 110V: 900W 800W hot-plug, 92% (equivalent to Gold efficiency) –48V DC 1300W hot plug, 94% (equivalent to Platinum efficiency) 380V DC
Power supply notes	Power Safeguard adapts system performance in case the power requirements exceeds supply limits. 96% Titanium Power supply unit is only released for 200-240V

Compliance

Global	CB RoHS (Substance limitations in accordance with global RoHS regulations) WEEE (Waste electrical and electronical equipment)
Germany	GS
Europe	CE
USA/Canada	CSAc/us FCC Class A ICES-003 / NMB-003 Class A
Japan	VCCI:V3 Class A + JIS 61000-3-2
Russia	EAC
South Korea	KC
China	CCC (planned)
Australia/New Zealand	RCM
Taiwan	BSMI (planned)
India	BIS R41004006 (planned)
Compliance link	https://sp.ts.fujitsu.com/sites/certificates

Compliance	
Compliance notes	There is general compliance with the safety requirements of all European countries and North America. National approvals required in order to satisfy statutory regulations or for other reasons can be applied for on request. * Warning: This is a class A product. In a domestic environment this product may cause radio interference in which case the user may be required to take adequate measures.

Components

Optical drives	Blu-ray Disc™ Triple Writer, (6x BD-RW, 8x DVD, 24x CD), ultraslim, SATA I
	DVD Super Multi ultra slim , (8x DVD; 24x CD), ultraslim, SATA I
Hard disk drives	HDD SATA, 6 Gb/s, 12 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 8 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 4 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical
	HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical
	HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical
	HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical

Hard disk drives	HDD SAS, 12 Gb/s, 900 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 900 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 900 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 900 GB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 600 GB , 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 12 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 12 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 10 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 8 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 4 TB, 7,200 rpm, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 2.4 TB, 10,000 rpm, 512e, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 2.4 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 2.4 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 2 TB, 7,200 rpm, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical
	HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 1.2 TB , 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 1 TB, 7,200 rpm, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical

Solid-State-Drive	SSD SATA, 6 Gb/s, 960 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 960 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1.4 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1.4 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 7.68 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.5 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 7.68 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.5 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 3.84 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1.0 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 3.84 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1.0 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 3.84 TB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 3.84 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 1.92 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 1.92 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD M.2 SATA, 6 Gb/s, 480 GB, non hot plug, enterprise, 1.4 DWPD (Drive Writes Per Day for 5 years)
	SSD M.2 SATA, 6 Gb/s, 240 GB, non hot plug, enterprise, 1.4 DWPD (Drive Writes Per Day for 5 years)
	SSD M.2 SATA, 6 Gb/s, 240 GB, non hot plug, enterprise

Solid-State-Drive	SSD SAS, 12 Gb/s, 960 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 960 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 800 GB, Write-Intensive, hot-plug, 3.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 800 GB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years), SED
	SSD SAS, 12 Gb/s, 800 GB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 800 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 800 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 480 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 480 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 400 GB, Write-Intensive, hot-plug, 3.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 400 GB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years), SED
	SSD SAS, 12 Gb/s, 400 GB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 400 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 400 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 7.68 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 3.84 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 3.84 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 3.2 TB, Mixed-use, hot-plug, 3.5-inch, enterprise, 2.3 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 3.2 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 2.3 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 1.92 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 1.92 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 1.6 TB, Write-Intensive, hot-plug, 3.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 1.6 TB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years), SED
	SSD SAS, 12 Gb/s, 1.6 TB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 1.6 TB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (Drive Writes Per Day for 5 years)
	SSD SAS, 12 Gb/s, 1.6 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (Drive Writes Per Day for 5 years)
PCIe SSD & SATA DOM SSD	PCIe-SSD SFF, 750 GB, Write-Intensive, hot-plug, 2.5-inch, Flash drive, 30 DWPD (Drive Writes Per Day for 5 years)
	PCIe-SSD SFF, 6.4 TB, Mixed-use, hot-plug, 2.5-inch, Flash drive, 3.2 DWPD (Drive Writes Per Day for 5 years)
	PCIe-SSD SFF, 6.4 TB, Mixed-use, hot-plug, 2.5-inch, Flash drive, 3.0 DWPD (Drive Writes Per Day for 5 years)
	PCIe-SSD SFF, 4 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 3.0 DWPD (Drive Writes Per Day for 5 years)
	PCIe-SSD SFF, 4 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 0.6 DWPD (Drive Writes Per Day for 5 years)
	PCIe-SSD SFF, 3.2 TB, Mixed-use, hot-plug, 2.5-inch, Flash drive, 3.1 DWPD (Drive Writes Per Day for 5 years)
	PCIe-SSD SFF, 3.2 TB, Mixed-use, hot-plug, 2.5-inch, Flash drive, 3.0 DWPD (Drive Writes Per Day for 5 years)
	PCIe-SSD SFF, 2 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 3.0 DWPD (Drive Writes Per Day for 5 years)
	PCIe-SSD SFF, 2 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 0.6 DWPD (Drive Writes Per Day for 5 years)
	PCIe-SSD SFF, 1.6 TB, Mixed-use, hot-plug, 2.5-inch, Flash drive, 3.0 DWPD (Drive Writes Per Day for 5 years)
	PCIe-SSD SFF, 1 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 3.0 DWPD (Drive Writes Per Day for 5 years)
	PCIe-SSD SFF, 1 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 1 DWPD (Drive Writes Per Day for 5 years)
	PCIe-SSD AIC, 750 GB, Write-Intensive, HHHL, Flash drive, 30 DWPD (Drive Writes Per Day for 5 years)
	PCIe-SSD AIC, 375 GB, Write-Intensive, HHHL, Flash drive, 30 DWPD (Drive Writes Per Day for 5 years)
	Dual microSD 64GB Enterprise
SCSI / SAS Controller	LSI PSAS CP400e LP SAS Ctrl. 12 Gbit/s 8 ports ext. PCIe 3.0 x8
	Fujitsu PSAS CP403i SAS Ctrl. 12 Gbit/s 8 ports int. PCIe 3.0 x8
	Fujitsu PSAS CP400i SAS Ctrl. 12 Gbit/s 8 ports int. PCIe 3.0 x8
	Fujitsu PSAS CP400e FH SAS Ctrl. 12 Gbit/s 8 ports ext. PCIe 3.0 x8

RAID Controller	Fujitsu PRAID EP580i LP, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, NVMe-PCIe 8 Gbit/s, 8 Gbit/s 16 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 8 GB, Optional FBU based on LSI SAS3516
	Fujitsu PRAID EP540i LP, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, NVMe-PCIe 8 Gbit/s, 8 Gbit/s 16 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 4 GB, Optional FBU based on LSI SAS3516
	Fujitsu PRAID EP540e LP, RAID 5/6 Ctrl., SAS 12 Gbit/s, 8 ports ext. RAID level: 0, 1, 10, 5, 50, 6, 60, 4 GB, Optional FBU based on LSI SAS3516
	Fujitsu PRAID EP520i LP, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, NVMe-PCIe 8 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3516
	Fujitsu PRAID EP420i, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3108
	Fujitsu PRAID EP420i for SafeStore, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3108
	Fujitsu PRAID EP400i, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 1 GB, Optional FBU based on LSI SAS3108
	Fujitsu PRAID CP400i, RAID Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 1E, 10, 5, 50, No FBU support
Fibre Channel controller	Fibre Channel Host Bus Adapter 1 x 32 Gbit/s Cavium QLE2740 MMF LC-style
	Fibre Channel Host Bus Adapter 2 x 32 Gbit/s Cavium QLE2742 MMF LC-style
	Fibre Channel Host Bus Adapter 1 x 32 Gbit/s Emulex LPe32000-M6-F MMF LC-style
	Fibre Channel Host Bus Adapter 2 x 32 Gbit/s Emulex LPe32002-M6-F MMF LC-style
	Fibre Channel Host Bus Adapter 1 x 16 Gbit/s Qlogic QLE2690 LC-style
	Fibre Channel Host Bus Adapter 2 x 16 Gbit/s Qlogic QLE2692 LC-style
	Fibre Channel Host Bus Adapter 1 x 16 Gbit/s Emulex LPe31000-M6-F MMF LC-style
	Fibre Channel Host Bus Adapter 2 x 16 Gbit/s Emulex LPe31002-M6-F MMF LC-style
Communication, Network	Converged Network Adapter 2 x 10 Gbit/s / 25 Gbit/s PCIe 3.0 x8 SFP28 (Cavium)
	Ethernet Ctrl. 1 x 100 Gbit/s PCIe 3.0 x16 QSFP28 (Cavium)
	Ethernet Ctrl. 1 x 100 Gbit/s PCIe 3.0 x16 QSFP28 (Mellanox)
	Ethernet Ctrl. 2 x 10 Gbit/s ; 1 Gbit/s PCIe 3.0 x8 RJ45 (Cavium)
	Ethernet Ctrl. 2 x 10 Gbit/s ; 1 Gbit/s PCIe 3.0 x8 RJ45 (Intel®)
	Ethernet Ctrl. 2 x 10 Gbit/s ; 1 Gbit/s PCIe 3.0 x8 SFP+ (Cavium)
	Ethernet Ctrl. 2 x 10 Gbit/s / 25 Gbit/s PCIe 3.0 x8 SFP28 (Cavium)
	Ethernet Ctrl. 2 x 10 Gbit/s / 25 Gbit/s PCIe 3.0 x8 SFP28 (Intel®)
	Ethernet Ctrl. 2 x 10 Gbit/s / 25 Gbit/s PCIe 3.0 x8 SFP28 (Mellanox)
	Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 SFP+ (Intel®)
	Ethernet Ctrl. 2 x 1 Gbit/s PCIe 2.1 x4 RJ45 (Intel®)
	Ethernet Ctrl. 2 x 40 Gbit/s PCIe 3.0 x16 QSFP (Mellanox)
	Ethernet Ctrl. 4 x 10 Gbit/s ; 1 Gbit/s PCIe 3.0 x8 RJ45 (Cavium)
	Ethernet Ctrl. 4 x 10 Gbit/s ; 1 Gbit/s PCIe 3.0 x8 RJ45 (Intel®)
	Ethernet Ctrl. 4 x 10 Gbit/s PCIe 3.0 x8 SFP+ (Intel®)
	Ethernet Ctrl. 4 x 1 Gbit/s PCIe 2.1 x4 RJ45 (Intel®)
	InfiniBand HCA 1 x 100 Gbit/s PCIe 3.0 x16 QSFP for the US market max. one IB HCA 100Gb controller can be installed (Mellanox)
	InfiniBand HCA 2 x 100 Gbit/s PCIe 3.0 x16 QSFP for the US market max. one IB HCA 100Gb controller can be installed (Mellanox)
	Interface modul for Dynamic LoM 2 x 10 Gbit/s RJ45 (Intel®)
	Interface modul for Dynamic LoM 2 x 10 Gbit/s SFP+ (Intel®)
	Interface modul for Dynamic LoM 4 x 10 Gbit/s SFP+ (Intel®)
	Interface modul for Dynamic LoM 4 x 1 Gbit/s RJ45 (Intel®)
	MPO x 40 Gbit/s ( )
	Omni Path 1 x PCIe 3.0 x16 (Intel®)
Graphics	NVIDIA® Quadro® P400 , 2 GB, PCIe x16, 3 x miniDP

Rack infrastructure	Rackmount kit full extraction (815mm), tool less mounting, length variable 559-914mm
	Rackmount kit full extraction (815mm), tool less mounting, length variable 559-914mm
	Rackmount kit tool less mounting
	Cable Management 1U for PRIMECENTER- and 3rd-party racks

Warranty

Warranty period	3 years
Warranty type	Onsite warranty
Warranty Terms & Conditions	http://support.ts.fujitsu.com/warranty/Index.asp?LNG=COM

Product Support Services - the perfect extension

Support Pack Options	Globally available in major business areas: 9x5, Next Business Day Onsite Response Time 9x5, 4h Onsite Response Time (depending on country) 24x7, 4h Onsite Response Time (depending on country)
Recommended Service	24x7, Onsite Response Time: 4h - For locations outside of EMEIA please contact your local Fujitsu partner.
Service Lifecycle	5 years after end of product life
Service Weblink	http://www.fujitsu.com/emeia/products/product-support-services/

More information

Fujitsu products, solutions & services

In addition to FUJITSU Server PRIMERGY RX2530 M5, Fujitsu provides a range of platform solutions. They combine reliable Fujitsu products with the best in services, know-how and worldwide partnerships.

Fujitsu Portfolio

Built on industry standards, Fujitsu offers a full portfolio of IT hardware and software products, services, solutions and cloud offering, ranging from clients to datacenter solutions and includes the broad stack of Business Solutions, as well as the full stack of Cloud offerings. This allows customers to select from alternative sourcing and delivery models to increase their business agility and to improve their IT operation's reliability.

Computing Products

www.fujitsu.com/global/products/computing/

Software

www.fujitsu.com/software/

More information

Learn more about FUJITSU Server PRIMERGY RX2530 M5, please contact your Fujitsu sales representative or Fujitsu Business partner, or visit our website.
www.fujitsu.com/primergy

Fujitsu green policy innovation

Fujitsu Green Policy Innovation is our worldwide project for reducing burdens on the environment.
Using our global know-how, we aim to contribute to the creation of a sustainable environment for future generations through IT. Please find further information at http://www.fujitsu.com/global/about/environment

Copyrights

All rights reserved, including intellectual property rights. Designations may be trademarks and/or copyrights of the respective owner, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see http://www.fujitsu.com/fts/resources/navigation/terms-of-use.html
Copyright 2019 FUJITSU LIMITED

Disclaimer

Technical data is subject to modification and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective owner, the use of which by third parties for their own purposes may infringe the rights of such owner.

---

http://www.fujitsu.com/global/products/computing/servers/primergy/rack/rx2530m5/