



新普科技股份有限公司
新世電子(常熟)有限公司
新普科技(重慶)有限公司
華普電子(常熟)有限公司

Control Number: SASU-2110002

Rechargeable Li-ion Battery UN38.3 Test Report

Recommendations on the TRANSPORT OF DANGEROUS GOODS

(Manual of Tests and Criteria, Seventh revised edition)

Customer: ASUS

Model: C41N2109

Rating/ Mass: 15.52V , 90Wh/ 317(g)

Version of Test Report: 01

Issue date: 2021/10/21

Approved By	Checked By	Prepared By
Project Manager	Authorized Signatory	Test Engineer
<i>Siung Sin</i>	<i>Ennab Huang</i>	<i>Mia cheng</i>

●	SIMPLO TECHNOLOGY CO., LTD. ADD : No. 471 Pa Teh Rd, Sec 2 Hu Kou, Hsinchu Hsien, 303 Taiwan TEL: +886-3-5695920 FAX: +886-3-5695931	
	SIMPLO TECHNOLOGY (CHANGSHU) INC. ADD : No.888 Dongnan Avenue, Changshu New & Hi-Tech Industrial Development Zone, Changshu, Jiangsu, China TEL: +86-512-52302255 FAX: +86-512-52302277	
	SIMPLO TECHNOLOGY (CHONGQING) INC. ADD : No.2 Zongbao Avenue, Shapingba District, ChongQing, China TEL: +86-23-61718899 FAX: +86-23-61210488	
	HUAPU TECHNOLOGY (CHANGSHU) INC. ADD : No.888 Dongnan Avenue, Changshu New & Hi-Tech Industrial Development Zone, Changshu, Jiangsu, China TEL: +86-512-52302255 FAX: +86-512-52302277	

Email : Test_Lab@simplo.com.tw

Website : <http://www.simplo.com.tw/>

Form No. : W11-002-B05

本資料為新普科技股份有限公司之智慧財產權，非經本公司書面授權許可，不得透露或使用本資料，亦不得複印、複製或轉變成其它任何形式使用。
The information contained herein is the exclusive property of SIMPLO TECHNOLOGY CO., LTD, and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission.

本測試報告僅對上述測試項目有效，本報告分離使用無效

Page 1 of 8

This test report is valid only to the items, Invalid for separation using.



新普科技股份有限公司
新世電子(常熟)有限公司
新普科技(重慶)有限公司
華普電子(常熟)有限公司

Control Number: SASU-2110002

1. Purpose of the Test :

To test each cell/battery is of the type proved to meet the requirements in United Nations Recommendations on the TRANSPORT OF DANGEROUS GOODS, Manual of Tests and Criteria, Seventh revised edition, Section 38.3.

2. Test Result :

Test results of the UN Recommendations on the Transport of Dangerous Goods

No.	Test Item	Test results
T.1	Altitude simulation	PASS
T.2	Thermal test	PASS
T.3	Vibration test	PASS
T.4	Shock test	PASS
T.5	External short circuit	PASS
T.6	Impact, Crush test	PASS
T.7	Overcharge	PASS
T.8	Forced discharge	PASS

3. Test Lab: Email : Test_Lab@simplo.com.tw Website : <http://www.simplo.com.tw/>

●	SIMPLO (Taiwan) Laboratory ADD : No. 471 Pa Teh Rd, Sec 2 Hu Kou, Hsinchu Hsien, 303 Taiwan TEL: +886-3-5695920 FAX: +886-3-5695931
	SIMPLO (CHANGSHU) Laboratory ADD : No.888 Dongnan Avenue, Changshu New & Hi-Tech Industrial Development Zone, Changshu, Jiangsu, China TEL: +86-512-52302255 FAX: +86-512-52302277
	SIMPLO (CHONGQING) Laboratory. ADD : No.2 Zongbao Avenue, Shapingba District, ChongQing, China TEL: +86-23-61718899 FAX: +86-23-61210488

Form No. : W11-002-B05

本資料為新普科技股份有限公司之智慧財產權，非經本公司書面授權許可，不得透露或使用本資料，亦不得複印、複製或轉變成其它任何形式使用。
The information contained herein is the exclusive property of SIMPLO TECHNOLOGY CO., LTD, and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission.

本測試報告僅對上述測試項目有效,本報告分離使用無效

This test report is valid only to the items, Invalid for separation using.



新普科技股份有限公司
新世電子(常熟)有限公司
新普科技(重慶)有限公司
華普電子(常熟)有限公司

Control Number: SASU-2110002

4. Product manufacturer : Email : Test_Lab@simplo.com.tw Website : <http://www.simplo.com.tw/>

●	SIMPLO TECHNOLOGY CO., LTD. ADD : No. 471 Pa Teh Rd, Sec 2 Hu Kou, Hsinchu Hsien, 303 Taiwan TEL: +886-3-5695920 FAX: +886-3-5695931
	SIMPLO TECHNOLOGY (CHANGSHU) INC. ADD : No.888 Dongnan Avenue, Changshu New & Hi-Tech Industrial Development Zone, Changshu, Jiangsu, China TEL: +86-512-52302255 FAX: +86-512-52302277
●	SIMPLO TECHNOLOGY (CHONGQING) INC. ADD : No.2 Zongbao Avenue, Shapingba District, ChongQing, China TEL: +86-23-61718899 FAX: +86-23-61210488
	HUAPU TECHNOLOGY (CHANGSHU) INC. ADD : No.888 Dongnan Avenue, Changshu New & Hi-Tech Industrial Development Zone, Changshu, Jiangsu, China TEL: +86-512-52302255 FAX: +86-512-52302277

5. Test Quantity :

- 5.1 Four batteries, at first cycle, in fully charged states. (For T.1~T.5)
- 5.2 Four batteries, after 25 cycles ending in fully charged states. (For T.1~T.5)
- 5.3 Five component cells, at first cycle at 50% of the design rated capacity. (For T.6)
- 5.4 Five component cells, after 25 cycles at 50% of the design rated capacity. (For T.6)
- 5.5 Four batteries, at first cycle, in fully charged states. (For T.7)
- 5.6 Four batteries, after 25 cycles ending in fully charged states. (For T.7)
- 5.7 Ten component cells, at first cycle in fully discharge states. (For T.8)
- 5.8 Ten component cells, after 25 cycles ending in fully discharged states. (For T.8)

Form No. : W11-002-B05

本資料為新普科技股份有限公司之智慧財產權，非經本公司書面授權許可，不得透露或使用本資料，亦不得複印、複製或轉變成其它任何形式使用。
The information contained herein is the exclusive property of SIMPLO TECHNOLOGY CO., LTD, and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission.

本測試報告僅對上述測試項目有效，本報告分離使用無效

Page 3 of 8


This test report is valid only to the items, Invalid for separation using.



6. Test Procedure :

6.1 All detailed test procedures must be based on United Nations Recommendations on the TRANSPORT OF DANGEROUS GOODS, Manual of Tests and Criteria, Seventh revised edition, Section 38.3.

6.2 Test flow shall be followed as below.



Conclusion: The samples had passed the test items of UN38.3.

7. Comment :

Version	Modify content	Issue date
01	First publish	2021/10/21



新普科技股份有限公司
新世電子(常熟)有限公司
新普科技(重慶)有限公司
華普電子(常熟)有限公司

Control Number: SASU-2110002

8. Test Equipment :

SMP SIMPLO TECHNOLOGY CO., LTD.

Address : No.471, Sec.2, Pa Teh Rd., Hu Kou, Hsin Chu Hsien 303, Taiwan

TEL: +886-3-5695920; FAX: +886-3-5695931

Revised Date: 2021-10-21

Test Instruments Reference List								
Used	Instrument ID	Instrument Name	Type	Range of use	Manufacturer	Calibration Date_Last	Calibration Date_Next	Remarks
	Pretest							
V	ML-761	Learning	715C	0~18V 0~8A	SMP	2021/2/4	2022/3/4	
V	ML-762	Learning	715C	0~18V 0~8A	SMP	2021/1/4	2022/2/4	
V	ML-763	Learning	715C	0~18V 0~8A	SMP	2021/2/4	2022/3/4	
V	ML-764	Learning	715C	0~18V 0~8A	SMP	2021/1/4	2022/2/4	
	ML-925	Learning	750C8	0~60V 0~30A	SMP	2021/1/4	2022/2/4	
	T.1 Altitude Simulation							
V	ML-522	Altitude	SVT-120	kPa:30~90	HSIN JIANG	2021/6/11	2022/7/11	
V	ML-257	Multimeter	34401A	Note 1	Agilent	2021/2/4	2022/3/4	
V	ML-955	Electronic Balance	UX1020H	1-1220 gf	SHIMADZU	2021/1/4	2022/2/4	
	ML-1035	Electronic Balance	JWI-700W	30*0.005kg	JADEVER	2021/6/11	2022/7/11	
V	ML-550	Data Logger	313	15~35 °C; 30~80 %RH	CENTER	2021/7/28	2022/8/28	
V	ML-964	Barometric Air Pressure	MP55	750 to 1100 mbar	KIMO	2021/6/10	2022/7/10	
	T.2 Thermal Test							
V	ML-789	Thermal Shock	GTST-080-65-AW	T:-40 to 100°C	GF	2021/1/4	2022/2/4	
V	ML-257	Multimeter	34401A	note 1	Agilent	2021/2/4	2022/3/4	
V	ML-955	Electronic Balance	UX1020H	1-1220 gf	SHIMADZU	2021/1/4	2022/2/4	
	ML-1035	Electronic Balance	JWI-700W	30*0.005kg	JADEVER	2021/6/11	2022/7/11	
V	ML-551	Data Logger	313	15~35 °C; 30~80 %RH	CENTER	2021/7/28	2022/8/28	
	T.3 Vibration							
V	ML-233	Vibration	KD-9636-EM-300F2K-30N80	F:5~2000Hz G:0.2~20G	King Design	2021/7/29	2022/7/29	
V	ML-257	Multimeter	34401A	note 1	Agilent	2021/2/4	2022/3/4	
V	ML-955	Electronic Balance	UX1020H	1-1220 gf	SHIMADZU	2021/1/4	2022/2/4	
	ML-1035	Electronic Balance	JWI-700W	30*0.005kg	JADEVER	2021/6/11	2022/7/11	
V	ML-552	Data Logger	313	15~35 °C; 30~80 %RH	CENTER	2021/7/28	2022/8/28	
	T.4 Shock							
V	ML-056	Shock	DP-1200-25	G:10~600G	King Design	2021/7/29	2022/7/29	
V	ML-257	Multimeter	34401A	note 1	Agilent	2021/2/4	2022/3/4	
V	ML-955	Electronic Balance	UX1020H	1-1220 gf	SHIMADZU	2021/1/4	2022/2/4	
	ML-1035	Electronic Balance	JWI-700W	30*0.005kg	JADEVER	2021/6/11	2022/7/11	
V	ML-551	Data Logger	313	15~35 °C; 30~80 %RH	CENTER	2021/7/28	2022/8/28	
	T.5 External Short Circuit							
V	ML-894	Battery Hister	BT3562	10mΩ ~ 30kΩ	HIOKI	2021/5/6	2022/6/6	
V	ML-459	Data Acquisition	MX100-E-1D	1-100 Vdc, -50 to 200°C	Yokogawa	2021/7/23	2022/8/23	
V	ML-460	Data Acquisition	MX100-E-1D	1-100 Vdc, -50 to 200°C	Yokogawa	2021/7/23	2022/8/23	
V	ML-521	Oven	9031	30~80 °C	YEOU LONG	2021/8/4	2022/9/4	
V	ML-1083	Data Logger	1161	15~35 °C; 30~80 %RH	TES	2021/9/13	2022/10/13	
	T.6 Impact / Crush							
V	ML-458	Data Acquisition	XL122-D	1-100 Vdc, -50 to 150°C	Yokogawa	2021/5/11	2022/6/11	
	ML-1016	Impact Tester			King Design	2021/3/29	2022/4/29	
	ML-553	Crush Tester	BCT-01		Simplo	2021/4/7	2022/5/7	
V	ML-866	Crush Tester	M0654		JYI SHENG	2021/4/7	2022/5/7	
	ML-459	Data Acquisition	MX100-E-1D	1-100 Vdc, -50 to 200°C	Yokogawa	2021/7/23	2022/8/23	

Form No. : W11-002-B05

本資料為新普科技股份有限公司之智慧財產權，非經本公司書面授權許可，不得透露或使用本資料，亦不得複印、複製或轉變成其它任何形式使用。
The information contained herein is the exclusive property of SIMPLO TECHNOLOGY CO., LTD, and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission.

本測試報告僅對上述測試項目有效，本報告分離使用無效

Page 5 of 8

This test report is valid only to the items, Invalid for separation using.



新普科技股份有限公司
新世電子(常熟)有限公司
新普科技(重慶)有限公司
華普電子(常熟)有限公司

Control Number: SASU-2110002

SMP SIMPLO TECHNOLOGY CO., LTD.

Address : No.471, Sec.2, Pa Teh Rd., Hu Kou, Hsin Chu Hsien 303, Taiwan

TEL: +886-3-5695920; FAX: +886-3-5695931

Revised Date: 2021-10-21

Test Instruments Reference List								
Used	Instrument ID	Instrument Name	Type	Range of use	Manufacturer	Calibration Date_Last	Calibration Date_Next	Remarks
	T.7 Overcharge							
	ML-482	Programmable DC Source	DS10014	1-100Vdc, 0.3-14.4A	MOTECH	2021/5/5	2022/6/5	
	ML-484	Programmable DC Source	DS10014	1-100Vdc, 0.3-14.4A	MOTECH	2021/5/5	2022/6/5	
	ML-486	Programmable DC Source	DS10014	1-100Vdc, 0.3-14.4A	MOTECH	2021/5/5	2022/6/5	
	ML-487	Programmable DC Source	DS6024	1-60 Vdc, 0.3-24A	MOTECH	2021/5/5	2022/6/5	
V	ML-1083	Data Logger	1161	15~35 °C; 30~80 %RH	TES	2021/9/13	2022/10/13	
	ML-459	Data Acquisition	MX100-E-1D	1-100 Vdc, -50 to 200°C	Yokogawa	2021/7/23	2022/8/23	
	ML-460	Data Acquisition	MX100-E-1D	1-100 Vdc, -50 to 200°C	Yokogawa	2021/7/23	2022/8/23	
V	ML-918	Overcharge & Forced discharge tester	T901	3~30 Vdc, Charge: 0.05~20A Discharge: 0.02~10A	SMP	2021/5/5	2022/6/5	
	T.8 Forced Discharge							
	ML-132	Electronic Load	3311C	60V,60A, 300W	Prodigit	2021/2/3	2022/3/3	
	ML-133	Electronic Load	3311C	60V,60A, 300W	Prodigit	2021/2/3	2022/3/3	
	ML-136	Electronic Load	3311C	60V,60A, 300W	Prodigit	2021/2/3	2022/3/3	
	ML-192	Electronic Load	3311C	60V,60A, 300W	Prodigit	2021/2/3	2022/3/3	
	ML-269	Electronic Load	3311C	60V,60A, 300W	Prodigit	2021/2/3	2022/3/3	
	ML-532	DC Electronic Load	33511-01	120V, 240A, 3600W	Prodigit	2021/6/11	2022/7/11	
	ML-482	Programmable DC Source	DS10014	1-100Vdc, 0.3-14.4A	MOTECH	2021/5/5	2022/6/5	
	ML-484	Programmable DC Source	DS10014	1-100Vdc, 0.3-14.4A	MOTECH	2021/5/5	2022/6/5	
	ML-486	Programmable DC Source	DS10014	1-100Vdc, 0.3-14.4A	MOTECH	2021/5/5	2022/6/5	
	ML-487	Programmable DC Source	DS6024	1-60 Vdc, 0.3-24A	MOTECH	2021/5/5	2022/6/5	
V	ML-1083	Data Logger	1161	15~35 °C; 30~80 %RH	TES	2021/9/13	2022/10/13	
	ML-459	Data Acquisition	MX100-E-1D	1-100 Vdc, -50 to 200°C	Yokogawa	2021/7/23	2022/8/23	
	ML-460	Data Acquisition	MX100-E-1D	1-100 Vdc, -50 to 200°C	Yokogawa	2021/7/23	2022/8/23	
V	ML-918	Overcharge & Forced discharge tester	T901	3~30 Vdc, Charge: 0.05~20A Discharge: 0.02~10A	SMP	2021/5/5	2022/6/5	
Note 1: DC Voltage: 0.1-1000V; AC Voltage: 0.5-700V at 60Hz, 1kHz; Resistance: 10Ω-10MΩ; DC Current: 0.1mA-3A; AC Current: 0.01-3A at 60Hz, 0.01-1A, at 1kHz.								

Form No. : W11-002-B05

本資料為新普科技股份有限公司之智慧財產權，非經本公司書面授權許可，不得透露或使用本資料，亦不得複印、複製或轉變成其它任何形式使用。
The information contained herein is the exclusive property of SIMPLO TECHNOLOGY CO., LTD, and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission.

本測試報告僅對上述測試項目有效,本報告分離使用無效

Page 6 of 8

This test report is valid only to the items, Invalid for separation using.



新普科技股份有限公司
新世電子(常熟)有限公司
新普科技(重慶)有限公司
華普電子(常熟)有限公司

Control Number: SASU-2110002

9. T.1~T.8 Detail Reports:

UN 38.3 Test Datasheet

UN38.3/ST/SG/AC.10/11/Rev.7

Control Number: SASU-2110002	Customer: ASUS	Model Name: C41N2109	SMP Project Name: NR2203
Pack P/N: 906QA337H (B)	Configuration: 4S1P	Test Duration: 2021/10/04~2021/10/21	Reviewer: Esmond
Cell Vendor: ATL	Cell Model: 4251D9	Cell P/N: 110-2406HB	N/A

Test Sample Identification: ☐ Large Battery ☒ Small Battery ☐ Single-cell Battery

Battery Pack						Component Cell		
Used	Sample No.	Sample State	Used	Sample No.	Sample State	Used	Sample No.	Sample State
V	01~04	1 Cycle, Fully charged	V	05~08	25 Cycles, Fully charged	V	01C~05C	1 Cycle, 50% SOC
V	09~12	1 Cycle, Fully charged	V	13~16	25 Cycles, Fully charged	V	06C~10C	25 Cycles, 50% SOC
						V	11C~20C	1 Cycle, Fully discharged (0% SOC)
						V	21C~30C	25 Cycles, Fully discharged (0% SOC)

T.1 Altitude Simulation

Start time: 2021/10/12 09:10		Ambient temp.: 23.6 °C						Operator: Mia	
Finish time: 2021/10/12 16:07		Sample 01	Sample 02	Sample 03	Sample 04	Sample 05	Sample 06	Sample 07	Sample 08
OCV (V)	Before	17.240	17.158	17.202	17.106	17.173	17.234	17.190	17.112
	After	17.226	17.143	17.190	17.090	17.156	17.223	17.178	17.100
	Residual OCV %	99.92%	99.91%	99.93%	99.91%	99.90%	99.94%	99.93%	99.93%
Mass (g)	Before	315.896	316.703	316.335	315.922	316.046	316.550	315.894	316.262
	After	315.890	316.696	316.329	315.914	316.038	316.544	315.886	316.254
	Mass loss %	0.00%	0.00%	0.00%	0.00%	0.00%	0.00%	0.00%	0.00%
Results		P	P	P	P	P	P	P	P

T.2 Thermal Test

Start time: 2021/10/12 16:30		Ambient temp.: 23.9 °C						Operator: Mia	
Finish time: 2021/10/19 08:41		Sample 01	Sample 02	Sample 03	Sample 04	Sample 05	Sample 06	Sample 07	Sample 08
OCV (V)	Before	17.226	17.143	17.190	17.090	17.156	17.223	17.178	17.100
	After	17.040	16.960	17.002	16.902	16.973	17.034	16.993	16.913
	Residual OCV %	98.92%	98.93%	98.91%	98.90%	98.93%	98.90%	98.92%	98.91%
Mass (g)	Before	315.890	316.696	316.329	315.914	316.038	316.544	315.886	316.254
	After	315.867	316.678	316.307	315.891	316.013	316.525	315.862	316.233
	Mass loss %	0.01%	0.01%	0.01%	0.01%	0.01%	0.01%	0.01%	0.01%
Results		P	P	P	P	P	P	P	P

T.3 Vibration

Start time: 2021/10/19 08:46		Ambient temp.: 23.5 °C						Operator: Mia	
Finish time: 2021/10/20 08:50		Sample 01	Sample 02	Sample 03	Sample 04	Sample 05	Sample 06	Sample 07	Sample 08
OCV (V)	Before	17.040	16.960	17.002	16.902	16.973	17.034	16.993	16.913
	After	17.025	16.950	16.989	16.892	16.958	17.022	16.978	16.901
	Residual OCV %	99.91%	99.94%	99.92%	99.94%	99.91%	99.93%	99.91%	99.93%
Mass (g)	Before	315.867	316.678	316.307	315.891	316.013	316.525	315.862	316.233
	After	315.860	316.672	316.299	315.885	316.006	316.520	315.856	316.228
	Mass loss %	0.00%	0.00%	0.00%	0.00%	0.00%	0.00%	0.00%	0.00%
Results		P	P	P	P	P	P	P	P

T.4 Shock

Start time: 2021/10/20 09:11		Ambient temp.: 23.6 °C						Operator: Mia	
Finish time: 2021/10/20 14:05		Sample 01	Sample 02	Sample 03	Sample 04	Sample 05	Sample 06	Sample 07	Sample 08
OCV (V)	Before	17.025	16.950	16.989	16.892	16.958	17.022	16.978	16.901
	After	17.013	16.935	16.977	16.879	16.947	17.008	16.967	16.889
	Residual OCV %	99.93%	99.91%	99.93%	99.92%	99.94%	99.92%	99.94%	99.93%
Mass (g)	Before	315.860	316.672	316.299	315.885	316.006	316.520	315.856	316.228
	After	315.855	316.671	316.297	315.882	316.004	316.517	315.852	316.225
	Mass loss %	0.00%	0.00%	0.00%	0.00%	0.00%	0.00%	0.00%	0.00%
Results		P	P	P	P	P	P	P	P

Form No. : W11-002-B05

本資料為新普科技股份有限公司之智慧財產權，非經本公司書面授權許可，不得透露或使用本資料，亦不得複印、複製或轉變成其它任何形式使用。
The information contained herein is the exclusive property of SIMPLO TECHNOLOGY CO., LTD, and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission.

本測試報告僅對上述測試項目有效，本報告分離使用無效

This test report is valid only to the items, Invalid for separation using.



新普科技股份有限公司
新世電子(常熟)有限公司
新普科技(重慶)有限公司
華普電子(常熟)有限公司

Control Number: SASU-2110002

T.5 External Short Circuit

Start time: 2021/10/20 14:30	Ambient temp.: 24.0 °C				Operator: Mia			
Finish time: 2021/10/21 08:58	Sample 01	Sample 02	Sample 03	Sample 04	Sample 05	Sample 06	Sample 07	Sample 08
OCV (V)	Before	17.013	16.935	16.977	16.879	16.947	17.008	16.967
	After	0.000	0.000	0.000	0.000	0.000	0.000	0.000
Resistance (<100mΩ)		58.4	60.6	61.7	59.8	60.5	57.9	58.8
Max Temp. (< 170°C)		57.6	57.7	57.3	57.1	57.4	57.6	57.7
Results		P	P	P	P	P	P	P

T.6 Impact / Crush (Component Cell)

UN38.3/ST/SG/AC.10/11/Rev.7

□ Impact - Cylindrical cells not less than 18.0 mm in diameter

■ Crush - Prismatic, pouch, coin/button cells and cylindrical cells less than 18.0 mm in diameter

Start time: 2021/10/13 10:24	Ambient temp.: 23.9 °C				Operator: Mia			
Finish time: 2021/10/21 14:30	Sample 01C	Sample 02C	Sample 03C	Sample 04C	Sample 05C	Sample 06C	Sample 07C	Sample 08C
Initial OCV (V)	3.840	3.833	3.835	3.846	3.841	3.837	3.849	3.842
Max Temp. (< 170°C)	23.9	24.1	23.8	24.2	24.0	24.1	24.3	24.0
Results	P	P	P	P	P	P	P	P
Sample No.	Sample 09C	Sample 10C	Sample 11C	Sample 12C	Sample 13C	Sample 14C	Sample 15C	Sample 16C
Initial OCV (V)	3.837	3.849	3.842	3.834	3.833	3.837	3.849	3.842
Max Temp. (< 170°C)	24.1	24.3	24.0	23.8	24.1	24.3	24.0	23.8
Results	P	P	P	P	P	P	P	P


T.7 Overcharge

Start time: 2021/10/12 10:40	Ambient temp.: 23.7 °C				Operator: Mia			
Finish time: 2021/10/20 11:50	Sample 09	Sample 10	Sample 11	Sample 12	Sample 13	Sample 14	Sample 15	Sample 16
Initial OCV (V)	17.240	17.156	17.203	17.103	17.173	17.236	17.189	17.115
Results	P	P	P	P	P	P	P	P

T.8 Forced Discharge (Component Cell)

Start time: 2021/10/13 08:50	Ambient temp.: 23.7 °C				Operator: Mia			
Finish time: 2021/10/21 10:27	Sample 11C	Sample 12C	Sample 13C	Sample 14C	Sample 15C	Sample 16C	Sample 17C	Sample 18C
Initial OCV (V)	3.446	3.470	3.463	3.455	3.474	3.449	3.467	3.480
Results	P	P	P	P	P	P	P	P
Sample No.	Sample 19C	Sample 20C	Sample 21C	Sample 22C	Sample 23C	Sample 24C	Sample 25C	Sample 26C
Initial OCV (V)	3.451	3.443	3.475	3.469	3.442	3.455	3.458	3.479
Results	P	P	P	P	P	P	P	P
Sample No.	Sample 27C	Sample 28C	Sample 29C	Sample 30C				
Initial OCV (V)	3.460	3.450	3.445	3.476				
Results	P	P	P	P				

9. Test Sample:



Form No. : W11-002-B05

本資料為新普科技股份有限公司之智慧財產權，非經本公司書面授權許可，不得透露或使用本資料，亦不得複印、複製或轉變成其它任何形式使用。
The information contained herein is the exclusive property of SIMPLO TECHNOLOGY CO., LTD, and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission.

本測試報告僅對上述測試項目有效，本報告分離使用無效

This test report is valid only to the items, Invalid for separation using.