

x510 Series

Including x510, x510DP and x510L Series Switches

The Allied Telesis x510 Series of stackable Gigabit Layer 3 switches includes a full range of security and resiliency features, coupled with easy management, making them the ideal choice for network access applications.



Overview

110011001010010

Allied Telesis x510 Series switches are a high-performing and feature-rich choice for today's networks. They offer a versatile solution for Enterprise applications. With a choice of 24- and 48-port models with 1/10Gigabit uplink ports, plus the power of Allied Telesis Virtual Chassis Stacking (VCStackTM), the x510 Series can connect anything from a small workgroup to a large business.

Powerful Network Management

Meeting the increased management requirements of modern converged networks, Allied Telesis Management Framework™ (AMF) automates many everyday tasks including configuration management. The complete network can be managed as a single virtual device with powerful centralized management features. Growing the network can be accomplished with plug-and-play simplicity, and network node recovery is fully zero-touch. AMF Guestnode allows third party devices, such as IP phones and security cameras, to be part of an AMF network.

Network Resiliency

The convergence of network services in the enterprise has led to increasing demand for highly available networks with minimal downtime. VCStack, in conjunction with link aggregation, provides a network with no single point of failure and an easy solution for resiliency in access applications.

Ethernet Protection Switched Ring (EPSRingTM) resilient ring protocol ensures distributed networks have high-speed access to online resources and applications.

The x510 Series can form a VCStack of up to four units for enhanced resiliency

and simplified device management. Full EPSRing support and VCStack LD (Long Distance), which enables stacks to be created over long distance fiber links, make the x510 Series the perfect choice for distributed environments.

Reliable

The x510 Series was designed with reliability in mind, and guarantees continual delivery of essential services. With dual built-in power supplies and near-hitless online stack reconfiguration, maintenance may be performed without affecting network uptime.

The x510DP features dual hotswappable load-sharing power supplies for maximum uptime. With front-to-back or back-to-front cooling options, the x510DP is ideal for data center applications.

The x510L Series switches enable highvalue solutions at the network edge.

Secure

Advanced security features protect the network. Unprecedented control over user access is provided with Network Access Control (NAC), mitigating threats to network infrastructure. This ensures the network is accessed only by known users and devices — all users' adherence to network security policies is checked, and then either access is granted or remediation is offered. Secure access can also be provided for guests.

A secure network environment is guaranteed. The x510 Series offers powerful control over network traffic types, secure management options, loop guard to protect against cabling mistakes, and tri-authentication for comprehensive access control.







Future-proof

The x510 Series ensures a future-proof network, with superior flexibility coupled with the ability to stack multiple units. All x510 Series models feature 1/10 Gigabit uplinks ports and a comprehensive IPv6 feature set, to ensure they are ready for future network traffic demands. All x510 24-port models are Software Defined Networking (SDN) ready and are able to support OpenFlow v1.3.

Environmentally Friendly

The x510 Series supports Energy
Efficient Ethernet (EEE),
automatically reducing the
power consumed by the
switch whenever there is no traffic on
a port. This sophisticated feature can
significantly reduce operating costs by
reducing the power requirements of
the switch and any associated cooling
equipment.

New Features

- ► Allied Telesis Management Framework (AMF) Master
- ► AMF Guestnode
- ▶ Active Fiber Monitoring
- ▶ OpenFlow for SDN
- Microsoft Network Load Balancing (MS NLB) support
- ► VLAN Mirroring (RSPAN)









Key Features

Allied Telesis Management Framework (AMF)

- Allied Telesis Management Framework (AMF) is a sophisticated suite of management tools that provide a simplified approach to network management. Powerful features like centralized management, auto-backup, auto-upgrade, auto-provisioning and auto-recovery enable plug-and-play networking and zero-touch management.
- Any x510 Series switch can operate as the AMF network master, storing firmware and configuration backups for other network nodes. The AMF master enables auto-provisioning and auto-upgrade by providing appropriate files to new network members. New network devices can be pre-provisioned making installation easy because no on-site configuration is required.
- AMF Guestnode allows Allied Telesis wireless access points and further switching products, as well as third party devices such as IP phones and security cameras, to be part of an AMF network.

VCStack (Virtual Chassis Stacking)

▶ Create a VCStack of up to four units with 40 Gbps of stacking bandwidth to each unit. Stacking links are connected in a ring so each device has dual connections to further improve resiliency. VCStack provides a highly available system where network resources are spread out across stacked units, reducing the impact if one of the units fails. Aggregating switch ports on different units across the stack provides excellent network resiliency.

Long-distance Stacking

 Long-distance stacking allows a VCStack to be created over longer distances, perfect for a distributed network environment.

EPSRing (Ethernet Protection Switched Ring)

- ➤ EPSRing and 10 Gigabit Ethernet allow several x510 switches to form high-speed protected rings capable of recovery within as little as 50ms. This feature is perfect for high performance and high availability in enterprise networks.
- Super-Loop Protection (SLP) enables a link between two EPSR nodes to be in separate EPSR domains, improving redundancy and network fault resiliency.

Industry-leading Quality of Service (QoS)

➤ Comprehensive low-latency wire speed QoS provides flow-based traffic management with full classification, prioritization, traffic shaping and min/max bandwidth profiles. Boosted network performance and guaranteed delivery of business-critical Ethernet services and applications are provided. Time-critical services such as voice and video take precedence over non-essential services such as file downloads, maintaining responsiveness of Enterprise applications.

Loop Protection

- ➤ Thrash limiting, also known as rapid MAC movement, detects and resolves network loops. It is highly user-configurable from the rate of looping traffic to the type of action the switch should take when it detects a loop.
- ▶ With thrash limiting, the switch only detects a loop when a storm has occurred, which can potentially cause disruption to the network. To avoid this, loop detection works in conjunction with thrash limiting to send special Loop Detection Frame (LDF) packets that the switch listens for. If a port receives an LDF packet, you can choose to disable the port, disable the link, or send an SNMP trap. This feature can help to detect loops before a network storm occurs, avoiding the risk and inconvenience of traffic disruption.

Power over Ethernet Plus (PoE+)

▶ With PoE, a separate power connection to media endpoints such as IP phones and wireless access points is not necessary. PoE+ reduces costs and provides even greater flexibility, providing the capability to connect devices requiring more power (up to 30 Watts) such as pan, tilt and zoom security cameras.

High Reliability

► The x510 Series switches feature front to back cooling and dual power supply units (PSUs). The x510DP features dual hot-swappable load sharing power supplies for maximum uptime, and the option of either front-to-back or back-to-front cooling. This makes it ideal for use as a top-ofrack data center switch.

Voice VLAN

Voice VLAN automatically separates voice and data traffic into two different VLANs. This automatic separation places delay-sensitive traffic into a voice- dedicated VLAN, which simplifies QoS configurations.

Open Shortest Path First (OSPFv3)

 OSPF is a scalable and adaptive routing protocol for IP networks. The addition of OSPFv3 adds support for IPv6 and further strengthens the Allied Telesis focus on next generation networking.

sFlow

SFlow is an industry-standard technology for monitoring high-speed switched networks. It provides complete visibility into network use, enabling performance optimization, usage accounting/billing, and defense against security threats. Sampled packets sent to a collector ensure it always has a real-time view of network traffic.

VLAN Mirroring (RSPAN)

VLAN mirroring allows traffic from a port on a remote switch to be analysed locally. Traffic being transmitted or received on the port is duplicated and sent across the network on a special VLAN.

Dynamic Host Configuration Protocol (DHCP) Snooping

▶ DHCP servers allocate IP addresses to clients, and the switch keeps a record of addresses issued on each port. IP source guard checks against this DHCP snooping database to ensure only clients with specific IP and/or MAC addresses can access the network. DHCP snooping can be combined with other features, like dynamic ARP inspection, to increase security in Layer 2 switched environments, and also provides a traceable history, which meets the growing legal requirements placed on service providers.

Optical DDM

Most modern optical SFP/SFP+/XFP transceivers support Digital Diagnostics Monitoring (DDM) functions according to the specification SFF-8472. This enables real time monitoring of the various parameters of the transceiver, such as optical output power, temperature, laser bias current and transceiver supply voltage. Easy access to this information simplifies diagnosing problems with optical modules and fiber connections.

Active Fiber Monitoring

Active Fiber Monitoring prevents eavesdropping on fiber communications by monitoring received optical power. If an intrusion is detected, the link can be automatically shut down, or an operator alert can be sent.

Tri-authentication

▶ Authentication options on the x510 Series also include alternatives to IEEE 802.1x port-based authentication, such as web authentication, to enable guest access and MAC authentication for endpoints that do not have an IEEE 802.1x supplicant. All three authentication methods—IEEE 802.1x, MAC-based and Web-based—can be enabled simultaneously on the same port for tri-authentication.

Premium Software License

▶ By default, the x510 Series offers a comprehensive Layer 2 and basic Layer 3 feature set that includes static routing and IPv6 management features. The feature set can easily be elevated to full Layer 3 by applying the premium software license. This adds dynamic routing protocols and Layer 3 multicasting capabilities.


Software Defined Networking (SDN)

 OpenFlow is a key technology that enables the use of SDN to build smart applications that unlock value and reduce cost.

Microsoft Network Load Balancing (MS NLB) Support

 Support for MS NLB, which clusters identical servers together for increased performance through load-sharing.

Key Solutions



Resilient distribution switching

Allied Telesis x510 Series switches are ideal for distribution solutions, where resiliency and flexibility are required. In the above diagram, distribution switches utilize long-distance Virtual Chassis Stacking (VCStackLD) to create a single virtual unit out of multiple devices. By using fiber stacking connectivity, units can be kilometers apart – perfect for a distributed environment.

When combined with link aggregation, VCStack provides a solution with no single point of failure that fully utilizes all network bandwidth.


Allied Telesis x510 Series switches support Enterprises and their use of business-critical online resources and applications, with a resilient and reliable distribution solution.

Peace of mind at the network edge

Allied Telesis x510L Series switches make the ideal choice at the network edge where security, resiliency and flexibility are required. In the above diagram, security is enforced using Network Access Control (NAC) combined with triauthentication to prevent unauthorized users and devices from connecting to the network. Link aggregations are used to provide both resiliency back to the core chassis, and an increase in available bandwidth over a single link. Flexibility is ensured with the range of interface types and PoE options available on the x510L Series.

NETWORK SMARTER x510 Series | 3

Key Solutions



Resilient small network core

The x510DP models have two hot-swappable loadsharing PSUs for the ultimate in reliability and ease of maintenance. The x510DP switches also feature the power of Virtual Chassis Stacking (VCStack), removing any single point of failure from the network, and making them perfect for small business or education solutions.

The diagram shows a pair of x510DP switches in an education environment, where link aggregation between the VCStack core and servers, the firewall, and edge switches provides resilient connectivity.

Allied Telesis edge switches connect and power access points for wireless network connectivity for staff and students, as well as IP security cameras to ensure a safe learning environment.

The Allied Telesis Management Framework (AMF) simplifies and automates many day to day administration tasks, easing the burden of network management. The x510DP switches act as the AMF master, automatically backing up the entire network, and providing plug-and-play network growth and zero-touch unit replacement.

Specifications

PRODUCT	10/100/1000T (RJ-45) COPPER PORTS	100/1000X SFP PORTS	1/10 GIGABIT SFP+ PORTS	10 GIGABIT Stacking Ports	POE+ ENABLED Ports	SWITCHING Fabric	FORWARDING RATE
AT-x510-28GTX	24	-	4 (2 if stacked)	2**	-	128Gbps	95.2Mpps
AT-x510-28GPX	24	-	4 (2 if stacked)	2**	24	128Gbps	95.2Mpps
AT-x510-28GSX	-	24	4 (2 if stacked)	2**	-	128Gbps	95.2Mpps
AT-x510-28GSX-80	-	24	4 (2 if stacked)	2**	-	128Gbps	95.2Mpps
AT-x510-52GTX	48	-	4 (2 if stacked)	2**	-	228Gbps	130.9Mpps
AT-x510-52GPX	48	-	4 (2 if stacked)	2**	48	228Gbps	130.9Mpps
AT-x510DP-28GTX	24	-	4 (2 if stacked)	2**	-	128Gbps	95.2Mpps
AT-x510DP-52GTX	48	-	4 (2 if stacked)	2**	-	228Gbps	130.9Mpps
AT-x510L-28GT	24	-	4 (2 if stacked)*	2**	-	128Gbps	95.2Mpps
AT-x510L-28GP	24	-	4 (2 if stacked)*	2**	24	128Gbps	95.2Mpps
AT-x510L-52GT	48	-	4 (2 if stacked)*	2**	-	228Gbps	130.9Mpps
AT-x510L-52GP	48	-	4 (2 if stacked)*	2**	48	228Gbps	130.9Mpps

^{*} A feature license is required on x510L Series switches to upgrade uplink ports from 1G to 10G

Performance

- 40Gbps of stacking bandwidth
- ► Supports 13KB jumbo frames
- Wirespeed multicasting
- ▶ 4094 configurable VLANs
- Up to 16K MAC addressesUp to 256 OpenFlow v1.3 entries
- ► 512MB DDR SDRAM, 64MB flash memory
- ► Packet buffer memory: AT-x510-28 2MB AT-x510-52 - 4MB

Reliability

- Modular AlliedWare Plus™ operating system
- ► The x510 features dual internal redundant PSUs
- ► The x510-28GSX-80 features dual DC PSUs
- ► The x510DP features dual hot-swappable PSUs, providing uninterrupted power and extra reliability
- ► The x510L has a single internal PSU
- ► Full environmental monitoring of PSUs, fans, temperature and internal voltages. SNMP traps alert network managers in case of any failure

Power Characteristics

- ► AC voltage: 90 to 260V (auto-ranging)
- Frequency: 47 to 63Hz
- ► DC voltage (x510-28GSX-80): -48/-60V

Expandability

- ▶ Stack up to four units in a VCStack
- ▶ Premium license option for additional features
- ► 10G upgrade license for using uplink ports at 10Gbps (x510L models only)

Flexibility and Compatibility

- Gigabit SFP ports on x510-28GSX will support any combination of Allied Telesis 100Mbps and 1000Mbps SFP modules listed in this document under Ordering Information
- ▶ 10G SFP+ ports will support any combination of Allied Telesis 1000Mbps SFP and 10GbE SFP+ modules and direct attach cables listed in this document under Ordering Information*
- Stacking ports can be configured as 10G Ethernet ports*

Diagnostic Tools

- Active Fiber Monitoring detects tampering on optical links
- ▶ Built-In Self Test (BIST)
- ► Find-me device locator
- Automatic link flap detection and port shutdown
- ► Optical Digital Diagnostic Monitoring (DDM)
- ▶ Ping polling and TraceRoute for IPv4 and IPv6
- ► Port and VLAN mirroring (RSPAN)
- ► Cable fault locator (TDR)
- ► UniDirectional Link Detection (UDLD)

IPv4 Features

- ▶ Black hole routing
- ▶ Directed broadcast forwarding
- ▶ DHCP server and relay
- ▶ DNS relay
- ► Equal Cost Multi Path (ECMP) routing
- Policy-based routing
- ► Route redistribution (OSPF, RIP)
- ▶ Static unicast and multicast routes for IPv4
- ► UDP broadcast helper (IP helper)

IPv6 Features

- ► DHCPv6 relay, DHCPv6 client
- ► DNSv6 relay, DNSv6 client
- IPv4 and IPv6 dual stack
- ► IPv6 hardware ACLs
- ▶ Device management over IPv6 networks with SNMPv6, Telnetv6 and SSHv6
- NTPv6 client and server
- Static unicast and multicast routes for IPv6

Management

- ▶ Front panel 7-segment LED provides at-a-glance status and fault information
- Allied Telesis Management Framework (AMF) enables powerful centralized management and zero-touch device installation and recovery
- Try AMF for free with the built-in AMF Starter license

- Console management port on the front panel for ease of access
- Eco-friendly mode allows ports and LEDs to be disabled to save power
- ► Web-based Graphical User Interface (GUI)
- ► Industry-standard CLI with context-sensitive help
- ► Powerful CLI scripting engine
- Comprehensive SNMP MIB support for standardsbased device management
- Built-in text editor
- Event-based triggers allow user-defined scripts to be executed upon selected system events
- USB interface allows software release files, configurations and other files to be stored for backup and distribution to other devices

Quality of Service

- 8 priority queues with a hierarchy of high priority queues for real-time traffic, and mixed scheduling, for each switch port
- Limit bandwidth per port or per traffic class down to 64kbps
- Wirespeed traffic classification with low latency essential for VoIP and real-time streaming media applications
- Policy-based QoS based on VLAN, port, MAC and general packet classifiers
- ▶ Policy-based storm protection
- ► Extensive remarking capabilities
- ► Taildrop for queue congestion control
- Strict priority, weighted round robin or mixed scheduling
- ▶ IP precedence and DiffServ marking based on layer 2, 3 and 4 headers

Resiliency Features

- Stacking ports can be configured as 10G Ethernet norts
- Control Plane Prioritization (CPP) ensures the CPU always has sufficient bandwidth to process network control traffic
- ► Dynamic link failover (host attach)
- ► EPSRing (Ethernet Protection Switched Rings) with SuperLoop Protection (SLP)
- ► EPSR enhanced recovery for extra resiliency

NETWORK SMARTER x510 Series | 5

^{**} Stacking ports can be configured as additional 1G/10G Ethernet ports when unit is not stacked

[►] Port speed and duplex configuration can be set manually or by auto-negotiation

^{*} License required for 10G operation on x510L models

- ► Long-Distance stacking (VCStack-LD)
- ▶ Loop protection: loop detection and thrash limiting
- ▶ PVST+ compatibility mode
- ▶ STP root guard
- ► VCStack fast failover minimizes network disruption

Security Features

- Access Control Lists (ACLs) based on layer 3 and 4 headers
- ► Configurable ACLs for management traffic
- ► Auth-fail and guest VLANs
- Authentication, Authorization and Accounting (AAA)
- Bootloader can be password protected for device security
- ▶ BPDU protection
- ► DHCP snooping, IP source guard and Dynamic ARP Inspection (DAI)
- ► DoS attack blocking and virus throttling
- ▶ Dynamic VLAN assignment
- MAC address filtering and MAC address lockdown

- Network Access and Control (NAC) features manage endpoint security
- ► Port-based learn limits (intrusion detection)
- ▶ Private VLANs provide security and port isolation for multiple customers using the same VLAN
- ► Secure Copy (SCP)
- Strong password security and encryption
- ► Tri-authentication: MAC-based, web-based and IEEE 802.1x
- ▶ RADIUS group selection per VLAN or port

Environmental Specifications

- Operating temperature range: 0°C to 45°C (32°F to 113°F)
 Derated by 1°C per 305 meters (1,000 ft)
- ► Storage temperature range: -25°C to 70°C (-13°F to 158°F)
- Operating relative humidity range: 5% to 90% non-condensing
- Storage relative humidity range: 5% to 95% non-condensing
- Operating altitude: 3,048 meters maximum (10,000 ft)

Electrical Approvals and Compliances

- ► EMC: EN55022 class A, FCC class A, VCCI class A, ICFS-003 class A
- ► Immunity: EN55024, EN61000-3-levels 2 (Harmonics), and 3 (Flicker) AC models only

Safety

- ► Standards: UL60950-1, CAN/CSA-C22.2 No. 60950-1-03, EN60950-1, EN60825-1, AS/NZS 60950-1
- Certification: UL, cUL, TUV (TUV is on all models except the AT-x510DP-52GTX)

Restrictions on Hazardous Substances (RoHS) Compliance

- ► EU RoHS compliant
- ► China RoHS compliant

Country of Origin

▶ China

Physical Specifications

PRODUCT	WIDTH	DEPTH	HEIGHT	MOUNTING	WEIGHT		
rnuuuti	WIDIN	VEFIN	nciuni	MOONTING	UNPACKAGED	PACKAGED	
AT-x510-28GTX	440 mm (17.32 in)	325 mm (12.80 in)	44 mm (1.73 in)	Rack-mount	4.3 kg (9.48 lb)	6.3 kg (13.89 lb)	
AT-x510-28GPX	440 mm (17.32 in)	400 mm (15.75 in)	44 mm (1.73 in)	Rack-mount	5.8 kg (12.79 lb)	7.8 kg (17.20 lb)	
AT-x510-28GSX	440 mm (17.32 in)	325 mm (12.80 in)	44 mm (1.73 in)	Rack-mount	4.8 kg (10.58 lb)	6.8 kg (14.99 lb)	
AT-x510-28GSX-80	440 mm (17.32 in)	325 mm (12.80 in)	44 mm (1.73 in)	Rack-mount	4.8 kg (10.58 lb)	6.8 kg (14.99 lb)	
AT-x510-52GTX	440 mm (17.32 in)	325 mm (12.80 in)	44 mm (1.73 in)	Rack-mount	5.2 kg (11.47 lb)	7.2 kg (15.88 lb)	
AT-x510-52GPX	440 mm (17.32 in)	400 mm (15.75 in)	44 mm (1.73 in)	Rack-mount	6.2 kg (13.67 lb)	8.2 kg (18.08 lb)	
AT-x510DP-28GTX	440 mm (17.32 in)	480 mm (18.89 in)	44 mm (1.73 in)	Rack-mount	5.3 kg (11.68 lb)	7.3 kg (16.09 lb)	
AT-x510DP-52GTX	440 mm (17.32 in)	480 mm (18.89 in)	44 mm (1.73 in)	Rack-mount	5.7 kg (12.57 lb)	7.7 kg (16.98 lb)	
AT-x510L-28GT	440 mm (17.32 in)	325 mm (12.80 in)	44 mm (1.73 in)	Rack-mount	4.2 kg (9.26 lb)	6.2 kg (13.67 lb)	
AT-x510L-28GP	440 mm (17.32 in)	400 mm (15.75 in)	44 mm (1.73 in)	Rack-mount	5.2 kg (11.47 lb)	7.2 kg (15.88 lb)	
AT-x510L-52GT	440 mm (17.32 in)	325 mm (12.80 in)	44 mm (1.73 in)	Rack-mount	4.8 kg (10.58 lb)	6.8 kg (14.99 lb)	
AT-x510L-52GP	440 mm (17.32 in)	400 mm (15.75 in)	44 mm (1.73 in)	Rack-mount	5.7 kg (12.57 lb)	7.7 kg (16.98 lb)	

Power and Noise Characteristics

		NO POE LOAD		FU	FULL POE+ LOAD				BEAV COW
PRODUCT	MAX POWER CONSUMPTION	MAX HEAT DISSIPATION	NOISE	MAX POWER CONSUMPTION	MAX HEAT DISSIPATION	NOISE	MAX POE POWER	MAX 15.4W POE PORTS	MAX 30W POE+ PORTS
AT-x510-28GTX	52W	177 BTU/h	45 dBA	-	-	-	-	-	-
AT-x510-28GPX	67W	229 BTU/h	45 dBA	530W	605 BTU/h	55 dBA	370W	24	12
AT-x510-28GSX	74W	252 BTU/h	45 dBA	-	-	-	-	-	-
AT-x510-28GSX-80	74W	252 BTU/h	45 dBA	-	-	-	-	-	-
AT-x510-52GTX	86W	293 BTU/h	45 dBA	-	-	-	-	-	-
AT-x510-52GPX	93W	317 BTU/h	45 dBA	550W	620 BTU/h	55 dBA	370W	24	12
AT-x510DP-28GTX	66W	225 BTU/h	44 dBA	-	-	-	-	-	-
AT-x510DP-52GTX	95W	324 BTU/h	44 dBA	-	-	-	-	-	-
AT-x510L-28GT	52W	177 BTU/h	45 dBA	-	-	-	-	-	-
AT-x510L-28GP	67W	229 BTU/h	45 dBA	290W	330 BTU/h	55 dBA	185W	12	6
AT-x510L-52GT	86W	293 BTU/h	45 dBA	-	-	-	-	-	-
AT-x510L-52GP	93W	317 BTU/h	45 dBA	320W	365 BTU/h	55 dBA	185W	12	6

Noise: tested to IS07779; front bystander position

Latency (microseconds)

PRODUCT		PORT SP	EED	
PRUDUCI	10MBPS	100MBPS	1GBPS	10GBPS
AT-x510-28GTX	66µs	9.3µs	3.9µs	3.0µs
AT-x510-28GSX	65 μs	9.4µs	3.9µs	3.0µs
AT-x510-28GPX	66 μs	9.3µs	3.9µs	3.0µs
AT-x510-28GSX-80	66 μs	9.3µs	3.9µs	3.0µs
AT-x510-52GTX	68 μs	11.7µs	6.2µs	4.8µs
AT-x510-52GPX	68 μs	11.7µs	6.2µs	4.8µs
AT-x510DP-28GTX	66 μs	9.3µs	3.9µs	3.0µs
AT-x510DP-52GTX	68 μs	11.7µs	6.2µs	4.8µs
AT-x510L-28GT	66 μs	9.3µs	3.9µs	3.0µs
AT-x510L-28GP	66 μs	9.3µs	3.9µs	3.0µs
AT-x510L-52GT	68 μs	11.7µs	6.2µs	4.8µs
AT-x510L-52GP	68 μs	11.7µs	6.2µs	4.9 µs

Standards	and	Protocols
-----------	-----	------------------

AlliedWare Plus Operating System

Version 5.4.6-1

Cryptographic Algorithms FIPS Approved Algorithms

Encryption (Block Ciphers):

- ► AES (ECB, CBC, CFB and OFB Modes)
- ▶ 3DES (ECB, CBC, CFB and OFB Modes)
- Block Cipher Modes:
- ► CCM
- ► CMAC ► GCM
- ► XTS

Digital Signatures & Asymmetric Key Generation:

- ► DSA
- ► ECDSA
- ► RSA

Secure Hashing:

- ► SHA-1
- ► SHA-2 (SHA-224, SHA-256, SHA-384. SHA-512) Message Authentication:
- ► HMAC (SHA-1, SHA-2(224, 256, 384, 512)

Random Number Generation:

► DRBG (Hash, HMAC and Counter)

Non FIPS Approved Algorithms

RNG (AES128/192/256)

DES MD5

Ethernet

IEEE 802.1AXLink aggregation (static and LACP)

IEEE 802.2 Logical Link Control (LLC)

IEEE 802.3 Ethernet

IEEE 802.3ab1000BASE-T

IEEE 802.3adStatic and dynamic link aggregation

IEEE 802.3ae10 Gigabit Ethernet

IEEE 802.3af Power over Ethernet (PoE)

IEEE 802.3at Power over Ethernet Plus (PoE+)
IEEE 802.3azEnergy Efficient Ethernet (EEE)

IEEE 802.3azEnergy Effici

IEEE 802.3x Flow control – full-duplex operation

IEEE 802.3z 1000BASE-X

IPv4 Features

RFC 768 User Datagram Protocol (UDP) RFC 791 Internet Protocol (IP)

RFC 792	Internet Control Message Protocol (ICMP)
RFC 793	Transmission Control Protocol (TCP)
RFC 826	Address Resolution Protocol (ARP)
RFC 894	Standard for the transmission of IP
	datagrams over Ethernet networks
RFC 919	Broadcasting Internet datagrams
RFC 922	Broadcasting Internet datagrams in the
	presence of subnets
RFC 932	Subnetwork addressing scheme
RFC 950	Internet standard subnetting procedure
RFC 951	Bootstrap Protocol (BootP)
RFC 1027	Proxy ARP
RFC 1035	DNS client
RFC 1042	Standard for the transmission of IP
	datagrams over IEEE 802 networks
RFC 1071	Computing the Internet checksum
RFC 1122	Internet host requirements
RFC 1191	Path MTU discovery
RFC 1256	ICMP router discovery messages
RFC 1518	An architecture for IP address allocation with CIDR
RFC 1519	Classless Inter-Domain Routing (CIDR)
RFC 1542	Clarifications and extensions for BootP
RFC 1591	Domain Name System (DNS)
RFC 1812	Requirements for IPv4 routers
RFC 1918	IP addressing
RFC 2581	TCP congestion control

IPv6 Features

RFC 1981 Path MTU discovery for IPv6

REC 2460 IPv6 specification

111 6 2400	ir vo specification
RFC 2464	Transmission of IPv6 packets over Ethernet
	networks
RFC 3056	Connection of IPv6 domains via IPv4 clouds
RFC 3484	Default address selection for IPv6
RFC 3596	DNS extensions to support IPv6
RFC 4007	IPv6 scoped address architecture
RFC 4193	Unique local IPv6 unicast addresses
RFC 4291	IPv6 addressing architecture
RFC 4443	Internet Control Message Protocol (ICMPv6)
RFC 4861	Neighbor discovery for IPv6
RFC 4862	IPv6 Stateless Address Auto-Configuration
	(SLAAC)
RFC 5014	IPv6 socket API for source address selection
RFC 5095	Deprecation of type 0 routing headers in IPv6
RFC 5175	IPv6 Router Advertisement (RA) flags option
RFC 6105	IPv6 Router Advertisement (RA) guard

Management

AT Enterprise MIB AMF MIB and traps Optical DDM MIB SNMPv1, v2c and v3

IEEE 802.1ABLink Layer Discovery Protocol (LLDP)

RFC 1155	Structure and identification of management information for TCP/IP-based Internets
RFC 1157	Simple Network Management Protocol (SNMP)
RFC 1212	Concise MIB definitions
RFC 1213	MIB for network management of TCP/
	IP-based Internets: MIB-II
RFC 1215	Convention for defining traps for use with the SNMP
RFC 1227	SNMP MUX protocol and MIB
RFC 1239	Standard MIB
RFC 1724	RIPv2 MIB extension
RFC 2096	IP forwarding table MIB
RFC 2578	Structure of Management Information v2 (SMIv2)
RFC 2579	Textual conventions for SMIv2
RFC 2580	Conformance statements for SMIv2
RFC 2674	Definitions of managed objects for bridges
	with traffic classes, multicast filtering and
	VLAN extensions
RFC 2741	Agent extensibility (AgentX) protocol
RFC 2787	Definitions of managed objects for VRRP
RFC 2819	RMON MIB (groups 1,2,3 and 9)
RFC 2863	Interfaces group MIB
RFC 3164	Syslog protocol
RFC 3176	sFlow: a method for monitoring traffic in switched and routed networks
RFC 3411	An architecture for describing SNMP
	management frameworks
RFC 3412	Message processing and dispatching for the SNMP
RFC 3413	SNMP applications
RFC 3414	User-based Security Model (USM) for SNMPv3
RFC 3415	View-based Access Control Model (VACM) for SNMP
RFC 3416	Version 2 of the protocol operations for the SNMP
RFC 3417	Transport mappings for the SNMP
RFC 3418	MIB for SNMP
RFC 3621	Power over Ethernet (PoE) MIB
RFC 3635	Definitions of managed objects for the Ethernet-like interface types
RFC 3636	IEEE 802.3 MAU MIB
RFC 4022	SNMPv2 MIB for TCP using SMIv2
RFC 4113	SNMPv2 MIB for UDP using SMIv2
RFC 4293	SNMPv2 MIB for IP using SMIv2
RFC 4188	Definitions of managed objects for bridges
RFC 4318	Definitions of managed objects for bridges with RSTP
RFC 4560	Definitions of managed objects for remote
	ping, traceroute and lookup operations
DEC CEAT	Definitions of managed chicate for VDDDv2

RFC 6527 Definitions of managed objects for VRRPv3

NETWORK SMARTER x510 Series | 7

Multica	st Support	Quality	of Service (QoS)	RFC 4251	Secure Shell (SSHv2) protoco
Bootstrap R	outer (BSR) mechanism for PIM-SM	IEEE 802.1p	Priority tagging	RFC 4252	Secure Shell (SSHv2) authent
IGMP query	solicitation	RFC 2211	Specification of the controlled-load network	RFC 4253	Secure Shell (SSHv2) transpo
IGMP snoop	oing (v1, v2 and v3)		element service	RFC 4254	Secure Shell (SSHv2) connect
IGMP/MLD	multicast forwarding (IGMP/MLD proxy)	RFC 2474	DiffServ precedence for eight queues/port	RFC 5246	TLS v1.2
MLD snoop	ing (v1 and v2)	RFC 2475	DiffServ architecture		
PIM for IPv6	S and SSM for IPv6	RFC 2597	DiffServ Assured Forwarding (AF)	Service	S
RFC 2236	Internet Group Management Protocol v2	RFC 2697	A single-rate three-color marker	RFC 854	Telnet protocol specification
	(IGMPv2)	RFC 2698	A two-rate three-color marker	RFC 855	Telnet option specifications
RFC 2710	Multicast Listener Discovery (MLD) for IPv6	RFC 3246	DiffServ Expedited Forwarding (EF)	RFC 857	Telnet echo option
RFC 2818	HTTP over TLS ("HTTPS")			RFC 858	Telnet suppress go ahead opt
RFC 3280	Internet X.509 PKI Certificate and Certificate	Resilien	cy Features	RFC 1091	Telnet terminal-type option
	Revocation List (CRL) profile		MAC bridges	RFC 1350	Trivial File Transfer Protocol (7
RFC 3376	IGMPv3		Multiple Spanning Tree Protocol (MSTP)	RFC 1985	SMTP service extension
RFC 3810	Multicast Listener Discovery v2 (MLDv2) for		Rapid Spanning Tree Protocol (RSTP)	RFC 2049	MIME
	IPv6	RFC 5798	Virtual Router Redundancy Protocol version 3	RFC 2131	DHCPv4 (server, relay and clie
RFC 3973	PIM Dense Mode (DM)		(VRRPv3) for IPv4 and IPv6	RFC 2132	DHCP options and BootP vend
RFC 4541	IGMP and MLD snooping switches		(**************************************	RFC 2554	SMTP service extension for a
RFC 4601	Protocol Independent Multicast - Sparse	Routing	Information Protocol (RIP)	RFC 2616	Hypertext Transfer Protocol -
	Mode (PIM-SM): protocol specification	RFC 1058	Routing Information Protocol (RIP)	RFC 2821	Simple Mail Transfer Protocol
	(revised)	RFC 2080	RIPng for IPv6	RFC 2822	Internet message format
RFC 4604	Using IGMPv3 and MLDv2 for source-	RFC 2081	RIPng protocol applicability statement	RFC 3046	DHCP relay agent information
	specific multicast	RFC 2082	RIP-2 MD5 authentication		option 82)
RFC 4607	Source-specific multicast for IP	RFC 2453	RIPv2	RFC 3315	DHCPv6 (server, relay and clie
		111 0 2400	1111 1/2	RFC 3633	IPv6 prefix options for DHCPv
Open S	hortest Path First (OSPF)	Coourity	. Eastures	RFC 3646	DNS configuration options for
•	ocal signaling	-	r Features	RFC 3993	Subscriber-ID suboption for D
	authentication	SSH remote	0		agent option
		SSLv2 and S	ODLV3	DEC 4000	Cincola Nationali Tinca Dueta an

OSPF restart signaling Out-of-band LSDB resync OSPF protocol analysis RFC 1245 Experience with the OSPF protocol RFC 1246 RFC 1370 Applicability statement for OSPF RFC 1765 OSPF database overflow RFC 2328 OSPFv2 RFC 2370 OSPF opaque LSA option OSPFv3 for IPv6 RFC 2740 RFC 3101 OSPF Not-So-Stubby Area (NSSA) option RFC 3509 Alternative implementations of OSPF area border routers RFC 3623 Graceful OSPF restart Traffic engineering extensions to OSPF RFC 3630 RFC 4552 Authentication/confidentiality for OSPFv3

Traffic engineering extensions to OSPFv3

RFC 5329

TACACS+ accounting and authentication IEEE 802.1X authentication protocols (TLS, TTLS, PEAP and MD5) IEEE 802.1X multi-supplicant authentication IEEE 802.1X port-based network access control RFC 2818 HTTP over TLS ("HTTPS") RFC 2865 RADIUS RADIUS accounting RFC 2866 RFC 2868 RADIUS attributes for tunnel protocol support RFC 3280 Internet X.509 PKI Certificate and Certificate Revocation List (CRL) profile RFC 3546 Transport Layer Security (TLS) extensions RADIUS support for Extensible RFC 3579 Authentication Protocol (EAP) RFC 3580 IEEE 802.1x RADIUS usage guidelines

PPP Extensible Authentication Protocol (EAP)

RFC 4251	Secure Shell (SSHv2) protocol architecture
RFC 4252	Secure Shell (SSHv2) authentication protocol
RFC 4253	Secure Shell (SSHv2) transport layer protocol
RFC 4254	Secure Shell (SSHv2) connection protocol
RFC 5246	TLS v1.2

RFC 855	Telnet option specifications
RFC 857	Telnet echo option
RFC 858	Telnet suppress go ahead option
RFC 1091	Telnet terminal-type option
RFC 1350	Trivial File Transfer Protocol (TFTP)
RFC 1985	SMTP service extension
RFC 2049	MIME
RFC 2131	DHCPv4 (server, relay and client)
RFC 2132	DHCP options and BootP vendor extensions
RFC 2554	SMTP service extension for authentication
RFC 2616	Hypertext Transfer Protocol - HTTP/1.1
RFC 2821	Simple Mail Transfer Protocol (SMTP)
RFC 2822	Internet message format
RFC 3046	DHCP relay agent information option (DHCF
	option 82)
RFC 3315	DHCPv6 (server, relay and client)
RFC 3633	IPv6 prefix options for DHCPv6
RFC 3646	DNS configuration options for DHCPv6
RFC 3993	Subscriber-ID suboption for DHCP relay
	agent option
RFC 4330	Simple Network Time Protocol (SNTP)
	version 4
RFC 5905	Network Time Protocol (NTP) version 4

VLAN Support

Generic VLAN Registration Protocol (GVRP) IEEE 802.1ad Provider bridges (VLAN stacking, Q-in-Q) IEEE 802.1Q Virtual LAN (VLAN) bridges IEEE 802.1v VLAN classification by protocol and port IEEE 802.3acVLAN tagging

Voice over IP (VoIP)

LLDP-MED ANSI/TIA-1057 Voice VLAN

Ordering Information

RFC 3748

NAME	DESCRIPTION	INCLUDES	STACK LICENSING
AT-FL-x510-01	x510 premium license	 ▶ RIP (256 routes) ▶ OSPF (256 routes) ▶ PIMv4-SM, DM and SSM ▶ EPSR master ▶ VLAN double tagging (Q-in-Q) ▶ RIPng (256 routes) ▶ OSPFv3 (256 routes) ▶ MLDv1 and v2 ▶ PIMv6-SM ▶ UDLD 	➤ One license per stack member
AT-FL-x510L-10G	10G upgrade license (x510L only)	 Upgrades the 1G uplink ports to 1G/10G on x510L for Ethernet operation. License not required to enable stacking. 	One license per stack member
AT-FL-x510-AM20-1YR	AMF Master license	► AMF Master 20 nodes for 1 year	► One license per stack
AT-FL-x510-AM20-5YR	AMF Master License	► AMF Master 20 nodes for 5 years	► One license per stack
AT-FL-x510-0F13	OpenFlow license	► OpenFlow v1.3	Not supported on a stack

8 | x510 Series alliedtelesis.com

Switches

AT-x510-28GTX-xx

24-port 10/100/1000T stackable switch with 4 SFP+ ports and 2 fixed power supplies

AT-x510-28GPX-xx

24-port 10/100/1000T PoE+ stackable switch with 4 SFP+ ports and 2 fixed power supplies

AT-x510-28GSX-xx

24-port 100/1000X SFP stackable switch with 4 SFP+ ports and 2 fixed power supplies

AT-x510-28GSX-80

24-port 100/1000X SFP stackable switch with 4 SFP+ ports and 2 fixed DC power supplies

AT-x510-52GTX-xx

48-port 10/100/1000T stackable switch with 4 SFP+ ports and 2 fixed power supplies

AT-x510-52GPX-xx

48-port 10/100/1000T PoE+ stackable switch with 4 SFP+ ports and 2 fixed power supplies

AT-x510DP-28GTX-00

24-port 10/100/1000T stackable switch with 4 SFP+ ports and 2 hot-swappable power supplies*

AT-x510DP-52GTX-00

48-port 10/100/1000T stackable switch with 4 SFP+ ports and 2 hot-swappable power supplies*

AT-x510L-28GT-xx

24-port 10/100/1000T switch with 4x1G SFP uplink ports (software upgradeable to 10G SFP+ ports) and a single fixed PSU

AT-x510L-28GP-xx

24-port 10/100/1000T PoE+ switch with 4x1G SFP uplink ports (software upgradeable to 10G SFP+ ports) and a single fixed PSU

AT-x510L-52GT-xx

48-port 10/100/1000T switch with 4x1G SFP uplink ports (software upgradeable to 10G SFP+ ports) and a single fixed PSU

AT-x510L-52GP-xx**

48-port 10/100/1000T PoE+ switch with 4x1G SFP uplink ports (software upgradeable to 10G SFP+ ports) and a single fixed PSU

AT-RKMT-SL01

Sliding rack mount kit for x510DP models

Where xx = 10 for US power cord

20 for no power cord 30 for UK power cord

40 for Australian power cord

50 for European power cord

Power Supplies (for the x510DP Series)

AT-PWR100R-xx

100W AC system power supply (reverse airflow)

AT- PWR250-xx

250W AC system power supply

AT-PWR250R-80

250W DC system power supply (reverse airflow)

1000Mbps SFP Modules

AT-SPTX

1000T 100 m copper

AT-SPSX

1000SX GbE multi-mode 850 nm fiber up to 550 m

AT-SPE

1000X GbE multi-mode 1310 nm fiber up to 2 km $\,$

AT-SPLX10

1000LX GbE single-mode 1310 nm fiber up to 10 km $\,$

AT-SPLX10/I

1000LX GbE single-mode 1310 nm fiber up to 10 km industrial temperature

AT-SPBD10-13

1000LX GbE Bi-Di (1310 nm Tx, 1490 nm Rx) fiber up to 10 km $\,$

AT-SPBD10-14

1000LX GbE Bi-Di (1490 nm Tx, 1310 nm Rx) fiber up to 10 km

AT-SPLX40

1000LX GbE single-mode 1310 nm fiber up to 40 km

AT-SPZX80

1000ZX GbE single-mode 1550 nm fiber up to 80 km $\,$

100Mbps SFP Modules

100Mbps SFP modules are only compatible with the SFP ports on the AT-x510-28GSX switch.

AT-SPFX/2

100FX multi-mode 1310 nm fiber up to 2 km

AT-SPFX/15

100FX single-mode 1310 nm fiber up to 15 km

AT-SPFXBD-LC-13

100BX Bi-Di (1310 nm Tx, 1550 nm Rx) fiber up to 10 km $\,$

AT-SPFXBD-LC-15

100BX Bi-Di (1550 nm Tx, 1310nm Rx) fiber up to 10 km $\,$

10GbE SFP+ Modules

AT-SP10SR***

10GSR 850 nm short-haul, 300 m with MMF

AT-SP10SR/I

10GSR 850 nm short-haul, 300 m with MMF industrial temperature

AT-SP10LRM

10GLRM 1310 nm short-haul, 220 m with MMF

AT-SP10LR***

10GLR 1310 nm medium-haul, 10 km with SMF

AT-SP10LR/I

10GLR 1310 nm medium-haul, 10 km with SMF industrial temperature

AT-SP10LR20/I

10GER 1310nm long-haul, 20 km with SMF industrial temperature

AT-SP10ER40/I***

10GER 1310nm long-haul, 40 km with SMF industrial temperature

AT-SP10ZR80/I***

10GER 1550nm long-haul, 80 km with SMF industrial temperature

AT-SP10TW1

1 meter SFP+ direct attach cable

AT-SP10TW3

3 meter SFP+ direct attach cable

AT-SP10TW7

7 meter SFP+ direct attach cable

✓ Allied Telesis

NETWORK SMARTER

North America Headquarters | 19800 North Creek Parkway | Suite 100 | Bothell | WA 98011 | USA | T: +1 800 424 4284 | F: +1 425 481 3895 Asia-Pacific Headquarters | 11 Tai Seng Link | Singapore | 534182 | T: +65 6383 3832 | F: +65 6383 3830 EMEA & CSA Operations | Incheonweg 7 | 1437 EK Rozenburg | The Netherlands | T: +31 20 7950020 | F: +31 20 7950021

^{*} Power supplies ordered separately

^{**} AT-x510L-52GP not available in NA

^{***} These modules support dual-rate 1G/10G operation