

Data Sheet

FUJITSU Server PRIMERGY TX1330 M2 Tower Server

Expandable all-round server for SMEs

FUJITSU Server PRIMERGY will give you the servers you need to power any workload and changing business requirements. As business processes expand so does the need for applications. Each has its own resource footprint, so you need a way to optimize your computing to better serve your users. PRIMERGY systems will help you match your computing capabilities to your business priorities with our complete portfolio of expandable PRIMERGY tower servers for remote and branch offices, versatile rack-mount servers, compact and scalable blade systems, as well as hyper-converged scale-out servers. They convince by business proven quality with a wide range of innovations, highest efficiency cutting operational cost and complexity, provide more agility in daily operations, and integrate seamlessly to let help you concentrate on core business functions.

Perfect for small and medium businesses as well as branch offices, FUJITSU Server PRIMERGY TX tower systems are robust and cost-efficient servers by providing rock solid reliability. Additionally they are characterized by simple IT operations, low power consumption and quiet operation so that they can be handled by non-technically trained staff and can be used in standard office environments. By the way: Almost all PRIMERGY TX servers can be rack-mounted to offer best flexibility.

PRIMERGY TX1330 M2

The FUJITSU Server PRIMERGY TX1330 M2 is the ideal robust, expandable, and cost-efficient server for small and medium-sized businesses (SMB) or branch offices. It offers best Intel® Xeon® E3 family performance and great expandability thanks to up to 24 hot-plug storage drives. The optional redundancy features and a choice of different RAID controllers ensure high availability and peace of mind. Thanks to its compact housing and low operating noise the server is ideally suited for

showrooms or offices, for example under the desk. The support of legacy PCI adapter cards makes the PRIMERGY TX1330 M2 optimally suited for special solutions, such as telephone or security systems. Furthermore, the comprehensive Fujitsu ServerView® Suite provides support for administrators during server installation, deployment and administration.



Features & Benefits

Main Features	Benefits
<p>Cost-effective performance meets high availability</p> <ul style="list-style-type: none"> ■ Latest Intel® Xeon® processor E3 v5 family technology ■ Optional redundant fans and hot-plug power supply units <p>Optimized for SMEs</p> <ul style="list-style-type: none"> ■ Low noise emissions through optimized air flow and Fujitsu's Cool-safe® technology ■ Compact 4 U chassis ■ Fujitsu ServerView Suite including tools for installation and deployment, permanent status monitoring and control <p>Lifecycle investment protection</p> <ul style="list-style-type: none"> ■ Great scalability with up to 64 GB DDR4 memory, up to 24 storage drives and 4 PCI slots ■ Support for legacy PCI cards ■ Tower to rack conversion kit and extensive connectivity options <p>Integrated UPS - Easy & reliable</p> <ul style="list-style-type: none"> ■ The Fujitsu FJBU internal battery backup is an alternative for classical UPS devices ■ Compact battery unit that fits into modular PSU slot ■ Ni-MH battery allows for a very long life time (5 years) ■ Full integration into server management environment 	<ul style="list-style-type: none"> ■ Optimized for classic server tasks like business applications, file, print or databases ■ Lean server or high availability? Redundancy features exactly tailored to suit the business ■ Silent operation for use in offices or showrooms ■ Small and silent enough to be placed under desks ■ The comprehensive tools of the Fujitsu ServerView Suite eases the administrator's life ■ Meet today's demand and be prepared for future requirements ■ Support for special solutions like telephone or security systems ■ The PRIMERGY TX1330 M2 grows as the company grows, making it an excellent long-term investment ■ Keeps the server running during short blackouts or voltage fluctuations and enables a graceful shutdown ■ Same life time as the server – no maintenance necessary ■ Easy and clean setup: no cabling, no separate device

Technical details

PRIMERGY TX1330 M2

Base unit	PRIMERGY TX1330 M2	PRIMERGY TX1330 M2	PRIMERGY TX1330 M2
Housing types	Tower	Tower	Rack
Power supply	Standard	Hot-plug	Hot-plug
Product Type	Mono Socket Tower Server	Mono Socket Tower Server	Mono Socket Tower Server

Mainboard

Mainboard type	D3373
Chipset	Intel® C236
Processor quantity and type	1 x Intel® Pentium® processor / Intel® Core™ i3 processor / Intel® Xeon® processor E3-1200 v5 product family

Processor

Intel® Celeron® processor G3900 (2C/2T, 2.80 GHz, TLC: 2 MB, Turbo: No, 2,133 MHz, 51 W)
Intel® Core™ i3-6100 processor (2C/4T, 3.70 GHz, TLC: 3 MB, Turbo: No, 2,133 MHz, 51 W)
Intel® Pentium® processor G4400 (2C/2T, 3.30 GHz, TLC: 3 MB, Turbo: No, 2,133 MHz, 54 W)
Intel® Xeon® processor E3-1220v5 (4C/4T, 3.00 GHz, TLC: 8 MB, Turbo: 3.50 GHz, 2,133 MHz, 80 W)
Intel® Xeon® processor E3-1225v5 (4C/4T, 3.30 GHz, TLC: 8 MB, Turbo: 3.70 GHz, 2,133 MHz, 80 W)
Intel® Xeon® processor E3-1230v5 (4C/8T, 3.40 GHz, TLC: 8 MB, Turbo: 3.80 GHz, 2,133 MHz, 80 W)
Intel® Xeon® processor E3-1240Lv5 (4C/8T, 2.10 GHz, TLC: 8 MB, Turbo: 3.20 GHz, 2,133 MHz, 25 W)
Intel® Xeon® processor E3-1240v5 (4C/8T, 3.50 GHz, TLC: 8 MB, Turbo: 3.90 GHz, 2,133 MHz, 80 W)
Intel® Xeon® processor E3-1270v5 (4C/8T, 3.60 GHz, TLC: 8 MB, Turbo: 4.00 GHz, 2,133 MHz, 80 W)
Intel® Xeon® processor E3-1280v5 (4C/8T, 3.70 GHz, TLC: 8 MB, Turbo: 4.00 GHz, 2,133 MHz, 80 W)

Memory slots	4
Memory slot type	DIMM (DDR4)
Memory capacity (min. - max.)	4 GB - 64 GB
Memory protection	ECC
Memory notes	Mix and match possible; with dual channel operation better performance (2 modules with equal capacity necessary). Single channel (1 module) configuration possible.

Memory options

4 GB (1 module(s) 4 GB) DDR4, unbuffered, ECC, 2,133 MHz, PC4-2133, DIMM, 1Rx8
8 GB (1 module(s) 8 GB) DDR4, unbuffered, ECC, 2,133 MHz, PC4-2133, DIMM, 2Rx8
16 GB (1 module(s) 16 GB) DDR4, unbuffered, ECC, 2,133 MHz, PC4-2133, DIMM, 2Rx8

Memory modules notes	2,133 MHz memory modules
----------------------	--------------------------

Interfaces

USB 2.0 ports	5 (4x external rear, 1x internal for UFM, no USB wakeup supported)
USB 3.0 ports	5 (2x external rear, 2x external front, 1x internal)
Graphics (15-pin)	1 analog graphics interface derived from iRMC (up to 1600x1200 or 1920x1080 at 16bpp)
Serial connection	1 x serial RS-232-C
LAN / Ethernet	2 x1 Gb/s Ethernet; RJ45
Management LAN (RJ45)	1 x dedicated management LAN port for iRMC S4 (10/100/1000 Mbit/s) Management LAN traffic can be switched to shared onboard Gbit LAN port

Onboard or integrated Controller

RAID controller	Optionally integrated RAID 0/1 or RAID 5/6 controller for SAS base units (occupies one PCIe slot). All hardware storage controller options are described under Components
SATA Controller	Intel® C236, 2 ports used for accessible drives
SATA controller type notes	4 port for internal SATA HDDs with RAID 0, 1, 10 for Windows and Linux;
LAN Controller	Intel® i210 onboard. 2 x 10/100/1000 Mbit/s Ethernet. iSCSI, PXE-Boot and WoL are supported
Remote management controller	Integrated Remote Management Controller (iRMC S4, 256 MB attached memory incl. graphics controller) IPMI 2.0 compatible
Trusted Platform Module (TPM)	Infineon / TPM 1.2 or TPM 2.0 module; TCG compliant (option)

Slots

PCI-Express 3.0 x1 (mech. x4)	1 x (up to 167 mm length)
-------------------------------	---------------------------

Slots

PCI-Express 3.0 x4	1 x (up to 167 mm length)
PCI-Express 3.0 x8	2 x (up to 240 mm length)
Slot Notes	Optional PCIe to legacy PCI adapter available. In SAS configuration 1x PCI-Express occupied by modular RAID controller.

Drive bays

Storage drive bays	3.5-inch or 2.5-inch hot-plug SAS/SATA
Accessible drive bays	3 x 5.25/1.6-inch
Notes accessible drives	all possible options described in relevant system configurator

Drive bays

Storage drive bays	Max. 4x 3.5-inch or 8x 2.5-inch	Max. 12x 3.5-inch or 24x 2.5-inch
Accessible drive bays	3 x 5.25/1.6-inch for 1 x backup drive + 1 x ODD	3 x 5.25/1.6-inch for 1 x backup drive + 1 x ODD

Fan Configuration

Number of fans	1	2
Fan configuration	1 standard fan	redundant fans
Fan notes	non redundant / non hot-plug	non hot-plug

Operating panel

Operating buttons	On/off switch NMI button Reset button
Status LEDs	System status (orange / yellow) Identification (blue) Hard disks access (green) Power (orange / green) At system rear side: System status (orange / yellow) Identification (blue) LAN connection (green) LAN speed (green / yellow) CSS (yellow)

BIOS

BIOS features	ROM based setup utility Recovery BIOS BIOS settings save and restore Local BIOS update from USB device Online update tools for main Linux versions Local and remote update via ServerView Update Manager Remote PXE boot support Remote iSCSI boot support
---------------	---

Operating Systems and Virtualization Software

Certified or supported operating systems and virtualization software	Microsoft® Hyper-V Server 2012 R2
	Microsoft® Windows Server® 2012 R2 Datacenter
	Microsoft® Windows Server® 2012 R2 Standard
	Microsoft® Windows Server® 2012 R2 Essentials
	Microsoft® Windows Server® 2012 R2 Foundation
	Microsoft® Windows Storage Server 2012 R2 Standard
	Microsoft® Hyper-V Server 2012
	Microsoft® Windows Server® 2012 Datacenter
	Microsoft® Windows Server® 2012 Standard
	Microsoft® Windows Server® 2012 Essentials
	Microsoft® Windows Server® 2012 Foundation
	Microsoft® Windows Storage Server 2012 Standard
	Microsoft® Hyper-V™ Server 2008 R2
	Microsoft® Windows Server® 2008 R2 Datacenter
	Microsoft® Windows Server® 2008 R2 Enterprise
	Microsoft® Windows Server® 2008 R2 Standard
	Microsoft® Windows Server® 2008 R2 Foundation
	VMware vSphere™ 6.0
	VMware vSphere™ 5.5
	SUSE® Linux Enterprise Server 12
SUSE® Linux Enterprise Server 11	
Red Hat® Enterprise Linux 7	
Red Hat® Enterprise Linux 6	
Univention Corporate Server 4	
Operating system release link	http://docs.ts.fujitsu.com/dl.aspx?id=d4ebd846-aa0c-478b-8f58-4cfbf3230473
Operating system notes	Support of other Linux derivatives on demand

Server Management

Standard	<ul style="list-style-type: none"> ServerView Suite - Deploy <ul style="list-style-type: none"> Installation Manager Scripting Toolkit ServerView Suite - Control <ul style="list-style-type: none"> Operations Manager incl. PDA and ASR & R (Prefailure and Analysis; Automatic Server Recovery and Restart) Agents and CIM Providers / Agentless Service System Monitor RAID Manager Capacity Management Power Management Storage Support ServerView Suite - Maintain <ul style="list-style-type: none"> Remote Management (iRMC in combination with Intel® Node Manager) Update Management (BIOS, Firmware, Windows Drivers, Agents and CIM Providers) Performance Measurement Asset Management Online Diagnostics ServerView Suite - Integrate <ul style="list-style-type: none"> Integration packs for Microsoft System Center, VMware vCenter, VMware vRealize, Nagios, and HP SIM Deployment tools and others
Option	<ul style="list-style-type: none"> ServerView embedded Lifecycle Management <ul style="list-style-type: none"> Enhanced management functionalities for simplified, highly integrated and automated management processes ServerView Suite - Maintain <ul style="list-style-type: none"> iRMC Advanced Pack incl. Advanced Video Redirection (AVR), video capturing and Virtual Media
Server Management notes	Regarding dependencies for ServerView Suite software products see dedicated product data sheets.
Dimensions / Weight	
Floor-stand (W x D x H)	177 x 560 x 455 mm

Dimensions / Weight	
Rack (W x D x H)	483 x 495 x 175 mm
Dimension notes	Floorstand Width 306 mm with tilt protection; depth measured excludes handles on redundant PSU. Rack depth excludes handles of redundant PSU and rack front.
Mounting Depth Rack	543 mm
Height Unit Rack	4 U
Weight	Rack: 13 kg - 25 kg; Tower: 15kg - 28 kg
Weight notes	Actual weight may vary depending on configuration
Rack integration kit	Rack integration kit can be ordered as option
Environment	
Operating ambient temperature	5 - 40 °C (41 - 104 °F)
Operating temperature note	Cool-safe® Advanced Thermal Design (above 35 °C or below 10 °C) depending on configuration. For detailed information see relevant system configurator.
Operating relative humidity	10 - 85 % (non condensing)
Operating environment	FTS 04230 – Guideline for Data Center (installation specification)
Operating environment link	http://docs.ts.fujitsu.com/dl.aspx?id=e4813edf-4a27-461a-8184-983092c12dbe
Sound pressure (LpAm)	SATA: 23 dB(A) idle mode/ 23 dB(A) operation mode; SAS: 33 dB(A) idle mode/ 37 dB(A) operation mode
Sound power (LWAd; 1B = 10dB)	SATA: 4.1 B idle mode/ 4.1 B operation mode ; SAS: 4.8 B idle mode/ 5.2 B operation mode
Noise notes	Noise emissions depend on operation modes, system configuration and ambient temperature.
Electrical values	
Power supply configuration	1 x standard power supply or 1 x hot-plug power supply or 2x hot-plug power supply for redundancy depending on model
Hot-plug power supply redundancy	Optional
Active power (max. configuration)	231 W
Apparent power (max. configuration)	235 VA
Heat emission (max. configuration)	831.6 kJ/h (788.2 BTU/h)
Rated current max.	5 A (100 V) / 2.5 A (240 V)
Active power note	To estimate the power consumption of different configurations use the Power Calculator of the System Architect: http://configurator.ts.fujitsu.com/public/
Power supply	300W standard, 90% (Gold efficiency), 100-240V, 50 / 60Hz 450W hot-plug, 94% (Platinum efficiency), 100-240V, 50 / 60Hz
Power supply notes	Power Safeguard adapts system performance in case the power requirements exceeds supply limits.
Battery backup	Fujitsu Battery Unit 380W, 12V (as option)
Compliance	
Global	CB RoHS (Substance limitations in accordance with global RoHS regulations) WEEE (Waste electrical and electronic equipment)
Germany	GS
Europe	CE
USA/Canada	CSA us ULc/us FCC Class A
Japan	VCCI:V3 Class A + JIS 61000-3-2
Russia	GOST-R
South Korea	KC
China	CCC
Australia/New Zealand	C-Tick
Taiwan	BSMI
Compliance link	http://globalsp.ts.fujitsu.com/sites/certificates
Compliance notes	* Warning: This is a class A product. In a domestic environment this product may cause radio interference in which case the user may be required to take adequate measures.

Components

Backup Drives

LTO4HH Ultrium, 800 GB, 120 MB/s, half height, SAS 6Gb/s
 LTO5HH Ultrium, 1,500 GB, 140 MB/s, half height, SAS 6Gb/s
 LTO6HH Ultrium, 2,500 GB, 160 MB/s, half height, SAS 6Gb/s
 LTO7HH Ultrium, 2,500 GB, 300 MB/s, half height, SAS 6Gb/s
 RDX Drive, 320 GB, 500 GB, 1 TB , 25 MB/s, half height, USB 3.0

Optical drives

Blu-ray Disc™ Triple Writer, (6x BD-ROM; 8x DVD; 24x CD), slimline, SATA I
 Blu-ray Disc™ Triple Writer, (6x BD-RW, 8x DVD, 24x CD), ultraslim, SATA I
 DVD-ROM, (16xDVD; 48xCD), half height, SATA I
 DVD Super Multi, (16xDVD, 8xDVD+RW 6xDVD-RW, 12xDVD-RAM; 48xCD, 32xCD-RW), half height, SATA I
 DVD Super Multi, (8xDVD/DVD+RW, 6xDVD-RW, 5xDVD-RAM; 24xCD/CD-R, 16xCD-RW), slimline, SATA I
 DVD Super Multi ultra slim , (8x DVD; 24x CD), ultraslim, SATA I

Hard disk drives

HDD SATA, 6 Gb/s, 7,200 rpm, 512e, hot-plug, 3.5-inch, economic
 HDD SATA, 6 Gb/s, 500 GB, 7,200 rpm, hot-plug, 2.5-inch, business critical
 HDD SATA, 6 Gb/s, 500 GB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
 HDD SATA, 6 Gb/s, 500 GB, 7,200 rpm, 512e, hot-plug, 3.5-inch, economic
 HDD SATA, 6 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
 HDD SATA, 6 Gb/s, 4 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
 HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
 HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical
 HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical
 HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, hot-plug, 2.5-inch, business critical
 HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
 HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical

Hard disk drives

HDD SAS, 12 Gb/s, 900 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 900 GB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 600 GB , 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 450 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 450 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SAS, 12 Gb/s, 4 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SAS, 12 Gb/s, 2 TB , 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SAS, 12 Gb/s, 2 TB , 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical
HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 1.2 TB , 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 1 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical

Solid-State-Drive	SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 800 GB, Write-Intensive, hot-plug, 3.5-inch, enterprise, 10 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 800 GB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 800 GB, Read-Intensive Endurance, hot-plug, 3.5-inch, enterprise, 0.3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 800 GB, hot-plug, 2.5-inch, enterprise, 0.3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 512 GB, hot-plug, 2.5-inch
	SSD SATA, 6 Gb/s, 480 GB, Read-Intensive Endurance, hot-plug, 3.5-inch, enterprise, 0.3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, hot-plug, 2.5-inch, enterprise, 0.3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 400 GB, Write-Intensive, hot-plug, 3.5-inch, enterprise, 10 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 400 GB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 256 GB, hot-plug, 2.5-inch
	SSD SATA, 6 Gb/s, 240 GB, Read-Intensive Endurance, hot-plug, 3.5-inch, enterprise, 0.3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, hot-plug, 2.5-inch, enterprise, 0.3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 200 GB, Write-Intensive, hot-plug, 3.5-inch, enterprise, 10 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 200 GB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 120 GB, Read-Intensive Endurance, hot-plug, 3.5-inch, enterprise, 0.3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 120 GB, Read-Intensive Endurance, hot-plug, 2.5-inch, enterprise, 0.3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 120 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
SSD SATA, 6 Gb/s, 120 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)	
SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)	
SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)	
SSD SATA, 6 Gb/s, 1.2 TB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (drive writes per day for 5 years)	
PCIe SSD & SATA DOM SSD	DOM SATA, 6 Gb/s, 128 GB, non hot plug, enterprise, 0.054 DWPD (drive writes per day for 5 years)
	DOM SATA, 6 Gb/s, 64 GB, non hot plug, enterprise, 0.054 DWPD (drive writes per day for 5 years)
SCSI / SAS Controller	Fujitsu PSAS CP400i SAS Ctrl. 12 Gbit/s 8 ports int. PCIe 3.0 x8
RAID Controller	Fujitsu PRAID EP420i for SafeStore, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3108
	Fujitsu PRAID EP420i, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3108
	Fujitsu PRAID EP400i, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 1 GB, Optional FBU based on LSI SAS3108
	Fujitsu PRAID CP400i, RAID Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 1E, 10, 5, 50, No FBU support
Communication, Network	Ethernet Ctrl. 1 x 1 Gbit/s PCIe 2.1 x1 RJ45 (Intel®)
	Ethernet Ctrl. 2 x 10 Gbit/s PCIe 2.0 x8 SFP+ (Fujitsu)
	Ethernet Ctrl. 2 x 10 Gbit/s PCIe 2.1 x8 RJ45 (Intel®)
	Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 SFP+ (Emulex)
	Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 SFP+ (Intel®)
	Ethernet Ctrl. 2 x 1 Gbit/s PCIe 2.1 x4 RJ45 (Intel®)
Ethernet Ctrl. 4 x 1 Gbit/s PCIe 2.1 x4 RJ45 (Intel®)	
Graphics add on cards	NVIDIA® NVS™ 315, PCIe x16, 2x DVI/VGA

Rack infrastructure	Rack Mount Kit Cable Management for 19-inch DataCenter / PRIMECENTER Racks Cable Arm 2U for PRIMECENTER- and 3rd-party racks
Warranty	
Warranty period	1 year
Warranty type	Onsite warranty
Warranty Terms & Conditions	http://support.ts.fujitsu.com/warranty/Index.asp?LNG=COM
Product Support Services - the perfect extension	
Support Pack Options	Globally available in major business areas: 9x5, Next Business Day Onsite Response Time 9x5, 4h Onsite Response Time 24x7, 4h Onsite Response Time
Recommended Service	24x7, Onsite Response Time: 4h - For locations outside of EMEA please contact your local Fujitsu partner.
Service Lifecycle	5 years after end of product life
Service Weblink	http://www.fujitsu.com/fts/services

More information

Fujitsu OPTIMIZATION Services

In addition to Fujitsu PRIMERGY TX1330 M2, Fujitsu provides a range of platform solutions. They combine reliable Fujitsu products with the best in services, know-how and worldwide partnerships.

Fujitsu Portfolio

Built on industry standards, Fujitsu offers a full portfolio of IT hardware and software products, services, solutions and cloud offering, ranging from clients to datacenter solutions and includes the broad stack of Business Solutions, as well as the full stack of Cloud offerings. This allows customers to select from alternative sourcing and delivery models to increase their business agility and to improve their IT operation's reliability.

Computing Products

www.fujitsu.com/global/products/computing/

Software

www.fujitsu.com/software/

More information

Learn more about Fujitsu PRIMERGY TX1330 M2, please contact your Fujitsu sales representative or Fujitsu Business partner, or visit our website.
<http://www.fujitsu.com/primergy>

Fujitsu green policy innovation

Fujitsu Green Policy Innovation is our worldwide project for reducing burdens on the environment. Using our global know-how, we aim to contribute to the creation of a sustainable environment for future generations through IT. Please find further information at <http://www.fujitsu.com/global/about/environment>



Copyrights

All rights reserved, including intellectual property rights. Changes to technical data reserved. Delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see <http://www.fujitsu.com/fts/resources/navigation/terms-of-use.html>
©2016 Fujitsu Technology Solutions GmbH

Disclaimer

Technical data is subject to modification and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

Contact
FUJITSU LIMITED

Website: www.fujitsu.com
2017-01-01 CE-EN

All rights reserved, including intellectual property rights. Changes to technical data reserved. Delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see <http://www.fujitsu.com/fts/resources/navigation/terms-of-use.html>
©2016 Fujitsu Technology Solutions GmbH