Huawei AR100,AR120,AR150,AR160 and AR200 Series Enterprise Routers Datasheet







AR100, AR120, AR150, AR160 and AR200 Series Enterprise Routers Datasheet

Huawei's next-generation routers, the AR100, AR120, AR150, AR160 and AR200 series are designed

Product Overview

The AR100, AR120, AR150, AR160 and AR 200 series are fixed interface routers that provide a comprehensive platform for a variety of network topologies, including IMS, NGN, WAN and PSTN. The AR100, AR120, AR 150, AR160 and AR 200 also employ embedded hardware encryption for security as well as a voice Digital Signal Processor (DSP) for voice services.

The AR100, AR120, AR150, AR160 and AR 200 series are mature, stable and quiet routers that offer high performance functionality for small networks, enabling small businesses to greatly increase productivity at a lower cost.

AR100s, AR120s, AR150s, AR160s and AR 200s are easy to deploy, configure and customize, greatly reducing cost of deployment and maintenance, while offering maximum value to customers. These models allow network administrators to expand their networks easily and quickly, saving time and costs. Both models support firewalls, call processing, and application program functionalities.

The AR100, AR120, AR150, AR160 and AR200 series includes the following models:

- AR109, AR109W, AR109GW-L
- AR129CVW, AR129CGVW-L, AR121, AR121W, AR129, AR129W
- AR151, AR151G-HSPA+7, AR157, AR157G-HSPA+7, AR157VW, AR157W, AR158E, AR158EVW
- AR161, AR161F, AR161F-DGP, AR161FG-L, AR161FGW-L, AR161FW, AR161G-L, AR161W, AR161FV-1P AR162F,AR168F, AR169, AR169F, AR169FVW,AR169FVW-8S, AR169FGW-L, AR169FGVW-L, AR169G-L, AR169W, AR169CVW, AR169CVW-4B4S, AR161EW, AR169EW, AR169EGW-L, AR161EW-LM1
- AR201, AR207, AR207G-HSPA+7 and AR208E

The specifications for these models are shown in the following table.

Table 1: AR100 Models



- WAN speed with services (IMIX): 40 Mbps
- Fixed ports: 4 x GE LAN, 1 x VDSL2, 1 x GE WAN
- Dimensions (H x W x D): 30 mm x 230mm x 130 mm(1.18 in. x 9.1 in. x 5.1 in.)



- WAN speed with services (IMIX): 40 Mbps
- Fixed ports: 4 x GE LAN, 1 x VDSL2, 1 x GE WAN
- WLAN: 802.11b/q/n
- Dimensions (H x W x D): 30 mm x 230mm x 130 mm (1.18 in. x 9.1 in. x 5.1 in.)

AR109GW-L

- WAN speed with services (IMIX): 40 Mbps
- Fixed ports: 4 x GE LAN, 1 x VDSL2, 1 x GE WAN
- LTE: LTE FDD
- WLAN: 802.11b/g/n
- Dimensions (H x W x D): 30 mm x 230mm x 130 mm (1.18 in. x 9.1 in. x 5.1 in.)

Table 2: AR120 Models



- WAN speed with services (IMIX): 50 Mbps
- Fixed ports: 4 x GE LAN, 1 x VDSL2, 1 x GE WAN
- Voice ports: 2 x FXS
- WLAN: 802.11ac, 802.11b/g/n
- Dimensions (H x W x D): 30 mm x 230mm x 130 mm(1.18 in. x 9.1 in. x 5.1 in.)



- WAN speed with services (IMIX): 50 Mbps
- Fixed ports: 4 x GE LAN, 1 x VDSL2, 1 x GE WAN
- Voice ports: 2 x FXS
- LTE: LTE FDD
- WLAN: 802.11ac, 802.11b/g/n
- Dimensions (H x W x D): 30 mm x 230mm x 130 mm (1.18 in. x 9.1 in. x 5.1 in.)



- WAN speed with services (IMIX): 50 Mbps
- Fixed ports: 4 x FE LAN(can be configured as WAN interfaces), 1 x FE WAN
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)



- WAN speed with services (IMIX): 50 Mbps
- Fixed ports: 4 x FE LAN(can be configured as WAN interfaces), 1 x FE WAN, 802.11 b/g/n
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)



- WAN speed with services (IMIX): 50 Mbps
- Fixed ports: 4 x FE LAN(can be configured as WAN interfaces), 1 x VDSL2 WAN
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR129W



- WAN speed with services (IMIX): 50 Mbps
- Fixed ports: 4 x FE LAN(can be configured as WAN interfaces), 1 x VDSL2 WAN, 802.11 b/g/n
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

Table3: AR150 Models

AR151



- WAN speed with services (IMIX): 100 Mbps
- Fixed ports: 4 x FE LAN(can be configured as WAN interfaces), 1 x FE WAN
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR151G-HSPA+7



- WAN speed with services (IMIX): 100 Mbps
- Fixed ports: 4 x FE LAN(can be configured as WAN interfaces),
 1 x FE WAN, WCDMA HSPA+7
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR157



- WAN speed with services (IMIX): 100 Mbps
- Fixed ports: 4 x FE LAN(can be configured as WAN interfaces),
 1 x ADSL2+ Annex J, 802.11 b/g/n
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR157G-HSPA+7



- WAN speed with services (IMIX): 100 Mbps
- Fixed ports: 4 x FE LAN(can be configured as WAN interfaces), 1 x ADSL2+ Annex A/M, WCDMA HSPA+7
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR157VW



- WAN speed with services (IMIX): 100 Mbps
- Fixed ports: 4 x FE LAN(can be configured as WAN interfaces),
 1 x ADSL2+ Annex A/M, 802.11 b/g/n
- Fixed Voice ports: 4 x FXS, 1 x FXO
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR157W



- WAN speed with services (IMIX): 100 Mbps
- Fixed ports: 4 x FE LAN(can be configured as WAN interfaces),
 1 x ADSL2+ Annex A/M, 802.11 b/g/n
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR158E



- WAN speed with services (IMIX): 100 Mbps
- Fixed ports: 4 x FE LAN(can be configured as WAN interfaces), 1 x G.SHDSL 4-pair
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR158EVW



- WAN speed with services (IMIX): 100 Mbps
- Fixed ports: 4 x FE LAN(can be configured as WAN interfaces), 1 x G.SHDSL 4-pair, 802.11 b/g/n
- Fixed Voice ports: 4 x FXS, 1 x FXO
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

Table4: AR160 Models

AR161



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces), 1 x GE WAN
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR161F



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces), 1 x GE Combo WAN
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR161F-DGP



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces), 1 x GE Combo WAN
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR161FW



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces), 1 x GE Combo WAN, 802.11 b/g/n
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR161FG-L



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces), 1 x GE Combo WAN, FDD LTE
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR161FGW-L



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces),
 1 x GE Combo WAN, FDD LTE, 802.11 b/g/n
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR161G-L



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces),
 1 x GE WAN, FDD LTE
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR161W



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces), 1 x GE WAN, 802.11 b/g/n
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR161FV-1P



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces), 1 x GE Combo WAN
- Fixed Voice ports: 1 x VE1
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR162F



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces),
 1 x GE Combo WAN, 1 x SA
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR168F



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces), 1 x G.SHDSL 4-pair, 1 x GE Combo WAN
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR169



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces), 1 x VDSL2 compatible with ADSL2+ Annex A/M
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR169F



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces), 1 x VDSL2 with bonding, 1 x GE Combo WAN
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR169FVW



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces), 1 x GE Combo WAN, 1 x VDSL2 with bonding, 802.11 b/g/n
- Fixed Voice ports: 4 x FXS, 1 x FXO
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR169FVW-8S



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces), 1 x GE Combo WAN, 1 x VDSL2 with bonding, 802.11 b/g/n
- Fixed Voice ports: 8 x FXS, 1 x FXO
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR169FGW-L



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces), 1 x GE Combo WAN, 1 x VDSL2 with bonding, LTE FDD, 802.11 b/g/n
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR169FGVW-L



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces), 1 x GE Combo WAN, 1 x VDSL2 with bonding, LTE FDD, 802.11 b/g/n
- Fixed Voice ports: 4 x FXS, 1 x FXO
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR169G-L



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces), 1 x VDSL2, FDD LTE
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR169W



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces), 1 x VDSL2, 802.11 b/g/n
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR169CVW



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces), 1 x GE SFP, 1 x VDSL2, 802.11 ac/b/g/n
- Fixed Voice ports: 4 x FXS, 1 x FXO
- Dimensions (H x W x D): 30 mm x 270 mm x 155 mm (1.18 in. x 11.4 in. x 6.1 in.)

AR169CVW-4B4S



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 4 x GE LAN(can be configured as WAN interfaces), 1 x GE SFP, 1 x VDSL2, 802.11 ac/b/g/n
- Fixed Voice ports: 4 x ISDN BRI, 4 x FXS, 1 x FXO
- Dimensions (H x W x D): 30 mm x 270 mm x 155 mm (1.18 in. x 11.4 in. x 6.1 in.)

AR161EW



- WAN speed with services (IMIX): 600 Mbps
- Fixed ports: 4 x GE RJ45 LAN, 1 x GE Combo WAN
- WLAN: 802.11a/b/g/n/ac/ac wave2, 4x4:4 MU-MIMO
- Dimensions (H x W x D): 44.0 mm x 300.0 mm x 216.4 mm (1.73 in. x 11.8 in. x 8.5 in.)

AR169EW



- WAN speed with services (IMIX): 600 Mbps
- Fixed ports: 4 x GE RJ45 LAN, 1 x VDSL2 with Bonding, 1 x GE Combo WAN
- WLAN: 802.11a/b/g/n/ac/ac wave2, 4x4:4 MU-MIMO
- Dimensions (H x W x D): 44.0 mm x 300.0 mm x 216.4 mm (1.73 in. x 11.8 in. x 8.5 in.)

AR169EGW-L



- WAN speed with services (IMIX): 600 Mbps
- Fixed ports: 4 x GE RJ45 LAN, 1 x VDSL2 with Bonding, 1 x GE Combo WAN
- WWAN: LTE FDD
- WLAN: 802.11a/b/g/n/ac/ac wave2, 4x4:4 MU-MIMO
- Dimensions (H x W x D): 44.0 mm x 300.0 mm x 216.4 mm (1.73 in. x 11.8 in. x 8.5 in.)

AR161EW-M1



- WAN speed with services (IMIX): 600 Mbps
- Fixed ports: 4 x GE RJ45 LAN, 1 x GE Combo WAN
- WLAN: 802.11a/b/g/n/ac/ac wave2, 4x4:4 MU-MIMO
- Hard disk: 2.5-inch hard disk (optional)
- Dimensions (H x W x D): 44.0 mm x 300.0 mm x 216.4 mm (1.73 in. x 11.8 in. x 8.5 in.)

Table4: AR200 Models





- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 8 x FE LAN(can be configured as WAN interfaces), 1 x FE WAN
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR207



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 8 x FE LAN(can be configured as WAN interfaces), 1 x ADSL2+ Annex A/M
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR207G-HSPA+7



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 8 x FE LAN(can be configured as WAN interfaces), WCDMA HSPA+7, 1 x ADSL2+ Annex A/M
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

AR208E



- WAN speed with services (IMIX): 150 Mbps
- Fixed ports: 8 x FE LAN(can be configured as WAN interfaces), 1 x G.SHDSL 4-pair
- Dimensions (H x W x D): 44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)

Product Features and Benefits

1 Small Size and High Performance

- More applications: Huawei series routers use the dual-core processor that isolates the control plane from the forwarding plane and processes more enterprise applications. Huawei series routers improve user experience for multimedia service when streams overlap.
- Higher performance: The AR100s, AR120s, AR150s, AR160s and AR 200s can process various enterprise applications, and its service processing capability is four times that in the industry.
- Greater potential: Huawei series routers provide the capability to migrate services to the 3G and LTE networks.

ullet LOW Investment with ullet ullet Returns

- Easy to construct: The AR100s, AR120s, AR150s, AR160s and AR 200s supports plug-and-play, intelligent configuration, and deployment using the USB flash drive. It can function immediately after being installed. Users do not need to configure an IP address manually. The PPP and VPN indicators show the status of corresponding services. The AR100s, AR120s, AR150s, AR160s and AR 200s helps to quickly construct an enterprise IT network.
- Simplified solution: Huawei provides an all-around solution that integrates the routing, switching, voice, security, and wireless services. Customers can customize solutions as required.
- Easy to expand: Huawei series routers have four/eight FE/GE ports, can access more employee for small enterprises. The two uplink WAN ports implement load balancing and link protection, maximizing the return on investments.


3 Small footprint on a Comprehensive Platform

- Maturity and Stableness: The AR100s, AR120s, AR150s, AR160s and AR 200s uses the Huawei VRP operating system and VSP voice platform. In addition, the AR100s, AR120s, AR150s, AR160s and AR 200s uses modularized hardware design, which brings good user experience.
- Low-noise office: Huawei series routers have no fan, which brings low noise and good user experience.
- Secure environment: The lightning failure rate of AR100s, AR120s, AR150s, AR160s and AR 200s is only 3% of industry average. The AR100s, AR120s, AR150s, AR160s and AR 200s can be applied in the harsh environment.


Sample Deployments

WAN Access

Example deployment in branch networks for WAN access. In this example, the AR100s, AR120s, AR150s , AR160s and AR 200s function as the egress routers on enterprise branch networks and provide multiple access methods, including Ethernet, xDSL, 3G, LTE and WLAN.




Enterprise Voice Services Deployment



This illustration shows an AR150, AR160 and AR200 series router deployed at an enterprise branch with access to a WAN and a PSTN. If a fault occurs on the WAN, the PSTN acts as a backup to the WAN and ensures that call services remain uninterrupted. AR 150s, AR160s and AR 200s are deployed at enterprise branch offices to provide intelligent, integrated dialing across the network. When deployed as voice service gateways, AR 150s, AR160s and AR 200s can function as IP PBX boxes and SIP access gateways.

IP PBX. AR 150s, AR160s and AR 200s have a built-in PBX, which supports the enterprise main number, interactive voice response (IVR), and billing query functions. These features help enhance the corporate image of small businesses by allowing them to look more professional to their customers, while simultaneously improving the efficiency of their enterprise communications.

SIP Server. AR 150s, AR160s and AR 200s have a built-in SIP server that ensures reliability of voice services. If the SIP server at the headquarters office becomes unreachable, the local built-in SIP server at the branch office ensures that communication remains uninterrupted between branch offices and the PSTN network.



The AR120s, AR 150, AR160 and AR200 series routers provide integrated voice, fax, and IP services. The AR120s, AR150s, AR160s and AR200s can function as SIP access gateways for enterprise branch offices that transform traditional phone signals into Voice over IP (VoIP). Typically, AR120s, AR150s, AR160s and AR200s are connected upstream from the IMS and NGN networks to enable anytime voice communication on any media, such as phones, handsets, and computers.

VPN Deployment for Secure Enterprise Communications

VPNs Connecting Branches and Partners to Headquarters

This illustration shows how to deploy AR100s, AR120s, AR150s, AR 160s and AR 200s using VPNs to connect branches and partners to headquarters.


AR100s, AR120s, AR150s, AR 160s and AR 200s provide various VPN tunnel protocols to ensure secure communications between:

- Enterprise branches and other branch offices
- Enterprise branches and headquarters
- Partners and enterprise resources

AR100s, AR120s, AR150s, AR 160s and AR 200s support the following VPN tunnel protocols:

- **GRE VPN**
- **IPSEC VPN**
- **DSVPN**
- L2TP VPN

AR100s, AR120s, AR150s, AR 160s and AR 200s support fast tunnel set-up and authentication.



Wireless Access and Management in Branch


3G/LTE and Wi-Fi Wireless Access application

The AR100s, AR120s, AR150s, AR 160s and AR 200s routers complied with 3G and LTE standards including HSPA+ and FDD LTE, meeting the wireless communication requirements between branches and the

headquarters. In addition, the 3G or LTE data link can be used as a backup for wired link to protect the xDSL, FE/GE, and ISDN uplinks. The backup link improves network stability and reduces network construction costs.

Some models of AR100s, AR120s and AR160s routers are dual SIM devices, providing dual SIM standby. The customers can switch the SIM card manually according to 3G/LTE network standards. In addition, the device can switch to the backup SIM card when signal is weak to avoid link interruption.


The AR100s, AR 120s, AR150s,




AR160s and AR 200s routers integrated WLAN wireless access capabilities, support 802.11a/b/g/n standard communication, Built-in AC function make the deployment and management more conveniently. Its wireless features can meet users' demand for wireless access, and help enterprises to build a branch network flexibly.

Wireless AC Management application

The AR120s, AR150s, AR160s and AR200s routers integrated AC (Access Controller, a wireless controller) functionality, which can manage the wireless AP (Access Point, Access Point) in wireless LAN. AR supported rich certification and flexible user access control, which can provide security access guarantee for Wi-Fi users. The rich wireless capabilities integrated in one device, this can realize centralized management of wired and wireless network, meet the customers' requirements of building different scale enterprises networks.



Copper and Fiber integration Access Solution



Huawei new generation AR160 routers integrated 4 GE LAN and 1 GE WAN ports, some models support VDSL2 access, which can provide 100M access bandwidth (800 meters). This new box device can bring a high bandwidth experience to the enterprise and carrier customers.

In the future, if the customers have optical access requirements, they don't need to replace the devices. As the GE WAN port supports Combo switch. The one box solution can meet the customers' requirements perfectly, thereby protect their investments.

Technical Specifications

Table1: AR100s Technical Specifications

Item AR109		AR109W	AR109GW-L				
Hardware							
WAN speed with services* (IMIX)	40 Mbps	40 Mbps	40 Mbps				
Number of recommended users 20		20	20				
Fixed WAN ports 1 x VDSL2(compatible with ADSL2+ Annex A/M, Annex B/J), 1 x GE		1 x VDSL2(compatible with ADSL2+ Annex A/M, Annex B/J), 1 x GE	1 x VDSL2(compatible with ADSL2+ Annex A/M,Annex B/J), 1 x GE				

Item	AR109	AR109W	AR109GW-L	
Fixed Ethernet switching ports	ted Ethernet switching ports 4 x GE(can be configured as WAN interfaces)		4 x GE(can be configured as WAN interfaces)	
Integrated LTE	_	_	FDD LTE	
Wi-Fi	_	802.11 b/g/n	802.11 b/g/n	
USB 2.0 ports	SB 2.0 ports 1		1	
console ports 1		1	1	
Memory size	256 MB	256 MB	256 MB	
Flash memory	256 MB	256 MB	256 MB	
Maximum power	24 W	24 W	24W	
Power supply (AC)	100 V to 240 V	100 V to 240 V	100 V to 240 V	
Frequency	50/60 Hz	50/60 Hz	50/60 Hz	
Dimensions (H x W x D)	30 mm x 230 mm x 130 mm (1.18 in. x 9.1 in. x 5.1 in.)	30 mm x 230 mm x 130 mm (1.18 in. x 9.1 in. x 5.1 in.)	30 mm x 230 mm x 130 mm (1.18 in. x 9.1 in. x 5.1 in.)	
Operating temperature	0°C to 40°C	0°C to 40°C	0°C to 40°C	
Relative humidity	5% to 95% (non- condensing)	5% to 95% (non- condensing)	5% to 95% (non- condensing)	

Software

Basic features	ARP , PBR, DNS, DHCP, NAT				
WLAN(AP)	_	AP management, WLAN QoS, WLAN security, WLAN radio management, WLAN user management			
LAN	IEEE 802.1P, IEEE 802.1Q, IEEE 802.3, VLAN management, MAC address management, MSTP, etc.				
IPv4routing	static route, RIP				
IPv6 routing	static route, RIPng				
Multicast	IGMP version1/2/3				
VPN	IPSec VPN, GRE VPN, L2TP Clie	ent			
QoS		ng (CAR), traffic shaping, congestion avoidance (based on IP gestion management (LAN interface: SP/WRR/SP+WRR; WAN			
Security	ACL, firewall, AAA authentication, ICMP attack defense, HTTPS				
Management and maintenance	Upgrade management, device management, web-based GUI, RMON, CWMP, Auto-Config, site deployment using USB disk, CLI				

Table 2: AR120s Technical Specifications

Item	AR129CVW	AR129CGVW-L	AR121	AR121W	AR129	AR129W
			Hardware			
WAN speed with services* (IMIX)	50 Mbps	50 Mbps	50 Mbps	50 Mbps	50 Mbps	50 Mbps
Number of recommended users	20	20	20	20	20	20
Fixed WAN ports	1 x VDSL2 (compatible with ADSL2+ Annex A/M, Annex B/J), 1 x GE	1 x VDSL2 (compatible with ADSL2+ Annex A/M, Annex B/J), 1 x GE	1 x FE	1 x FE	1 x VDSL2 (compatible with ADSL2+ Annex A/M, AnnexB/J)	1 x VDSL2 (compatible with ADSL2+ Annex A/M, AnnexB/J)
Fixed Ethernet switching ports	4 x GE(can be configured as WAN interfaces)	4 x GE(can be configured as WAN interfaces)	4 x FE(can be configured as WAN interfaces)	4 x FE(can be configured as WAN interfaces)	4 x FE(can be configured as WAN interfaces)	4 x FE(can be configured as WAN interfaces)
Fixed voice ports	2 x FXS	2 x FXS	_	_	_	_
Integrated LTE	-	FDD LTE	_	_	_	_
WiFi	802.11b/g/n, 2 x 2 MIMO 802.11ac, 2 x 2MIMO	802.11b/g/n, 2.4GHz, 2 x 2 MIMO 802.11ac, 5GHz, 2 x 2MIMO	_	802.11 b/g/n	_	802.11 b/g/n
USB 2.0 ports	1	1	1	1	1	1
Console ports	1	1	1	1	1	1
Memory size	256 MB	256 MB	256 MB	256 MB	256 MB	256 MB
Flash memory	256 MB	256 MB	256 MB	256 MB	256 MB	256 MB
PoE power	_	_	_	_	_	_
Maximum power	24 W	24 W	24 W	24 W	24 W	24 W
Power supply (AC)	100 V to 240 V	100 V to 240 V	100 V to 240 V	100 V to 240 V	100 V to 240 V	100 V to 240 V
Frequency	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz
Dimensions (H x W x D)	30 mm x 230 mm x 130 mm (1.18 in. x 9.1 in. x 5.1 in.)	30 mm x 230 mm x 130 mm (1.18 in. x 9.1 in. x 5.1 in.)	44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)	44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)	44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)	44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)
Operating temperature	0°C to 40°C	0°C to 40°C	0°C to 45°C	0°C to 45°C	0°C to 45°C	0°C to 45°C
Relative humidity	5% to 95% (non- condensing)	5% to 95% (non- condensing)	5% to 95% (non- condensing)	5% to 95% (non- condensing)	5% to 95% (non- condensing)	5% to 95% (non- condensing)

Item	AR129CVW	AR129CGVW-L	AR121	AR121W	AR129	AR129W			
	Software								
Basic features	ARP , PBR, DNS, [DHCP, NAT							
WLAN(AC)	AP management(AC discovery/AP access/AP management), CAPWAP, WLAN user management , WLAN vLAN(AC) radio management (802.11a/b/g/n) , WLAN QoS (WMM), WLAN security (WEP/WPA/WPA2/Key management)								
LAN	IEEE 802.1P, IEEE	802.1Q, IEEE 802	.3, VLAN manager	ment, MAC addre	ess managemer	nt, MSTP, etc.			
IPv4routing	static route, RIP, E	3GP							
IPv6 routing	static route, RIPn	g, BGP4+							
Multicast	IGMP version1/2/	3,MLD,							
VPN	IPSec VPN, GRE V	'PN, DSVPN, L2TP	VPN, Smart VPN						
QoS	precedence/DSCF	MQC, priority mapping, traffic policing (CAR), traffic shaping, congestion avoidance (based on IP precedence/DSCP WRED), congestion management (LAN interface: SP/WRR/SP+WRR; WAN interface: PQ/CBWFQ), MQC (traffic classification, traffic behavior, and traffic policy),							
Security		ACL, firewall, 802.1x authentication, AAA authentication, RADIUS authentication, broadcast storm suppression, ARP security, ICMP attack defense, URPF, blacklist, IP source tracing, PKI, HTTPS,							
Management and maintenance	, ,		agement, web-ba site deployment us			9CGVW-L only),			

Table 3: AR150&200 Technical Specifications

Item	AR201/AR151	AR207/AR157	AR207G-HSPA+7/ AR157G-HSPA+7	AR208E/ AR158E
		Hardware		
WAN speed with services* (IMIX)	150 Mbps/ 100 Mbps	150 Mbps/ 100 Mbps	150 Mbps/ 100 Mbps	150 Mbps/ 100 Mbps
Number of recommended users	50	50	50	50
Fixed WAN ports	1 x FE	1 x ADSL2+ Annex A/M	1 x ADSL2+ Annex A/M	1 x G.SHDSL 4-pair
Fixed Ethernet switching ports	8 x FE/4 x FE(can be configured as WAN interfaces)	8 x FE/4 x FE(can be configured as WAN interfaces)	8 x FE/4 x FE(can be configured as WAN interfaces)	8 x FE/4 x FE(can be configured as WAN interfaces)
Fixed voice ports	_	_	_	
Integrated 3G	_	_	WCDMA HSPA+7	_
USB 2.0 ports	1	1	1	1
Console ports	1	1	1	1
Memory size	512 MB	512 MB	512 MB	512 MB
Flash memory	512 MB	512 MB	512 MB	512 MB

Item	AR201/AR151	AR207/AR157	AR207G-HSPA+7/ AR157G-HSPA+7	AR208E/ AR158E
PoE power	_	_	_	_
Maximum power	36 W / 24 W			
Power supply (AC)	100 V to 240 V	100V to 240V	100V to 240V	100V to 240V
Frequency	50/60 Hz	50/60 Hz	50/60Hz	50/60 Hz
Dimensions (H x W x D)	44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)	44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)	44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)	44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)
Operating temperature	0°C to 45°C	0°C to 45°C	0°C to 45°C	0°C to 45°C
Relative humidity	5% to 95% (non- condensing)			

Software

Basic features	DHCP server/client, PPPoE server/client, PPPoA server/client, PPPoEoA server/client, NAT, Sub interface management			
Voice	RTP, SIP, SIP AG, IP PBX/TDM PBX, FXO/FXS, VoIP, BEST, DISA, SBC (Only voice models support voice features)			
WLAN(AP)	AP management, WLAN QoS, WLAN security, WLAN radio management, WLAN user management(Only WLAN models support WLAN AP features)			
WLAN(AC)	AP management(AC discovery/AP access/AP management),CAPWAP,WLAN user management , WLAN adio management(802.11a/b/g/n),WLAN QoS(WMM), WLAN security(WEP/WPA/WPA2/Key management)			
LAN	IEEE 802.1P, IEEE 802.1Q, IEEE 802.3, VLAN management, MAC address management, MSTP, etc.			
IPv4 unicast routing	Routing policy, static route, RIP, OSPF, IS-IS, BGP			
IPv6 unicast routing	Routing policy, static route, RIPng, OSPFv3, IS-ISv6, BGP4+			
Multicast	IGMP version1/2/3, PIM SM, PIM DM, MSDP			
VPN	IPSec VPN, GRE VPN, DSVPN, L2TP VPN, Smart VPN			
QoS	Diffserv mode, Priority mapping, traffic policing (CAR), traffic shaping, congestion avoidance (based on IP precedence/DSCP WRED), congestion management (LAN interface: SP/WRR/SP+WRR; WAN interface: PQ/CBWFQ), MQC (traffic classification, traffic behavior, and traffic policy), Hierarchical QoS, Smart Application Control (SAC)			
Security	ACL, firewall, 802.1x authentication, AAA authentication, RADIUS authentication, HWTACACS authentication, broadcast storm suppression, ARP security, ICMP attack defense, URPF, CPCAR, blacklist, IP source tracing, PKI			
Management and maintenance	Upgrade management, device management, web-based GUI, GTL, SNMP(v1/v2c/v3), RMON, NTP, CWMP, Auto-Config, site deployment using USB disk, NetConf, CLI			

Table 4: AR150&200 Technical Specifications

Item	AR151G-HSPA+7	AR157VW	AR157W	AR158EVW	
		Hardware			
WAN speed with services* (IMIX)	100 Mbps	100 Mbps	100 Mbps	100 Mbps	
Number of recommended users	50	50	50	50	
Fixed WAN ports	1 x FE	1 x ADSL2+ Annex A/M	1 x ADSL2+ Annex A/M	1 x G.SHDSL 4-pair	
Fixed Ethernet switching ports	4 x FE(can be configured as WAN interfaces)	4 x FE(can be configured as WAN interfaces)	4 x FE(can be configured as WAN interfaces)	4 x FE(can be configured as WAN interfaces)	
Fixed voice ports	_	4 x FXS, 1 x FXO	_	4 x FXS, 1 x FXO	
Integrated 3G	WCDMA HSPA+7	_	_	_	
USB 2.0 ports	1	1	1	1	
Console ports	1	1	1	1	
Memory size	512 MB	512 MB	512 MB	512 MB	
Flash memory	512 MB	512 MB	512 MB	512 MB	
PoE power	_	_	_	_	
Maximum power	24 W	60 W	24 W	60 W	
Power supply (AC)	100V to 240V	100V to 240V	100V to 240V	100V to 240V	
Frequency	50/60 Hz	50/60 Hz	50/60 Hz	50/60Hz	
Dimensions (H x W x D)	44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)	44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)	44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)	44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)	
Operating temperature	0°C to 45°C	0°C to 45°C	0°C to 45°C	0°C to 45°C	
Relative humidity	5% to 95% (non- condensing)				
		Software			
Basic features	DHCP server/client, PPPoE management	server/client, PPPoA server/	client, PPPoEoA server/clien	t, NAT, Sub interface	
Voice	RTP, SIP, SIP AG, IP PBX/TD	M PBX, FXO/FXS, VoIP, BES	T, DISA, SBC(Only voice mo	dels support voice features)	
WLAN(AP)	AP management, WLAN C (Only WLAN models suppo	oS, WLAN security, WLAN ort WLAN AP features)	radio management, WLAN	user management	
WLAN(AC)	_	very/AP access/AP manager 11a/b/g/n),WLAN QoS(\		_	

Item	AR151G-HSPA+7	AR157VW	AR157W	AR158EVW					
LAN	IEEE 802.1P, IEEE 802.1Q,	IEEE 802.1P, IEEE 802.1Q, IEEE 802.3, VLAN management, MAC address management, MSTP, etc.							
IPv4 unicast routing	Routing policy, static route	, RIP, OSPF, IS-IS, BGP							
IPv6 unicast routing	Routing policy, static route, RIPng, OSPFv3, IS-ISv6, BGP4+								
Multicast	IGMP version1/2/3, PIM SN	л, PIM DM, MSDP							
VPN	IPSec VPN, GRE VPN, DSVF	IPSec VPN, GRE VPN, DSVPN, L2TP VPN, Smart VPN							
QoS	Diffserv mode, Priority mapping, traffic policing (CAR), traffic shaping, congestion avoidance (based on IP precedence/DSCP WRED), congestion management (LAN interface: SP/WRR/SP+WRR; WAN interface: PQ/CBWFQ), MQC (traffic classification, traffic behavior, and traffic policy), Hierarchical QoS, Smart Application Control (SAC)								
Security	ACL, firewall, 802.1x authentication, AAA authentication, RADIUS authentication, HWTACACS authentication, broadcast storm suppression, ARP security, ICMP attack defense, URPF, CPCAR, blacklist, IP source tracing, PKI								
Management and maintenance	Upgrade management, device management, web-based GUI, GTL, SNMP(v1/v2c/v3), RMON, NTP, CWMP, Auto-Config, site deployment using USB disk, NetConf, CLI								

Table 5: AR160s Technical Specifications

Item	AR161	AR161W	AR161G-L	AR169	AR169W	AR169G-L
			Hardware			
WAN speed with services* (IMIX)	150Mbps	150Mbps	150Mbps	150Mbps	150Mbps	150Mbps
Number of recommended users	50	50	50	50	50	50
Fixed WAN ports	1 x GE	1 x GE	1 x GE	1 x VDSL2 (compatible with ADSL2+ Annex A/M, Annex B/J)	1 x VDSL2 (compatible with ADSL2+ Annex A/M, Annex B/J)	1 x VDSL2 (compatible with ADSL2+ Annex A/M, Annex B/J)
Fixed Ethernet switching ports	4 x GE(can be configured as WAN interfaces)	4 x GE(can be configured as WAN interfaces)	4 x GE(can be configured as WAN interfaces)			
Fixed voice ports	_	_	_	_	_	_
Integrated LTE	_	_	FDD LTE	_	_	FDD LTE
Wi-Fi	_	802.11 b/g/n	_	_	802.11 b/g/n	_
USB 2.0 ports	1	1	1	1	1	1
Console ports	1	1	1	1	1	1
Memory size	512 MB	512 MB	512 MB	512 MB	512 MB	512 MB

Item	AR161	AR161W	AR161G-L	AR169	AR169W	AR169G-L		
Flash memory	512 MB	512 MB	512 MB	512 MB	512 MB	512 MB		
PoE power	_	_	_	_	_	_		
Maximum power	24W	24W	24W	24W	24W	36 W		
Power supply (AC)	100 V to 240 V	100 V to 240 V						
Frequency	50/60 Hz	50/60 Hz						
Dimensions (H x W x D)	44.5 mm x 300 mm x 220 mm (1.75 in. x 11.8 in. x 8.66 in.)							
Operating temperature	0°C to 45°C							
Relative humidity	5% to 95% (non-condensing)							

Software

Basic features	DHCP server/client, PPPoE server/client, PPPoA server/client, PPPoEoA server/client, NAT, Sub interface management
Voice	RTP, SIP, SIP AG, IP PBX/TDM PBX, FXO/FXS, VoIP, BEST, DISA, SBC (Only voice models support voice features)
WLAN(AP)	AP management, WLAN QoS, WLAN security, WLAN radio management, WLAN user management(Only WLAN models support WLAN AP features)
WLAN(AC)	AP management(AC discovery/AP access/AP management), CAPWAP, WLAN user management , WLAN radio management (802.11a/b/g/n) , WLAN QoS (WMM), WLAN security (WEP/WPA/WPA2/Key management)
LAN	IEEE 802.1P, IEEE 802.1Q, IEEE 802.3, VLAN management, MAC address management, MSTP, etc.
IPv4 unicast routing	Routing policy, static route, RIP, OSPF, IS-IS, BGP
IPv6 unicast routing	Routing policy, static route, RIPng, OSPFv3, IS-ISv6, BGP4+
Multicast	IGMP version1/2/3, PIM SM, PIM DM, MSDP
VPN	IPSec VPN, GRE VPN, DSVPN, L2TP VPN, Smart VPN
QoS	Diffserv mode, Priority mapping, traffic policing (CAR), traffic shaping, congestion avoidance (based on IP precedence/DSCP WRED), congestion management (LAN interface: SP/WRR/SP+WRR; WAN interface: PQ/CBWFQ), MQC (traffic classification, traffic behavior, and traffic policy), Hierarchical QoS, Smart Application Control (SAC)
Security	ACL, firewall, 802.1x authentication, AAA authentication, RADIUS authentication, HWTACACS authentication, broadcast storm suppression, ARP security, ICMP attack defense, URPF, CPCAR, blacklist, IP source tracing, PKI,
Management and maintenance	Upgrade management, device management, Cloud-managed(Only AR161W can support cloud-managed now), web-based GUI, GTL, SNMP(v1/v2c/v3), RMON, NTP, CWMP, Auto-Config, site deployment using USB disk, CLI
<u> </u>	

Table 6: AR160s Technical Specifications

Item	AR161F	AR161F-DGP	AR161FW	AR161FG-L	AR161FGW-L	AR161FV-1P	AR162F
	'		Hard	ware			
WAN speed with services* (IMIX)	150 Mbps	150 Mbps	150 Mbps	150 Mbps	150Mbps	150 Mbps	150 Mbps
Number of recommended users	50	50	50	50	50	50	50
Fixed WAN ports	1x GE Combo	1x GE Combo (support dying gasp)	1x GE Combo	1x GE Combo	1x GE Combo	1x GE Combo	1 x SA 1x GE Combo
Fixed Ethernet switching ports	4 x GE(can be configured as WAN interfaces)						
Fixed voice ports	_	_	_	_	_	1VE1	_
Integrated LTE	_	_	_	FDD LTE	FDD LTE	_	_
Wi-Fi	_	_	802.11 b/g/n	_	802.11 b/g/n	_	_
USB 2.0 ports	1	1	1	1	1	1	1
Console ports	1	1	1	1	1	1	1
Memory size	512 MB	512 MB	1 GB	512 MB	512 MB	512 MB	512 MB
Flash memory	512 MB						
PoE power	_	_	_	_	_	_	_
Maximum power	24W	24W	24W	24W	24W	24W	36 W
Power supply (AC)	100 V to 240 \	/					
Frequency	50/60 Hz						
Dimensions (H x W x D)	44.5 mm x 300) mm x 220 mm	(1.75 in. x 11.8	in. x 8.66 in.)			
Operating temperature	0°C to 45°C	0°C to 45°C					
Relative humidity	5% to 95% (non-condensing)						
			Softv	Naro.			
Basic features	DHCP server/cl management	ent, PPPoE serve		server/client, PP	PoEoA server/cli	ent, NAT, Sub in	terface
Voice		i, IP PBX/TDM PE	BX, FXO/FXS, Va	IP, BEST, DISA, S	BC (Only voice r	nodels support v	voice features)
WLAN(AP)	AP manageme		WLAN security, '	WLAN radio ma	· · · · · · · · · · · · · · · · · · ·		

Item	AR161F	AR161F-DGP	AR161FW	AR161FG-L	AR161FGW-L	AR161FV-1P	AR162F
WLAN(AC)		AP management(AC discovery/AP access/AP management), CAPWAP, WLAN user management , WLAN radio management (802.11a/b/g/n) , WLAN QoS (WMM), WLAN security (WEP/WPA/WPA2/Key management)					
LAN	IEEE 802.1P, IEE	EE 802.1Q, IEEE	802.3, VLAN m	anagement, MA	AC address mana	igement, MSTP,	etc.
IPv4 unicast routing	Routing policy,	static route, RIP,	OSPF, IS-IS, BO	iP			
IPv6 unicast routing	Routing policy,	Routing policy, static route, RIPng, OSPFv3, IS-ISv6, BGP4+					
Multicast	IGMP version1/	IGMP version1/2/3, PIM SM, PIM DM, MSDP					
VPN	IPSec VPN, GRE	IPSec VPN, GRE VPN, DSVPN, L2TP VPN, Smart VPN					
QoS	precedence/DS	CP WRED), cong	gestion manage	ment (LAN inter	haping, congest face: SP/WRR/SF c policy), Hierarc	+WRR; WAN in	terface: PQ/
Security					IJUS authenticati se, URPF, CPCAR		
Management and maintenance		gement, device te deployment u	-		GTL, SNMP(v1/v	2c/v3), RMON,	ntp, cwmp,

Table 7: AR160s Technical Specifications

Item	AR168F	AR169F	AR169FVW	AR169FVW-8S	AR169FGW-L	AR169FGVW-L
	Hardware					
WAN speed with services* (IMIX)	150 Mbps	150 Mbps	150 Mbps	150 Mbps	150 Mbps	150 Mbps
Number of recommended users	50	50	50	50	50	50
Fixed WAN ports	1 x G.SHDSL 4-pair, 1x GE Combo	1 x VDSL2 with bonding (compatible with ADSL2+ Annex A/M), 1x GE Combo	1 x VDSL2 with bonding (compatible with ADSL2+ Annex A/M), 1x GE Combo	1 x VDSL2 with bonding (compatible with ADSL2+ Annex A/M), 1x GE Combo	1 x VDSL2 with bonding (compatible with ADSL2+ Annex A/M), 1x GE Combo	1 x VDSL2 with bonding (compatible with ADSL2+ Annex A/M), 1x GE Combo
Fixed Ethernet switching ports	4 x GE(can be configured as WAN interfaces)	4 x GE(can be configured as WAN interfaces)	4 x GE(can be configured as WAN interfaces)	4 x GE(can be configured as WAN interfaces)	4 x GE(can be configured as WAN interfaces)	4 x GE(can be configured as WAN interfaces)
Fixed voice ports	_	_	4 x FXS, 1 x FXO	8 x FXS, 1 x FXO	_	4 x FXS, 1 x FXO
Integrated 3G/ LTE	_	_	_	_	FDD LTE	FDD LTE
Wi-Fi	_	_	802.11b/g/n	802.11b/g/n	802.11b/g/n	802.11b/g/n
USB 2.0 ports	1	1	1	1	1	1

Item	AR168F	AR169F	AR169FVW	AR169FVW-8S	AR169FGW-L	AR169FGVW-L
Console ports	1	1	1	1	1	1
Memory size	512 MB	512 MB	1GB	1GB	1GB	1GB
Flash memory	512 MB	512 MB	512 MB	512 MB	512 MB	512 MB
PoE power	_	_	_	_	_	_
Maximum power	24W	24 W	24W	24W	24 W	24 W
Power supply (AC)	100 V to 240 V					
Frequency	50/60 Hz					
Dimensions (H x W x D)	44.5 mm x 300 m	nm x 220 mm (1.7	5 in. x 11.8 in. x 8.	.66 in.)		
Operating temperature	0°C to 45°C					
Relative humidity	5% to 95% (non-	-condensing)				
			Software			
Basic features	DHCP server/clien	t, PPPoE server/clie	ent, PPPoA server/c	lient, PPPoEoA serv	ver/client, NAT, Sub	o interface
Voice	RTP, SIP, SIP AG, I	P PBX/TDM PBX, F	XO/FXS, VoIP, BEST	, DISA, SBC(Only vo	oice models suppo	rt voice features)
WLAN(AP)		WLAN QoS, WLA pport WLAN AP fe		adio management,	, WLAN user mana	gement(Only
WLAN(AC)				nent),CAPWAP,WLA VMM), WLAN secu		
LAN	IEEE 802.1P, IEEE	802.1Q, IEEE 802.	3, VLAN managem	nent, MAC address	management, MS	TP, etc.
IPv4 unicast routing	Routing policy, st	atic route, RIP, OSF	PF, IS-IS, BGP			
IPv6 unicast routing	Routing policy, st	atic route, RIPng, (DSPFv3, IS-ISv6, BG	5P4+		
Multicast	IGMP version1/2/	3, PIM SM, PIM DI	M, MSDP			
VPN	IPSec VPN, GRE V	PN, DSVPN, L2TP	VPN, Smart VPN			
QoS	Diffserv mode, Priority mapping, traffic policing (CAR), traffic shaping, congestion avoidance (based on IP precedence/DSCP WRED), congestion management (LAN interface: SP/WRR/SP+WRR; WAN interface: PQ/CBWFQ), MQC (traffic classification, traffic behavior, and traffic policy), Hierarchical QoS, Smart Application Control (SAC)					
Security	ACL, firewall, 802.1x authentication, AAA authentication, RADIUS authentication, HWTACACS authentication, broadcast storm suppression, ARP security, ICMP attack defense, URPF, CPCAR, blacklist, IP source tracing, PKI,					
Management and maintenance		Upgrade management, device management, web-based GUI, GTL, SNMP(v1/v2c/v3), RMON, NTP, CWMP, Auto-Config, site deployment using USB disk, CLI				

Table 8: AR160s Technical Specifications

Item	AR169CVW	AR169CVW-4B4S		
	Hardware			
WAN speed with services* (IMIX)	150 Mbps 150 Mbps			
Number of recommended users	50	50		
Fixed WAN ports	1 x VDSL2(compatible with ADSL2+ Annex A/M, Annex B/J) 1 x GE SFP	1 x VDSL2(compatible with ADSL2+ Annex A/M, Annex B/J) 1 x GE SFP		
Fixed Ethernet switching ports	4 x GE RJ45(can be configured as WAN interfaces)	4 x GE RJ45(can be configured as WAN interfaces)		
Fixed voice ports	4 x FXS, 1 x FXO	4 x ISDN BRI 4 x FXS, 1 x FXO		
Integrated LTE	_	_		
Wi-Fi	802.11b/g/n, 2.4GHz, 2 x 2 MIMO 802.11ac, 5GHz, 2 x 2MIMO	802.11b/g/n, 2.4GHz, 2 x 2 MIMO 802.11ac, 5GHz, 2 x 2MIMO		
USB	1 USB3.0, compatible with USB2.0	1 USB3.0, compatible with USB2.0		
Console ports	1	1		
Memory size	512 MB	512 MB		
Flash memory	512 MB	512 MB		
PoE power	_	_		
Maximum power	24W	24 W		
Power supply (AC)	100 V to 240 V			
Frequency	50/60 Hz			
Dimensions (H x W x D)	30 mm x 270 mm x 155 mm (1.18 in. x 11.4 in. x	c 6.1 in.)		
Operating temperature	0°C to 45°C			
Relative humidity	5% to 95% (non-condensing)			
	Software			
Basic features	DHCP server/client, PPPoE server/client, PPPoA ser interface management	ver/client, PPPoEoA server/client, NAT, Sub		
Voice	RTP, SIP, SIP AG, IP PBX/TDM PBX, FXO/FXS, VoIP, BEST, DISA, SBC (Only voice models support voice features)			
WLAN(AP)	AP management, WLAN QoS, WLAN security, WLAN radio management, WLAN user management(Only WLAN models support WLAN AP features)			
WLAN(AC)	AP management(AC discovery/AP access/AP management), CAPWAP, WLAN user management , WLAN radio management (802.11a/b/g/n) , WLAN QoS (WMM), WLAN security (WEP/WPA/WPA2/Key management)			
LAN	EEE 802.1P, IEEE 802.1Q, IEEE 802.3, VLAN management, MAC address management, MSTP, etc.			

Item	AR169CVW	AR169CVW-4B4S			
IPv4 unicast routing	Routing policy, static route, RIP, OSPF, IS-IS, BGP				
IPv6 unicast routing	Routing policy, static route, RIPng, OSPFv3, IS-ISv6	5, BGP4+			
Multicast	IGMP version1/2/3, PIM SM, PIM DM, MSDP				
VPN	IPSec VPN, GRE VPN, DSVPN, L2TP VPN, Smart VPN				
QoS	Diffserv mode, Priority mapping, traffic policing (CAR), traffic shaping, congestion avoidance (based on IP precedence/DSCP WRED), congestion management (LAN interface: SP/WRR/SP+WRR; WAN interface: PQ/CBWFQ), MQC (traffic classification, traffic behavior, and traffic policy), Hierarchical QoS, Smart Application Control (SAC)				
Security	ACL, firewall, 802.1x authentication, AAA authentication, RADIUS authentication, HWTACACS authentication, broadcast storm suppression, ARP security, ICMP attack defense, URPF, CPCAR, blacklist, IP source tracing, PKI,				
Management and maintenance	Upgrade management, device management, web CWMP, Auto-Config, site deployment using USB of				

Table 9: AR160s Technical Specifications

Item	AR161EW	AR169EW	AR169EGW-L			
	Hardware					
WAN speed with services* (IMIX)	600Mbps	600Mbps	600Mbps			
Number of recommended users	50	50	50			
Fixed WAN ports	1 x GE Combo	1 x VDSL2 over POTS with Bondin 1 x GE Combo	g (support dying gasp)			
Fixed Ethernet switching ports	4 x GE RJ45(can be configured as WAN interfaces)					
Integrated LTE	_	_	FDD LTE Dual SIM slots, one active, one standby			
Wi-Fi	802.11a/b/g/n/ac/ac wave2, 4x4:4 MU-MIMO	802.11a/b/g/n/ac/ac wave2, 4x4:4 MU-MIMO	802.11a/b/g/n/ac/ac wave2, 4x4:4 MU-MIMO			
USB	1 USB3.0, compatible with USB	2.0				
Serial auxiliary/console ports	1					
Memory size	1 GB					
Flash memory	512 MB					
Maximum power	24W	36W	36W			
Power supply (AC)	100 V to 240 V					
Frequency	50/60 Hz					

Itama	AR161EW	AR169EW	AR169EGW-L		
Item	ANTOTEVV	AKTOSEVV	AK 109EGVV-L		
Dimensions (H x W x D)	44.0 mm x 300.0 mm x 216.4	mm(1.73 in. x 11.8 in. x 8.5 in.)			
Operating temperature	0°C to 45°C				
Relative humidity	5% to 95% (non-condensing)				
		Software			
Basic features	DHCP server/client, PPPoE serve interface management	er/client, PPPoA server/client, PPPoE	oA server/client, NAT, Sub		
WLAN(AP)	AP management, WLAN QoS, WLAN security, WLAN radio management, WLAN user management(Only WLAN models support WLAN AP features)				
WLAN(AC)	AP management(AC discovery/AP access/AP management), CAPWAP, WLAN user management , WLAN radio management (802.11a/b/g/n) ,WLAN QoS (WMM), WLAN security (WEP/WPA/WPA2/Key management)				
LAN	IEEE 802.1P, IEEE 802.1Q, IEEE	802.3, VLAN management, MAC a	ddress management, MSTP, etc.		
IPv4 unicast routing	Routing policy, static route, RIP,	OSPF, IS-IS, BGP			
IPv6 unicast routing	Routing policy, static route, RIP	ng, OSPFv3, IS-ISv6, BGP4+			
Multicast	IGMP version1/2/3, PIM SM, PI	M DM, MSDP			
VPN	IPSec VPN, GRE VPN, DSVPN, L	2TP VPN, Smart VPN			
QoS	Diffserv mode, Priority mapping, traffic policing (CAR), traffic shaping, congestion avoidance (based on IP precedence/DSCP WRED), congestion management (LAN interface: SP/WRR/SP+WRR; WAN interface: PQ/CBWFQ), MQC (traffic classification, traffic behavior, and traffic policy), Hierarchical QoS, Smart Application Control (SAC)				
Security	ACL, firewall, 802.1x authentication, AAA authentication, RADIUS authentication, HWTACACS authentication, broadcast storm suppression, ARP security, ICMP attack defense, URPF, CPCAR, blacklist, IP source tracing, PKI,				
Management and maintenance	Upgrade management, device management, web-based GUI, GTL, SNMP(v1/v2c/v3), RMON, NTP, CWMP, Auto-Config, site deployment using USB disk, CLI				

Table 10: AR160s Technical Specifications

Item	AR161EW-M1
	Hardware
WAN speed with services* (IMIX)	600Mbps
Number of recommended users	50
Fixed WAN ports	1 x GE Combo
Fixed Ethernet switching ports	4 x GE RJ45
Integrated LTE	_

Item	AR161EW-M1
Wi-Fi	802.11a/b/g/n/ac/ac wave2, 4x4:4 MU-MIMO
USB	1 USB3.0, compatible with USB2.0
Serial auxiliary/console ports	1
Memory size	1 GB
Flash memory	512 MB
Hard disk	2.5-inch hard disk (optional)
Maximum power	36W
Power supply (AC)	100 V to 240 V
Frequency	50/60 Hz
Dimensions (H x W x D)	44.0 mm x 300.0 mm x 216.4 mm(1.73 in. x 11.8 in. x 8.5 in.)
Operating temperature	0°C to 45°C
Relative humidity	5% to 95% (non-condensing)
	Software
Basic features	DHCP server/client, PPPoE server/client, PPPoA server/client, PPPoEoA server/client, NAT, Sub interface management
WLAN(AP)	AP management, WLAN QoS, WLAN security, WLAN radio management, WLAN user management(Only WLAN models support WLAN AP features)
WLAN(AC)	AP management(AC discovery/AP access/AP management), CAPWAP, WLAN user management , WLAN radio management (802.11a/b/g/n) , WLAN QoS (WMM), WLAN security (WEP/WPA/WPA2/Key management)
LAN	IEEE 802.1P, IEEE 802.1Q, IEEE 802.3, VLAN management, MAC address management, MSTP, etc.
IPv4 unicast routing	Routing policy, static route, RIP, OSPF, IS-IS, BGP
IPv6 unicast routing	Routing policy, static route, RIPng, OSPFv3, IS-ISv6, BGP4+
Multicast	IGMP version1/2/3, PIM SM, PIM DM, MSDP
VPN	IPSec VPN, GRE VPN, DSVPN, L2TP VPN, Smart VPN
QoS	Diffserv mode, Priority mapping, traffic policing (CAR), traffic shaping, congestion avoidance (based on IP precedence/DSCP WRED), congestion management (LAN interface: SP/WRR/SP+WRR; WAN interface: PQ/CBWFQ), MQC (traffic classification, traffic behavior, and traffic policy), Hierarchical QoS, Smart Application Control (SAC)
Security	ACL, firewall, 802.1x authentication, AAA authentication, RADIUS authentication, HWTACACS authentication, broadcast storm suppression, ARP security, ICMP attack defense, URPF, CPCAR, blacklist, IP source tracing, PKI,
Management and maintenance	Upgrade management, device management, web-based GUI, GTL, SNMP(v1/v2c/v3), RMON, NTP, CWMP, Auto-Config, site deployment using USB disk, CLI

^{*}Service performance depending on specific feature configuration.

How to Configure the Modular AR100, AR120, AR150, AR160 and AR200 Routers

Ordering Information

The AR100, AR120, AR150, AR160 and AR200 series routers are configured by selecting and installing the appropriate configuration module. The configuration module ordering information and descriptions are shown in the following table 11-14.

Table 11: Chassis Options

Chassis Configuration	Description
AR109	AR109,1 GE WAN,1 VDSL WAN,4 GE LAN,1 USB2.0
AR109W	AR109W,1 GE WAN,1 VDSL WAN,4 GE LAN,WIFI 2.4G,1 USB2.0
AR109GW-L	AR109GW-L,1 GE WAN,1 VDSL WAN,4 GE LAN,1 LTE,WIFI 2.4G,1 USB2.0
AR129CVW	AR129CVW,1 GE WAN,1 VDSL WAN,4 GE LAN,2 FXS,WIFI 2.4G+5G,1 USB2.0
AR129CGVW-L	AR129CGVW-L,1 GE WAN,1 VDSL WAN,4 GE LAN,1 LTE,2 FXS,WIFI 2.4G+5G,1 USB2.0
AR121	AR121,1FE WAN,4FE LAN
AR121W	AR121W,1FE WAN,4FE LAN,WIFI 2.4G
AR129	AR129,1VDSL WAN,4FE LAN
AR129W	AR129W,1VDSL WAN,4FE LAN,WIFI 2.4G
AR0M0001BA00	AR201,1FE WAN,8FE LAN,1USB
AR0M0007BA00	AR207,ADSL2+ ANNEX A/M WAN,8FE LAN,1USB
AROM2074BA	AR207G-HSPA+7,WCDMA HSPA+7,ADSL2+ ANNEX A/M WAN,8FE LAN,1USB
AROM008EBA00	AR208E,4 copper pair G.SHDSL WAN,8FE LAN,1USB
AROM1510BA00	AR151,1FE WAN,4FE LAN,1USB
AR0M1513BA00	AR151G-HSPA+7,1FE WAN,WCDMA HSPA+7,4FE LAN,1 USB
AR0M1570BA00	AR157,ADSL2+ ANNEX A/M WAN,4FE LAN,1USB
AR0M1576BA00	AR157W,ADSL2+ ANNEX A/M WAN,4FE LAN,802.11b/g/n AP,1 USB
AR0M1577BA00	AR157VW,ADSL2+ ANNEX A/M WAN,4FE LAN,802.11b/g/n AP,4FXS+1FXO,1 USB

Chassis Configuration	Description
AR0M1574BA00	AR157G-HSPA+7,ADSL2+ ANNEX A/M WAN,WCDMA HSPA+7,4FE LAN,1 USB
AROM1580BA	AR158E,4 copper pair G.SHDSL WAN,4FE LAN,1USB
AR0M1582BA00	AR158EVW,4 copper pair G.SHDSL WAN,4FE LAN,802.11b/g/n AP,4FXS+1FXO,1 USB
AR161	AR161,1GE WAN,4GE LAN
AR161F	AR161F,1GE COMB WAN,4GE LAN,1 USB
AR161FG-L	AR161FG-L,1GE COMB WAN,LTE FDD,4GE LAN,1 USB
AR161FGW-L	AR161FGW-L,1GE COMB WAN,LTE FDD,4GE LAN,802.11b/g/n AP,1 USB
AR161FW	AR161FW,1GE COMBO WAN,4GE LAN,1 USB,1 WLAN
AR161G-L	AR161G-L,1GE WAN,4GE LAN,LTE
AR161W	AR161W,1GE WAN,4GE LAN,WIFI 2.4G
AR161FV-1P	AR161FV-1P,1GE COMBO WAN,4GE LAN,1 USB,1 VE1
AR162F	AR162F,1SA,1GE COMBO WAN,4GE LAN,1 USB
AR168F	AR168F,4 copper pair G.SHDSL WAN,1GE COMB WAN,4GE LAN,1 USB
AR169	AR169,1VDSL WAN,4GE LAN
AR169F	AR169F,VDSL over POTS with bonding WAN,1GE COMB WAN,4GE LAN,1 USB
AR169FVW	AR169FVW,1GE COMBO WAN,4GE LAN,1 USB,4 FXS,1FXO,1 WLAN
AR169FVW-8S	AR169FVW-8S,1GE COMBO WAN,4GE LAN,1 USB,8 FXS,1FXO,1 WLAN
AR169FGW-L	AR169FGW-L,1GE COMBO WAN,4GE LAN,1 USB,4 1 WLAN
AR169FGVW-L	AR169FGVW-L,1GE COMBO WAN,4GE LAN,1 USB,4 FXS,1FXO,1 WLAN
AR169G-L	AR169G-L,1VDSL WAN,4GE LAN,LTE
AR169W	AR169W,1VDSL WAN,4GE LAN,WIFI 2.4G
AR169CVW	AR169CVW,1 VDSL WAN,1 GE SFP WAN,4 GE LAN,4 FXS,1 FXO,WIFI 2.4G+5G,1 USB2.0
AR169CVW-4B4S	AR169CVW-4B4S,1 VDSL WAN,1 GE SFP WAN,4 GE LAN,4 FXS,1 FXO,4 ISDN,WIFI 2.4G+5G,1 USB3.0
AR161EW	AR161EW,1*GE Combo WAN,4*GE LAN,4*4 MIMO WIFI,1*USB
AR169EW	AR169EW,1*GE Combo WAN,VDSL over POTS with bonding WAN,4*GE LAN,4*4 MIMO WIFI,1*USB
AR169EGW-L	AR169EGW-L,1*GE Combo WAN,VDSL over POTS with bonding WAN,4*GE LAN,4*4 MIMO WIFI,FDD,1*USB
AR161EW-M1	AR161EW-M1,1*GE Combo WAN,4*GE LAN,4*4 MIMO WIFI,1*USB,1*HDD

Table 12: Power Module Options

Power Module	Description
AROMPSAP1000	100W POE Power Module
W0ACPSE03	Adapter,0degC,40degC,90V,264V,12V/3A,C8/4pin

Table 13: License Options

License	Description
LARODATAE01	AR150&160&200 Value-Added Data Package
LAR0AC01	AR150&160&200 AC Express License
LAROVOICEE01	AR150&160&200 Value-Added Voice Package
LAROCMBEST01	AR CM&BEST License-5 telephones
LAROCMBEST02	AR CM&BEST License-25 telephones
LAROSECE01	AR150&160&200 Value-Added Security Package

Table 14: SD Card and USB Disk Options

SD Cards & USB Disks	Description
NUSBDSK01	Storage USB DISK,4GB,USB 2.0

For more information, visit http://enterprise.huawei.com/en/ or contact the Huawei local sales office.

Professional Service and Support

Huawei Professional Services provides expert network design and service optimization tasks, helping customers design and deploy a high-performance network that is reliable and secure, maximizing return on investment as well as reducing operational expenses.

Company Addendum

For more information, please visit http://enterprise.huawei.com/en/ or contact your local Huawei office.



Copyright © Huawei Technologies Co., Ltd. 2017. All rights reserved.

No part of this document may be reproduced or transmitted in any form or by any means without prior written consent of Huawei Technologies Co., Ltd.

Trademark Notice

, HUAWEI, and are trademarks or registered trademarks of Huawei Technologies Co., Ltd.

Other trademarks, product, service and company names mentioned are the property of their respective owners.

General Disclaimer

The information in this document may contain predictive statements including, without limitation, statements regarding the future financial and operating results, future product portfolio, new technology, etc. There are a number of factors that could cause actual results and developments to differ materially from those expressed or implied in the predictive statements. Therefore, such information is provided for reference purpose only and constitutes neither an offer nor an acceptance. Huawei may change the information at any time without notice.

HUAWEI TECHNOLOGIES CO.,LTD. Huawei Industrial Base Bantian Longgang Shenzhen 518129,P.R.China Tel: +86 755 28780808

www.huawei.com