# TS-251A & TS-451A

2-bay & 4-bay Turbo NAS



Use your Turbo NAS as a PC

QmailAgent email client helps you manage, access and backup multiple email accounts

# **USB QuickAccess Port**

Directly set up your NAS and access your NAS data by connecting your Windows® or Mac computer to the USB QuickAccess port

- Hardware-accelerated HDMI 4K Ultra HD playback and transcoding
- AES-NI hardware-accelerated encryption to deliver up to 196 MB/s throughput
- QTS-Ubuntu dual systems enables users to enjoy rich apps from QTS App Center & Linux
- Block-level snapshot helps you easily backup and restore data
- QNAP VJBOD (Virtual JBOD) allows you to expand the storage of the NAS by using unused storage from other QNAP NAS units
- Build a personal karaoke system with OceanKTV by 3.5 mm microphone jack



14nm Intel<sup>®</sup> Celeron<sup>®</sup> N3060 dual-core 1.6GHz (burst up to 2.48GHz)

(intel)

ONRP

0

9

69



Free Remote Control

00



# USB QuickAccess/NAS/ iSCSI-SAN triple solution

The TS-251A & TS-451A innovatively re-defines what NAS can do byproviding a USB QuickAccess/NAS/iSCSI SAN triple solution. It discards the restriction of conventional USB QuickAccess that only allows connecting to one device, and breaks the cost barrier for a dual Gigabit Ethernet solution.

# NAS USB QuickAccess ISCSI SAN

# Direct access to files with the USB QuickAccess port

The TS-251A & TS-451A features an innovative USB 3.0 QuickAccess port that allows you to complete the first-time installation and setup of your TS-251A & TS-451A without requiring network connectivity. The files and data stored on the TS-251A & TS-451A can also be directly accessed by using Qfinder Pro\* and a USB 3.0 A-Male to Micro B-Male cable or a USB 2.0 Micro B cable\*\*. Furthermore, you can assign access rights to users for different folders to prevent unauthorized access to important files.

\* Qfinder Pro only supports Windows and Mac OS X

\*\* A USB cable is not included. USB QuickAccess supports Windows 8.1/10 and Mac OS X 10.8 (and newer). Other versions may require driver installation,



# 2 Ethernet NAS mode

The TS-251A & TS-451A features Ethernet networking for flexible and simultaneous file sharing across multiple devices, using SMB/CIFS, NFS and AFP protocols for sharing across Windows, Mac and Linux/UNIX networks.



# Enjoy the best audiovisual experience with HDMI output and a free remote control



HybridDesk Station integrates 3rd-party media players and a web browser. With HDMI connectivity, you can connect the TS-251A & TS-451A to a HDTV or an A/V receiver to enjoy your rich multimedia content and 4K H.264 videos. The NAS includes a free QNAP remote control for you to conveniently control HybridDesk Station through its builtin IR receiver. With the help of the new smart remote control learning function, you can also pair up to three TV or stereo IR remote controls.

Playback capability and quality may vary due to factors including the original file formats/quality, hardware and software limitations, system load and the output devices.



Write

# Intel® Celeron® N3060 guad-core CPU and hardware-accelerated encryption engine

The TS-251A & TS-451A is powered by an advanced 14nm Intel® Celeron® quad-core 1.6GHz processor that features low TDP (only 6 watts) and can automatically burst up to 2.48GHz. Coupled with dual-channel 2GB / 4GB DDR3L-1600 dual-channel RAM (upgradable to 8GB), dual Gigabit LAN ports, and SATA 6Gb/s, the TS-251A & TS-451A can deliver up to 220MB/ s throughput for optimizing missioncritical tasks while still being energy efficient. The TS-251A & TS-451A also features Intel® AES-NI hardwareaccelerated encryption to deliver up to 196MB/s throughput with AES 256-bit encryption for both full NAS volume and shared folders, boosting system performance & security while ensuring the safety of sensitive business data stored in the NAS.



NAS-TS-451A OTS 4 2 2

Volume type: RAID 5; 4 x Seagate 1TB ST1000NM0033 HDDs: NAS and PCs are connected. Client PCs: Intel® Core™ i7-4770 3.40GHz CPU; DDR3L 1600Hz 16GB; 10GbE NIC: QNAP LAN-10G2SF-MLX; Windows® 10

### 3 iSCSI SAN block-based mode

The TS-251A & TS-451A supports iSCSI SAN. After creating an iSCSI



# Enjoy media freely with multi-zone multimedia controls



Use your NAS as a multi-zone multimedia system to fill every corner of your house with your choice of media. You can centrally manage and stream photos, music and videos from the NAS to different rooms from a single device using Bluetooth® & USB devices connected to the NAS (for music streaming only), HDMI, DLNA®, Apple TV<sup>®</sup> and Chromecast<sup>™</sup>\*. Alternatively, to enjoy multimedia yourself, you can choose DLNAcompatible devices, use the Qfile app on an iOS® device to browse videos/photos and play on the TV via Apple TV®, or transform the NAS into a powerful streaming machine with DLNA®, Roku<sup>®</sup>, Amazon<sup>®</sup> Fire TV, Google TV<sup>™</sup> and Plex Media Server support.

\* To stream multimedia via Chromecast, you must first install the multimedia extension pack from the QTS App Center.

# Superior 4K video transcoding

Featuring advanced 8th-generation Intel® HD Graphics, the TS-251A & TS-451A supports 4K H.264 hardware decoding and delivers superior real-time 4K and 1080p video transcoding to convert videos to universal formats that can be smoothly played on PCs, mobile devices and Smart TVs. With offline transcoding,

even when you can only connect using a low-speed Internet connection, you can still enjoy smooth video playback.



# Centralize backup, restoration and synchronization with Hybrid Backup Sync

Hybrid Backup Sync consolidates backup, restoration and synchronization functions into a single QTS application for you to easily transfer your data to local or remote QNAP NAS and to cloud storage spaces. You can synchronize files between the TS-251A & TS-451A and cloud storage in real time - including Amazon<sup>®</sup> Cloud Drive, Google Drive<sup>™</sup>, Dropbox<sup>®</sup>, Microsoft OneDrive<sup>®</sup>, Yandex<sup>®</sup> Disk, and Box<sup>®</sup>, and back up files to Amazon<sup>®</sup> S3, Amazon<sup>®</sup> Glacier, Microsoft<sup>®</sup> Azure<sup>™</sup>, Google Cloud Storage<sup>™</sup>, OpenStack Swift and WebDAV cloud services. Hybrid Backup Sync can detect sparse files to avoid backing up unnecessary data, and supports file compression to save storage space.



# Restore files with snapshot for volume & LUN

QTS Storage Manager features an easy-to-use webbased snapshot tool to easily backup and restore data on the TS-251A & TS-451A back to any point of time in the event of data loss. You can take snapshots for volumes and LUN (up to 64 snapshots per volume/ LUN and maximum 256 snapshots per NAS), efficiently replicate volume/LUN snapshots via Snapshot Replica to remote servers by copying only the changes made, and quickly clone a volume /LUN snapshot as a local volume without interrupting current system operations. You can even set up the system to automatically take a snapshot of the volume before backup via RTRR/rsync, even if files are opened.

# Use NAS to expand NAS capacity with Virtual JBOD

QNAP VJBOD (Virtual JBOD) is network-based JBOD that allows you to expand the storage of the TS-251 & TS-451 by using unused storage from other QNAP NAS units. You can mount this storage space to the NAS as virtual disks and create virtual storage pools and volumes for NAS functions. VJBOD supports port trunking (link aggregation with dual LAN ports) that increase the performance and reliability of your VJBOD storage.

# QTS-Ubuntu dual systems for IoT applications

The QTS-Linux dual systems are based on QNAP's advanced virtualization technologies. The TS-251A & TS-451A enables users to not only to download rich apps from QTS App Center but also supports Ubuntu and allows users to develop and install various IoT packages. Simply plug in a keyboard, mouse and HDMI monitor to the TS-251A & TS-451A, and use the Linux Station as if you were using a PC. You can also operate Ubuntu in Linux Station as a remote desktop via web browser for instant management\*.

Linux Station requires a QNAP NAS with at least 4GB RAM & Container Station v1.5.1343+.





VJBOD + Port Trunking (with connection fault tolerance)



USB expansion unit (JBOD) (without fault tolerance)



# Storage for hosting virtual machines and containerized applications

Virtualization Station allows you to host virtual machines (VM) on the TS-251A & TS-451A and access them via a web browser or VNC. Virtualization Station supports multiple operating systems, fast VM creation, VM backup & restoration, VM import/ export, snapshot, and Device Management for centrally managing VM. The TS-251A & TS-451A also features the game changingcontainer technology for server virtualization with Container Station. It exclusively integrates LXC and Docker® lightweight virtualization technologies. Container Station now also provides the QIoT Containers platform to help you quickly structure your IoT environment and deployment in your private cloud.





### Enjoy an exclusive karaoke experience

OceanKTV is the first NAS-based karaoke application and allows you to create a quality karaoke experience at home or in the office. The NAS comes with a 3.5 mm microphone jack and can transmit audio to your amplifier using HDMI or the 3.5 mm line out port. Simply attach an HDMI display to the NAS and start singing with OceanKTV.



# Extensive apps and utilities

The NAS provides several useful applications to extend beyond basic storage functionality. Use Download Station to download files without switching on your PC. Enjoy easy access to your files from your mobile devices using mobile Apps like File, Qphoto, and Qmusic. Use Qfinder Pro to help you find, access and manage your QNAP NAS on your network easily.



# QmailAgent: a mailroom center for your private cloud

QmailAgent is an online email client that helps you manage multiple email accounts, allowing you to access all of your emails and to easily switch between different accounts. It provides complete functionality for composing, reading and organizing emails. You can even attach files, photos and documents from the NAS when composing emails. Qmail also allows iOS<sup>®</sup> and Android<sup>™</sup> users to quickly check multiple email accounts with mobile devices, and to browse & send emails using the QmailAgent on their NAS.

### Back up all emails to high-capacity NAS

QmailAgent supports automatically backing up your emails to the NAS. After you import email account details and upon logging in, QmailAgent will start backing up your emails from the servers (or cloud) to your NAS, allowing you to be protected against accidental email deletion.



### Receive and send emails with your mobile devices through NAS



You can also download Qmail Client (a companion app for iOS and Android devices) to allow you to access your emails via your NAS. With Qmail Client on your mobile device, the system will display and cache new emails on your mobile device to keep you updated, and you can read them even when an Internet connection is unavailable.

# Comprehensive surveillance solution providing 24/7 security

Surveillance Station is a professional network surveillance Video Management System (VMS) that offers a user-friendly management interface, over 3,000 compatible IP camera models, and expandable IP camera channel licenses. It supports real-time monitoring, video & audio recording and playback with a wide range of customizable settings. You can also install the Vmobile app on your iOS<sup>®</sup> or Android<sup>™</sup> devices to manage monitored channels anytime and anywhere to safeguard your office environment, or install the Vcam mobile app to turn your device into a network camera to instantly record to your NAS. The NAS includes 2 free IP camera channels and you can expand up to 32 channels by purchasing additional licenses.



Supports VM import and export, cloning & snapshot, backup and restore
 VM console can be displayed via HDMI output -

• HTML5-based shared remote console • Supports three different networking modes:

 Download applications from the built-in Docker Bulk registry
 Supports one-click installation, container
 export/import & console mode
 Supports two network modes (NAT and host)

Isolated, External-only and Bridged

QVM

Osirch

**iSCSI (IP SAN)** 

restoration

bar

Android)

VPN Server

protocol)

VPN Client

**DLNA** Server

OceanKTV

App Center

of some countries.

PlayStation 4 and Xbox On

Use the NAS as a karaoke machine

Surveillance Station

**Container Station** 

Supports LXC and Docker

 Supports auto-start containers Supports downloading Docker certificates
 Supports adding private registries

Supports full-text search in real-time
 Bar chart to show data distribution

Supports previews for photos, music, videos, Gmail, PDF.etc

Show search results using thumbnails or a list
 Supports search Chrome extension

ISCSI (IP SAN) SISCI target with multi-LUNs per target (Up to 256 targets/LUNs combined) Supports LUN mapping & masking Online LUN capacity expansion Support for SPC-3 persistent reservation Support MPIO & M/C5 SUPPORTS MPIO & M/C5

iSCSI connection and management by ONAP

Supports over 3,000 IP cameras
 Includes 2 free camera licenses, up to 32 camera channels by purchasing additional licenses
 Instant playback to check recent events
 Visual aid by e-map
 Playback and speed control using the shuttle

bar - Video preview on playback timeline - Intelligent video analytics (IVA) for advanced video searching - Surveillance client for Mac - Mobile surveillance app: Vmobile (iOS and Andreiei

Mobile recording app: Vcam (iOS and Android)

Secure remote access: PPTP \ L2TP/IPsec & OpenVPN VPN services
 Max number of clients: 45 (15 clients for each

Supported VPN protocols: PPTP and OpenVPN

• PPTP Authentication: PAP, CHAP, MS-CHAP, MS-CHAP, 2 • PPTP Encryption: None, AES 40/128 bit, AES 256 bit • OpenVPN Encryption: None, AES 40/128 bit, AES 256 bit

Transmission package monitor
 OpenVPN port control & link compression

Supports DLNA/UPnPTVs and players such as

Support CUE indexing file for APE, FLAC audio format.
Video and Audio On-the-fly Transcoding

Use the NAS as a karaoke machine.
 Display songs by artists, languages, and favorites.
 Enhance the experience with effects such as tuning echo, key, or applause
 Control the playlist with a mobile app.
 Supports keyboard and remote control (RM-RF001/ RM-IR002)

Ofinder Pro with Storage Plug & Connect

Creating and mapping shared folders by QNAP
 Windows Qfinder Pro

Creation of and connection to iSCSI target/LUN

Over 100 official and community software add-ons such as Q' center, Signage Station, Notes Station,
 1 Not all IPv6 services are supported.
 2 Data encryption functions may be unavailable in accordance with the legislative restrictions of some cumption;

3 This feature may vary by model. 4 DRM-protected content is not supported

Designs and specifications are subject to change without notice.

Windows Qfinder • Virtual disk drive (via iSCSI initiator) • Stack chaining master • Max No. of virtual disk drives: 8

### **Operating System** • QTS 4.2 (embedded Linux)

Supported Client OS

Windows 7, Windows 8, Windows 10, Windows Server 2003/2008 R2/2012/2012R2
 Apple Mac OS X, Linux & UNIX

### Supported Browsers

Microsoft Internet Explorer 10+ , Google Chrome, Apple Safari 7+, Mozilla Firefox

Multilingual Support • Chinese (Traditional & Simplified), Czech, Danish, Dutch, English, Finish, French, German, Greek, Hungarian, Italian, Japanese, Korean, Norwegian, Polish, Portuguese (Brazil), Romanian, Russian, Spanish, Swedish, Thai, Turkish

### File System

Internal Hard Drive: EXT4
 External Hard Drive: EXT3, EXT4, NTFS, FAT32, HFS+

- Networking TCP/IP (IPv4 & IPv6: Dual Stack)1 Dual Gigabit NICs with jumbo frame (failover, multi-IP settings, port trunking/NIC teaming) Service binding based on network interfaces Squid Proxy server & Proxy client Protocols: CIFS/MB, AFP (v3.3), NFS(v3), FTP, FTPS, SFTP, TFTP, HTTP(S), Telnet, SSH, iSCSI, SNMR, SMTP, and SMSC UPnP & Bonjour Discovery
- UPnP & Bonjour Discovery

### Network & Virtual Switch

• DHCP client, DHCP server • USB Wi-Fi Adapter Support • Virtual Switch

### Security

- Network access protection with auto-blocking: SSH, Telnet, HTTP(S), FTP, CIFS/SMB, AFP
   CIFS host access control for shared folders
   FIPS 140-2 validated AES 256-bit volume-based and shared folder data encryption2
   AES 256-bit external drive encryption2
   Iwanasthele SLL actificate

- Importable SSL certificates Instant alerts via email, SMS, beep, and push
- service
  2-step verification

### Storage Management

- Storage Space Utilization monitoring
   QNAP flexible Volume/LUN with thin

- QNAP flexible Volume/LUN with thin provisioning and space reclaim3 Disk volume types -2 Fay: RAID 0,1, JBOD, single -4 Bay: RAID 0,1, 5, 6, 10, 5 + hot spare, JBOD, single Supports volume/LUN snapshots, up to 256 per system (4GB System RAM required)3 -Online torage pool expansion -Online RAID capacity expansion and online RAID level migration -SMART data migration SMART data migration Storage expansion via a QNAP UX-500P/UX-800P expansion unit
   -

- 800P expansion unit JBOD enclosure roaming
- SSD read-only/read-write cache

### Power Management

# • Wake on LAN • Internal hard drive standby mode

- Internal hard arrive standoy mode
   Scheduled power on/off
   Automatic power on after power recovery
   USB and network UPS support with SNMP
   management
   System sleep mode (S3)

### Access Right Management

- Batch users creation, import/export users
   User quota management
   Local user access control for CIFS, AFP, FTP, and WebDAV
   Application access control for Photo Station, Music Station, Video Station, and File Station
   Subfolder permissions support for CIFS/SMB, AFP ETP and File Station
- AFP, FTP, and File Station

### Domain Authentication Integration Microsoft Active Directory (AD) & Domain

- Controller support LDAP server, LDAP client Domain users login via CIFS/SMB, AFP, FTP, and File Station

### mvONAPcloud Service

- Private cloud storage and sharing
   Private cloud storage and sharing
   Free host name registration (DDNS)
   Optional myQNAPcloud SSL certificates (DDNS)
   Auto router configuration (via UPnP)
   Web-based file manager with HTTPS 2048-bit
   encryption

- •Web-based file manager with HTTPS 2048-bit encryption
   •CloudLink for remote access without any complicated router setup
   •MyQNAPCloud connect for easy VPN connection (Windows VPN utility)

### Qsynd

Print Server

Photo Station

**Music Station** 

iTunes Server

Video Station

iTunes

email

Up to 8 music alarms

maps

Max number of printers: 3
 Supports Internet Printing Protocol
 Print job display and management
 IP-based and domain name-based privilege
 control

Show photos by thumbnails, list, timeline, or folder view
 Tag photos with text, colors, and ratings
 Slideshows with background music and different transition effects

Geotag photos and display them on Google

maps Supports uploading photos/videos to Picasa, Flickr, Weibo, YouTube Supports face detection (with the Photo Station Extension) Supports PDF to image conversion (with the Photo Extrins Extension)

Play or share music via web browser
 Supports changing album covers via Google search or by uploading photos.
 Internet radio (MP3)

Mobile app: Qmusic for music streaming and management

Audio and video sharing for Windows & Mac

• Show photos by thumbnails, list, timeline, or folder view • Tag videos with text, color, and ratings

Share video links to social websites or through

email • Display movie information and posters from Internet sources or user-uploaded files • Supports displaying subtitles (\*.SRT,\*ASS, \* SSA), online searching and downloading of subtitles as well as importing subtitle files • Supports Facebook friends login Mobile app: Qvideo for online video browsing and management

Streams videos, photos and music from NAS to

Apple TV or Chromecast via File Station, Music Station, Photo Station, Video Station or mobile

Note: The Media Streaming add-on app must be installed from the QTS App Center.

PC-less BT, FTP/FTPS, and HTTP/HTTPS, Thunder, FlashGet and qqdl download (up to 500 Tasks) The maximum number of concurrent downloads: 90 (30 BT/PT, 30 HTTP, 30FTP

downloads) • BT download with search, Magnet Link and PT support • Scheduled download and bandwidth control

Scheduled download and bandwidth control RSS subscription and download (broadcatching)
 Proxy support for BT download
 Mobile app: Qget for downloads browsing and

Playback videos, music, photos on TV with Kodi via HDMI
 Watch various online contents
 Web Neurope Conference

mouse Supports QNAP Qremote app and the official Kodi remote app Supports user login permissions A variety of applications are available including Skype, Plex Home Theater, and more Up to 7.1 channel audio passthrough is currented a

Note:The playback and quality of some video files may be affected by the system's CPU and GPU decoding abilities.

Linux Station - Use your NAS as a Ubuntu PC using the NAS HDMI output. - Download and use a variety of applications from the Ubuntu Software Center. - Supports remote desktop to monitor and access Ubuntu remotely. - An open source software platform for developmer

Note: The NAS requires at least 4GB RAM and Container Station must be installed.

Supports Virtual Machine (VM) creation to run
operating systems such as Windows, Linux, Unix
and Android

Web browsers (Chrome, Firefox)
 Supports international keyboards, input and

app (Qfile, Qmusic, Qphoto or Qvideo).

AirPlay & Chromecastk

**Download Station** 

management

mouse

supported

Linux Station

developers.

Virtualization Station

HD (HybridDesk) Station

Photo Station Extension) • Supports Facebook friends login

- Sync files across multiple devices with SSL secure connection
   Selective synchronization for only syncing specific folders
   Use team folders as a file center for greater team collaboration (maximum sync tasks:32)
   Shares files by links via e-mail
- Shares files by links via e-mail
   Policy settings for conflicting files and file type
   filter support
   Version control: up to 64 versions.
   Supports central configuration mode
   Supports remote erase/restore
   Supports Windows & Mac OS

### Web Administration

 Multi-window, multi-tasking based system management Dynamic DNS (DDNS) SNMP (v2 & v3)

- Resource monitor
- · Network recycle bin for file deletion via
- CIFS/SMB, AFP, and File Station
- Comprehensive logs (events & connection)
   Syslog client/server
   Mobile app: Qmanager for remote system
   monitoring & management

### File Server

- File sharing across Windows, Mac, and Linux/ INIX
- Windows ACL Advanced folder permissions for CIFS/SMB, AFP,
- Shared folder aggregation (CIFS/SMB)

### FTP Server

- FTP over SSL/TLS (Explicit)
   FXP support

### **File Station**

- Supports mounting cloud drives (such as Google Drive, Dropbox, Microsoft OneDrive, Amazon Cloud Drive, Yandex Disk and Box). Supports mounting remote shared folders through FTP, WebDAV or Microsoft networking (SMB/CIFS) Emports receive degree and in Office Online
- (SMIS/CIFS) Supports opening documents via Office Online, Google Docs or Chrome Extension (Edit Office files in Google Docs, Sheets, and Slides) Supports ISO Mounting (Up to 256 ISO Files) Drag-n-drop Files via Chrome and Firefox Browsora
- Browsers
- Photo, music, and video preview and playback with hardware-accelerated transcoding File Compression (ZIP or 7z) • Supports displaying subtitles (\*.SRT, UTF-8 format)

- Video seeking support for video playback during on-the-fly transcoding
   Supports slideshow playback in media viewer
   Mobile App: Qfile for file browsing and management

### Transcode Management

transcoding

**Backup Station** 

**Cloud Drive Sync** 

**Cloud Backup Station** 

Google Cloud Storage
 WebDAV-based cloud storage
 Microsoft Azure
 OpenStack Swift

- Transcode video files to 240p, 360p, 480p, 720p and 1080p resolution
   Automatic video transcoding for watched
- folders Hardware accelerated transcoding support
   Embed subtitles into videos for background

Remote replication server (over rsync)
 Real-time remote replication (RTRR) to another
 QNAP NAS, FTP or CIFS/SMB server

QNAP NAS, FIP or CIF-JSMB server Works as both RTRR servers & client with bandwidth control Real-time & scheduled backup Backup versioning for RTRR 5 Snapshot support for RTRR/Rsync Encryption, compression, file filter, and transfer rate limitation Deskton backup with DNAP NetBat Beolicator.

 Desktop backup with QNAP NetBak Replicator for Windows Apple Time Machine backup support
 Data backup to multiple external storage

devices Third party backup software support: Veeam

Arcserve backup, emc retrospect, Symantec Backup & replication, Acronis True Image, Arcserve backup, emc retrospect, Symantec

Multiple Could account management like Google Drive, Dropbox, OneDrive, and hubiC Supports multiple cloud accounts Concurrent job execution and multi-threaded data transfer • Per-account bandwidth throttling

Amazon S3 Plus (including Amazon S3), Glacier

# Hardware Specifications







Console port 3.5 mm microphone iack 3.5 mm line out port HDMI - 2 x USB 3.0

2 x GbE - DC Input 12V

Kensington lock

Ordering P/N	TS-251A-4G	TS-251A-2G	TS-451A-4G	TS-451A-2G	
Processor	14nm Intel® Celeron® N3060 dual-core 1.6GHz (up to 2.48GHz)				
Hardware Encryption Accleration	√, AES-NI				
System Memory	4GB DDR3L (2 x 2GB)	2GB DDR3L (2 x 1GB)	4GB DDR3L (2 x 2GB)	2GB DDR3L (2 x 1GB)	
Maximum Memory	8GB				
Memory Slot	2 x SODIMM DDR3L (For dual-DIMM configurations, you must use a pair of identical DDR3L modules.)				
Flash Memory	4GB, pre-loaded with QTS system				
Drive Type	2 x 3.5"/2.5" SATA 6Gb/s HDDs/SSDs				
GbE LAN	2 x Gigabit RJ45 LAN port				
USB Port	3 x USB 3.0 ports (Front: 1, Rear:2)				
SD Card Reader	√				
USB QuickAccess Port	✓ (USB 3.0 Micro-B); USB cable is not included				
HDMI	1, max. resolution 3840 x 2160 @ 30Hz				
Audio Input	3.5mm Microphone Input jack (for dynamic microphone)				
Audio Output	3.5mm Line Out jack (for ampliers or speakers)				
LED Indicator	Status/Power, USB, HDD 1, HDD 2		Status/Power, USB, HDD	Status/Power, USB, HDD 1, HDD 2, HDD 3, HDD 4	
Button	Power/Status, USB one-touch-backup, reset				
IR Receiver	$\checkmark$ , supports QNAP RM-IR002 and MCE-compliant remote controls				
Others	Kensington security slot , system maintenance port				
		168.5 x 102 x 225 mm         168.5 x 160 x 225 mm           6.63 x 4.02 x 8.86 inch (HxWxD)         6.63 x 6.30 x 8.86 inch (HxWxD)			
Weight	Net : 1.28 kg (2.82 lbs)         Net : 3 kg (6.61 lbs)           Gross : 2.64 kg (5.82 lbs)         Gross : 3.6 kg (7.94 lbs)				
Operating Temperature	0~40°C				
Relative Humidity	5~95% RH non-condensing, wet bulb: 27°C				
Noise Level	18.3 dB (A)*		18.1 dB (A)*		
Power Consumption	System sleep : 0.72W         System sleep : 0.65W           HDD standby : 7.9W         HDD standby : 12.1W           In operation : 16.2W         In operation : 27W           (with 2 x 2TB HDDs)         (with 4 x 2TB HDDs)		by : 12.1W ion : 27W		
Power	65W AC power ad	65W AC power adapter, 100-240V AC 96W AC power adapter, 100-240V AC		apter, 100-240V AC	
Fan	1 x 7cm system	1 x 7cm system fan (12V DC) 1 x 12cm system fan (12V DC)			

\*Refer to ISO 7779 Maximum HDD loaded ; Bystander Position ; Average data from 1 meter in front of operating NAS. Model specifications are subject to change without notice. Please refer to www.qnap.com for the latest information.

### Accessories

	Category	Order P/N	Description
For a start start start	1	UX-800P	QNAP 8-bay Expansion unit 185.2 x 298.2 x 235.4 mm , 7.3 Kg 7.29 x 11.74 x 9.27 inch (H x W x D), 16.08 lbs
Expansion units		UX-500P	QNAP 5-bay Expansion unit 185.2 x 210.6 x 235.4 mm , 5.1Kg 7.29 x 8.29 x 9.27 inch (H x W x D), 11.24 lbs
	-	RAM-1GDR3L-SO-1600	1GB DDR3L RAM, 1600MHz, SO-DIMM
Memory		RAM-2GDR3L-SO-1600	2GB DDR3L RAM, 1600 MHz, SO-DIMM
Merrory		RAM-4GDR3L-SO-1600	4GB DDR3L RAM, 1600 MHz, SO-DIMM
		RAM-8GDR3L-SO-1600	8GB DDR3L RAM, 1600 MHz, SO-DIMM
Remote control	:0::	RM-IR002	Infrared (IR) remote control (Included)

# Package content

NAS Server

- Ethernet Cable x 2
- AC Adapter and Power Cord • Quick Installation Guide (QIG)
- Remote Control

Hot-Swappable HDD trays

• Screws for 3.5" & 2.5" HDD

# **QNAP** Systems, Inc.

TEL : +886-2-2641-2000 FAX : +886-2-2641-0555 Email: qnapsales@qnap.com Address : 3F, No.22, Zhongxing Rd., Xizhi Dist., New Taipei City, 221, Taiwan

Netherlands (Warehouse Services) Email:nlsales@qnap.com TEL:+31(0)107600830

India Email:indiasales@qnap.com

Germany
Email:desale
TEL . 40.00

Thailand Email:thsales@qnap.com TEL:+66-2-5415988

