

Data Sheet

FUJITSU Server PRIMERGY TX1330 M3 Tower Server

Expandable server designed to meet typical SME business requirements

FUJITSU Server PRIMERGY will give you the servers you need to power any workload and changing business requirements. As business processes expand so does the need for applications. Each has its own resource footprint, so you need a way to optimize your computing to better serve your users. PRIMERGY systems will help you match your computing capabilities to your business priorities with our complete portfolio of expandable PRIMERGY tower servers for remote and branch offices, versatile rack-mount servers, compact and scalable blade systems, as well as hyper-converged scale-out servers. They convince by business proven quality with a wide range of innovations, highest efficiency cutting operational cost and complexity, provide more agility in daily operations, and integrate seamlessly to let help you concentrate on core business functions.

Perfect for small and medium businesses as well as branch offices, FUJITSU Server PRIMERGY TX tower systems are robust and cost-efficient servers by providing rock solid reliability. Additionally they are characterized by simple IT operations, low power consumption and quiet operation so that they can be handled by non-technically trained staff and can be used in standard office environments. By the way: Almost all PRIMERGY TX servers can be rack-mounted to offer best flexibility.

PRIMERGY TX1330 M3

The FUJITSU Server PRIMERGY TX1330 M3 is a highly expandable and robust mono-socket server designed for Small and Medium Enterprise requirements. It also features the latest in processing and memory for classic infrastructure workloads such as file, print, web or collaborative ones such as email, as well as business specific applications. This mono-socket tower system can be equipped with the latest Intel® Xeon® E3-1200 v6 product family processors and up to

64 GB DDR4 memory, which improve application performance. The server is designed for high levels of secure expandability with up to 24x 2.5-inch hot-plug drives (3.5-inch drive configurations are also available), advanced RAID controllers (1/2GB cache and more advanced units on the roadmap) and data back-up options, making it ideal for consolidating and managing large datasets. Up to 4 PCIe slots are available for additional growth requirements. Operator concerns are eased with high availability features such as the optional Fujitsu Battery Backup Unit, high-efficiency (94%) redundant power supplies and redundant fans. The compact server housing and the unit's extremely low operating noise also make it suitable for deployment in public areas such as showrooms, retail premises or offices. Furthermore, advanced server management is enabled via the iRMC S4 which enables remote management capabilities and the Fujitsu ServerView® Suite which provides administrators comprehensive support during server installation, deployment and administration.



Features & Benefits

Main Features	Benefits
<p>Powerful Performance combined with high expandability</p> <ul style="list-style-type: none"> ■ Business computing needs are met with the latest Intel® Xeon® E3-1200 v6 product family processors, and up to 64GB DDR4 memory (4 DIMMs). Affordable Core™ i3 and Pentium® processors are also available ■ Server is designed for substantial, reliable storage expandability. It supports up to 12x3.5-inch drives (120 TB max.) or up to 24x2.5-inch drives (48TB max.) and Fujitsu's powerful RAID controllers (including SAS 3.0, 1/2 GB cache with more advanced units on the roadmap). Backup options include LTO and RDX. Security optimization includes TPM 2.0 support plus Fujitsu's secure 3-way lock for server access ■ Redundant (2x1GbE) LAN as standard plus additional advanced connectivity options available ■ Future ready with 4x PCIe Gen3 slots <p>Reliability features tailored to protect your business investment</p> <ul style="list-style-type: none"> ■ High efficiency 450W power supplies (94% efficiency) are available with both hot-plug capability and redundancy ■ Fujitsu Battery Backup Unit an optional Internal UPS in modular PSU form-factor, 5 years lifetime, fully integrated <p>Silent and versatile design - optimized for the SME environment</p> <ul style="list-style-type: none"> ■ Incredibly low noise emissions by design, with optimized air flow and Fujitsu's CoolSafe® Advanced Thermal Design technology ■ Deployment flexibility with a 4U design. Can be used as a tower server or deployed in a rack <p>Full server management features and easy accessibility</p> <ul style="list-style-type: none"> ■ Comprehensive software management suite available with the iRMC S4 and the Fujitsu ServerView Suite ■ Screw-less chassis with hot-plug 2.5-inch drives, hot-plug PSUs and "Easy Rails" for 3.5-inch storage disks 	<ul style="list-style-type: none"> ■ The server compute and memory can be optimized per the workload requirement. Xeon® E3-1200 v6 product family processors offer higher quad-core performance for more demanding compute needs. The workloads can range from classic infrastructure ones such as file, print, collaborative ones such as email to more demanding business specific applications ■ Ideal for customers who are looking for a secure, cost-effective server to consolidate and manage large datasets, or a system which features high-capacity secure local storage, combined with growth potential ■ Reliable data connectivity out of the box. Networking options (for example: 2x10GbE capability networking cards) offer data transfer headroom above and beyond the standard, redundant 2x1Gb Ethernet capability ■ The server grows in synch with your business. Upgrade the server with a Graphics card, or Fujitsu RAID controllers for reliable data storage and management (high grade SAS 3.0 with up to 1/2 GB cache, more advanced units on the roadmap) or networking cards (including 10GbE options) for seamless data transmission ■ Good for the environment, and your business – the high efficiency, redundant power supplies offer enhanced reliability and lower energy expenditure ■ The Battery Backup Unit protects your valuable investment by supporting safe power down and conflict free power up in case of power loss ■ Silent Operation and expanded range of operation (5 °C to 40 °C). The server can also be used in offices, showrooms ■ Tower based form factor for standard SME needs. Rackmount kit ensures an excellent long term investment. Customers can expand capabilities as their business grows, by deploying multiple PRIMERGY TX1330 M3s in a rack ■ Reduce your IT administrator's burden by simplifying server management via a comprehensive software suite which can include the iRMC S4 and the Fujitsu ServerView suite, which includes tools for installation and deployment, permanent status monitoring and control ■ Enhanced serviceability with easy, fast and comfortable access to critical components

Technical details

PRIMERGY TX1330 M3

Base unit	PRIMERGY TX1330 M3	PRIMERGY TX1330 M3	PRIMERGY TX1330 M3
Housing types	Tower	Tower	Rack
Power supply	Standard	Hot-plug	Hot-plug
Product Type	Mono Socket Tower Server	Mono Socket Tower Server	Mono Socket Tower Server

Mainboard

Mainboard type	D3373
Chipset	Intel® C236
Processor quantity and type	1 x Intel® Xeon® processor E3-1200 v6 product family / Intel® Pentium® processor / Intel® Core™ i3 processor

Processor

Intel® Core™ i3-7100 processor (2C/4T, 3.90 GHz, TLC: 3 MB, Turbo: No, 2,400 MHz, 51 W)
Intel® Pentium® processor G4560 (2C/4T, 3.50 GHz, TLC: 3 MB, Turbo: No, 2,400 MHz, 54 W)
Intel® Xeon® processor E3-1220v6 (4C/4T, 3.00 GHz, TLC: 8 MB, Turbo: 3.30 GHz, 2,400 MHz, 72 W)
Intel® Xeon® processor E3-1225v6 (4C/4T, 3.30 GHz, TLC: 8 MB, Turbo: 3.50 GHz, 2,400 MHz, 73 W)
Intel® Xeon® processor E3-1230v6 (4C/8T, 3.50 GHz, TLC: 8 MB, Turbo: 3.70 GHz, 2,400 MHz, 72 W)
Intel® Xeon® processor E3-1240v6 (4C/8T, 3.70 GHz, TLC: 8 MB, Turbo: 3.90 GHz, 2,400 MHz, 72 W)
Intel® Xeon® processor E3-1270v6 (4C/8T, 3.80 GHz, TLC: 8 MB, Turbo: 4.00 GHz, 2,400 MHz, 72 W)
Intel® Xeon® processor E3-1280v6 (4C/8T, 3.90 GHz, TLC: 8 MB, Turbo: 4.00 GHz, 2,400 MHz, 72 W)

Memory slots	4
Memory slot type	DIMM (DDR4)
Memory capacity (min. - max.)	4 GB - 64 GB
Memory protection	ECC
Memory notes	Mix and match possible; with dual channel operation better performance (2 modules with equal capacity necessary). Single channel (1 module) configuration possible.

Memory options

4 GB (1 module(s) 4 GB) DDR4, unbuffered, ECC, 2,400 MHz, PC4-2400, DIMM, 1Rx8
8 GB (1 module(s) 8 GB) DDR4, unbuffered, ECC, 2,400 MHz, PC4-2400, DIMM, 1Rx8
16 GB (1 module(s) 16 GB) DDR4, unbuffered, ECC, 2,400 MHz, PC4-2400, DIMM, 2Rx8

Interfaces

USB 2.0 ports	5 (4x external rear, 1x internal for UFM, no USB wakeup supported)
USB 3.0 ports	5 (2x external rear, 2x external front, 1x internal)
Graphics (15-pin)	1 analog graphics interface derived from iRMC (up to 1600x1200 or 1920x1080 at 16bpp)
Serial connection	1 x serial RS-232-C
LAN / Ethernet	2 x1 Gb/s Ethernet; RJ45
Management LAN (RJ45)	1 x dedicated management LAN port for iRMC S4 (10/100/1000 Mbit/s) Management LAN traffic can be switched to shared onboard Gbit LAN port

Onboard or integrated Controller

RAID controller	Optionally integrated RAID 0/1 or RAID 5/6 controller for SAS base units (occupies one PCIe slot). All hardware storage controller options are described under Components
SATA Controller	Intel® C236, 2 ports used for accessible drives
SATA controller type notes	4 port for internal SATA HDDs with RAID 0, 1, 10 for Windows and Linux;
LAN Controller	Intel® i210 onboard 2 x 10/100/1000 Mbit/s Ethernet iSCSI, PXE-Boot and WoL are supported
Remote management controller	Integrated Remote Management Controller (iRMC S4, 256 MB attached memory incl. graphics controller) IPMI 2.0 compatible
Trusted Platform Module (TPM)	Infineon / TPM 1.2 or TPM 2.0 module; TCG compliant (option)

Slots

PCI-Express 3.0 x1 (mech. x4)	1 x Full height, up to 168 mm length
-------------------------------	--------------------------------------

Slots

PCI-Express 3.0 x4	1 x Full height, up to 168 mm length
PCI-Express 3.0 x8	2 x Full height, up to 240 mm length notched
Slot Notes	Optional PCIe to legacy PCI adapter available. In SAS configuration 1x PCI-Express occupied by modular RAID controller.

Drive bays

Storage drive bays	3.5-inch or 2.5-inch hot-plug SAS/SATA
Accessible drive bays	3 x 5.25/1.6-inch
Notes accessible drives	all possible options described in relevant system configurator

Drive bays

Storage drive bays	Max. 4x 3.5-inch or 8x 2.5-inch	Max. 12x 3.5-inch or 24x 2.5-inch
Accessible drive bays	3 x 5.25/1.6-inch for 1 x backup drive + 1 x ODD	3 x 5.25/1.6-inch for 1 x backup drive + 1 x ODD

Fan Configuration

Number of fans	1	2
Fan configuration	1 standard fan	redundant fans
Fan notes	non redundant / non hot-plug	non hot-plug

Operating panel

Operating buttons	On/off switch NMI button Reset button
Status LEDs	System status (orange / yellow) Identification (blue) Hard disks access (green) Power (orange / green) At system rear side: System status (orange / yellow) Identification (blue) LAN connection (green) LAN speed (green / yellow) CSS (yellow)

BIOS

BIOS features	ROM based setup utility Recovery BIOS BIOS settings save and restore Local BIOS update from USB device Online update tools for main Linux versions Local and remote update via ServerView Update Manager Remote PXE boot support Remote iSCSI boot support
---------------	---

Operating Systems and Virtualization Software

Certified or supported operating systems and virtualization software	Microsoft® Hyper-V Server 2016
	Microsoft® Windows Server® 2016 Datacenter
	Microsoft® Windows Server® 2016 Standard
	Microsoft® Windows Server® 2016 Essentials
	Microsoft® Windows Storage Server 2016 Standard
	Microsoft® Hyper-V Server 2012 R2
	Microsoft® Windows Server® 2012 R2 Datacenter
	Microsoft® Windows Server® 2012 R2 Standard
	Microsoft® Windows Server® 2012 R2 Essentials
	Microsoft® Windows Server® 2012 R2 Foundation
	Microsoft® Windows Storage Server 2012 R2 Standard
	Microsoft® Hyper-V Server 2012
	Microsoft® Windows Server® 2012 Datacenter
	Microsoft® Windows Server® 2012 Standard
	Microsoft® Windows Server® 2012 Essentials
	Microsoft® Windows Server® 2012 Foundation
	VMware vSphere™ 6.5
	VMware vSphere™ 6.0
	SUSE® Linux Enterprise Server 12
	Red Hat® Enterprise Linux 7
	Univention Corporate Server 4
Operating system release link	http://docs.ts.fujitsu.com/dl.aspx?id=d4ebd846-aa0c-478b-8f58-4cfbf3230473
Operating system notes	Support of other Linux derivatives on demand

Server Management

Standard	ServerView Suite - Deploy Installation Manager Scripting Toolkit
	ServerView Suite - Control Operations Manager incl. PDA and ASR & R Agents and CIM Providers / Agentless Service System Monitor RAID Manager Capacity Management Power Management Storage Support
Option	ServerView Suite - Maintain Remote Management (iRMC in combination with Intel® Node Manager) Update Management (BIOS, Firmware, Windows Drivers, Agents and CIM Providers) Performance Measurement Asset Management Online Diagnostics
	ServerView Suite - Integrate Integration packs for Microsoft System Center, VMware vCenter, VMware vRealize, Nagios, and HP SIM Deployment tools and others
Server Management notes	ServerView embedded Lifecycle Management (eLCM) Lifecycle management ServerView Suite - Maintain iRMC Advanced Pack incl. Advanced Video Redirection (AVR), video capturing and Virtual Media
Server Management notes	Regarding dependencies for ServerView Suite software products see dedicated product data sheets.

Dimensions / Weight

Floor-stand (W x D x H)	177 x 560 x 455 mm
Rack (W x D x H)	483 x 495 x 175 mm
Dimension notes	Floorstand Width 306 mm with tilt protection; depth measured excludes handles on redundant PSU. Rack depth excludes handles of redundant PSU and rack front.
Mounting Depth Rack	543 mm

Dimensions / Weight

Height Unit Rack	4 U
Weight	Rack: 13 kg - 25 kg; Tower: 15kg - 28 kg
Weight notes	Actual weight may vary depending on configuration
Rack integration kit	Rack integration kit can be ordered as option

Environment

Operating ambient temperature	5 - 40 °C (41 - 104 °F)
Operating temperature note	Cool-safe® Advanced Thermal Design (above 35 °C or below 10 °C) depending on configuration. For detailed information see relevant system configurator.
Operating relative humidity	10 - 85 % (non condensing)
Operating environment	FTS 04230 – Guideline for Data Center (installation specification)
Operating environment link	http://docs.ts.fujitsu.com/dl.aspx?id=e4813edf-4a27-461a-8184-983092c12dbe
Sound pressure (LpAm)	SATA: 23 dB(A) idle mode/ 23 dB(A) operation mode; SAS: 33 dB(A) idle mode/ 37 dB(A) operation mode
Sound power (LWAd; 1B = 10dB)	SATA: 4.1 B idle mode/ 4.1 B operation mode ; SAS: 4.8 B idle mode/ 5.2 B operation mode
Noise notes	Noise emissions depend on operation modes, system configuration and ambient temperature.

Electrical values

Power supply configuration	1 x standard power supply or 1 x hot-plug power supply or 2x hot-plug power supply for redundancy depending on model
Hot-plug power supply redundancy	Optional
Active power (max. configuration)	231 W
Apparent power (max. configuration)	235 VA
Heat emission (max. configuration)	831.6 kJ/h (788.2 BTU/h)
Rated current max.	5 A (100 V) / 2.5 A (240 V)
Active power note	To estimate the power consumption of different configurations use the Power Calculator of the System Architect: http://configurator.ts.fujitsu.com/public/
Power supply	300W standard, 90% (Gold efficiency), 100-240V, 50 / 60Hz 450W hot-plug, 94% (Platinum efficiency), 100-240V, 50 / 60Hz
Power supply notes	Power Safeguard adapts system performance in case the power requirements exceeds supply limits.
Battery backup	Fujitsu Battery Unit 380W, 12V (as option)

Compliance

Global	CB RoHS (Substance limitations in accordance with global RoHS regulations) WEEE (Waste electrical and electronic equipment)
Germany	GS
Europe	CE
USA/Canada	CSA us ULc/us FCC Class A
Japan	VCCI:V3 Class A + JIS 61000-3-2
Russia	GOST-R
South Korea	KC
China	CCC
Australia/New Zealand	C-Tick
Taiwan	BSMI
Compliance link	https://sp.ts.fujitsu.com/sites/certificates
Compliance notes	* Warning: This is a class A product. In a domestic environment this product may cause radio interference in which case the user may be required to take adequate measures.

Components

Backup Drives	LTO5HH Ultrium, 1,500 GB, 140 MB/s, half height, SAS 6Gb/s
	LTO6HH Ultrium, 2,500 GB, 160 MB/s, half height, SAS 6Gb/s
	LTO7HH Ultrium, 2,500 GB, 300 MB/s, half height, SAS 6Gb/s
	RDX Drive, 320 GB, 500 GB, 1 TB , 25 MB/s, half height, USB 3.0
Optical drives	Blu-ray Disc™ Triple Writer, (6x BD-RW, 8x DVD, 24x CD), ultraslim, SATA I
	DVD-ROM, (16xDVD; 48xCD), half height, SATA I
	DVD Super Multi, (16xDVD, 8xDVD+RW 6xDVD-RW, 12xDVD-RAM; 48xCD, 32xCD-RW), half height, SATA I
	DVD Super Multi, (8xDVD/DVD+RW, 6xDVD-RW, 5xDVD-RAM; 24xCD/CD-R, 16xCD-RW), slimline, SATA I
	DVD Super Multi ultra slim , (8x DVD; 24x CD), ultraslim, SATA I
Hard disk drives	HDD SATA, 6 Gb/s, 500 GB, 7,200 rpm, 512e, hot-plug, 3.5-inch, economic
	HDD SATA, 6 Gb/s, 10 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 8 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 7,200 rpm, 512e, hot-plug, 3.5-inch, economic
	HDD SATA, 6 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 4 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical
	HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical
	HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical
	HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical

Hard disk drives

HDD SAS, 12 Gb/s, 900 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 900 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 900 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 900 GB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 450 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 450 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 10 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 10 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SAS, 12 Gb/s, 8 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SAS, 12 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SAS, 12 Gb/s, 4 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SAS, 12 Gb/s, 2 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SAS, 12 Gb/s, 2 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical
HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 1 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical

Solid-State-Drive	SSD SATA, 6 Gb/s, 960 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPDP (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 960 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPDP (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPDP (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPDP (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 800 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPDP (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 800 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPDP (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPDP (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPDP (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.6 DWPDP (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPDP (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3.6 DWPDP (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPDP (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPDP (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPDP (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.6 DWPDP (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3.6 DWPDP (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPDP (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, hot-plug, 3.5-inch, enterprise, 3 DWPDP (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPDP (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPDP (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 1.6 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPDP (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 1.6 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPDP (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 1.2 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPDP (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 1.2 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPDP (Drive Writes Per Day for 5 years)
PCIe SSD & SATA DOM SSD	DOM SATA, 6 Gb/s, 128 GB, non hot plug, enterprise, 0.13 DWPDP (Drive Writes Per Day for 5 years)
	DOM SATA, 6 Gb/s, 64 GB, non hot plug, enterprise, 0.14 DWPDP (Drive Writes Per Day for 5 years)
SCSI / SAS Controller	Fujitsu PSAS CP400i SAS Ctrl. 12 Gbit/s 8 ports int. PCIe 3.0 x8
RAID Controller	Fujitsu PRAID EP420i, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3108
	Fujitsu PRAID EP420i for SafeStore, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3108
	Fujitsu PRAID EP400i, RAID 5/6 Ctrl., SAS/SATA/PCIe-NVMe 12 Gbit/s, 16 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 1 GB, Optional FBU based on LSI SAS3108
	Fujitsu PRAID CP400i, RAID Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 1E, 10, 5, 50, No FBU support
Communication, Network	Ethernet Ctrl. 1 x 1 Gbit/s PCIe 2.1 x1 RJ45 (Intel®)
	Ethernet Ctrl. 2 x 10 Gbit/s PCIe 2.1 x8 RJ45 (Intel®)
	Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 RJ45 (Intel®)
	Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 SFP+ (Emulex)
	Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 SFP+ (Intel®)
	Ethernet Ctrl. 2 x 1 Gbit/s PCIe 2.1 x4 RJ45 (Intel®)
	Ethernet Ctrl. 4 x 1 Gbit/s PCIe 2.1 x4 RJ45 (Intel®)
Graphics add on cards	NVIDIA® NVS™ 315, PCIe x16, 2x DVI/VGA
Rack infrastructure	Rack Mount Kit
	Cable Management for 19-inch DataCenter / PRIMECENTER Racks
	Cable Arm 2U for PRIMECENTER- and 3rd-party racks
Warranty	
Warranty period	1 year
Warranty type	Onsite warranty

Warranty	
Warranty Terms & Conditions	http://support.ts.fujitsu.com/warranty/Index.asp?LNG=COM
Product Related Services - the perfect extension	
Support Pack Options	Globally available in major business areas: 9x5, Next Business Day Onsite Response Time 9x5, 4h Onsite Response Time 24x7, 4h Onsite Response Time
Recommended Service	24x7, Onsite Response Time: 4h - For locations outside of EMEA please contact your local Fujitsu partner.
Service Lifecycle	5 years after end of product life
Service Weblink	http://www.fujitsu.com/fts/services

More information

Fujitsu OPTIMIZATION Services

In addition to Fujitsu PRIMERGY TX1330 M3, Fujitsu provides a range of platform solutions. They combine reliable Fujitsu products with the best in services, know-how and worldwide partnerships.

Fujitsu Portfolio

Built on industry standards, Fujitsu offers a full portfolio of IT hardware and software products, services, solutions and cloud offering, ranging from clients to datacenter solutions and includes the broad stack of Business Solutions, as well as the full stack of Cloud offerings. This allows customers to select from alternative sourcing and delivery models to increase their business agility and to improve their IT operation's reliability.

Computing Products

www.fujitsu.com/global/products/computing/

Software

www.fujitsu.com/software/

More information

Learn more about Fujitsu PRIMERGY TX1330 M3, please contact your Fujitsu sales representative or Fujitsu Business partner, or visit our website.
<http://www.fujitsu.com/primergy>

Fujitsu green policy innovation

Fujitsu Green Policy Innovation is our worldwide project for reducing burdens on the environment. Using our global know-how, we aim to contribute to the creation of a sustainable environment for future generations through IT. Please find further information at <http://www.fujitsu.com/global/about/environment>



Copyrights

All rights reserved, including intellectual property rights. Changes to technical data reserved. Delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see <http://www.fujitsu.com/fts/resources/navigation/terms-of-use.html>
Copyright 2017 FUJITSU LIMITED

Disclaimer

Technical data is subject to modification and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

Contact

FUJITSU LIMITED

Website: www.fujitsu.com
2017-10-05 INT-EN

All rights reserved, including intellectual property rights. Changes to technical data reserved. Delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see <http://www.fujitsu.com/fts/resources/navigation/terms-of-use.html>
Copyright 2017 FUJITSU LIMITED