

# Data Sheet

## FUJITSU Server PRIMERGY TX2550 M4 Tower Server

Tower powerhouse with the richest feature set

FUJITSU Server PRIMERGY will give you the servers you need to power any workload and changing business requirements. As business processes expand so does the need for applications. Each has its own resource footprint, so you need a way to optimize your computing to better serve your users. PRIMERGY systems will help you match your computing capabilities to your business priorities with our complete portfolio of expandable PRIMERGY tower servers for remote and branch offices, versatile rack-mount servers, compact and scalable blade systems, as well as hyper-converged scale-out servers. They convince by business proven quality with a wide range of innovations, highest efficiency cutting operational cost and complexity, provide more agility in daily operations, and integrate seamlessly to let help you concentrate on core business functions.

Perfect for small and medium businesses as well as branch offices, FUJITSU Server PRIMERGY TX tower systems are robust and cost-efficient servers by providing rock solid reliability. Additionally they are characterized by simple IT operations, low power consumption and quiet operation so that they can be handled by non-technically trained staff and can be used in standard office environments. By the way: Almost all PRIMERGY TX servers can be rack-mounted to offer best flexibility.

### PRIMERGY TX2550 M4

The FUJITSU Server PRIMERGY TX2550 M4 is a brand new dual socket tower server designed for demanding business needs to deliver the highest levels of workload versatile performance, expandability and cost-effectiveness. This office ready, powerful system comes with the latest Intel® Xeon® Processor Scalable Family CPUs with 26 cores, along with DDR4 memory technology with up to 768GB capacity and is ideal for most CPU/memory driven requirements such

as demanding business applications (industry-specific, analytics apps), business processing (ERP, CRM) and virtualized workloads. The server is designed for huge expandability with up to 32 storage drives, advanced RAID and a range of high-throughput networking cards including DynamicLOM options, making it highly suitable for storage centric requirements such as collaboration/IT infrastructure workloads and even high-data transfer web or big-data configurations. Up to 8 expansion slots are available for future growth. An optional high-end graphics card can boost performance for graphics intensive applications, display infrastructure. The server is designed for silent operation, ideal for offices. The server also delivers world-class reliability and energy efficiency up to 96% efficient, dual power supplies. Operation in higher ambient temperatures is ensured by the Cool-safe® Advanced Thermal Design, avoiding the need for expenditure on special cooling. Furthermore, the server supports the Fujitsu iRMC S5, to enhance admin productivity and ease server usage across the entire lifecycle.



# Features & Benefits

Main Features	Benefits
<p><b>Power packed performance across workloads</b></p> <ul style="list-style-type: none"> <li>■ Intel® Xeon® Processor Scalable family CPUs with up to 26 cores relying on Intel® UltraPath Interconnect for an increased data rate between the CPUs. Up to 768 GB DDR4 memory with 2,666 MHz (12 DIMM slots)</li> <li>■ Highly expandable and flexible storage configurations: Up to 32x hot plug 2.5" HDD/SSD including 8xPCIe SSD, or up to 12x hot plug 3.5" HDD/SSD + 2x non-hp 2.5" HDD/SSD and up to 3x 1.6" drive bays for ODD or backup. Advanced RAID controllers (RAID 0,1,1E,10,5,50,6,60) with up to 2GB cache for enhanced data protection and reliability beyond embedded basic RAID capability</li> <li>■ Onboard LAN for basic requirements, DynamicLoM via OCP for extended requirements. Additional high throughput networking cards (25/10Gb) also available</li> <li>■ Up to 1x GFX card support</li> </ul> <p><b>Designed for growth</b></p> <ul style="list-style-type: none"> <li>■ 8 Expansion slots (in maximal optional configuration; 7x PCIe and 1x PCI-32)</li> <li>■ Rack Form factor available from the factory and as an upgrade option</li> </ul> <p><b>Go green, with cost savings and reliability improvements</b></p> <ul style="list-style-type: none"> <li>■ Power supply units with 96% energy efficiency</li> <li>■ Fujitsu's Cool-safe® Advanced Thermal Design for higher ambient temperatures in the data center</li> </ul>	<ul style="list-style-type: none"> <li>■ Enhanced Dual-socket compute and high bandwidth DDR4 memory - optimal for demanding enterprise and SME requirements. These can include Business processing, demanding enterprise applications and virtualized workloads</li> <li>■ Ideal for securely managing extremely large datasets and flexible enough to be matched to a range of storage centric requirements such as IT infrastructure or collaboration workloads. Drives and RAID controllers can be tailored to specific business needs and budgets</li> <li>■ Range of Ethernet configurations depending on your business need and budget. Combination of Basic capabilities via onboard LAN, plus higher performance, optional DynamicLoM via OCP offers excellent flexibility and cost effective growth capability. High throughput cards enable growth for the highest data rate requirements</li> <li>■ Improves capability for Graphics intensive apps; get more from your display infrastructure</li> <li>■ Flexible expandability for the integration of existing and new storage controllers, networking cards, GFX card capability. Add capabilities per your business needs</li> <li>■ Invest in a system designed for scalability to match your business growth</li> <li>■ High efficiency redundant power supplies for energy cost savings and enhanced reliability</li> <li>■ Operate your equipment without having to invest in expensive cooling equipment</li> </ul>

# Technical details

<b>PRIMERGY TX2550 M4</b>						
<b>Base unit</b>	TX2550 M4 Tower LFF	TX2550 M4 Tower LFF	TX2550 M4 Tower SFF	TX2550 M4 Tower SFF	TX2550 M4 Tower SFF	TX2550 M4 Tower SFF
<b>Housing types</b>	Tower	Tower	Tower	Tower	Tower	Tower
<b>Storage drive architecture</b>	4x 3.5-inch SAS/SATA expandable	8x 3.5-inch SAS/SATA expandable	8x 2.5-inch SAS/SATA/PCIe	16x 2.5-inch SAS/SATA/PCIe	8x 2.5-inch SAS/SATA/PCIe expandable	24x 2.5-inch SAS/SATA/PCIe expandable
<b>Power supply</b>	Hot-plug	Hot-plug	Hot-plug	Hot-plug	Hot-plug	Hot-plug
<b>Product Type</b>	Dual Socket Tower Server	Dual Socket Tower Server	Dual Socket Tower Server	Dual Socket Tower Server	Dual Socket Tower Server	Dual Socket Tower Server
<b>Mainboard</b>						
<b>Mainboard type</b>	D3386					
<b>Chipset</b>	Intel® C624					
<b>Processor quantity and type</b>	1 - 2 x Intel® Xeon® Processor Scalable Family					
<b>Intel® Xeon® Bronze Processor</b>	Intel® Xeon® Bronze 3104 processor (6C nHT, 1.70 GHz, TLC: 8.25 MB, Turbo: 1.70 GHz, 9.6 GT/s, Mem bus: 2,133 MHz, 85 W, AVX Base 1.30 GHz, AVX Turbo 1.30 GHz)					
	Intel® Xeon® Bronze 3106 processor (8C nHT, 1.70 GHz, TLC: 11 MB, Turbo: 1.70 GHz, 9.6 GT/s, Mem bus: 2,133 MHz, 85 W, AVX Base 1.30 GHz, AVX Turbo 1.30 GHz)					
<b>Intel® Xeon® Silver Processor</b>	Intel® Xeon® Silver 4108 processor (8C, 1.80 GHz, TLC: 11 MB, Turbo: 2.10 GHz, 9.6 GT/s, Mem bus: 2,400 MHz, 85 W, AVX Base 1.30 GHz, AVX Turbo 1.30 GHz)					
	Intel® Xeon® Silver 4110 processor (8C, 2.10 GHz, TLC: 11 MB, Turbo: 2.40 GHz, 9.6 GT/s, Mem bus: 2,400 MHz, 85 W, AVX Base 1.70 GHz, AVX Turbo 2.10 GHz)					
	Intel® Xeon® Silver 4112 processor (4C, 2.60 GHz, TLC: 8.25 MB, Turbo: 2.90 GHz, 9.6 GT/s, Mem bus: 2,400 MHz, 85 W, AVX Base 2.20 GHz, AVX Turbo 2.60 GHz)					
	Intel® Xeon® Silver 4114 processor (10C, 2.20 GHz, TLC: 13.75 MB, Turbo: 2.50 GHz, 9.6 GT/s, Mem bus: 2,400 MHz, 85 W, AVX Base 1.80 GHz, AVX Turbo 2.20 GHz)					
	Intel® Xeon® Silver 4116 processor (12C, 2.10 GHz, TLC: 16.5 MB, Turbo: 2.40 GHz, 9.6 GT/s, Mem bus: 2,400 MHz, 85 W, AVX Base 1.70 GHz, AVX Turbo 2.10 GHz)					

<b>Intel® Xeon® Gold Processor</b>	Intel® Xeon® Gold 5115 processor (10C, 2.40 GHz, TLC: 13.75 MB, Turbo: 2.80 GHz, 10.4 GT/s, Mem bus: 2,400 MHz, 85 W, AVX Base 2.00 GHz, AVX Turbo 2.40 GHz)
	Intel® Xeon® Gold 5118 processor (12C, 2.30 GHz, TLC: 16.5 MB, Turbo: 2.70 GHz, 10.4 GT/s, Mem bus: 2,400 MHz, 105 W, AVX Base 1.90 GHz, AVX Turbo 2.30 GHz)
	Intel® Xeon® Gold 5120 processor (14C, 2.20 GHz, TLC: 19.25 MB, Turbo: 2.60 GHz, 10.4 GT/s, Mem bus: 2,400 MHz, 105 W, AVX Base 1.80 GHz, AVX Turbo 2.20 GHz)
	Intel® Xeon® Gold 5122 processor (4C, 3.60 GHz, TLC: 16.5 MB, Turbo: 3.70 GHz, 10.4 GT/s, Mem bus: 2,667 MHz, 105 W, AVX Base 3.30 GHz, AVX Turbo 3.60 GHz)
	Intel® Xeon® Gold 6126 processor (12C, 2.60 GHz, TLC: 19.25 MB, Turbo: 3.30 GHz, 10.4 GT/s, Mem bus: 2,667 MHz, 125 W, AVX Base 2.20 GHz, AVX Turbo 2.90 GHz)
	Intel® Xeon® Gold 6128 processor (6C, 3.40 GHz, TLC: 19.25 MB, Turbo: 3.70 GHz, 10.4 GT/s, Mem bus: 2,667 MHz, 115 W, AVX Base 2.90 GHz, AVX Turbo 3.60 GHz)
	Intel® Xeon® Gold 6130 processor (16C, 2.10 GHz, TLC: 22 MB, Turbo: 2.80 GHz, 10.4 GT/s, Mem bus: 2,667 MHz, 125 W, AVX Base 1.70 GHz, AVX Turbo 2.40 GHz)
	Intel® Xeon® Gold 6132 processor (14C, 2.60 GHz, TLC: 19.25 MB, Turbo: 3.30 GHz, 10.4 GT/s, Mem bus: 2,667 MHz, 140 W, AVX Base 2.20 GHz, AVX Turbo 2.90 GHz)
	Intel® Xeon® Gold 6134 processor (8C, 3.20 GHz, TLC: 24.75 MB, Turbo: 3.70 GHz, 10.4 GT/s, Mem bus: 2,667 MHz, 130 W, AVX Base 2.70 GHz, AVX Turbo 3.40 GHz)
	Intel® Xeon® Gold 6136 processor (12C, 3.00 GHz, TLC: 24.75 MB, Turbo: 3.30 GHz, 10.4 GT/s, Mem bus: 2,667 MHz, 150 W, AVX Base 2.60 GHz, AVX Turbo 3.30 GHz)
	Intel® Xeon® Gold 6138 processor (20C, 2.00 GHz, TLC: 27.5 MB, Turbo: 2.70 GHz, 10.4 GT/s, Mem bus: 2,667 MHz, 125 W, AVX Base 1.60 GHz, AVX Turbo 2.30 GHz)
	Intel® Xeon® Gold 6140 processor (18C, 2.30 GHz, TLC: 24.75 MB, Turbo: 3.00 GHz, 10.4 GT/s, Mem bus: 2,667 MHz, 140 W, AVX Base 1.90 GHz, AVX Turbo 2.60 GHz)
	Intel® Xeon® Gold 6142 processor (16C, 2.60 GHz, TLC: 22 MB, Turbo: 3.30 GHz, 10.4 GT/s, Mem bus: 2,667 MHz, 150 W, AVX Base 2.20 GHz, AVX Turbo 2.90 GHz)
	Intel® Xeon® Gold 6148 processor (20C, 2.40 GHz, TLC: 27.5 MB, Turbo: 3.10 GHz, 10.4 GT/s, Mem bus: 2,667 MHz, 150 W, AVX Base 1.90 GHz, AVX Turbo 2.60 GHz)
Intel® Xeon® Gold 6152 processor (22C, 2.10 GHz, TLC: 30.25 MB, Turbo: 2.80 GHz, 10.4 GT/s, Mem bus: 2,667 MHz, 140 W, AVX Base 1.70 GHz, AVX Turbo 2.40 GHz)	
<b>Intel® Xeon® Platinum Processor</b>	Intel® Xeon® Platinum 8153 processor (16C, 2.00 GHz, TLC: 22 MB, Turbo: 2.30 GHz, 10.4 GT/s, Mem bus: 2,667 MHz, 125 W, AVX Base 1.60 GHz, AVX Turbo 2.00 GHz)
	Intel® Xeon® Platinum 8160 processor (24C, 2.10 GHz, TLC: 33 MB, Turbo: 2.80 GHz, 10.4 GT/s, Mem bus: 2,667 MHz, 150 W, AVX Base 1.80 GHz, AVX Turbo 2.50 GHz)
	Intel® Xeon® Platinum 8164 processor (26C, 2.00 GHz, TLC: 35.75 MB, Turbo: 2.70 GHz, 10.4 GT/s, Mem bus: 2,667 MHz, 150 W, AVX Base 1.60 GHz, AVX Turbo 2.30 GHz)
<b>Memory slots</b>	12 (6 DIMMs per CPU, 6 channels with one DIMM per channel)
<b>Memory slot type</b>	DIMM (DDR4)
<b>Memory capacity (min. - max.)</b>	4 GB - 768 GB
<b>Memory protection</b>	Advanced ECC SDDC
<b>Memory notes</b>	Performance Mode requires identical modules in all channels of each bank per CPU.
<b>Memory options</b>	8 GB (1 module(s) 8 GB) DDR4, registered, ECC, 2,666 MHz, PC4-2666, DIMM, 1Rx4
	8 GB (1 module(s) 8 GB) DDR4, registered, ECC, 2,666 MHz, PC4-2666, DIMM, 2Rx8
	16 GB (1 module(s) 16 GB) DDR4, registered, ECC, 2,666 MHz, PC4-2666, DIMM, 1Rx4
	16 GB (1 module(s) 16 GB) DDR4, registered, ECC, 2,666 MHz, PC4-2666, DIMM, 2Rx4
	16 GB (1 module(s) 16 GB) DDR4, registered, ECC, 2,666 MHz, PC4-2666, DIMM, 2Rx8
	32 GB (1 module(s) 32 GB) DDR4, registered, ECC, 2,666 MHz, PC4-2666, DIMM, 2Rx4
	64 GB (1 module(s) 64 GB) DDR4 3DS, registered, ECC, 2,666 MHz, PC4-2666, DIMM, 4Rx4
64 GB (1 module(s) 64 GB) DDR4, registered, ECC, 2,666 MHz, PC4-2666, LRDIMM, 4Rx4	
<b>Interfaces</b>	
<b>USB 2.0 ports</b>	1 x USB 2.0 internal for backup devices
<b>USB 3.0 ports</b>	7 x USB 3.0 (2x front, 4 x rear, 1x internal (type A))
<b>Graphics (15-pin)</b>	1 x VGA

**Interfaces**

Serial 1 (9-pin)	1 x optional serial RS-232-C (9 pin)
LAN / Ethernet (RJ-45)	2 x RJ45 (additional 2x RJ45 are optional available)
Management LAN (RJ45)	1 x dedicated management LAN port for iRMC S5 (10/100/1000 Mbit/s) Management LAN traffic can be switched to shared onboard LAN port

**Onboard or integrated Controller**

RAID controller	All hardware storage controller options are described under Components
SATA Controller	Intel® C624, 6-port SATA (4 x for internal hard disks, 2 x for accessible drives)
SATA controller type notes	On board SATA controller supports RAID levels 0, 1, 10
LAN Controller	2 x 1 Gbit/s Ethernet (RJ45) Optional 2x 10Gb T or 2x 10Gb SFP+ interface card onboard with OCP carrier card (OCP carrier card blocks PCIe slot 8).
Remote management controller	IPMI 2.0 compatible Integrated Remote Management Controller (iRMC S5, 512 MB attached memory incl. graphics controller)
Trusted Platform Module (TPM)	optional TPM

**Slots**

PCI-Express 3.0 x8	5 x Full height Note: 2 of the slots become available via optional riser card. Refer to configurator for details
PCI-Express 3.0 x16	3 x Full height Note: 2 of the slots become available with second CPU. Refer to configurator for details. One x16 PCIe slot is available with the first CPU
PCI-slots	1 x PCI 32Bit, available via optional riser card. Refer to configurator for details
Slot Notes	in SAS configuration 1x PCI-Express occupied by modular RAID controller

**Drive bays**

Storage drive bays	3.5-inch or 2.5-inch hot-plug SAS/SATA
Accessible drive bays	3 x 5.25/1.6-inch
Notes accessible drives	All possible options described in relevant system configurator.

**Drive bays (Base unit specific)**

Storage drive bays	4 x 3.5-inch hot-plug SAS/SATA	8 x 3.5-inch hot-plug SAS/SATA	8 x 2.5-inch hot-plug SAS/SATA	16 x 2.5-inch hot-plug SAS/SATA	8 x 2.5-inch hot-plug SAS/SATA	24 x 2.5-inch hot-plug SAS/SATA
Storage drive bay configuration	optional expandable up to 8 storage drives	optional expandable up to 12 storage drives	not expandable	not expandable	optional expandable up to 24 storage drives	optional expandable up to 32 storage drives
Optional accessible drives	3x 1.6x5.25" bays for an optical and/or backup drives	3x 1.6x5.25" bays for an optical and/or backup drives	3x 1.6x5.25" bays for an optical and/or backup drives	3x 1.6x5.25" bays for an optical and/or backup drives	3x 1.6x5.25" bays for an optical and/or backup drives	3x 1.6x5.25" bays for an optical and/or backup drives

**Fan Configuration**

Number of fans	3
Fan configuration	3x120mm high power fans (optional non-hot plug redundant or single hot plug red.)
Fan notes	Fans with optimized blades and fan control for silent and safe operation

**Operating panel**

Operating buttons	On/off switch NMI button Reset button
-------------------	---

**Operating panel**

<b>Status LEDs</b>	System status (orange / yellow) Identification (blue) Hard disks access (green) Power (amber / green) CPU status Fan status Hard disk error Temperature CSS (yellow) Memory status PSU status (green/ amber) At system rear side: System status (orange / yellow) Identification (blue) LAN connection (green) LAN speed (green / yellow)
--------------------	--

<b>Service display</b>	Optional: ServerView Local Service Display (LSD)
------------------------	---

**BIOS**

<b>BIOS features</b>	ROM based setup utility Recovery BIOS BIOS settings save and restore Local BIOS update from USB device Online update tools for main Linux versions Local and remote update via ServerView Update Manager SMBIOS V2.4 Remote PXE boot support
----------------------	---

**Operating Systems and Virtualization Software**

<b>Certified or supported operating systems and virtualization software</b>	Microsoft® Hyper-V Server 2016 Microsoft® Windows Server® 2016 Datacenter Microsoft® Windows Server® 2016 Standard Microsoft® Windows Server® 2016 Essentials Microsoft® Windows Storage Server 2016 Standard Microsoft® Hyper-V Server 2012 R2 Microsoft® Windows Server® 2012 R2 Datacenter Microsoft® Windows Server® 2012 R2 Standard Microsoft® Windows Server® 2012 R2 Essentials Microsoft® Windows Storage Server 2012 R2 Standard VMware vSphere™ 6.5 VMware vSphere™ 6.0 SUSE® Linux Enterprise Server 12 Red Hat® Enterprise Linux 7 Red Hat® Enterprise Linux 6
---	---

**Operating system notes**

<b>Operating system release link</b>	<a href="http://docs.ts.fujitsu.com/dl.aspx?id=d4ebd846-aa0c-478b-8f58-4cfbf3230473">http://docs.ts.fujitsu.com/dl.aspx?id=d4ebd846-aa0c-478b-8f58-4cfbf3230473</a>
--------------------------------------	---

## Server Management

<b>Standard</b>	ServerView Suite - Deploy ServerView Installation Manager ServerView Scripting Toolkit ServerView Suite - Control ServerView Operations Manager incl. PDA and ASR & R ServerView Agents and CIM Providers ServerView Agentless Management ServerView System Monitor SVOM - Event Manager ServerView RAID Manager SVOM - Threshold Manager Power Monitor (monitoring the Power Consumption) Power Management (iRMC) Storage Management (server) with SVOM/SV-RAID ServerView Suite - Maintain Remote Management (iRMC S5) Update Management (BIOS, Firmware, Windows Drives and SV Agents) Performance Measurement Asset Management Online Diagnostics ServerView Suite - Integrate Integration packs for Microsoft System Center, VMware vCenter, VMware vRealize, Nagios, and HP SIM					
<b>Option</b>	ServerView Suite (Maintain) ServerView eLCM iRMC Advanced Pack incl. Advanced Video Redirection (AVR), video capturing and Virtual Media ServerView Suite (Dynamize) Resource Orchestrator- Cloud edition Resource Orchestrator- virtual edition					
<b>Server Management notes</b>	Regarding dependencies for ServerView Suite software products see dedicated product data sheets.					
<b>Dimensions / Weight</b>						
<b>Floor-stand (W x D x H)</b>	177 x 777 x 456 mm					
<b>Rack (W x D x H)</b>	483 (Bezel); 448 mm (body) x 721 x 177 mm					
<b>Dimension notes</b>	Floorstand Width 177 mm without tilt protection (420 mm with tilt protection); depth measured includes handles on redundant PSU. Rack depth includes handles of redundant PSU, excludes rack handles / front					
<b>Height Unit Rack</b>	4 U					
<b>Weight</b>	Up to 35.5 kg					
<b>Weight notes</b>	Actual weight may vary depending on configuration					
<b>Rack integration kit</b>	Rack mount options available from the factory or with retrofit upgrade.					
<b>Floor-stand (W x D x H)</b>						
<b>Rack integration kit</b>	Rack mount option available as a retrofit upgrade	Rack mount options available from the factory or with retrofit upgrade	Rack mount option available as a retrofit upgrade	Rack mount options available from the factory or with retrofit upgrade	Rack mount options available from the factory or with retrofit upgrade	Rack mount options available from the factory or with retrofit upgrade
<b>Environment</b>						
<b>Operating ambient temperature</b>	5 - 45 °C (41 - 113 °F)					
<b>Operating temperature note</b>	Cool-safe® Advanced Thermal Design (above 35 °C or below 10 °C) depending on configuration. For detailed information see relevant system configurator.					
<b>Operating relative humidity</b>	10 - 85 % (non condensing)					
<b>Operating environment</b>	FTS 04230 – Guideline for Data Center (installation specification)					
<b>Operating environment link</b>	<a href="http://docs.ts.fujitsu.com/dl.aspx?id=e4813edf-4a27-461a-8184-983092c12dbe">http://docs.ts.fujitsu.com/dl.aspx?id=e4813edf-4a27-461a-8184-983092c12dbe</a>					
<b>Noise emission</b>	Measured according to ISO 7779 and declared according to ISO 9296					
<b>Sound pressure (LpAm)</b>	Noise minimum configuration: 24 dB(A) (idle) / 32 dB(A) (operating) Noise typical configuration: 24 dB(A) (idle) / 32 dB(A) (operating)					
<b>Sound power (LWAd; 1B = 10dB)</b>	Noise minimum configuration: 4.2 B (idle) / 5.0 B (operating) Noise typical configuration: 4.2 B (idle) / 5.0 B (operating)					

Environment	
Noise notes	Noise emissions depends on operation modes, system configuration and ambient temperature. Operating mode measured based on OLTIS with 50% load. *OLTIS = FUJITSU Load Profile which stresses all components of a server with a given load level.
Electrical values	
Power supply configuration	1x non hot-plug power supply or 2x hot-plug power supply for redundancy
Hot-plug power supply redundancy	Optional
Active power (max. configuration)	748 W
Apparent power (max. configuration)	752 VA
Heat emission (max. configuration)	2692.8 kJ/h (2552.3 BTU/h)
Rated current max.	9 A (100 V) / 3.5 A (240 V)
Active power note	To estimate the power consumption of different configurations use the Power Calculator of the System Architect: <a href="http://configurator.ts.fujitsu.com/public/">http://configurator.ts.fujitsu.com/public/</a>
Power supply	450W hot-plug, 94% (Platinum efficiency), 100-240V, 50 / 60Hz 800W hot-plug, 94% (Platinum efficiency), 100-240V, 50 / 60Hz 800W hot-plug, 96% (Titanium efficiency), 200-240V, 50 / 60Hz 1200W hot-plug, 94% (Platinum efficiency), 100-240V, 50 / 60Hz; 110V range: 1000W, less than 110V: 900W
Power supply notes	Power Safeguard adapts system performance in case the power requirements exceeds supply limits. 96% Titanium Power supply unit is only released for 200-240V
Compliance	
Global	CB RoHS (Substance limitations in accordance with global RoHS regulations) WEEE (Waste electrical and electronical equipment)
Germany	GS
Europe	CE
USA/Canada	CSAc/us FCC Class A
Japan	VCCI:V3 Class A + JIS 61000-3-2
South Korea	KN32 KN35
China	CCC
Australia/New Zealand	C-Tick
Taiwan	BSMI
Compliance link	<a href="https://sp.ts.fujitsu.com/sites/certificates">https://sp.ts.fujitsu.com/sites/certificates</a>
Compliance notes	There is general compliance with the safety requirements of all European countries and North America. National approvals required in order to satisfy statutory regulations or for other reasons can be applied for on request. * Warning: This is a class A product. In a domestic environment this product may cause radio interference in which case the user may be required to take adequate measures.

## Components

Backup Drives	LTO5HH Ultrium, 1,500 GB, 140 MB/s, half height, SAS 6Gb/s
	LTO6HH Ultrium, 2,500 GB, 160 MB/s, half height, SAS 6Gb/s
	LTO7HH Ultrium, 2,500 GB, 300 MB/s, half height, SAS 6Gb/s
	RDX Drive, 320 GB, 500 GB, 1 TB , 25 MB/s, half height, USB 3.0
Optical drives	Blu-ray Disc™ Triple Writer, (6x BD-RW, 8x DVD, 24x CD), ultraslim, SATA I
	DVD-ROM, (16xDVD; 48xCD), half height, SATA I
	DVD Super Multi, (16xDVD, 8xDVD+RW 6xDVD-RW, 12xDVD-RAM; 48xCD, 32xCD-RW), half height, SATA I
	DVD Super Multi ultra slim , (8x DVD; 24x CD), ultraslim, SATA I



## Hard disk drives

HDD SATA, 6 Gb/s, 10 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SATA, 6 Gb/s, 8 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SATA, 6 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SATA, 6 Gb/s, 4 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical
HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical
HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512n, non hot plug, 2.5-inch, business critical
HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical
HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical

## Hard disk drives

HDD SAS, 12 Gb/s, 900 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 900 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 900 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 900 GB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 450 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 450 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, non hot plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 10 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 10 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SAS, 12 Gb/s, 8 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SAS, 12 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SAS, 12 Gb/s, 4 TB, 7,200 rpm, hot-plug, 3.5-inch, business critical
HDD SAS, 12 Gb/s, 4 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SAS, 12 Gb/s, 2 TB, 7,200 rpm, hot-plug, 3.5-inch, business critical
HDD SAS, 12 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical
HDD SAS, 12 Gb/s, 2 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SAS, 12 Gb/s, 2 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical
HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
HDD SAS, 12 Gb/s, 1 TB, 7,200 rpm, hot-plug, 3.5-inch, business critical
HDD SAS, 12 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical
HDD SAS, 12 Gb/s, 1 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical

**Solid-State-Drive**

SSD SATA, 6 Gb/s, 960 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
SSD SATA, 6 Gb/s, 960 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
SSD SATA, 6 Gb/s, 800 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
SSD SATA, 6 Gb/s, 800 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
SSD SATA, 6 Gb/s, 480 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
SSD SATA, 6 Gb/s, 480 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)
SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)
SSD SATA, 6 Gb/s, 240 GB, Read-Intensive, non hot plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
SSD SATA, 6 Gb/s, 240 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
SSD SATA, 6 Gb/s, 240 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
SSD SATA, 6 Gb/s, 240 GB, Mixed-use, non hot plug, 2.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)
SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)
SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)
SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
SSD SATA, 6 Gb/s, 1.6 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
SSD SATA, 6 Gb/s, 1.6 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
SSD SATA, 6 Gb/s, 1.2 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
SSD SATA, 6 Gb/s, 1.2 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
SSD M.2 SATA, 6 Gb/s, 150 GB, non hot plug, enterprise, 1.5 DWPD (Drive Writes Per Day for 5 years)
SSD M.2 SATA, 6 Gb/s, 150 GB, non hot plug, enterprise

**Solid-State-Drive**

SSD SAS, 12 Gb/s, 960 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
SSD SAS, 12 Gb/s, 800 GB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years), SED
SSD SAS, 12 Gb/s, 800 GB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years)
SSD SAS, 12 Gb/s, 800 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (Drive Writes Per Day for 5 years)
SSD SAS, 12 Gb/s, 480 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
SSD SAS, 12 Gb/s, 400 GB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years), SED
SSD SAS, 12 Gb/s, 400 GB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years)
SSD SAS, 12 Gb/s, 400 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (Drive Writes Per Day for 5 years)
SSD SAS, 12 Gb/s, 7.68 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)
SSD SAS, 12 Gb/s, 3.84 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
SSD SAS, 12 Gb/s, 3.2 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 2.3 DWPD (Drive Writes Per Day for 5 years)
SSD SAS, 12 Gb/s, 1.92 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
SSD SAS, 12 Gb/s, 1.6 TB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years), SED
SSD SAS, 12 Gb/s, 1.6 TB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years)
SSD SAS, 12 Gb/s, 1.6 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (Drive Writes Per Day for 5 years)

**PCIe SSD & SATA DOM SSD**

PCIe-SSD SFF, 500 GB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 0.7 DWPD (Drive Writes Per Day for 5 years)
PCIe-SSD SFF, 4 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 0.6 DWPD (Drive Writes Per Day for 5 years)
PCIe-SSD SFF, 2 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 0.6 DWPD (Drive Writes Per Day for 5 years)
PCIe-SSD SFF, 1 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 1 DWPD (Drive Writes Per Day for 5 years)
PCIe-SSD AIC, 4 TB, Mixed-use, HHHL, Flash drive, 3.1 DWPD (Drive Writes Per Day for 5 years)
PCIe-SSD AIC, 2 TB, Mixed-use, HHHL, Flash drive, 3.0 DWPD (Drive Writes Per Day for 5 years)
Dual microSD 64GB Enterprise

<b>SCSI / SAS Controller</b>	Fujitsu PSAS CP400i SAS Ctrl. 12 Gbit/s 8 ports int. PCIe 3.0 x8 Fujitsu PSAS CP400e FH SAS Ctrl. 12 Gbit/s 8 ports ext. PCIe 3.0 x8
<b>RAID Controller</b>	Fujitsu PRAID EP540i FH, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, NVMe-PCIe 8 Gbit/s (coming Q1/2018) 16 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 4 GB, Optional FBU based on LSI SAS3516 Fujitsu PRAID EP520i FH, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, NVMe-PCIe 8 Gbit/s (coming Q1/2018) 8 Gbit/s 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3516 Fujitsu PRAID EP420i, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3108 Fujitsu PRAID EP420i for SafeStore, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3108 Fujitsu PRAID EP400i, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 1 GB, Optional FBU based on LSI SAS3108 Fujitsu PRAID CP400i, RAID Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 1E, 10, 5, 50, No FBU support
<b>Fibre Channel controller</b>	Fibre Channel Host Bus Adapter 1 x 32 Gbit/s Cavium QLE2740 MMF LC-style Fibre Channel Host Bus Adapter 2 x 32 Gbit/s Cavium QLE2742 MMF LC-style Fibre Channel Host Bus Adapter 1 x 32 Gbit/s Emulex LPe32000-M6-F MMF LC-style Fibre Channel Host Bus Adapter 2 x 32 Gbit/s Emulex LPe32002-M6-F MMF LC-style Fibre Channel Host Bus Adapter 1 x 16 Gbit/s Qlogic QLE2690 LC-style Fibre Channel Host Bus Adapter 2 x 16 Gbit/s Qlogic QLE2692 LC-style Fibre Channel Host Bus Adapter 1 x 16 Gbit/s Emulex LPe31000-M6-F MMF LC-style Fibre Channel Host Bus Adapter 2 x 16 Gbit/s Emulex LPe31002-M6-F MMF LC-style
<b>Communication, Network</b>	Converged Network Adapter 2 x 10 Gbit/s PCIe 3.0 x8 SFP+ ( Emulex ) Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 10Gbit/s Eth (RJ45) ( Emulex ) Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 RJ45 ( Intel® ) Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 SFP+ ( Emulex ) Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 SFP+ ( Intel® ) Ethernet Ctrl. 2 x 1 Gbit/s PCIe 2.1 x4 RJ45 ( Intel® ) Ethernet Ctrl. 4 x 10 Gbit/s PCIe 3.0 x8 SFP+ ( Intel® ) Ethernet Ctrl. 4 x 1 Gbit/s PCIe 2.1 x4 RJ45 ( Intel® ) Interface modul for Dynamic LoM 2 x 10 Gbit/s RJ45 ( Intel® ) Interface modul for Dynamic LoM 2 x 10 Gbit/s SFP+ ( Intel® )
<b>Warranty</b>	
<b>Warranty period</b>	3 years
<b>Warranty type</b>	Onsite warranty Warranty conditions tbd
<b>Warranty Terms &amp; Conditions</b>	<a href="http://support.ts.fujitsu.com/warranty/Index.asp?LNG=COM">http://support.ts.fujitsu.com/warranty/Index.asp?LNG=COM</a>
<b>Product Related Services - the perfect extension</b>	
<b>Support Pack Options</b>	X - Globally available in major business areas: 9x5, Next Business Day Onsite Response Time 9x5, 4h Onsite Response Time (depending on country) 24x7, 4h Onsite Response Time (depending on country)
<b>Recommended Service</b>	X - 24x7 Onsite Service with 4h Onsite Response Time
<b>Service Lifecycle</b>	5 years after end of product life
<b>Service Weblink</b>	<a href="http://www.fujitsu.com/fts/products/product-support-services/">http://www.fujitsu.com/fts/products/product-support-services/</a>

# More information

## Fujitsu products, solutions & services

In addition to FUJITSU Server PRIMERGY TX2550 M4, Fujitsu provides a range of platform solutions. They combine reliable Fujitsu products with the best in services, know-how and worldwide partnerships.

### Fujitsu Portfolio

Built on industry standards, Fujitsu offers a full portfolio of IT hardware and software products, services, solutions and cloud offering, ranging from clients to datacenter solutions and includes the broad stack of Business Solutions, as well as the full stack of Cloud offerings. This allows customers to select from alternative sourcing and delivery models to increase their business agility and to improve their IT operation's reliability.

### Computing Products

[www.fujitsu.com/global/products/computing/](http://www.fujitsu.com/global/products/computing/)

### Software

[www.fujitsu.com/software/](http://www.fujitsu.com/software/)

## More information

Learn more about Fujitsu PRIMERGY TX2550 M4, please contact your Fujitsu sales representative or Fujitsu Business partner, or visit our website.  
<http://www.fujitsu.com/global/products/computing/servers/primergy/tower/tx2550m4/index.html>

## Fujitsu green policy innovation

Fujitsu Green Policy Innovation is our worldwide project for reducing burdens on the environment. Using our global know-how, we aim to contribute to the creation of a sustainable environment for future generations through IT. Please find further information at <http://www.fujitsu.com/global/about/environment>



## Copyrights

All rights reserved, including intellectual property rights. Changes to technical data reserved. Delivery subject to availability. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

For further information see <http://www.fujitsu.com/fts/resources/navigation/terms-of-use.html>

Copyright 2018 FUJITSU LIMITED

## Disclaimer

Technical data is subject to modification and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

**Contact**  
FUJITSU LIMITED

Website: [www.fujitsu.com](http://www.fujitsu.com)  
2018-01-11 WW-EN

All rights reserved, including intellectual property rights. Changes to technical data reserved. Delivery subject to availability. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.  
For further information see <http://www.fujitsu.com/fts/resources/navigation/terms-of-use.html>  
Copyright 2018 FUJITSU LIMITED