Fujitsu recommends Windows 10 Pro.

Data Sheet FUJITSU Workstation CELSIUS J550/2

Powerfull Small Form Factor

No need to choose between size and performance in a Small Form Factor. As an industry first, the FUJITSU CELSIUS J550/2 offers full workstation performance in a 10 liter design. It is ideally suited for 2D and entry-level 3D performance and multi-monitor scenarios in control rooms, for surveillance and trading floors.

Breakthrough performance in a Small Form Factor

German design and engineering with performance and TCO in mind

- Choose between the energy-eficient Intel[®] Core[™] processors or the powerful Intel[®] Xeon[®] E3-1200 processor family
- Support of Windows 10 Pro
- Support of Windows 7 with selected processors
- 64 GB DDR4 2,400 MHz memory
- Full-height graphics cards
- Boost your storage performance to a capacity of up to 14 TB
- Take advantage of the super-fast PCIe SSDs to provide a quick loading of core applications
- PCI support
- Support of 24/7 operation with reliable high-endurance and business critical drives

An industry first - taking the Small Form Factor to the next level

No compromise between performance, design and office space

- 10 liter only
- Full-height graphics up to NVIDIA® Quadro® P2000
- 52% smaller form factor than the CELSIUS W570 micro-tower

Whisper quiet design, Made in Germany

Fujitsu's desktop workstations are designed, engineered and manufactured in the heart of Europe

- Optimized thermal management and cooling solutions
- Low noise emission of 19 dB(A) lead to a silent workplace and enhanced productivity

Multi-monitor experience

Ideal for control rooms, surveillance, trading floors or financial services companies

■ Up to 8 monitors with the NVIDIA[®] Mosaic[™] technology









FUjitsu

Components

Processor	Intel® Xeon® processor E3-1280v6 (4 Cores / 8 Threads, 3.90 GHz, up to 4.2 GHz, 8 MB) *
	Intel® Xeon® processor E3-1280v5 (4 Cores / 8 Threads, 3.70 GHz, up to 4.0 GHz, 8 MB) *
	Intel® Xeon® processor E3-1275v6 (4 Cores / 8 Threads, 3.80 GHz, up to 4.2 GHz, 8 MB) *
	Intel [®] Xeon [®] processor E3-1275v5 (4 Cores / 8 Threads, 3.60 GHz, up to 4.0 GHz, 8 MB, Intel [®] HD Graphics P530) *
	Intel® Xeon® processor E3-1270v6 (4 Cores / 8 Threads, 3.80 GHz, up to 4.2 GHz, 8 MB) *
	Intel® Xeon® processor E3-1270v5 (4 Cores / 8 Threads, 3.60 GHz, up to 4.0 GHz, 8 MB) *
	Intel® Xeon® processor E3-1245v6 (4 Cores / 8 Threads, 3.70 GHz, up to 4.1 GHz, 8 MB) *
	Intel® Xeon® processor E3-1245v5 (4 Cores / 8 Threads, 3.50 GHz, up to 3.9 GHz, 8 MB, Intel® HD Graphics P530) *
	Intel® Xeon® processor E3-1240v6 (4 Cores / 8 Threads, 3.70 GHz, up to 4.1 GHz, 8 MB) *
	Intel® Xeon® processor E3-1240v5 (4 Cores / 8 Threads, 3.50 GHz, up to 3.9 GHz, 8 MB) *
	Intel® Xeon® processor E3-1230v6 (4 Cores / 8 Threads, 3.50 GHz, up to 3.9 GHz, 8 MB) *
	Intel® Xeon® processor E3-1230v5 (4 Cores / 8 Threads, 3.40 GHz, up to 3.8 GHz, 8 MB) *
	Intel® Xeon® processor E3-1225v6 (4 Cores / 4 Threads, 3.30 GHz, up to 3.7 GHz, 8 MB) *
	Intel® Xeon® processor E3-1225v5 (4 Cores / 4 Threads, 3.30 GHz, up to 3.7 GHz, 8 MB, Intel® HD Graphics P530) *
	Intel® Xeon® processor E3-1220v6 (4 Cores / 4 Threads, 3.00 GHz, up to 3.5 GHz, 8 MB) *
	Intel® Xeon® processor E3-1220v5 (4 Cores / 4 Threads, 3.00 GHz, up to 3.5 GHz, 8 MB) *
	Intel® Core™ i7-7700 processor (4 Cores / 8 Threads, 3.60 GHz, up to 4.2 GHz, 8 MB, Intel® HD Graphics 630) *
	Intel® Core™ i7-6700 processor (4 Cores / 8 Threads, 3.40 GHz, up to 4.0 GHz, 8 MB, Intel® HD Graphics 530) *, **
	Intel® Core™ i5-7600 processor (4 Cores / 4 Threads, 3.50 GHz, up to 4.1 GHz, 6 MB, Intel® HD Graphics 630) *
	Intel® Core™ i5-7500 processor (4 Cores / 4 Threads, 3.40 GHz, up to 3.8 GHz, 6 MB, Intel® HD Graphics 630) *
	Intel® Core™ i5-6600 processor (4 Cores / 4 Threads, 3.30 GHz, up to 3.9 GHz, 6 MB, Intel® HD Graphics 530) *, **
	Intel® Core™ i5-6500 processor (4 Cores / 4 Threads, 3.20 GHz, up to 3.6 GHz, 6 MB, Intel® HD Graphics 530) *, **
	Intel® Core™ i3-7100 processor (2 Cores / 4 Threads, 3.90 GHz, 3 MB, Intel® HD Graphics 630)
	Intel® Core™ i3-6100 processor (2 Cores / 4 Threads, 3.70 GHz, 3 MB, Intel® HD Graphics 530) **
	Intel® vPro™ with all Intel® Xeon® processors
	No Intel® vPro™ technology with Intel® Core i5 and Core i7 processors
	*with Intel® Turbo Boost Technology (clock speed and performance will vary depending on workload and other variables)
Operating systems	
<mark>Operating systems</mark> Operating system pre-installed	Windows 10 Pro. Fujitsu recommends Windows 10 Pro.
	Windows 10 Home
Operating system pre-installed	Windows 10 Home Windows 7 Professional (available through downgrade rights from Windows 10 Pro)
Operating system pre-installed	Windows 10 Home Windows 7 Professional (available through downgrade rights from Windows 10 Pro) Windows 7 Professional 32-bit (available through downgrade rights from Windows 10 Pro) (with 6th generation
	 Windows 10 Home Windows 7 Professional (available through downgrade rights from Windows 10 Pro) Windows 7 Professional 32-bit (available through downgrade rights from Windows 10 Pro) (with 6th generation Intel® processors)
Operating system pre-installed Operating system compatible	 Windows 10 Home Windows 7 Professional (available through downgrade rights from Windows 10 Pro) Windows 7 Professional 32-bit (available through downgrade rights from Windows 10 Pro) (with 6th generation Intel® processors) Linux
Operating system pre-installed Operating system compatible	Windows 10 Home Windows 7 Professional (available through downgrade rights from Windows 10 Pro) Windows 7 Professional 32-bit (available through downgrade rights from Windows 10 Pro) (with 6th generation Intel® processors) Linux Systems with 7th generation Intel® processor receive support from Microsoft with Windows 10 Home / Windows 10
Operating system pre-installed Operating system compatible	Windows 10 Home Windows 7 Professional (available through downgrade rights from Windows 10 Pro) Windows 7 Professional 32-bit (available through downgrade rights from Windows 10 Pro) (with 6th generation Intel® processors) Linux
Operating system pre-installed Operating system compatible Microsoft OS support information	 Windows 10 Home Windows 7 Professional (available through downgrade rights from Windows 10 Pro) Windows 7 Professional 32-bit (available through downgrade rights from Windows 10 Pro) (with 6th generation Intel® processors) Linux Systems with 7th generation Intel® processor receive support from Microsoft with Windows 10 Home / Windows 10 Pro only. For more information, please see Microsoft Support Lifecycle. Downgrade to Microsoft Windows 7 Professional only available with 6th generation Intel® processor Certified for Red Hat© Enterprise Linux (pending)
Operating system pre-installed Operating system compatible Microsoft OS support information	 Windows 10 Home Windows 7 Professional (available through downgrade rights from Windows 10 Pro) Windows 7 Professional 32-bit (available through downgrade rights from Windows 10 Pro) (with 6th generation Intel® processors) Linux Systems with 7th generation Intel® processor receive support from Microsoft with Windows 10 Home / Windows 10 Pro only. For more information, please see Microsoft Support Lifecycle. Downgrade to Microsoft Windows 7 Professional only available with 6th generation Intel® processor Certified for Red Hat© Enterprise Linux (pending) Certified for SUSE Enterprise Desktop (pending)
Operating system pre-installed Operating system compatible Microsoft OS support information	 Windows 10 Home Windows 7 Professional (available through downgrade rights from Windows 10 Pro) Windows 7 Professional 32-bit (available through downgrade rights from Windows 10 Pro) (with 6th generation Intel® processors) Linux Systems with 7th generation Intel® processor receive support from Microsoft with Windows 10 Home / Windows 10 Pro only. For more information, please see Microsoft Support Lifecycle. Downgrade to Microsoft Windows 7 Professional only available with 6th generation Intel® processor Certified for Red Hat© Enterprise Linux (pending) Certified for SUSE Enterprise Server (pending) Certified for SUSE Enterprise Server (pending)
Operating system pre-installed Operating system compatible Microsoft OS support information	 Windows 10 Home Windows 7 Professional (available through downgrade rights from Windows 10 Pro) Windows 7 Professional 32-bit (available through downgrade rights from Windows 10 Pro) (with 6th generation Intel® processors) Linux Systems with 7th generation Intel® processor receive support from Microsoft with Windows 10 Home / Windows 10 Pro only. For more information, please see Microsoft Support Lifecycle. Downgrade to Microsoft Windows 7 Professional only available with 6th generation Intel® processor Certified for Red Hat© Enterprise Linux (pending) Certified for SUSE Enterprise Desktop (pending)
Operating system pre-installed Operating system compatible Microsoft OS support information Operating system notes	 Windows 10 Home Windows 7 Professional (available through downgrade rights from Windows 10 Pro) Windows 7 Professional 32-bit (available through downgrade rights from Windows 10 Pro) (with 6th generation Intel® processors) Linux Systems with 7th generation Intel® processor receive support from Microsoft with Windows 10 Home / Windows 10 Pro only. For more information, please see Microsoft Support Lifecycle. Downgrade to Microsoft Windows 7 Professional only available with 6th generation Intel® processor Certified for Red Hat© Enterprise Linux (pending) Certified for SUSE Enterprise Server (pending) Certified for SUSE Enterprise Server (pending)
Operating system pre-installed Operating system compatible Microsoft OS support information Operating system notes	 Windows 10 Home Windows 7 Professional (available through downgrade rights from Windows 10 Pro) Windows 7 Professional 32-bit (available through downgrade rights from Windows 10 Pro) (with 6th generation Intel® processors) Linux Systems with 7th generation Intel® processor receive support from Microsoft with Windows 10 Home / Windows 10 Pro only. For more information, please see Microsoft Support Lifecycle. Downgrade to Microsoft Windows 7 Professional only available with 6th generation Intel® processor Certified for Red Hat© Enterprise Linux (pending) Certified for SUSE Enterprise Desktop (pending) Certified for SUSE Enterprise Server (pending) For some configurations third party drivers are currently not available or configuration restrictions may apply.
Operating system pre-installed	 Windows 10 Home Windows 7 Professional (available through downgrade rights from Windows 10 Pro) Windows 7 Professional 32-bit (available through downgrade rights from Windows 10 Pro) (with 6th generation Intel® processors) Linux Systems with 7th generation Intel® processor receive support from Microsoft with Windows 10 Home / Windows 10 Pro only. For more information, please see Microsoft Support Lifecycle. Downgrade to Microsoft Windows 7 Professional only available with 6th generation Intel® processor Certified for Red Hat© Enterprise Linux (pending) Certified for SUSE Enterprise Desktop (pending) Certified for SUSE Enterprise Server (pending) For some configurations third party drivers are currently not available or configuration restrictions may apply. 4 GB (1 module(s) 4 GB) DDR4, unbuffered, ECC, 2,400 MHz, UDIMM
Operating system pre-installed Operating system compatible Microsoft OS support information Operating system notes	 Windows 10 Home Windows 7 Professional (available through downgrade rights from Windows 10 Pro) Windows 7 Professional 32-bit (available through downgrade rights from Windows 10 Pro) (with 6th generation Intel® processors) Linux Systems with 7th generation Intel® processor receive support from Microsoft with Windows 10 Home / Windows 10 Pro only. For more information, please see Microsoft Support Lifecycle. Downgrade to Microsoft Windows 7 Professional only available with 6th generation Intel® processor Certified for Red Hat© Enterprise Linux (pending) Certified for SUSE Enterprise Desktop (pending) Certified for SUSE Enterprise Server (pending) For some configurations third party drivers are currently not available or configuration restrictions may apply. 4 GB (1 module(s) 4 GB) DDR4, unbuffered, ECC, 2,400 MHz, UDIMM 4 GB (1 module(s) 4 GB) DDR4, unbuffered, non-ECC, 2,400 MHz, UDIMM
Operating system pre-installed Operating system compatible Microsoft OS support information Operating system notes	Windows 10 HomeWindows 7 Professional (available through downgrade rights from Windows 10 Pro)Windows 7 Professional 32-bit (available through downgrade rights from Windows 10 Pro) (with 6th generation Intel® processors) LinuxSystems with 7th generation Intel® processor receive support from Microsoft with Windows 10 Home / Windows 10 Pro only. For more information, please see Microsoft Support Lifecycle. Downgrade to Microsoft Windows 7 Professional only available with 6th generation Intel® processorCertified for Red Hat© Enterprise Linux (pending) Certified for SUSE Enterprise Desktop (pending) Certified for SUSE Enterprise Server (pending) For some configurations third party drivers are currently not available or configuration restrictions may apply.4 GB (1 module(s) 4 GB) DDR4, unbuffered, ECC, 2,400 MHz, UDIMM 8 GB (1 module(s) 8 GB) DDR4, unbuffered, ECC, 2,400 MHz, UDIMM

Graphics	Midrange 3D: NVIDIA® Quadro® P2000, 5 GB, PCIe x16, 4 x DisplayPort
	Midrange 3D: AMD Radeon™ Pro WX 5100, 8 GB, 320 stream processors, PCle x16, 4 x DisplayPort
	Entry 3D: NVIDIA® Quadro® P1000, 4 GB, PCIe x16, 4x miniDP
	Entry 3D: AMD Radeon™ Pro WX 3100, 4 GB, 320 stream processors, PCIe x16, 1x DisplayPort, 2x miniDP
	Entry 3D: NVIDIA® Quadro® P600, 2 GB, PCIe x16, 4x miniDP
	Entry 3D: AMD Radeon™ Pro WX 2100, 2 GB, 320 stream processors, PCIe x16, 1x DisplayPort, 2x miniDP
	Entry 3D: NVIDIA® Quadro® P400 , 2 GB, PCIe x16, 3x miniDP
Hard disk drives (internal)	SSD PCIe, 1024 GB M.2 NVMe Highend module
	SSD PCIe, 512 GB M.2 NVMe Highend module
	SSD PCIe, 256 GB M.2 NVMe Highend module
	SSD PCIe, 1x1024 GB M.2 NVMe Highend card
	SSD PCIe, 1x 512 GB M.2 NVMe Highend card
	SSD PCIe, 1x 256 GB M.2 NVMe Highend card
	SSD PCIe, 1024 GB M.2 NVMe module
	SSD PCIe, 512 GB M.2 NVMe module
	SSD PCIe, 256 GB M.2 NVMe module
	SSD PCIe, 128 GB M.2 NVMe module
	SSD PCIe, 1x 1024 GB M.2 NVMe card
	SSD PCIe, 1x 512 GB M.2 NVMe card
	SSD PCIe, 1x 256 GB M.2 NVMe card
	SSD SATA III, 960 GB High Endurance, 2.5-inch
	SSD SATA III, 480 GB High Endurance, 2.5-inch
	SSD SATA III, 240 GB High Endurance, 2.5-inch
	SSD SATA III, 1024 GB, 2.5-inch
	SSD SATA III, 512 GB, 2.5-inch
	SSD SATA III, 256 GB, 2.5-inch
	SSD SATA III, 128 GB, 2.5-inch
	SSD SATA III, 512 GB, 2.5-inch, SED
	SSD SATA III, 256 GB, 2.5-inch, SED
	HDD SATA III, 7,200 rpm, 6,000 GB, 3.5-inch, business critical
	HDD SATA III, 7,200 rpm, 4,000 GB, 3.5-inch, business critical
	HDD SATA III, 7,200 rpm, 2,000 GB, 3.5-inch, business critical
	HDD SATA III, 7,200 rpm, 1,000 GB, 3.5-inch, business critical
	HDD SATA III, 7,200 rpm, 2,000 GB, 2.5-inch, business critical
	HDD SATA III, 7,200 rpm, 1,000 GB, 2.5-inch, business critical
	HDD SATA III, 7,200 rpm, 2,000 GB, 3.5-inch
	HDD SATA III, 7,200 rpm, 1,000 GB, 3.5-inch
	HDD SATA III, 7,200 rpm, 500 GB, 3.5-inch
	HDD SATA II, 5,400 rpm, 500 GB, 2.5-inch
	16 GB, M.2 module, Flash drive
lard disk notes	One Gigabyte equals one billion bytes, when referring to hard disk drive capacity.
	24/7 ready (business critical HDDs required)
	Up to 20 GB of HDD space is reserved for system recovery SSHD (Solid State Hard Disk, Hybrid drive)
	SED (Self-Encrypting Drive)
	SSD (Solid State Disk)
Drives (optional)	BD Triple Writer SATA ultra slim (tray)
	DVD Super Multi ultra slim (tray)
	MultiCard Reader 24in1 USB 2.0 3.5"

Interface add on cards/components (optional)	
	WLAN 802.11ac (2x2) PCIe x1 FH and BT 4.1 (dedicated regions only, up to BT 4.2 depending on OS version)
	WLAN 802.11ac (2x2) PCIe x1 FH (dedicated regions only)
	Parallel Interface
	Gigabit Ethernet PCIe x1, DS
	eSATA Interface
	Dual serial card PCIe x1
Riser Cards	1 x PCI-Express 3.0 x16, Full height (174 mm / 6.85 inch) ; 1 x PCI-Express 3.0 x4 (mech. x16), Full height (174 mm / 6.85 inch)
	1 x PCI-Express 3.0 x16, Full height (174 mm / 6.85 inch) ; 1 x PCI, Full height (174 mm / 6.85 inch)
Base unit	CELSIUS J550/2
Mainboard	
Mainboard type	D3427-U
Formfactor	proprietary
Chipset	Intel® C236
Supported capacity RAM (max.)	64 GB
Memory slots	4 DIMM (DDR4) ECC/non-ECC
Memory frequency	2,400 MHz
Memory notes	Dual channel support For dual channel performance, 2 memory modules have to be ordered. Capacity per channel has to be the same. DDR4 2,400 MHz will be clocked with 2,133 MHz in combination with 6th generation Intel® processor
LAN	10/100/1,000 MBit/s Intel® I219LM
BIOS version	AMI Aptio V
BIOS features	BIOS Flash EPROM update by software Recovery BIOS Unified Extensible Firmware Interface (UEFI) CSM (Compatibility Support Module)
Audio type	On board
Audio codec	Realtek ALC671
Audio features	Internal speaker supports audio playback (optional), High Definition audio, 5.1 surround sound
I/O controller on board	
Serial ATA total	5
thereof SATA III	5
thereof eSATA	2 (optional)
Controller functions	Serial ATA III (6 Gbit) NCQ AHCI RAID 0/1/5/10
Interfaces	
Audio: line-in	1
Audio: line-out	1
Front audio: microphone	1
Front audio: headphone	1
Internal speakers	1
USB 2.0 total	2
USB 3.1 Gen1 (USB 3.0) total	9
USB 3.1 Gen2 total	optional via add on card
USB front	2x USB 3.0
USB rear	6x USB 3.0
USB internal	2x USB 2.0 + 1x USB A 3.0

la ta sfa cas	
Interfaces DisplayPort	2
DVI	1 (DVI-D)
	1 ; optional: 2nd serial port (9pin, 16 byte FIFO, 16550 compatible)
Serial (RS-232)	
Mouse / Keyboard (PS/2)	2
Ethernet (RJ-45)	
Parallel	1 (optional) (25pin with EPP and ECP)
eSATA	1 (optional)
Interface Module notes	Anytime USB charge functionality
Input device / components	
Input devices (optional)	Keyboard Mouse KBPC PX ECO Mouse M440 ECO Space Explorer USB
Drive bays total	
3.5-inch internal bays	1
5.25-inch external bays	1
Drive bay notes	5.25" bay: for slim optical disc drive only; internal 3.5" bay: 1x 3.5" drive (screwless) or 1x 2.5" drive (screws) or optional via adapter for 1x or 2x 2.5" drives (screws); external 3.5" bay: optional as internal 3.5" bay (screws)
M.2-2280	1 x on mainboard (for PCIe or SATA SSD modules), supports Intel® Optane™ technology
Graphics on board	
Graphics brand name	Intel® HD Graphics P630, Intel® HD Graphics 630, Intel® HD Graphics P530, Intel® HD Graphics 530
Shared video memory	up to 1,782 MB
TFT resolution (DVI)	1,280 x 1,024 pixel 1,360 x 768 pixel 1,440 x 900 pixel 1,600 x 900 pixel 1,680 x 1,050 pixel 1,920 x 1,080 pixel 1,920 x 1,200 pixel
TFT resolution (DisplayPort)	1,280 x 1,024 pixel 1,360 x 768 pixel 1,440 x 900 pixel 1,600 x 900 pixel 1,680 x 1,050 pixel 1,920 x 1,080 pixel 1,920 x 1,200 pixel 2,560 x 1,440 pixel 2,560 x 1,600 pixel 3,840 x 2,160 pixel 4,096 x 2,304 pixel
Graphics features	Support for up to three independent displays DirectX® 12 HDCP support OpenCL™ 2.0 (requires Intel® Core™ i3, i5 or i7 processors) OpenGL® 4.4 One DisplayPort connector can be converted to DVI-D or HDMI with an optional external adapter For multi monitoring mode, graphics card and integrated graphics run in parallel DisplayPort interface supports Ver. 1.2 incl. Multi-Stream DVI-D interface supports audio output for HDMI monitors
Graphics notes	up to 1 GB dedicated video memory (main memory owned and locked for graphics use) Tested resolutions, depending on display type additional resolutions and frequencies possible Shared memory depending on main memory size and operating system Resolution (color depth up to 32 Bit/pixel) For TFT we recommend using 60Hz

Electrical values	
Power efficiency note	power supply efficiency (at 230V; 10% / 20% / 50% / 100% load) : 84% / 90% / 92% / 91%
Rated voltage range	100 V - 240 V
Rated frequency range	50 Hz - 60 Hz
Operating voltage range	90 V - 264 V
Operating line frequency range	47 Hz - 63 Hz
Max. output of single power supply	280 W
Power factor correction/active power	active
· · ·	
Dimensions / Weight / Environmental	
Dimensions (W x D x H)	332 x 338 x 89 mm
	12.68 x 13.31 x 3.51 inch
Operating position	horizontal / vertical (optional, feet needed)
Weight	approx. 9 kg
Weight (lbs)	approx. 19.84 lbs
Weight notes	Actual weight may vary depending on configuration
Operating ambient temperature	10 - 35 ℃ (50 - 95 °F)
Operating relative humidity	5 - 85 % (relative humidity)
Compliance	
Product	CELSIUS J550/2
Model	DTF
Germany	TÜV GS
Europe	CE
USA/Canada	FCC Class B cCSAus
Global	RoHS (Restriction of hazardous substances) WEEE (Waste electrical and electronic equipment) Microsoft Operating Systems (HCT / HCL entry / WHQL) ENERGY STAR® 6.1 (dedicated regions) EPEAT® Gold (dedicated regions)
China	CCC TPM 2.0 for China (optional)
Compliance link	https://sp.ts.fujitsu.com/sites/certificates
Additional Software	
Additional software (preinstalled)	Adobe® Reader® (pdf reader) McAfee Multi Access Security (anti-virus and internet security software; 60 days trial version) Microsoft Office (buy license to activate the pre-installed Microsoft Office)
Additional software (optional)	Recovery DVD for Windows® Drivers & Utilities DVD (DUDVD) CyberLink PowerDVD BD (playback software for Blu-ray Disc™) CyberLink PowerDVD DVD (playback software for DVD) Nero Essentials XL
Security	
System and BIOS Security	Embedded security (TPM 2.0) EraseDisk (optional) Boot sector virus protection Write protect option for the Flash EPROM Control of all USB interfaces External USB ports can be disabled separately Control of external interfaces
User Security	User and supervisor BIOS password Hard disk password Access protection via external SmartCard reader (optional) Access protection via internal SmartCard reader (optional) Workplace Protect (secure authentication solution)

Security	
Workplace Embedded Tools	Auto BIOS Update via Fujitsu Server Auto BIOS Update via customer server (optional) Easy PC Protection (optional) Easy Restore (optional)
Manageability	
Manageability technology	DeskUpdate Driver management PXE 2.1 Boot code Wake up from S5 (off mode) Intrusion switch (optional) WoL (Wake on LAN) iAMT 11.6 (depending on processor)
Manageability software	DeskView Client DeskView Instant BIOS Management
DeskView components	On/Offline remote client management Detailed system inventory management and reports BIOS Management Remote power management System notifications Security Remote Control DeskView Helpdesk Integration WoL (Wake on LAN)
Supported standards	DMI (Desktop Management Interface) SMBIOS (System Management BIOS) PXE (Preboot Execution Environment) WMI (Windows Management Instrumentation) WBEM (Web Based Enterprise Management) CIM (Common Information Model)
Manageability link	http://www.fujitsu.com/fts/manageability
Miscellaneous	
	Keyboard on (Special Fujitsu keyboard required) Thermal management Extended lifetime 24/7 (limited configurations)
Packaging information	
Packaging dimension (mm)	467 x 265 x 540 mm
Packaging dimension (inch)	18.39 x 10.43 x 21.26 inch
Max. quantity / pallet	28
Material - Weight (g) Carton	1180 g
Material - Weight (lbs) Carton	2.6 lbs
Material - Weight (g) EPS / PS	180 g
Material - Weight (lbs) EPS / PS	0.4 lbs
Material - Weight (g) PE	60 g
Material - Weight (lbs) PE	0.13 lbs
Packaging notes	printed user documentation is bleached in chlorine free process
Warranty	
Warranty period	3 years (depending on country)
Warranty type	Bring-In / Onsite Service (for countries within region EMEIA, for all other countries depending on local regulations)
Warranty Terms & Conditions Product Related Services - the perfect of	http://support.ts.fujitsu.com/warranty
Recommended Service	X - 9x5, Onsite Response Time: Next Business Day
Spare Parts availability	5 years after end of product life
Service Weblink	http://www.fujitsu.com/fts/services/support

Recommended Accessories

SpaceMouse[™] Pro



Using the SpaceMouse[™] Pro 3D mouse to navigate 3D models or Order Code: environments is as simple as holding them in your hand. A slight S26381-K459-L100 movement of the controller cap delivers easy and precise control. SpaceMouse[™] Pro is a companion to the traditional mouse and is operated with the free hand. Your traditional mouse hand is free to select, create and edit.

UC&C USB Value Headset



The FUJITSU UC&C USB Value Headset is a lightweight bi-aural full-size Order stereo headset with high wearing comfort. This Lync-tested USB-Headset has an appropriate Inline-Controller which supports easy call management. A noise cancelling microphone facilitates undisturbing clear phone calls.

Order Code: S26391-F7139-L20

Keyboard KBPC PX ECO



Fujitsu's KBPC PX ECO keyboard is the perfect contribution to Green IT. The S26381-K341-L1** (**: keyboard is made out of 45% renewable raw material and comes with a PVC country specific variation) free USB cable. In addition, the KBPC PX ECO offers first class comfort and ergonomics. It attracts attention with its impressive modern design and useful extras.

More information

Fujitsu OPTIMIZATION Services

In addition to the FUJITSU Workstation CELSIUS J550/2, Fujitsu provides a range of platform solutions. They combine reliable Fujitsu products with the best in services, know-how and worldwide partnerships.

Fujitsu Portfolio

Build on industry standards, Fujitsu offers a full portfolio of IT hardware and software products, services, solutions and cloud offering, ranging from clients to datacenter solutions and includes the broad stack of Business Solutions, as well as the full stack of Cloud offering. This allows customers to leverage from alternative sourcing and delivery models to increase their business agility and to improve their IT operation's reliability.

Computing Products

www.fujitsu.com/global/products/computing/

Software

www.fujitsu.com/software/

More information

Learn more about the FUJITSU Workstation CELSIUS J550/2, please contact your Fujitsu sales representative or Fujitsu Business partner, or visit our website. www.fujitsu.com/fts/CELSIUS

Fujitsu green policy innovation

Fujitsu Green Policy Innovation is our worldwide project for reducing burdens on the environment.

Using our global know-how, we aim to contribute to the creation of a sustainable environment for future generations through IT. Please find further information at http://www. fujitsu.com/global/about/environment



Copyrights

All rights reserved, including intellectual property rights. Changes to technical data reserved. Delivery subject to availability. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see http://www. fujitsu.com/fts/resources/navigation/terms-ofuse.html

Copyright 2018 Fujitsu Technology Solutions

Disclaimer

Technical data is subject to modification and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

Contact

Fujitsu Technology Solutions Website: www.fujitsu.com/fts 2018-02-01 EM-EN All rights reserved, including intellectual property rights. Changes to technical data reserved. Delivery subject to availability. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see http://www.fujitsu.com/fts/resources/ navigation/terms-of-use.html

Copyright 2018 Fujitsu Technology Solutions