

Data Sheet

FUJITSU Server PRIMERGY RX1330 M3 Rack Server

Small in size and low in cost – rich in optional features

FUJITSU Server PRIMERGY will give you the servers you need to power any workload and changing business requirements. As business processes expand so does the need for applications. Each has its own resource footprint, so you need a way to optimize your computing to better serve your users. PRIMERGY systems will help you match your computing capabilities to your business priorities with our complete portfolio of expandable PRIMERGY tower servers for remote and branch offices, versatile rack-mount servers, compact and scalable blade systems, as well as hyper-converged scale-out servers. They convince by business proven quality with a wide range of innovations, highest efficiency cutting operational cost and complexity, provide more agility in daily operations, and integrate seamlessly to let help you concentrate on core business functions.

FUJITSU Server PRIMERGY RX rack systems are versatile rack-optimized servers providing best-in-class performance and energy efficiency, and thus form the "standard" in each data center. PRIMERGY RX servers deliver more than 20 years of development and production know-how resulting in extremely low failure rates below market average, and lead to continuous operations and outstanding hardware availability.

PRIMERGY RX1330 M3

The FUJITSU Server PRIMERGY RX1330 M3 is a mono-socket rack server designed to provide a solution for small budgets, yet enabling a rich set of optional expansions to best meet individual demands. Its usage patterns cover file, infrastructure and communication or collaboration applications by delivering up to 64 GB RAM, up to 3 PCIe slots and up to 10x 2.5-inch hard disk drives. Moreover, this 1U server allows for diverse individual configurations with optional features, such as hot-plug power supply units, redundant fans and RAID controller. By delivering high

energy efficiency and operation in higher ambient temperature thanks to optional Cool-safe® Advanced Thermal Design, the PRIMERGY RX1330 M3 also contributes to very low operational costs. ServerView™ Suite and remote management features (iRMC S4) simplify the administration.



Features & Benefits

Main Features	Benefits
Flexible Foundation for Infrastructure Tasks <ul style="list-style-type: none"> ■ 1x Intel® Xeon® E3 v6-family processor, Intel® Core i3 or Intel® Celeron® processor and up to 64 GB DDR4 memory with 2,400 MHz(4 DIMM slots),up to 3x PCIe Gen3 slots ■ Free choice: Up to 4x 3.5-inch or up to 10x 2.5-inch storage drives ■ Broad selection of Operating Systems 	<ul style="list-style-type: none"> ■ Cost-optimized foundation for file, infrastructure and communication applications ■ Flexible to meet the individual demand, the huge storage capacity fulfills requirements of storage demanding application or services ■ Red Hat Linux, Suse Linux, Microsoft Windows Server - it's up to you
Enhanced Features for enhanced Computing <ul style="list-style-type: none"> ■ Modular RAID controllers and full-height PCIe slot ■ Redundant fans, optional Hot-plug and redundant power supply (PSU) with 80 PLUS platinum energy efficiency (94 %) ■ The Fujitsu FJBU internal battery backup is an alternative for classical UPS devices. This compact Ni-MH battery unit that fits into modular PSU slot ■ Fujitsu's Cool-safe® Advanced Thermal Design for higher ambient temperatures in the data center 	<ul style="list-style-type: none"> ■ Perfectly meet the performance and space requirements with available budget ■ Match redundancy and power supply requirements with available budge ■ FJBU keeps the server running during short blackouts or voltage fluctuations and enables a graceful shutdown ■ Higher ambient temperatures lead to lower costs for cooling the data center
Foundation for Trust and Security <ul style="list-style-type: none"> ■ Fujitsu ServerView Suite including tools for installation and deployment, permanent status monitoring and control ■ BIOS, firmware and selected software are updated free of charge ■ TPM2.0 modules and latest operating system support 	<ul style="list-style-type: none"> ■ Lifecycle investment protection ■ The comprehensive tools of the Fujitsu ServerView Suite eases the administrators life ■ Hardware- and software-driven security features are very important in a fast-paced world, especially considering cybercrime.
Simplified management <ul style="list-style-type: none"> ■ iRMC S4 stressless connecting the RX1330 M3 to our Server Management tools 	<ul style="list-style-type: none"> ■ Optimized for both, data centers and SMEs

Technical details

PRIMERGY RX1330 M3

Base unit	RX1330 M3 LFF	RX1330 M3 LFF	RX1330 M3 SFF	RX1330 M3 SFF	RX1330 M3 SFF 10xSFF
Housing types	Rack	Rack	Rack	Rack	Rack
Storage drive architecture	3.5-inch SAS/SATA	3.5-inch SAS/SATA	2.5-inch SAS/SATA	2.5-inch SAS/SATA	2.5-inch SAS/SATA
Power supply	Standard	Hot-plug	Standard	Hot-plug	Hot-plug
Product Type	Mono Socket Rack Server	Mono Socket Rack Server	Mono Socket Rack Server	Mono Socket Rack Server	Mono Socket Rack Server
Mainboard					
Mainboard type	D3375				
Chipset	Intel® C236				
Processor quantity and type	1 x Intel® Xeon® processor E3-1200 v6 product family / Intel® Core™ i3 processor / Intel® Pentium® processor / Intel® Celeron® processor				
Processor	Intel® Celeron® processor G3930 (2C/2T, 2.90 GHz, TLC: 2 MB, Turbo: No, 2,133 MHz, 51 W) Intel® Core™ i3-7100 processor (2C/4T, 3.90 GHz, TLC: 3 MB, Turbo: No, 2,400 MHz, 51 W) Intel® Pentium® processor G4560 (2C/4T, 3.50 GHz, TLC: 3 MB, Turbo: No, 2,400 MHz, 54 W) Intel® Xeon® processor E3-1220v6 (4C/4T, 3.00 GHz, TLC: 8 MB, Turbo: 3.30 GHz, 2,400 MHz, 72 W) Intel® Xeon® processor E3-1225v6 (4C/4T, 3.30 GHz, TLC: 8 MB, Turbo: 3.50 GHz, 2,400 MHz, 73 W) Intel® Xeon® processor E3-1230v6 (4C/8T, 3.50 GHz, TLC: 8 MB, Turbo: 3.70 GHz, 2,400 MHz, 72 W) Intel® Xeon® processor E3-1240v6 (4C/8T, 3.70 GHz, TLC: 8 MB, Turbo: 3.90 GHz, 2,400 MHz, 72 W) Intel® Xeon® processor E3-1270v6 (4C/8T, 3.80 GHz, TLC: 8 MB, Turbo: 4.00 GHz, 2,400 MHz, 72 W) Intel® Xeon® processor E3-1280v6 (4C/8T, 3.90 GHz, TLC: 8 MB, Turbo: 4.00 GHz, 2,400 MHz, 72 W)				
Memory slots	4 (2 banks with 2 DIMMs each)				
Memory slot type	DIMM (DDR4)				
Memory capacity (min. - max.)	4 GB - 64 GB				
Memory protection	ECC				
Memory notes	Dual channel support. For dual channel performance, a minimum of 2 memory modules have to be ordered. Capacity per channel has to be the same.				
Memory options	4 GB (1 module(s) 4 GB) DDR4, unbuffered, ECC, 2,400 MHz, PC4-2400, DIMM, 1Rx8 8 GB (1 module(s) 8 GB) DDR4, unbuffered, ECC, 2,400 MHz, PC4-2400, DIMM, 1Rx8 16 GB (1 module(s) 16 GB) DDR4, unbuffered, ECC, 2,400 MHz, PC4-2400, DIMM, 2Rx8				
Interfaces					
USB 3.0 ports	6 x (2x front, 4x rear) (10x 2.5" HDD base unit: 1x USB 2.0, 4x rear USB 3.0)				
Graphics (15-pin)	1 x VGA (15-pin) / optional 1 x front VGA (not for 10x 2.5" HDD base unit)				
Serial connection	1 x serial RS-232-C				
LAN / Ethernet (RJ-45)	2 x 1 Gbit/s Ethernet				
Management LAN (RJ45)	1 x dedicated management LAN port for iRMC S4 (10/100/1000 Mbit/s) Management LAN traffic can be switched to shared onboard Gbit LAN port				
Onboard or integrated Controller					
RAID controller	Integrated RAID 0/1 or RAID 5/6 controller (option) All hardware storage controller options are described under Components				
SATA Controller	Intel® C236, 1 port used for accessible drive or SATA DOM 4 port for internal SATA HDDs with RAID 0, 1, 10 for Windows and Linux;				
LAN Controller	Intel® i210 onboard 2 x 10/100/1000 Mbit/s Ethernet (TCP/IP acceleration) iSCSI, PXE-Boot and WoL are supported				
Remote management controller	Integrated Remote Management Controller (iRMC S4, 256 MB attached memory incl. graphics controller) IPMI 2.0 compatible				

Onboard or integrated Controller

Trusted Platform Module (TPM)	Infineon / TPM 1.2 or TPM 2.0 module; TCG compliant (option)
--------------------------------------	--

Onboard or integrated Controller (Base unit specific)

RAID controller	4 port SATA with RAID 0/1/10 for HDDs	4 port SATA with RAID 0/1/10 for HDDs
SATA Controller	4-port SATA 6Gb with RAID 0, 1, 10	4-port SATA 3Gb with RAID 0, 1, 10
SATA controller type notes	for hot-plug SATA hard disks	for hot-plug SATA hard disks

Slots

PCI-Express 3.0 x4	1 x Low profile
PCI-Express 3.0 x8	2 x Low profile Length 175mm; PCIe slot#1 = dedicated Modular RAID slot
Slot Notes	Optional support of 1x full height PCIe Gen3 x8 card, instead of 1x PCIe Gen2 x4 and 1x PCIe Gen3 x8

Drive bays

Storage drive bays	4/8 x 2.5-inch hot-plug SAS/SATA or 4x 3.5-inch hot-plug SAS/SATA or 10 x 2.5-inch hot-plug SAS/SATA
Accessible drive bays	1 x 5.25/0.4-inch for CD-RW/DVD
Notes accessible drives	Following limitations applies to 10x 2.5-inch HDD base unit: No CD-RW/DVD, 1x USB 2.0 at the front, no front VGA

Drive bays (Base unit specific)

Storage drive bays	Max. 4x 3.5-inch	Max. 8x 2.5-inch	Max. 10x 2.5-inch
---------------------------	------------------	------------------	-------------------

Fan Configuration

Number of fans	4	5	4	5
Fan notes	4 fans in combination with standard power supply or 5 fans in combination with hot-plug PSU base unit for 1+4 redundancy.			
Number of fans	4	5	4	5
Fan configuration	4 standard fan	5 redundant fan	4 standard fan	5 redundant fan
Fan notes	non redundant / non hot-plug	redundant / non hot-plug	non redundant / non hot-plug	redundant / non hot-plug

Operating panel

Operating buttons	On/off switch NMI button Reset button
Status LEDs	System status (orange) Identification (blue) Hard disks access (green) Power (green) At system rear side: System status (orange) Identification (blue) LAN connection (green) LAN speed (green / yellow)

BIOS

BIOS features	ROM based setup utility Recovery BIOS BIOS settings save and restore Local BIOS update from USB device Online update tools for main Linux versions Local and remote update via ServerView Update Manager Remote PXE boot support Remote iSCSI boot support
----------------------	---

Operating Systems and Virtualization Software

Certified or supported operating systems and virtualization software	Hyper-V Server 2016 Windows Server 2016 Datacenter Windows Server 2016 Standard Windows Server 2016 Essentials Windows Storage Server 2016 Standard Hyper-V Server 2012 R2 Windows Server 2012 R2 Datacenter Windows Server 2012 R2 Standard Windows Server 2012 R2 Essentials Windows Server 2012 R2 Foundation Windows Storage Server 2012 R2 Standard Hyper-V Server 2012 Windows Server 2012 Datacenter Windows Server 2012 Standard Windows Server 2012 Essentials Windows Server 2012 Foundation Windows Storage Server 2012 Standard VMware vSphere™ 6.5 VMware vSphere™ 6.0 SUSE® Linux Enterprise Server 12 Red Hat® Enterprise Linux 7
Operating system release link	http://docs.ts.fujitsu.com/dl.aspx?id=d4ebd846-aa0c-478b-8f58-4cfbf3230473
Operating system notes	VMware ESX hints: - SATA RAID is not supported - Storing virtual machines locally requires a SAS RAID Controller Support of other Linux derivatives on demand Red Hat® certification starting with version 5.8 / 6.4. Hardware requirements of Software Defined Storage supported by i.e. Microsoft Storage Spaces or VMWare vSAN please see Systemarchitect or paper configurator or datasheet of PSAS CP400i.

Server Management and Infrastructure Management

Standard	ServerView Suite (Deploy) ServerView Installation Manager ServerView Scripting Toolkit ServerView Suite (Control) ServerView Operations Manager (incl. PDA and ASR & R) ServerView Agents and CIM provider ServerView Agentless Management ServerView System Monitor SVOM- Event Manager ServerView RAID Manager SVOM- Threshold Manager Power Monitor (monitoring the Power Consumption) Power Management (iRMC) Storage Management (server) with SVOM/SV-RAID ServerView Suite (Maintain) iRMC S4 (Remote Management) System Update Manager (BIOS, Firmware, Windows Drives and SV Agents) Performance management (SVOM) Asset Management Primecollect Customer Self Service Online Diagnostics ServerView Suite (Integrate) ServerView Integration packs for MS System Center, VMware vCenter, VMware vRealize, Nagios, and HP SIM
-----------------	--

Server Management and Infrastructure Management

Option	<p>ServerView Suite (Maintain)</p> <p>ServerView eLCM</p> <p>iRMC Advanced Pack incl. Advanced Video Redirection (AVR), video capturing and Virtual Media</p> <p>ServerView Suite (Dynamize)</p> <p>ServerView Virtual IO Manager (SVIOM)</p> <p>Resource Orchestrator- Cloud edition</p> <p>Resource Orchestrator- virtual edition</p> <p>ServerView Infrastructure Management</p> <p>Automate device configuration</p> <p>Mass OS installation</p> <p>Node Management</p> <p>Health status Monitoring and Control</p> <p>Capacity/Threshold Management</p> <p>Power Management</p> <p>Converged Management</p> <p>Auto Discovery</p> <p>Virtual-IO Management</p> <p>Network topology Management</p> <p>Remote Management</p> <p>Update Management</p> <p>Logging and Auditing</p> <p>Integrate in to</p> <p>Enterprise Management</p> <p>Vendor specific Management</p> <p>Monitor 3rd party platforms</p>
Server Management notes	Regarding dependencies for ServerView Suite software products see dedicated product data sheets.
Dimensions / Weight	
Rack (W x D x H)	482.6 mm (Bezel) / 435.4 mm (Body) x 572 x 42.8 mm
Height Unit Rack	1 U
Mounting Cable depth rack	200 mm cable depth
Weight	up to 13 kg
Weight notes	Actual weight may vary depending on configuration
Rack integration kit	Rack integration kit as option
Environment	
Operating ambient temperature	5 - 40 °C (41 - 104 °F)
Operating temperature note	Cool-safe® Advanced Thermal Design (above 35 °C or below 10 °C) depending on configuration. For detailed information see relevant system configurator.
Operating relative humidity	10 - 85 % (non condensing)
Operating environment	FTS 04230 – Guideline for Data Center (installation specification)
Operating environment link	http://docs.ts.fujitsu.com/dl.aspx?id=e4813edf-4a27-461a-8184-983092c12dbe
Sound pressure (LpAm)	25 / 35 dB(A) (min / max idle), 25 / 35 db(A) (min / max operating)
Sound power (LWAd; 1B = 10dB)	4.1 / 5.1 B (min / max idle), 4.1 / 5.1 B (min / max operating)
Noise notes	Noise emissions and operation modes depend on system configuration.
Electrical values	
Power supply configuration	1x standard power supply or 1x hot-plug power supply or 2x hot plug power supplies for redundancy depending on model
Hot-plug power supply redundancy	Optional
Active power (max. configuration)	152 W
Apparent power (max. configuration)	155 VA
Heat emission (max. configuration)	547.2 kJ/h (518.6 BTU/h)
Rated current max.	4.0 A (100 V) / 2.0 A (240 V)
Active power note	To estimate the power consumption of different configurations use the Power Calculator of the System Architect: http://configurator.ts.fujitsu.com/public/
Power supply	300W standard, 92% (Gold efficiency), 100-240V, 50 / 60Hz 450W hot-plug, 94% (Platinum efficiency), 100-240V, 50 / 60Hz

Electrical values

Power supply notes	Power Safeguard adapts system performance in case the power requirements exceeds supply limits.
Battery backup	Fujitsu Battery Unit 380W, 12V (as option)

Compliance

Global	CB RoHS (Substance limitations in accordance with global RoHS regulations) WEEE (Waste electrical and electronical equipment)
Germany	GS
Europe	CE
USA/Canada	CSA/us ULc/us FCC Class A
Japan	VCCI:V3 Class A + JIS 61000-3-2
Russia	GOST
South Korea	KC
China	CCC
Australia/New Zealand	C-Tick
Taiwan	BSMI
Compliance link	https://sp.ts.fujitsu.com/sites/certificates
Compliance notes	<p>There is general compliance with the safety requirements of all European countries and North America. National approvals required in order to satisfy statutory regulations or for other reasons can be applied for on request.</p> <p>* Warning: This is a class A product. In a domestic environment this product may cause radio interference in which case the user may be required to take adequate measures.</p>

Components

Optical drives

Blu-ray Disc™ Triple Writer, (6x BD-RW, 8x DVD, 24x CD), ultraslim, SATA I
DVD Super Multi ultra slim , (8x DVD; 24x CD), ultraslim, SATA I

Hard disk drives

HDD SATA, 6 Gb/s, 500 GB, 7,200 rpm, 512e, hot-plug, 3.5-inch, economic
HDD SATA, 6 Gb/s, 12 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SATA, 6 Gb/s, 10 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SATA, 6 Gb/s, 8 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SATA, 6 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
HDD SATA, 6 Gb/s, 4 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical
HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical
HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical
HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, economic
HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical

Hard disk drives	HDD SAS, 12 Gb/s, 900 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 900 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 900 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 900 GB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 12 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 12 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 10 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 10 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 8 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 4 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 2 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 2 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical
	HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 1 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical

Solid-State-Drive	SSD SATA, 6 Gb/s, 960 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 960 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 960 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 960 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.0 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 800 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 800 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.3 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1.4 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1.4 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.1 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 7.68 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.5 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 7.68 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.5 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 3.84 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1.0 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 3.84 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1.0 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 1.92 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 1.92 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.0 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 1.6 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 1.6 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 1.2 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
	SSD SATA, 6 Gb/s, 1.2 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)
PCIe SSD & SATA DOM SSD	DOM SATA, 6 Gb/s, 128 GB, non hot plug, enterprise, 0.13 DWPD (Drive Writes Per Day for 5 years)
	DOM SATA, 6 Gb/s, 64 GB, non hot plug, enterprise, 0.14 DWPD (Drive Writes Per Day for 5 years)
SCSI / SAS Controller	LSI PSAS CP400e LP SAS Ctrl. 12 Gbit/s 8 ports ext. PCIe 3.0 x8
	Fujitsu PSAS CP400i SAS Ctrl. 12 Gbit/s 8 ports int. PCIe 3.0 x8
RAID Controller	Fujitsu PRAID EP420i, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3108
	Fujitsu PRAID EP420i for SafeStore, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3108
	Fujitsu PRAID EP400i, RAID 5/6 Ctrl., SAS/SATA/PCIe-NVMe 12 Gbit/s, 16 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 1 GB, Optional FBU based on LSI SAS3108
	Fujitsu PRAID CP400i, RAID Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 1E, 10, 5, 50, No FBU support

Fibre Channel controller	Fibre Channel Host Bus Adapter 1 x 8 Gbit/s Qlogic QLE2560 MMF LC-style Fibre Channel Host Bus Adapter 2 x 8 Gbit/s Qlogic QLE2562 MMF LC-style Fibre Channel Host Bus Adapter 1 x 8 Gbit/s Emulex LPe1250 MMF LC-style Fibre Channel Host Bus Adapter 2 x 8 Gbit/s Emulex LPe12002 MMF LC-style
Communication, Network	Ethernet Ctrl. 1 x 1 Gbit/s PCIe 2.1 x1 RJ45 (Intel®) Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 RJ45 (Intel®) Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 SFP+ (Emulex) Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 SFP+ (Intel®) Ethernet Ctrl. 2 x 1 Gbit/s PCIe 2.1 x4 RJ45 (Intel®) Ethernet Ctrl. 4 x 1 Gbit/s PCIe 2.1 x4 RJ45 (Intel®)
Graphics add on cards	NVIDIA® NVS™315 LP, PCIe x16, 2x DVI/VGA
Rack infrastructure	Rackmount kit full extraction (665mm), tool less mounting, length variable 559-914mm Rackmount kit full extraction (815mm), tool less mounting, length variable 559-914mm Rackmount kit full extraction (815mm), tool less mounting, length variable 559-914mm Rackmount kit tool less mounting Cable Management 1U for PRIMECENTER- and 3rd-party racks
Warranty	
Warranty period	1 year
Warranty type	Onsite warranty
Warranty Terms & Conditions	www.fujitsu.com/support
Product Related Services - the perfect extension	
Support Pack Options	X - Globally available in major business areas: 9x5, Next Business Day Onsite Response Time 9x5, 4h Onsite Response Time (depending on country) 24x7, 4h Onsite Response Time (depending on country)
Recommended Service	X - 24x7 Onsite Service with 4h Onsite Response Time
Service Lifecycle	5 years after end of product life
Service Weblink	http://www.fujitsu.com/fts/products/product-support-services/

More information

Fujitsu products, solutions & services

In addition to FUJITSU Server PRIMERGY RX1330 M3, Fujitsu provides a range of platform solutions. They combine reliable Fujitsu products with the best in services, know-how and worldwide partnerships.

Fujitsu Portfolio

Built on industry standards, Fujitsu offers a full portfolio of IT hardware and software products, services, solutions and cloud offering, ranging from clients to datacenter solutions and includes the broad stack of Business Solutions, as well as the full stack of Cloud offerings. This allows customers to select from alternative sourcing and delivery models to increase their business agility and to improve their IT operation's reliability.

Computing Products

www.fujitsu.com/global/products/computing/

Software

www.fujitsu.com/software/

More information

Learn more about FUJITSU Server PRIMERGY RX1330 M3, please contact your Fujitsu sales representative or Fujitsu Business partner, or visit our website.

<http://www.fujitsu.com/primergy>

Fujitsu green policy innovation

Fujitsu Green Policy Innovation is our worldwide project for reducing burdens on the environment.

Using our global know-how, we aim to contribute to the creation of a sustainable environment for future generations through IT. Please find further information at <http://www.fujitsu.com/global/about/environment>



Copyrights

All rights reserved, including intellectual property rights. Changes to technical data reserved. Delivery subject to availability. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

For further information see <http://www.fujitsu.com/fts/resources/navigation/terms-of-use.html>

Copyright 2018 FUJITSU LIMITED

Disclaimer

Technical data is subject to modification and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

Contact

FUJITSU LIMITED

Website: www.fujitsu.com
2018-04-09 WW-EN

All rights reserved, including intellectual property rights. Changes to technical data reserved. Delivery subject to availability. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

For further information see <http://www.fujitsu.com/fts/resources/navigation/terms-of-use.html>

Copyright 2018 FUJITSU LIMITED