FUJITSU

Data Sheet FUJITSU Server PRIMERGY TX2550 M5 Tower Server

Tower powerhouse with the richest feature set

FUJITSU Server PRIMERGY will give you the servers you need to power any workload and changing business requirements. As business processes expand so does the need for applications. Each has its own resource footprint, so you need a way to optimize your computing to better serve your users. PRIMERGY systems will help you match your computing capabilities to your business priorities with our complete portfolio of expandable PRIMERGY tower servers for remote and branch offices, versatile rack-mount servers as well as hyper-converged multi-node servers. They convince by business proven quality with a wide range of innovations, highest efficiency cutting operational cost and complexity, provide more agility in daily operations, and integrate seamlessly to let help you concentrate on core business functions.

Perfect for small and medium businesses as well as branch offices, FUJITSU Server PRIMERGY TX tower systems are robust and cost-efficient servers by providing rock solid reliability. Additionally they are characterized by simple IT operations, low power consumption and quiet operation so that they can be handled by non-technically trained staff and can be used in standard office environments. By the way: Almost all PRIMERGY TX servers can be rack-mounted to offer best flexibility.

PRIMERGY TX2550 M5

The FUJITSU Server PRIMERGY TX2550 M5 is a sophisticated dual socket tower server enhanced with the latest technology to deliver the highest levels of workload versatile performance, expandability and cost-effectiveness. This office ready, powerful system comes with the latest Intel® Xeon® Processor Scalable Family CPUs with 24 cores, along with up to 1.5TB of high-speed 2,933 MT/s DDR4 and Intel® Optane™ DC persistent memory technology making this powerful system ideal for most CPU/memory driven requirements

such as demanding business applications (industry specific, analytics apps), business processing (ERP, CRM) and virtualized workloads. The server is designed for huge expandability with up to 32 hard drives, NVMe options, advanced RAID and a range of high-throughput networking cards including DynamicLOM options, making it highly suitable for storage centric requirements such as collaboration/IT infrastructure workloads and even high-data transfer web or big-data configurations. Up to 8 expansion slots are available for future growth. A high-end Graphics card boosts performance for VDI, CAD, web requirements. The server is designed for silent operation, ideal for offices. The server also delivers world-class reliability and energy efficiency with up to 96% efficient, dual power supplies. Operation in higher ambient temperatures is ensured by the Cool-safe® Advanced Thermal Design, avoiding the need for expenditure on special cooling. Furthermore, the server supports the Fujitsu iRMC S5, to enhance admin productivity and ease server usage across the entire lifecycle.















vmware

Features & Benefits

Main Features

Power packed performance across workloads

Intel® Xeon® Processor Scalable family CPUs with up to 24 cores (code named "Cascade Lake") relying on Intel® UltraPath Interconnect for an increased data rate between the CPUs. Up to 1.5TB memory (12 DIMM slots) including a mix of DDR4 @ 2,933 MT/s and Intel® Optane™ DC persistent memory.

Highly expandable and flexible storage

Up to 32x hot plug 2.5"HDD/SSD including up to 4xNVMe PCle SSD, or up to 12x hot plug 3.5" HDD/SSD + 2x non-hp 2.5" HDD/SSD and up to 3x 1.6" drive bays for ODD or backup. Advanced RAID controllers (RAID 0,1,1E,10,5,50,6,60) with up to 8GB cache for enhanced data protection and reliability beyond embedded basic RAID capability.

Powerful and cost-effective networking configurations

Onboard LAN for basic requirements, DynamicLoM via OCP for extended requirements. Range of additional high throughput networking cards (100/40/25/10Gb) also available.

Designed to keep pace with your business

8 Expansion slots (in maximal optional configuration; 7x PCIe and 1xPCI-32). Rack Form factor available from the factory and as an upgrade option.

Versatile Graphics support

■ Up to 1x GFX card support (FPGA also on roadmap).

Go green, with cost savings and reliability improvements

Power supply units with 96% energy efficiency, plus Fujitsu's Coolsafe® Advanced Thermal Design for higher ambient temperatures in the data center.

Secure, Efficient Administration across the server lifecycle

Fujitsu ServerView Suite including tools for installation and deployment, permanent status monitoring and control, The server also has regular, free updates of BIOS, firmware and selected software. The onboard iRMC S5 comes with interactive web UI and conforms to Redfish providing unified API support for heterogeneous environment. Furthermore, 2x Internal M.2 devices support hypervisor installations or mirroring while TPM2.0 modules enhance security.

Benefits

- Enhanced Dual-socket compute plus high bandwidth DDR4 and Intel® Optane[™] DC persistent memory - optimal for demanding enterprise and SME requirements. Intel® Optane[™] DC persistent memory is an innovative memory technology which delivers a unique combination of affordable large capacity and non-volatile persistence. It revolutionizes the data center memory-storage hierarchy of the past and brings massive data sets closer to the CPU for faster time to insight. As such, the TX2550 M5 is capable of handling a range of diverse tasks: Demanding Industry and Analytics apps, Business processing and enterprise applications as well as virtualized workloads.
- Ideal for securely managing extremely large datasets and flexible enough to be matched to a range of storage centric requirements such as IT infrastructure, database or collaboration workloads. Drives and RAID controllers can be tailored to specific business needs and budgets.
- Range of Ethernet configurations depending on your business need and budget. Combination of Basic capabilities via onboard LAN, plus higher performance, optional DynamicLoM via OCP offers excellent flexibility and cost effective growth capability. High throughput cards enable growth for the highest data rate requirements.
- Versatile PCIe slots offer flexible expandability for the integration of existing and new storage controllers, networking cards, Graphics capability. Add capabilities per your business needs. Rack upgrade kit allows you to invest in a system designed for scalability to match your business growth.
- Improve capability for Graphics intensive apps; get more from your display infrastructure.
- High efficiency redundant power supplies deliver energy cost savings and enhanced reliability, while the Cool-safe® Advanced Thermal Design allows you to operate your equipment without having to invest in expensive cooling equipment.
- ServerView enables ease of administration: IT Staff can focus on high-value tasks and business requirements versus transactional tasks. With BIOS upgrades, your server remains up-to-date consistently, without extra expenses, great for your budget and IT admin productivity. The onboard iRMC S5, is optimized for both: data centers and SMEs can rely on the latest generation server management by Fujitsu. M.2 devices are perfect for hassle-free hypervisor /operating system start-up, while TPM 2.0 provides ease of mind for administrators with the latest hardware and Software driven security features to address emerging threats and cybercrime challenges.

Technical details

PRIMERGY TX2550 M5							
Base unit	TX2550 M5 Tower LFF	TX2550 M5 Tower LFF	TX2550 M5 Tower SFF	TX2550 M5 Tower SFF	TX2550 M5 Tower SFF	TX2550 M5 Towe SFF	
Housing types	Tower	Tower	Tower	Tower	Tower	Tower	
Storage drive architecture	4x 3.5-inch SAS/ SATA expandable	8x 3.5-inch SAS/ SATA expandable	8x 2.5-inch SAS/ SATA/PCIe	16x 2.5-inch SAS/ SATA/PCIe	8x 2.5-inch SAS/SATA/PCIe expandable	24x 2.5-inch SAS/SATA/PCIe expandable	
Power supply	Hot-plug	Hot-plug	Hot-plug	Hot-plug	Hot-plug	Hot-plug	
Product Type	Dual Socket Tower Server	Dual Socket Tower Server	Dual Socket Tower Server	Dual Socket Tower Server	Dual Socket Tower Server	Dual Socket Towe Server	
Mainboard							
Mainboard type	D3386-B						
Chipset	Intel® C624						
Processor quantity and type	1 - 2 x Intel® Xeon® Processor Scalable Family						
Intel [®] Xeon [®] Bronze Processor	Intel® Xeon® Bronze 3204 (6C, 1.90 GHz, TLC: 8.25 MB, Turbo: 1.90 GHz, 9.6 GT/s, Mem bus: 2,133 MHz, 85 W, AVX Base 1.50 GHz, AVX Turbo 1.50 GHz)						
Intel [®] Xeon [®] Silver Processor	Intel® Xeon® Silver 4208 (8C, 2.10 GHz, TLC: 11 MB, Turbo: 2.50 GHz, 9.6 GT/s, Mem bus: 2,400 MHz, 85 W, AVX Base 1.60 GHz, AVX Turbo 2.00 GHz)						
	Intel® Xeon® Silver 4210 (10C, 2.20 GHz, TLC: 13.75 MB, Turbo: 2.70 GHz, 9.6 GT/s, Mem bus: 2,400 MHz, 85 W, AVX Base 1.90 GHz, AVX Turbo 2.30 GHz)						
	Intel® Xeon® Silver 4214 (12C, 2.20 GHz, TLC: 16.5 MB, Turbo: 2.70 GHz, 9.6 GT/s, Mem bus: 2,400 MHz, 85 W, AVX Base 1.80 GHz, AVX Turbo 2.40 GHz)						
	Intel® Xeon® Silver 4214Y (12C, 2.20 GHz, TLC: 16.5 MB, Turbo: 2.70 GHz, 9.6 GT/s, Mem bus: 2,400 MHz, 85 W, AVX Base 1.80 GHz, AVX Turbo 2.40 GHz)						
	Intel® Xeon® Silver 4215 (8C, 2.50 GHz, TLC: 11 MB, Turbo: 3.00 GHz, 9.6 GT/s, Mem bus: 2,400 MHz, 85 W, AVX Base 2.00 GHz, AVX Turbo 2.60 GHz)						
	Intel® Xeon® Silver Base 1.40 GHz, AV	⁻ 4216 (16C, 2.10 G X Turbo 2.30 GHz)	Hz, TLC: 22 MB, Turb	o: 2.70 GHz, 9.6 GT/	s, Mem bus: 2,400 N	MHz, 100 W, AVX	

Intel® Xeon® Gold Processor	Intel [®] Xeon [®] Gold 5215 (10C, 2.50 GHz, TLC: 13.75 MB, Turbo: 3.00 GHz, 10.4 GT/s, Mem bus: 2,666 MHz, 85 W, AVX Base 2.00 GHz, AVX Turbo 2.60 GHz)				
	Intel [®] Xeon [®] Gold 5217 (8C, 3.00 GHz, TLC: 11 MB, Turbo: 3.40 GHz, 10.4 GT/s, Mem bus: 2,666 MHz, 115 W, AVX Base 2.50 GHz, AVX Turbo 3.00 GHz)				
	Intel [®] Xeon [®] Gold 5218 (16C, 2.30 GHz, TLC: 22 MB, Turbo: 2.80 GHz, 10.4 GT/s, Mem bus: 2,666 MHz, 125 W, AVX Base 1.80 GHz, AVX Turbo 2.30 GHz)				
	Intel [®] Xeon [®] Gold 5218B (16C, 2.30 GHz, TLC: 22 MB, Turbo: 2.80 GHz, 10.4 GT/s, Mem bus: 2,666 MHz, 125 W, AVX Base 1.80 GHz, AVX Turbo 2.30 GHz)				
	Intel® Xeon® Gold 5220 (18C, 2.20 GHz, TLC: 24.75 MB, Turbo: 2.70 GHz, 10.4 GT/s, Mem bus: 2,666 MHz, 125 W, AV Base 1.80 GHz, AVX Turbo 2.50 GHz)				
	Intel® Xeon® Gold 5220S (18C, 2.70 GHz, TLC: 24.75 MB, Turbo: 2.70 GHz, 10.4 GT/s, Mem bus: 2,666 MHz, 125 W, AVX Base 1.80 GHz, AVX Turbo 2.20 GHz)				
	Intel® Xeon® Gold 5222 (4C, 3.80 GHz, TLC: 16.5 MB, Turbo: 3.90 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 105 W, AVX Base 3.80 GHz, AVX Turbo 3.80 GHz)				
	Intel® Xeon® Gold 6209U (20C, 2.10 GHz, TLC: 27.5 MB, Turbo: 2.80 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 125 W, AV Base 1.60 GHz, AVX Turbo 2.40 GHz)				
	Intel® Xeon® Gold 6210U(20C, 2.50 GHz, TLC: 27.5 MB, Turbo: 3.20 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 150 W, AV Base 1.90 GHz, AVX Turbo 2.80 GHz)				
	Intel® Xeon® Gold 6212U (24C, 2.40 GHz, TLC: 33 MB, Turbo: 3.10 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 165 W, AVX Base 1.90 GHz, AVX Turbo 2.60 GHz)				
	Intel® Xeon® Gold 6222V (20C, 1.80 GHz, TLC: 27.5 MB, Turbo: 2.40 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 115 W, AV Base 1.60 GHz, AVX Turbo 2.40 GHz)				
	Intel® Xeon® Gold 6226 (12C, 2.70 GHz, TLC: 19.25 MB, Turbo: 3.50 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 125 W, AVX Base 2.30 GHz, AVX Turbo 3.10 GHz)				
	Intel® Xeon® Gold 6230 (20C, 2.10 GHz, TLC: 27.5 MB, Turbo: 2.80 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 125 W, AVX Base 1.60 GHz, AVX Turbo 2.40 GHz)				
	Intel® Xeon® Gold 6234 (8C, 3.30 GHz, TLC: 24.75 MB, Turbo: 4.00 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 130 W, AVX Base 2.8 GHz, AVX Turbo 3.70 GHz)				
	Intel® Xeon® Gold 6238(22C, 2.10 GHz, TLC: 30.25 MB, Turbo: 3.70 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 140 W, AV Base 1.70 GHz, AVX Turbo 2.50 GHz)				
	Intel® Xeon® Gold 6240 (18C, 2.60 GHz, TLC: 24.75 MB, Turbo: 3.30 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 150 W, AV Base 2.00 GHz, AVX Turbo 2.80 GHz)				
	Intel® Xeon® Gold 6240Y (18C, 2.60 GHz, TLC: 24.75 MB, Turbo: 3.30 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 150 W, AVX Base 2.00 GHz, AVX Turbo 2.80 GHz)				
	Intel® Xeon® Gold 6242 (16C, 2.80 GHz, TLC: 22 MB, Turbo: 3.50 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 150 W, AVX Base 2.30 GHz, AVX Turbo 3.10 GHz)				
	Intel® Xeon® Gold 6248 (20C, 2.50 GHz, TLC: 27.5 MB, Turbo: 3.20 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 150 W, AVX Base 1.90 GHz, AVX Turbo 2.80 GHz)				
	Intel® Xeon® Gold 6252 (24C, 2.10 GHz, TLC: 35.75 MB, Turbo: 2.80 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 150 W, AV Base 1.70 GHz, AVX Turbo 2.40 GHz)				
	Intel® Xeon® Gold 6262V (24C, 1.90 GHz, TLC: 33 MB, Turbo: 2.50 GHz, 10.4 GT/s, Mem bus: 2,933 MHz, 135 W, AVX Base 1.60 GHz, AVX Turbo 2.80 GHz)				
Nemory slots	12 (6 DIMMs per CPU, 6 channels with one DIMM per channel)				
Nemory slot type	DIMM (DDR4 / DDR-T for non-volatile memory modules)				
Nemory capacity (min max.)	8 GB - 1.5 TB				
Nemory protection	Advanced ECC SDDC				
Memory notes	Possibility to populate 2 slots with DCPMM modules per CPU, please see relevant system configurator for details Memory Mirroring Mode with identical modules in both channel pairs of a bank (4 or 6 modules per bank) per CPU.				
Standard memory modules (for use in	64 GB (4 module(s) 16 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, DIMM, 1Rx4				
combination with non-volatile memory	128 GB (4 module(s) 32 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, DIMM, 2Rx4				
modules)	256 GB (4 module(s) 64 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, LRDIMM, 4Rx4				
Non-volatile memory modules	256 GB (2 module(s) 128 GB) DDR-T, registered, ECC, 2,666 MT/s, NVM, DCPMM, 1Rx4				
· · · · · · · · · · · · · · · · · · ·	512 GB (2 module(s) 256 GB) DDR-T, registered, ECC, 2,666 MT/s, NVM, DCPMM, 2Rx4				

Charles and the second se							
Standard memory modules	8 GB (1 module(s) 8 GB) DDR4, registered, ECC, 2,666 MT/s, PC4-2666, DIMM, 1Rx4 8 GB (1 module(s) 8 GB) DDR4, registered, ECC, 2,666 MT/s, PC4-2666, DIMM, 2Rx8						
	8 GB (1 module(s) 8 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2006, DIMM, 2KX8						
	16 GB (1 module(s) 16 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, DDMM, TRX8						
	16 GB (1 module(s) 16 GB) DDR4, registered, ECC, 2,666 MT/s, PC4-2666, DIMM, 2Rx8 16 GB (1 module(s) 16 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, DIMM, 1Rx4 16 GB (1 module(s) 16 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, DIMM, 2Rx8 32 GB (1 module(s) 32 GB) DDR4, registered, ECC, 2,666 MT/s, PC4-2666, DIMM, 2Rx4 32 GB (1 module(s) 32 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2666, DIMM, 2Rx4 64 GB (1 module(s) 64 GB) DDR4 aDDR4, registered, ECC, 2,666 MT/s, PC4-2666, DIMM, 2Rx4						
	64 GB (1 module(s) 64 GB) DDR4, registered, ECC, 2,666 MT/s, PC4-2666, LRDIMM, 4Rx4						
	64 GB (1 module(s) 64 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, DIMM, 2Rx4						
	64 GB (1 module(s) 64 GB) DDR4, registered, ECC, 2,933 MT/s, PC4-2933, LRDIMM, 4Rx4						
Interfaces							
USB 2.0 ports	1 x USB 2.0 internal for backup devices						
USB 3.0 ports	7 x USB 3.0 (2x front, 4 x rear, 1x internal (type A)						
Graphics (15-pin)	1 x VGA						
Serial 1 (9-pin)	1 x optional serial RS-232-C (9 pin)						
LAN / Ethernet (RJ-45)	2 x RJ45 (additional 2x RJ45 are optional available)						
Management LAN (RJ45)	1 x dedicated management LAN port for iRMC S5 (10/100/1000 Mbit/s) Management LAN traffic can be switched to shared onboard LAN port						
Onboard or integrated Controller							
RAID controller	All hardware storage controller options are described under Components						
SATA Controller	Intel® C624, 9-port SATA (8 x for internal hard disks, 1 x for accessible drives)						
SATA controller type notes	On board SATA controller supports RAID levels 0, 1, 10						
LAN Controller	2 x 1 Gbit/s onboard Optional 2x 10Gb T or 2x 10Gb SFP+ interface card onboard with OCP carrier card (OCP carrier card blocks PCIe slot 8)						
Remote management controller	IPMI 2.0 compatible Integrated Remote Management Controller (iRMC S5, 512 MB attached memory incl. graphics controller)						
Trusted Platform Module (TPM)	optional TPM						
Slots							
PCI-Express 3.0 x8	5 x Full height Note: 2 of the slots become available via optional riser card. Refer to configurator for details						
PCI-Express 3.0 x16	3 x Full height Note: Die x16 PCIe slot is available with the first CPU, can be occupied by the optional Riser card. Second CPU adds two more x16 PCIe slots. Refer to configurator for details.						
PCI-slots	1 x PCI 32Bit, available via optional riser card. Refer to configurator for details						
Slot Notes	in SAS configuration 1x PCI-Express occupied by modular RAID controller						
Drive bays							
Storage drive bays	3.5-inch or 2.5-inch hot-plug SAS/SATA						
Accessible drive bays	3.5-Incn of 2.5-Incn not-plug SAS/SATA 3 x 5.25/1.6-inch						
Notes accessible drives							
Drive have (Base unit execifie)	All possible options described in relevant system configurator.						
	All possible options described in relevant system configurator.						
Storage drive bays	All possible options described in relevant system configurator. 4 x 3.5-inch hot- 8 x 3.5-inch hot- 8 x 2.5-inch hot- 16 x 2.5-inch hot- 8 x 2.5-inch hot- 24 x 2.5-inch hot- plug SAS/SATA plug SAS/SATA plug SAS/SATA plug SAS/SATA plug SAS/SATA plug SAS/SATA						
Drive bays (Base unit specific) Storage drive bays Storage drive bay configuration	All possible options described in relevant system configurator. 4 x 3.5-inch hot- 8 x 3.5-inch hot- 8 x 2.5-inch hot- 16 x 2.5-inch hot- 8 x 2.5-inch hot- 24 x 2.5-inch h						
Storage drive bays	All possible options described in relevant system configurator. 4 x 3.5-inch hot- plug SAS/SATA 8 x 3.5-inch hot- plug SAS/SATA 8 x 2.5-inch hot- plug SAS/SATA 8 x 2.5-inch hot- plug SAS/SATA 24 x 2.5-inch hot- plug SAS/SATA 24 x 2.5-inch hot- plug SAS/SATA optional optional not expandable optional optional expandable up to expandable up to expandable up to expandable up to						
Storage drive bays Storage drive bay configuration	All possible options described in relevant system configurator. 4 x 3.5-inch hot-plug SAS/SATA 8 x 3.5-inch hot-plug SAS/SATA 16 x 2.5-inch hot-plug SAS/SATA 24 x 2.5-inch hot-plug SAS/SATA optional optional not expandable not expandable optional optional 8 x 1.6x5.25" bays 3x 1.6x5.25" bays<						

Fan Configuration				
Fan configuration	3x120mm high power fans (optional non-hot plug redundant or single hot plug red.)			
Fan notes	Fans with optimized blades and fan control for silent and safe operation			
Operating panel				
Operating buttons	On/off switch			
	NMI button			
	Reset button			
Status LEDs	System status (orange / yellow)			
	Identification (blue) Hard disks access (green)			
	Power (amber / green)			
	CPU status			
	Fan status			
	Hard disk error			
	Temperature CSS (yellow)			
	Memory status			
	PSU status (green/ amber)			
	At system rear side:			
	System status (orange / yellow) Identification (blue)			
	LAN connection (green)			
	LAN speed (green / yellow)			
Service display	Optional:			
	ServerView Local Service Display (LSD)			
BIOS				
BIOS features	ROM based setup utility			
	Recovery BIOS			
	BIOS settings save and restore Local BIOS update from USB device			
	Online update tools for main Linux versions			
	Local and remote update via ServerView Update Manager			
	SMBIOS V2.4			
	Remote PXE boot support			
Operating Systems and Virtualization S				
ertified or supported operating	Windows Server 2019 Datacenter			
ystems and virtualization software	Windows Server 2019 Standard			
	Windows Server 2019 Essentials			
	Windows Server Datacenter, version 1809			
	Windows Server Standard, version 1809			
	Hyper-V Server 2016			
	Windows Server 2016 Datacenter			
	Windows Server 2016 Standard			
	Windows Server 2016 Essentials			
	Windows Storage Server 2016 Standard			
	Windows Server Datacenter, version 1709			
	VMware vSphere™ 6.7			
	SUSE® Linux Enterprise Server 12			
	Red Hat® Enterprise Linux 7			
Operating system notes				
Operating system release link	http://docs.ts.fujitsu.com/dl.aspx?id=d4ebd846-aa0c-478b-8f58-4cfbf3230473			
r				

Infrastructure Manager (ISM) Essential
Node Management
Health status Monitoring and Control
Capacity/Threshold Management
Power Management
Converged Management
Auto Discovery
Remote Management
Update Management
Logging and Auditing ServerView Suite - Deploy
ServerView Installation Manager
ServerView Installation Manager
ServerView Suite - Control
ServerView Operations Manager incl. PDA and ASR & R
ServerView Agents and CIM Providers
ServerView Agentless Management
ServerView System Monitor
SVOM - Event Manager
ServerView RAID Manager
SVOM - Threshold Manager
Power Monitor (monitoring the Power Consumption)
Power Management (iRMC)
Storage Management (server) with SVOM/SV-RAID
ServerView Suite (Maintain)
iRMC S5 (Remote Management)
System Update Manager (BIOS, Firmware, Windows Drives and SV Agents)
Performance management (SVOM)
Asset Management
Primecollect
Customer Self Service
Online Diagnostics
ServerView Suite - Integrate
Integration packs for Microsoft System Center, VMware vCenter, VMware vRealize, Nagios, and HP SIM
ServerView Suite (Maintain)
ServerView eLCM
iRMC Advanced Pack incl. Advanced Video Redirection (AVR), video capturing and Virtual Media
Infrastructure Manager (ISM)
Automate device configuration Mass OS installation
Node Management
Health status Monitoring and Control
Capacity/Threshold Management
Power Management
Converged Management
Auto Discovery
Virtual-IO Management
Network topology Management
Remote Management
Update Management
Logging and Auditing
Integrate in to
Enterprise Management
Vendor specific Management
Monitor 3rd party platforms
Regarding dependencies for ServerView Suite software products see dedicated product data sheets.
177 x 777 x 456 mm
483 (Bezel); 448 mm (body) x 736 x 177 mm
Floorstand Width 177 mm without tilt protection (420 mm with tilt protection); depth measured includes handles or

Dimensions / Weight						
Height Unit Rack	4 U					
Weight	Up to 35.5 kg					
Weight notes	Actual weight may	vary depending on	configuration			
Rack integration kit			e factory or with retro	ofit upgrade.		
Floor-stand (W x D x H)						
Rack integration kit	Rack mount option available as a retrofit upgrade	Rack mount options available from the factory or with retrofit upgrade	Rack mount option available as a retrofit upgrade	Rack mount options available from the factory or with retrofit upgrade	Rack mount options available from the factory or with retrofit upgrade	Rack mount options available from the factory or with retrofit upgrade
Environment						
Operating ambient temperature	5 - 45 ℃ (41 - 113 ℃	'F)				
Operating temperature note	Cool-safe® Advanced Thermal Design (above 35 °C or below 10 °C) depending on configuration. For detailed information see relevant system configurator.					
Operating relative humidity	10 - 85 % (non condensing)					
Operating environment	FTS 04230 – Guidel	ine for Data Center	(installation specific	cation)		
Operating environment link			4813edf-4a27-461a		be	
Noise emission		•	leclared according to			
Sound pressure (LpAm)	Noise minimum configuration: 24 dB(A) (idle) / 32 dB(A) (operating) Noise typical configuration: 24 dB(A) (idle) / 32 dB(A) (operating)					
Sound power (LWAd; 1B = 10dB)	Noise minimum configuration: 4.2 B (idle) / 5.0 B (operating) Noise typical configuration: 4.2 B (idle) / 5.0 B (operating)					
Noise notes	Noise emissions depends on operation modes, system configuration and ambient temperature. Operating mode measured based on OLTIS with 50% load. *OLTIS = FUJITSU Load Profile which stresses all components of a server with a given load level.			esses all		
Electrical values						
Power supply configuration	1x non hot-plug po	wer supply or 2x ho	ot-plug power supply	for redundancy		
lot-plug power supply redundancy	Optional			· ·		
Active power (max. configuration)	748 W					
Apparent power (max. configuration)	752 VA					
Heat emission (max. configuration)	2692.8 kJ/h (2552.	3 BTU/h)				
Rated current max.	9 A (100 V) / 3.5 A					
Active power note	To estimate the power consumption of different configurations use the Power Calculator of the System Architect: http://configurator.ts.fujitsu.com/public/			stem Architect:		
Power supply	450W hot-plug, 94% (Platinum efficiency), 100-240V, 50 / 60Hz 800W hot-plug, 94% (Platinum efficiency), 100-240V, 50 / 60Hz 800W hot-plug, 96% (Titanium efficiency), 200-240V, 50 / 60Hz 1200W hot-plug, 94% (Platinum efficiency), 100-240V, 50 / 60Hz; 110V range: 1000W, less than 110V: 900W					
Power supply notes	Power Safeguard adapts system performance in case the power requirements exceeds supply limits. 96% Titanium Power supply unit is only released for 200-240V					
Compliance						
Global	CB RoHS (Substance li WEEE (Waste electr		ance with global Roł Il equipment)	HS regulations)		
Germany	GS		<i>·</i>			
urope	CE					
JSA/Canada	CSAc/us FCC Class A					
lapan	VCCI:V3 Class A + JIS	5 61000-3-2				
South Korea	KN32 KN35					
China	ССС					
Australia/New Zealand	C-Tick					

Compliance	
Taiwan	BSMI
Compliance link	https://sp.ts.fujitsu.com/sites/certificates
Compliance notes	There is general compliance with the safety requirements of all European countries and North America. National approvals required in order to satisfy statutory regulations or for other reasons can be applied for on request. * Warning: This is a class A product. In a domestic environment this product may cause radio interference in which case the user may be required to take adequate measures.

Components

Backup Drives	LTO7HH Ultrium, 2,500 GB, 300 MB/s, half height, SAS 6Gb/s
	RDX Drive, 320 GB, 500 GB, 1 TB , 25 MB/s, half height, USB 3.0
Optical drives	Blu-ray Disc™ Triple Writer, (6x BD-RW, 8x DVD, 24x CD), ultraslim, SATA I
	DVD-ROM, (16xDVD; 48xCD), half height, SATA I
	DVD Super Multi, (16xDVD, 8xDVD+RW 6xDVD-RW, 12xDVD-RAM; 48xCD, 32xCD-RW), half height, SATA I
	DVD Super Multi ultra slim , (8x DVD; 24x CD), ultraslim, SATA I
Hard disk drives	HDD SATA, 6 Gb/s, 14 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 12 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 8 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 4 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical
	HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical
	HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
	HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical
	HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical

Hard disk drives

rives	HDD SAS, 12 Gb/s, 900 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 900 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 900 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 900 GB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 600 GB , 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 14 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 14 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 12 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 12 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 10 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 8 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 4 TB, 7,200 rpm, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 2.4 TB, 10,000 rpm, 512e, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 2.4 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 2.4 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 2 TB, 7,200 rpm, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical
	HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
	HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
	HDD SAS, 12 Gb/s, 1.2 TB , 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED
	HDD SAS, 12 Gb/s, 1 TB, 7,200 rpm, hot-plug, 3.5-inch, business critical
	HDD SAS, 12 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical

Solid-State-Drive	SSD SATA, 6 Gb/s, 960 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)				
	SSD SATA, 6 Gb/s, 960 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)				
	SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)				
	SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)				
	SSD SATA, 6 Gb/s, 480 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)				
	SSD SATA, 6 Gb/s, 480 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)				
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)				
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)				
	SSD SATA, 6 Gb/s, 240 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1.4 DWPD (Drive Writes Per Day for 5 years)				
	SSD SATA, 6 Gb/s, 240 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1.4 DWPD (Drive Writes Per Day for 5 years)				
	SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)				
	SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)				
	SSD SATA, 6 Gb/s, 7.68 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.5 DWPD (Drive Writes Per Day for 5 years				
	SSD SATA, 6 Gb/s, 7.68 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.5 DWPD (Drive Writes Per Day for 5 years				
	SSD SATA, 6 Gb/s, 3.84 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1.0 DWPD (Drive Writes Per Day for 5 years				
	SSD SATA, 6 Gb/s, 3.84 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1.0 DWPD (Drive Writes Per Day for 5 years				
	SSD SATA, 6 Gb/s, 3.84 TB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)				
	SSD SATA, 6 Gb/s, 3.84 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)				
	SSD SATA, 6 Gb/s, 1.92 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)				
	SSD SATA, 6 Gb/s, 1.92 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)				
	SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)				
	SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)				
	SSD M.2 SATA, 6 Gb/s, 480 GB, non hot plug, enterprise, 1.4 DWPD (Drive Writes Per Day for 5 years)				
	SSD M.2 SATA, 6 Gb/s, 240 GB, non hot plug, enterprise, for VMware				
	SSD M.2 SATA, 6 Gb/s, 240 GB, non hot plug, enterprise, 1.4 DWPD (Drive Writes Per Day for 5 years)				
Solid-State-Drive	SSD SAS, 12 Gb/s, 960 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)				
	SSD SAS, 12 Gb/s, 800 GB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years) SED				
	SSD SAS, 12 Gb/s, 800 GB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years)				
	SSD SAS, 12 Gb/s, 800 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (Drive Writes Per Day for 5 years)				
	SSD SAS, 12 Gb/s, 480 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)				
	SSD SAS, 12 Gb/s, 400 GB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years) SED				
	SSD SAS, 12 Gb/s, 400 GB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years)				
	SSD SAS, 12 Gb/s, 400 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (Drive Writes Per Day for 5 years)				
	SSD SAS, 12 Gb/s, 3.84 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)				
	SSD SAS, 12 Gb/s, 3.2 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 2.3 DWPD (Drive Writes Per Day for 5 years)				
	SSD SAS, 12 Gb/s, 1.92 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1 DWPD (Drive Writes Per Day for 5 years)				
	SSD SAS, 12 Gb/s, 1.6 TB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years), SED				
	SSD SAS, 12 Gb/s, 1.6 TB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (Drive Writes Per Day for 5 years)				
	SSD SAS, 12 Gb/s, 1.6 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (Drive Writes Per Day for 5 years)				

PCIe SSD & SATA DOM SSD	PCIe-SSD SFF, 6.4 TB, Mixed-use, hot-plug, 2.5-inch, Flash drive, 3.2 DWPD (Drive Writes Per Day for 5 years)					
	PCIe-SSD SFF, 6.4 TB, Mixed-use, hot-plug, 2.5-inch, Flash drive, 3.0 DWPD (Drive Writes Per Day for 5 years)					
	PCIe-SSD SFF, 4 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 3.0 DWPD (Drive Writes Per Day for 5 years)					
	PCIe-SSD SFF, 4 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 0.6 DWPD (Drive Writes Per Day for 5 years)					
	 PCIe-SSD SFF, 3.2 TB, Mixed-use, hot-plug, 2.5-inch, Flash drive, 3.1 DWPD (Drive Writes Per Day for 5 years) PCIe-SSD SFF, 3.2 TB, Mixed-use, hot-plug, 2.5-inch, Flash drive, 3.0 DWPD (Drive Writes Per Day for 5 years) PCIe-SSD SFF, 2 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 3.0 DWPD (Drive Writes Per Day for 5 years) PCIe-SSD SFF, 2 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 0.6 DWPD (Drive Writes Per Day for 5 years) PCIe-SSD SFF, 1.6 TB, Mixed-use, hot-plug, 2.5-inch, Flash drive, 3.0 DWPD (Drive Writes Per Day for 5 years) PCIe-SSD SFF, 1 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 3.0 DWPD (Drive Writes Per Day for 5 years) 					
	PCle-SSD SFF, 1 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 1 DWPD (Drive Writes Per Day for 5 years)					
	PCle-SSD AIC, 750 GB, Write-Intensive, HHHL, Flash drive, 30 DWPD (Drive Writes Per Day for 5 years)					
	PCIe-SSD AIC, 375 GB, Write-Intensive, HHHL, Flash drive, 30 DWPD (Drive Writes Per Day for 5 years)					
	Dual microSD 64GB Enterprise					
RAID Controller	Fujitsu PRAID EP580i FH, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, NVMe-PCle 8 Gbit/s, 16 ports int. RAID level: 0, 1, 10, 5 50, 6, 60, 8 GB, Optional FBU based on LSI SAS3516					
	Fujitsu PRAID EP540i FH, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, NVMe-PCIe 8 Gbit/s, 16 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 4 GB, Optional FBU based on LSI SAS3516					
	Fujitsu PRAID EP540e FH, RAID 5/6 Ctrl., SAS 12 Gbit/s, 8 ports ext. RAID level: 0, 1, 10, 5, 50, 6, 60, 4 GB, Optional FBU based on LSI SAS3516					
	Fujitsu PRAID EP520i FH, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, NVMe-PCle 8 Gbit/s, 8 Gbit/s 8 ports int. RAID level: 0, 1 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3516					
	Fujitsu PRAID EP420i, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3108					
	Fujitsu PRAID EP420i for SafeStore, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3108					
	Fujitsu PRAID EP400i, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 1 GB, Optional FBU based on LSI SAS3108					
	Fujitsu PRAID CP400i, RAID Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 1E, 10, 5, 50, No FBU support					
Fibre Channel controller	Fibre Channel Host Bus Adapter 1 x 32 Gbit/s Cavium QLE2740 MMF LC-style					
	Fibre Channel Host Bus Adapter 2 x 32 Gbit/s Cavium QLE2742 MMF LC-style					
	Fibre Channel Host Bus Adapter 1 x 32 Gbit/s Emulex LPe32000-M6-F MMF LC-style					
	Fibre Channel Host Bus Adapter 2 x 32 Gbit/s Emulex LPe32002-M6-F MMF LC-style					
	Fibre Channel Host Bus Adapter 1 x 16 Gbit/s Qlogic QLE2690 LC-style					
	Fibre Channel Host Bus Adapter 2 x 16 Gbit/s Qlogic QLE2692 LC-style					
	Fibre Channel Host Bus Adapter 1 x 16 Gbit/s Emulex LPe31000-M6-F MMF LC-style					
	Fibre Channel Host Bus Adapter 2 x 16 Gbit/s Emulex LPe31002-M6-F MMF LC-style					

Communication, Network	Converged Network Adapter 2 x 10 Gbit/s / 25 Gbit/s PCIe 3.0 x8 SFP28 (Cavium)				
communication, network	Converged Network Adapter 2 x 10 Gbit/s PCle 3.0 x8 SFP+ (Emulex)				
	Ethernet Ctrl. 1 x 100 Gbit/s PCle 3.0 x16 QSFP28 (Cavium)				
	Ethernet Ctrl. 1 x 100 Gbit/s PCle 3.0 x16 QSFP28 (Mellanox)				
	Ethernet Ctrl. 2 x 10 Gbit/s ; 1 Gbit/s PCIe 3.0 x8 RJ45 (Cavium)				
	Ethernet Ctrl. 2 x 10 Gbit/s ; 1 Gbit/s PCle 3.0 x8 RJ45 (Intel®)				
	Ethernet Ctrl. 2 x 10 Gbit/s ; 1 Gbit/s PCle 3.0 x8 SFP+ (Cavium)				
	Ethernet Ctrl. 2 x 10 Gbit/s / 25 Gbit/s PCIe 3.0 x8 SFP28 (Cavium)				
	Ethernet Ctrl. 2 x 10 Gbit/s / 25 Gbit/s PCIe 3.0 x8 SFP28 (Intel®)				
	Ethernet Ctrl. 2 x 10 Gbit/s / 25 Gbit/s PCIe 3.0 x8 SFP28 (Mellanox)				
	Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 10Gbit/s Eth (RJ45) (Emulex)				
	Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 SFP+ (Emulex)				
	Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 SFP+ (Intel®)				
	Ethernet Ctrl. 2 x 1 Gbit/s PCle 2.1 x4 RJ45 (Intel®)				
	Ethernet Ctrl. 2 x 40 Gbit/s PCIe 3.0 x16 QSFP (Mellanox)				
	Ethernet Ctrl. 4 x 10 Gbit/s ; 1 Gbit/s PCle 3.0 x8 RJ45 (Cavium) Ethernet Ctrl. 4 x 10 Gbit/s ; 1 Gbit/s PCle 3.0 x8 RJ45 (Intel®) Ethernet Ctrl. 4 x 10 Gbit/s ; 1 Gbit/s PCle 3.0 x8 SFP+ (Cavium) Ethernet Ctrl. 4 x 10 Gbit/s PCle 3.0 x8 SFP+ (Intel®) Ethernet Ctrl. 4 x 1 Gbit/s PCle 2.1 x4 RJ45 (Intel®)				
	Interface modul for Dynamic LoM 2 x 10 Gbit/s RJ45 (Intel®)				
	Interface modul for Dynamic LoM 2 x 10 Gbit/s SFP+ (Intel®)				
	MPO x 40 Gbit/s ()				
Graphics	NVIDIA® Quadro® P400 , 2 GB, PCIe x16, 3 x miniDP				
Warranty					
Warranty period	3 years				
Warranty type	Onsite warranty Warranty conditions tbd				
Warranty Terms & Conditions Product Support Services - the perf	http://support.ts.fujitsu.com/warranty/Index.asp?LNG=COM ect extension				
Support Pack Options	Globally available in major business areas: 9x5, Next Business Day Onsite Response Time 9x5, 4h Onsite Response Time (depending on country) 24x7, 4h Onsite Response Time (depending on country)				
Recommended Service	24x7 Onsite Service with 4h Onsite Response Time				
Service Lifecycle	5 years after end of product life				
Service Weblink http://www.fujitsu.com/fts/products/product-support-services/					

More information

Fujitsu products, solutions & services

In addition to FUJITSU Server PRIMERGY TX2550 M5, Fujitsu provides a range of platform solutions. They combine reliable Fujitsu products with the best in services, know-how and worldwide partnerships.

Fujitsu Portfolio

Built on industry standards, Fujitsu offers a full portfolio of IT hardware and software products, services, solutions and cloud offering, ranging from clients to datacenter solutions and includes the broad stack of Business Solutions, as well as the full stack of Cloud offerings. This allows customers to select from alternative sourcing and delivery models to increase their business agility and to improve their IT operation's reliability.

Computing Products

www.fujitsu.com/global/products/computing/

Software

www.fujitsu.com/software/

More information

Learn more about Fujitsu PRIMERGY TX2550 M5, please contact your Fujitsu sales representative or Fujitsu Business partner, or visit our website.

http://www.fujitsu.com/global/products/ computing/servers/primergy/tower/tx2550m5/ index.html

Fujitsu green policy innovation

Fujitsu Green Policy Innovation is our worldwide project for reducing burdens on the environment.

Using our global know-how, we aim to contribute to the creation of a sustainable environment for future generations through IT. Please find further information at http://www. fujitsu.com/global/about/environment



Copyrights

All rights reserved, including intellectual property rights. Designations may be trademarks and/or copyrights of the respective owner, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see http:// www.fujitsu.com/fts/resources/navigation/ terms-of-use.html Copyright 2019 FUJITSU LIMITED

Disclaimer

Technical data is subject to modification and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective owner, the use of which by third parties for their own purposes may infringe the rights of such owner.

Contact FUJITSU LIMITED

Website: www.fujitsu.com 2019-08-01 WW-EN All rights reserved, including intellectual property rights. Designations may be trademarks and/or copyrights of the respective owner, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see http://www.fujitsu.com/fts/resources/navigation/terms-of-use.html Copyright 2019 FUJITSU LIMITED