Allied Telesis

x530L Series

Stackable Intelligent Layer 3 Switches

The Allied Telesis x530L Series stackable Layer 3 switches feature high capacity, resiliency and easy management, making them the ideal choice for network access applications.

Overview

The Allied Telesis x530L Series are a high-performing and feature-rich choice for today's networks. A choice of 24 or 48 Gigabit ports and 4 x 10 Gigabit uplinks, combined with the ability to stack multiple units, make the x530L Series a versatile solution for enterprise applications.

Power over Ethernet Plus (PoE+) models enable connecting and powering wireless access points, IP surveillance cameras, and other devices.

Powerful network management

Allied Telesis Autonomous Management Framework[™] (AMF) automates many everyday tasks including configuration management, easing the workload of modern networks. The entire network can be managed as a single virtual device with powerful centralized features. Growing the network can be accomplished with plug-and-play simplicity, and network node recovery is fully zero-touch.

AMF secure mode increases network security with management traffic encryption, authorization and monitoring. AMF Guestnode allows third-party devices, such as IP phones and security cameras, to be part of the AMF network.

Resilient

Today's converging online services mean there is increasing demand for highly-available networks with minimal downtime. Allied Telesis Virtual Chassis Stacking (VCStack[™]), in conjunction with link aggregation, provides a network with no single point of failure and application resiliency.

x530L Series switches can form a VCStack of up to eight units for enhanced resiliency and simplified device management. Mixed stacking allows the x530L Series to stack with x530 Series Switches. Virtual Chassis Stacking over Long Distance (VCStack[™] LD), which enables stacks to be created over long distance fiber links, makes the x530L Series the perfect choice for distributed environments too.

Allied Telesis Ethernet Protection Switched Ring (EPSRing[™]), and the standards-based G.8032 Ethernet Ring Protection, ensure that distributed network segments have high-speed, resilient access to online resources and applications.

Reliable

The x530L Series was designed with reliability in mind, and guarantees continual delivery of essential services. With dual built-in Power Supply Units (PSUs) and near-hitless online stack reconfiguration, maintenance can be performed without affecting network uptime.

Secure

A secure network environment is guaranteed. The x530L Series offers powerful control over network traffic types, secure management options, loop quard to protect against cabling mistakes, and tri-authentication for comprehensive access control.

Future proof

The x530L Series ensures a future-proof network, with superior flexibility and the ability to stack multiple units. All x530L models feature 10 Gigabit uplink ports and a comprehensive IPv6 feature set, to ensure they are ready for future network traffic demands.



Environmentally friendly

The x530L Series supports Energy Efficient Ethernet (EEE), automatically reducing the power consumed by the switch whenever there is no traffic on a port. This sophisticated feature significantly lowers operating costs by reducing the power requirements of the switch and any associated cooling equipment.



Key Features

- Autonomous Management Framework[™] (AMF)
- ▶ VCStack[™] up to 8 switches
- VCStack LD for distributed resilient backbones
- ▶ EPSR[™] and G.8032 Ethernet Ring Protection for resilient rings
- ▶ Up to 740W Power Over Ethernet (PoE+)
- Continuous PoE
- Active Fiber Monitoring (AFM)
- ▶ Dual fixed PSUs
- OpenFlow for SDN





EPSRing

4CTIVE Fiber Monitoring

Key Features

Autonomous Management Framework[™] (AMF)

- AMF is a sophisticated suite of management tools that provide a simplified approach to network management. Powerful features like centralized management, auto-backup, auto-upgrade, autoprovisioning and auto-recovery enable plug-andplay networking and zero-touch management.
- Any x530L Series switch can operate as the AMF network master, storing firmware and configuration backups for other network nodes. The AMF master enables auto-provisioning and auto-upgrade by providing appropriate files to new network members. New network devices can be pre-provisioned, making installation easy because no onsite configuration is required.
- AMF Guestnode allows Allied Telesis wireless APs and other switching products, as well as third-party devices such as IP phones and security cameras, to be part of an AMF network.

Virtual Chassis Stacking (VCStack™)

- Create a VCStack of up to 8 units with 40Gbps of stacking bandwidth for each unit. Stacking links are connected in a ring so each device has dual connections to further improve resiliency. VCStack provides a highly-available system where network resources are spread out across stacked units, reducing the impact if one of the units fails. Aggregating switch ports on different units across the stack provides excellent network resiliency.
- Mixed stacking allows the x530L Series to stack with x530 Series switches, providing flexible deployment options.

Long-Distance Stacking (VCStack™ LD)

 VCStack LD allows a VCStack to be created over longer distances, perfect for distributed network environments.

Ethernet Protection Switched Ring (EPSRing™)

- EPSRing and 10 Gigabit Ethernet allow several x530L Series switches to form high-speed protected rings capable of recovery within as little as 50ms. This feature is perfect for high performance and high availability in enterprise networks.
- Super-Loop Protection (SLP) enables a link between two EPSR nodes to be in separate EPSR domains, improving redundancy and network fault resiliency.
- The x530L Series switches can act as the ESPR Master, or be deployed as EPSR transit nodes, in a high-speed ring.

G.8032 Ethernet Ring Protection

- G.8032 provides standards-based high-speed ring protection, that can be deployed as standalone, or interoperate with Allied Telesis EPSR.
- Ethernet Connectivity Fault Monitoring (CFM) proactively monitors links and VLANs, and provides alerts when a fault is detected.

Power over Ethernet Plus (PoE+)

- With PoE, a separate power connection to media endpoints such as IP phones and wireless access points is not necessary. PoE+ reduces costs and provides even greater flexibility, providing the capability to connect devices requiring more power (up to 30 Watts) such as pan, tilt and zoom security cameras.
- The x530L Series allows the configuration of the overall power budget, as well as the power limit per port.

Active Fiber Monitoring (AFM)

AFM prevents eavesdropping on fiber communications by monitoring received optical power. If an intrusion is detected, the link can be automatically shut down, or an operator alert can be sent.

Continuous PoE

Continuous PoE allows the switch to be restarted without affecting the supply of power to connected devices. Smart lighting, security cameras, and other PoE devices will continue to operate during a software upgrade on the switch.

High Reliability

 The x530L Series feature front to back cooling and dual PSUs.

Voice VLAN

Voice VLAN automatically separates voice and data traffic into two different VLANs. This automatic separation places delay-sensitive traffic into a voice-dedicated VLAN, which simplifies QoS configurations.

sFlow

SFlow is an industry-standard technology for monitoring high-speed switched networks. It provides complete visibility into network use, enabling performance optimization, usage accounting/billing, and defense against security threats. Sampled packets sent to a collector ensure a real-time view of network traffic.

VLAN Mirroring (RSPAN)

VLAN mirroring allows traffic from a port on a remote switch to be analyzed locally. Traffic being transmitted or received on the port is duplicated and sent across the network on a special VLAN.

Optical DDM

Most modern optical SFP/SFP+/QSFP transceivers support Digital Diagnostics Monitoring (DDM). This enables real-time monitoring of various parameters of the transceiver, such as optical output power, temperature, laser bias current and transceiver supply voltage. Easy access to this information simplifies diagnosing problems with optical modules and fiber connections.

Tri-authentication

Authentication options on the x530L Series also include alternatives to IEEE 802.1x port-based authentication, such as web authentication to enable guest access and MAC authentication for endpoints that do not have an IEEE 802.1x supplicant. All three authentication methods— IEEE 802.1x, MAC-based and Web-based can be enabled simultaneously on the same port for tri-authentication.

TACACS+ Command Authorization

TACACS+ Command Authorization offers centralized control over which commands may be issued by each specific AlliedWare Plus device user. It complements authentication and accounting services for a complete AAA solution.

Premium Software License

By default, the x530L Series offers a comprehensive Layer 2 and basic Layer 3 feature set that includes static routing and IPv6 management features. The feature set can easily be elevated to full Layer 3 by applying the premium software license. This adds dynamic routing protocols and Layer 3 multicasting capabilities.

VLAN Access Control List (ACLs)

 ACLs simplify access and traffic control across entire segments of the network. They can be applied to a VLAN as well as a specific port.

Dynamic Host Configuration Protocol (DHCP) Snooping

DHCP servers allocate IP addresses to clients, and the switch keeps a record of addresses issued on each port. IP source guard checks against this DHCP snooping database to ensure only clients with specific IP and/or MAC address can access the network. DHCP snooping can be combined with other features, like dynamic ARP inspection, to increase security in Layer 2 switched environments, and also provides a traceable history, which meets the growing legal requirements placed on service providers.

Software Defined Networking (SDN)

 OpenFlow is a key technology that enables the use of SDN to build smart applications that unlock value and reduce cost.

Key Solutions



Resilient distribution switching

The x530L Series are ideal for distribution solutions, where resiliency and flexibility are required. In the above diagram, distribution switches utilize long-distance Virtual Chassis Stacking (VCStack LD) to create a single virtual unit out of multiple devices. By using fiber stacking connectivity, units can be kilometers apart—perfect for a distributed environment. Mixed stacking allows the x530L Series and x530 Series switches to be stacked together for even more deployment flexibility.

When combined with link aggregation, VCStack provides a solution with no single point of failure, which fully utilizes all network bandwidth.

The x530L Series supports Enterprises and their use of business-critical online resources and applications, with a resilient and reliable distribution solution.

Power at the network edge

The PoE models can provide 740 Watts of power, making the full 30 Watts of PoE+ available to highpower endpoints. This flexible PoE solution can power today's most advanced devices, including PTZ cameras with heaters/blowers, enhanced lighting management, wireless access points and more.

Dual internal PSUs provide redundancy, while Continuous PoE ensures power delivery to endpoints even during a switch firmware upgrade.

With advanced security and access control features, and built-in resiliency, the x530L Series are the ideal choice for connecting and powering devices at the network edge.

Specifications

Performance

- 40Gbps of stacking bandwidth using front panel 10G SFP+ ports
- Supports 10KB jumbo frames
- Wirespeed multicasting
- 4094 configurable VLANs
- 16K MAC addresses
- ▶ Up to 1250 OpenFlow v1.3 entries
- ► 1GB DDR3 SDRAM, 256MB NAND flash memory
- Packet buffer memory: 3MB

Reliability

- Modular AlliedWare Plus operating system
- Full environmental monitoring of PSUs, fans, temperature and internal voltages. SNMP traps alert network managers in case of any failure

Expandability

- Stack up to eight units in a VCStack
- Versatile licensing options for additional features

Flexibility and Compatibility

- 10G SFP+ ports will support any combination of Allied Telesis 1000Mbps SFP and 10GbE SFP+ modules and direct attach cables listed in this document under Ordering Information
- Port speed and duplex configuration can be set manually or by auto-negotiation
- Front-panel SFP+ stacking ports can be configured as 1G/10G Ethernet ports

Diagnostic Tools

- Connectivity Fault Management (CFM) Continuity Check Protocol (CCP) for use with G.8032 ERPS
- Built-In Self Test (BIST)
- ▶ Ping polling and TraceRoute for IPv4 and IPv6
- Optical Digital Diagnostic Monitoring (DDM)
- Find-me device locator
- ► Automatic link flap detection and port shutdown
- Cable fault locator (TDR)
- Uni-Directional Link Detection (UDLD)
- Active Fiber Monitoring detects tampering on optical links
- Port and VLAN mirroring (RSPAN)

IPv4 Features

- Equal Cost Multi Path (ECMP) routing
- Static unicast and multicast routing for IPv4
- ► UDP broadcast helper (IP helper)
- Directed broadcast forwarding
- Black hole routing
- DNS relay
- Policy-based routing
- Route redistribution (OSPF, RIP, and BGP)

IPv6 Features

- Device management over IPv6 networks with SNMPv6, Telnetv6 and SSHv6
- IPv4 and IPv6 dual stack
- IPv6 over IPv4 tunneling (manual configuration only)
- Log to IPv6 hosts with Syslog v6
- NTPv6 client and server

4 x5301 Series

- DNSv6 client, DNSv6 relay
- DHCPv6 relay and client
- ► Static IPv6 unicast and multicast routing
- ► IPv6 aware storm protection and QoS
- ► IPv6 hardware ACLs

Management

- ► Industry-standard CLI with context-sensitive help
- Built-in text editor and powerful CLI scripting engine
- Comprehensive SNMP MIB support for standardsbased device management
- Console management port on the front panel for ease of access
- Event-based triggers allow user-defined scripts to be executed upon selected system events
- Eco-friendly mode allows ports and LEDs to be disabled to save power
- USB interface allows software release files, configurations and other files to be stored for backup and distribution to other devices
- Front panel 7-segment LED provides at-a-glance status and fault information
- Autonomous Management Framework (AMF) enables powerful centralized management and zero-touch device installation and recovery. Try AMF for free with the built-in Starter license
- Web-based Graphical User Interface (GUI)

Quality of Service

- ► IP precedence and DiffServ marking based on Layer 2, 3 and 4 headers
- Queue scheduling options for strict priority, weighted round robin or mixed scheduling
- Taildrop for queue congestion control
- Extensive remarking capabilities
- Policy-based QoS based on VLAN, port, MAC and general packet classifiers
- Limit bandwidth per port or per traffic class down to 64kbps
- 8 priority queues with a hierarchy of high priority queues for real time traffic, and mixed scheduling, for each switch port
- Policy-based storm protection
- Wirespeed traffic classification with low latency essential for VoIP and real-time streaming media applications

Resiliency Features

- EPSRing (Ethernet Protection Switched Rings) with SuperLoop Protection (SLP) and enhanced recovery
- EPSR Master or transit node deployment
- ► STP root guard
- ► Loop protection: thrash limiting and loop detection
- ► Dynamic link failover (host attach)
- Control Plane Prioritization (CPP) ensures the CPU always has sufficient bandwidth to process network control traffic
- PVST+ compatibility mode
- VCStack fast failover minimizes network disruption
- SFP+ stacking ports can be configured as 10G Ethernet ports
- Long-Distance VCStack with 10G SFP+ modules (VCStack LD)
- BPDU forwarding

Security Features

- MAC address filtering and MAC address lockdown
- Port-based learn limits (intrusion detection)
- Access Control Lists (ACLs) based on layer 3 and 4 headers
- > Dynamic ACLs assigned via port authentication
- ACL Groups enable multiple hosts/ports to be included in a single ACL, reducing configuration
- Private VLANs provide security and port isolation for multiple customers using the same VLAN
- ► Secure Copy (SCP)
- ▶ BPDU protection
- Network Access and Control (NAC) features manage endpoint security
- Dynamic VLAN assignment

Auth fail and guest VLANs

(AAA)

security

- Tri-authentication: MAC-based, web-based and IEEE 802.1x
- ► DoS attack blocking and virus throttling
- DHCP snooping, IP source guard and Dynamic ARP Inspection (DAI)
- Strong password security and encryption

Secure File Transfer Protocol (SFTP) client

Configurable ACLs for management traffic

▶ RADIUS group selection per VLAN or port

Software Defined Networking (SDN)

connection interruption and inactivity probe

OpenFlow v1.3 with support for encryption,

Environmental Specifications

Operating temperature range:

0°C to 50°C (32°F to 122°F)

-25°C to 70°C (-13°F to 158°F)

• Operating relative humidity range:

Storage relative humidity range:

3,048 meters maximum (10,000 ft)

Power Supply Specifications

AC voltage: 90-264V (auto-ranging)

Electrical Approvals and Compliances

Immunity: EN55024, EN61000-3-levels 2

(Harmonics), and 3 (Flicker) - AC models only

Standards: UL60950-1, CAN/CSA-C22.2 No.

60950-1-03, EN60950-1, EN60825-1, AS/NZS

AlliedTelesis com

EMC: EN55032 class A, FCC class A, VCCI class

5% to 90% non-condensing

5% to 95% non-condensing

Operating altitude:

▶ Frequency: 50-60Hz

A. ICES-003 class A

Safety

60950.1

Certification: UL, cUL

▶ EU RoHS compliant

China RoHS compliant

Restrictions on Hazardous

Substances (RoHS) Compliance

Storage temperature range:

Authentication, Authorisation and Accounting

Bootloader can be password protected for device

x530L Series | Stackable Intelligent Layer-3 Switches

Product Specifications

PRODUCT	10/100/1000T (RJ-45) COPPER PORTS	1/10 GIGABIT SFP+ PORTS	STACKING PORTS	POE+ ENABLED PORTS	SWITCHING FABRIC	FORWARDING RATE
x530L-28GTX	24	4	2*	-	128Gbps	95.2Mpps
x530L-28GPX	24	4	2*	24	128Gbps	95.2Mpps
x530L-52GTX	48	4	2*	-	176Gbps	130.9Mpps
x530L-52GPX	48	4	2*	48	176Gbps	130.9Mpps

* Stacking ports can be configured as additional 1G/10G Ethernet ports when the switch is not stacked

Physical Specifications

PRODUCT	WIDTH X DEPTH X HEIGHT	MOUNTING	WEI	PACKAGED DIMENSIONS		
		MOONTING	UNPACKAGED PACKAGED		TACKAGED DIMENSIONS	
x530L-28GTX	441 x 323 x 44 mm (17.36 x 12.72 x 1.73 in)	Rack-mount	4.4 kg (9.07 lbs)	6.3 kg (13.89 lbs)	577 x 440 x 153 mm (22.72 x 17.32 x 6.02 in)	
x530L-28GPX	441 x 421 x 44 mm (17.36 x 16.57 x 1.73 in)	Rack-mount	6.2 kg (13.67 lbs)	8.4 kg (18.52 lbs)	577 x 548 x 153 mm (22.72 x 21.57 x 6.02 in)	
x530L-52GTX	441 x 323 x 44 mm (17.36 x 12.72 x 1.73 in)	Rack-mount	5.2 kg (11.46 lbs)	7.1 kg (15.65 lbs)	577 x 440 x 128 mm (22.72 x 17.32 x 6.02 in)	
x530L-52GPX	441 x 421 x 44 mm (17.36 x 16.57 x 1.73 in)	Rack-mount	6.7 kg (14.77 lbs)	8.9 kg (19.62 lbs)	577 x 548 x 153 mm (22.72 x 21.57 x 6.02 in)	

Power and Noise Characteristics

	6.0A MAX PER INPUT (28GPX/52GPX), 1.0A MAX PER INPUT (28GTX/52GTX)									
	NO POE LOAD			FULL POE+ LOAD			MAX POE	POE SOURCING PORTS		
PRODUCT	MAX POWER CONSUMPTION (W)	MAX HEAT DISSIPATION (BTU/H)	NOISE (DBA)	MAX POWER CONSUMPTION (W)	MAX HEAT DISSIPATION (BTU/H)	NOISE (DBA)	POWER (W)	P0E (7.5W)	POE (15.4W)	P0E+ (30W)
x530L-28GTX	39	133	42*	-	-	-	-	-	-	-
x530L-28GPX	70	239	42*	890	3037	42*	740	24	24	24
x530L-52GTX	60	205	42*	-	-	-	-	-	-	-
x530L-52GPX	95	324	42*	950	3242	42*	740	48	48	24

* This figure is under 30 degree C ambient temperature

Noise: tested to IS07779; front bystander position

Latency (microseconds)

PRODUCT	PORT SPEED						
FRUDUGI	10MBPS	100MBPS	1GBPS	10GBPS			
x530L-28GTX	29.91µs	6.06µs	3.98µs	1.63µs			
x530L-28GPX	29.91µs	6.06µs	3.98µs	1.63µs			
x530L-52GTX	30.98µs	8.34µs	5.27µs	1.67µs			
x530L-52GPX	30.98µs	8.34µs	5.27µs	1.67µs			

Standards and Protocols

AlliedWare Plus Operating System Version 5.5.0-1 Authentication						
RFC 1321						
RFC 1828	5					
Border	Gateway Protocol (BGP)					
BGP dynam	ic capability					
BGP outbou	nd route filtering					
RFC 1772	Application of the Border Gateway Protocol					
	(BGP) in the Internet					
RFC 1997	BGP communities attribute					
RFC 2385	Protection of BGP sessions via the TCP MD5					
	signature option					
RFC 2439	BGP route flap damping					
RFC 2858	Multiprotocol extensions for BGP-4					
RFC 2918	Route refresh capability for BGP-4					
RFC 3392	Capabilities advertisement with BGP-4					

RFC 3882	Configuring BGP to block Denial-of-Service
	(DoS) attacks
RFC 4271	Border Gateway Protocol 4 (BGP-4)
RFC 4360	BGP extended communities
RFC 4456	BGP route reflection - an alternative to full
	mesh iBGP
RFC 4724	BGP graceful restart
RFC 4893	BGP support for four-octet AS number space
RFC 5065	Autonomous system confederations
	for BGP

Cryptographic Algorithms

FIPS Approved Algorithms

- Encryption (Block Ciphers): AES (ECB, CBC, CFB and OFB Modes) 3DES (ECB, CBC, CFB and OFB Modes) Block Cipher Modes: CCM CMAC GCM XTS Digital Signatures & Asymmetric Key Generation: DSA ECDSA RSA Secure Hashing:
- SHA-1
- ► SHA-2 (SHA-224, SHA-256, SHA-384. SHA-512) Message Authentication:
- HMAC (SHA-1, SHA-2(224, 256, 384, 512)
- Random Number Generation:
- DRBG (Hash, HMAC and Counter)

Non FIPS Approved Algorithms

RNG (AES128/192/256) DES MD5

Encryption (management traffic only)

115 100-1	Secure mash stanuaru (SHA-T)
FIPS 186	Digital signature standard (RSA)
FIPS 46-3	Data Encryption Standard (DES and 3DES)
Ethernet	t Standards
IEEE 802.2	Logical Link Control (LLC)
IEEE 802.3	Ethernet
IEEE 802.3al	b1000BASE-T
IEEE 802.3a	e10 Gigabit Ethernet
IEEE 802.3af	f Power over Ethernet (PoE)
IEEE 802.3at	t Power over Ethernet up to 30W (PoE+)
IEEE 802.3a	zEnergy Efficient Ethernet (EEE)
IEEE 802.3u	100BASE-X
IEEE 802.3x	Flow control - full-duplex operation

- IEEE 802.3z 1000BASE-X
- IEEE 002.32 IUUUDASE-X

IPV4 realures	IPv4	Features
---------------	------	----------

RFC 768	User Datagram Protocol (UDP)
RFC 791	Internet Protocol (IP)
RFC 792	Internet Control Message Protocol (ICMP)
RFC 793	Transmission Control Protocol (TCP)
RFC 826	Address Resolution Protocol (ARP)
RFC 894	Standard for the transmission of IP
	datagrams over Ethernet networks
RFC 919	Broadcasting Internet datagrams
RFC 922	Broadcasting Internet datagrams in the
	presence of subnets
RFC 932	Subnetwork addressing scheme
RFC 950	Internet standard subnetting procedure
RFC 951	Bootstrap Protocol (BootP)
RFC 1027	Proxy ARP
RFC 1035	DNS client
RFC 1042	Standard for the transmission of IP
	datagrams over IEEE 802 networks
RFC 1071	Computing the Internet checksum
RFC 1122	Internet host requirements
RFC 1191	Path MTU discovery
RFC 1256	ICMP router discovery messages
RFC 1518	An architecture for IP address allocation with
	CIDR
RFC 1519	Classless Inter-Domain Routing (CIDR)
RFC 1542	Clarifications and extensions for BootP
RFC 1591	Domain Name System (DNS)
RFC 1812	Requirements for IPv4 routers
RFC 1918	IP addressing
RFC 2581	TCP congestion control

IPv6 Features

Path MTU discovery for IPv6 RFC 1981 RFC 2460 IPv6 specification RFC 2464 Transmission of IPv6 packets over Ethernet networks RFC 2711 IPv6 router alert option RFC 3484 Default address selection for IPv6 RFC 3587 IPv6 global unicast address format RFC 3596 DNS extensions to support IPv6 RFC 4007 IPv6 scoped address architecture Unique local IPv6 unicast addresses BEC 4193 Transition mechanisms for IPv6 hosts and RFC 4213 routers RFC 4291 IPv6 addressing architecture RFC 4443 Internet Control Message Protocol (ICMPv6) Neighbor discovery for IPv6 RFC 4861 IPv6 Stateless Address Auto-Configuration RFC 4862 (SLAAC) RFC 5014 IPv6 socket API for source address selection RFC 5095 Deprecation of type 0 routing headers in IPv6 RFC 5175 IPv6 Router Advertisement (RA) flags option RFC 6105 IPv6 Router Advertisement (RA) guard

Management

AT Enterprise	e MIB including AMF MIB and SNMP traps				
Optical DDM	0				
SNMPv1, v2c and v3					
,	BLink Layer Discovery Protocol (LLDP)				
RFC 1155	Structure and identification of management information for TCP/IP-based Internets				
RFC 1157	Simple Network Management Protocol (SNMP)				
RFC 1212	Concise MIB definitions				
RFC 1213	MIB for network management of TCP/ IP-based Internets: MIB-II				
RFC 1215	Convention for defining traps for use with the SNMP				
RFC 1227	SNMP MUX protocol and MIB				
RFC 1239	Standard MIB				
RFC 1724	RIPv2 MIB extension				
RFC 2578	Structure of Management Information v2 (SMIv2)				
RFC 2579	Textual conventions for SMIv2				
RFC 2580	Conformance statements for SMIv2				
RFC 2674	Definitions of managed objects for bridges with traffic classes, multicast filtering and VLAN extensions				
RFC 2741	Agent extensibility (AgentX) protocol				
RFC 2787 RFC 2819	Definitions of managed objects for VRRP RMON MIB (groups 1,2,3 and 9)				

RFC 2863	Interfaces group MIB				
RFC 3176	sFlow: a method for monitoring traffic in				
	switched and routed networks				
RFC 3411	An architecture for describing SNMP				
	management frameworks				
RFC 3412	Message processing and dispatching for the SNMP				
RFC 3413	SNMP applications				
RFC 3414	User-based Security Model (USM) for				
	SNMPv3				
RFC 3415	View-based Access Control Model (VACM)				
	for SNMP				
RFC 3416	Version 2 of the protocol operations for the				
	SNMP				
RFC 3417	Transport mappings for the SNMP				
RFC 3418	MIB for SNMP				
RFC 3621	Power over Ethernet (PoE) MIB				
RFC 3635	Definitions of managed objects for the				
	Ethernet-like interface types				
RFC 3636	IEEE 802.3 MAU MIB				
RFC 4022	MIB for the Transmission Control Protocol				
	(TCP)				
RFC 4113	MIB for the User Datagram Protocol (UDP)				
RFC 4188	Definitions of managed objects for bridges				
RFC 4292	IP forwarding table MIB				
RFC 4293	MIB for the Internet Protocol (IP)				
RFC 4318	Definitions of managed objects for bridges				
	with RSTP				
RFC 4502	RMON 2				
RFC 4560	Definitions of managed objects for remote				
	ping, traceroute and lookup operations				
RFC 5424	The Syslog protocol				
RFC 6527	Definitions of managed objects for VRRPv3				
	Multicast Support				
Rootetran R	outer (RSR) mechanism for PIM_SM				

Rootetran Do	outer (BSR) mechanism for PIM-SM		
IGMP guery :	. ,		
	ng (IGMPv1, v2 and v3)		
IGMP shoopi			
	nulticast forwarding (IGMP/MLD proxy)		
	ng (MLDv1 and v2)		
	SSM for IPv6		
RFC 1112 RFC 2236	Host extensions for IP multicasting (IGMPv1) Internet Group Management Protocol v2		
RFC 2230	(IGMPv2)		
RFC 2710	Multicast Listener Discovery (MLD) for IPv6		
RFC 2715	Interoperability rules for multicast routing protocols		
RFC 3306	Unicast-prefix-based IPv6 multicast		
	addresses		
RFC 3376	IGMPv3		
RFC 3810	Multicast Listener Discovery v2 (MLDv2) for		
	IPv6		
RFC 3956	Embedding the Rendezvous Point (RP)		
	address in an IPv6 multicast address		
RFC 3973	PIM Dense Mode (DM)		
RFC 4541	IGMP and MLD snooping switches		
RFC 4601	Protocol Independent Multicast - Sparse		
	Mode (PIM-SM): protocol specification		
	(revised)		
RFC 4604	Using IGMPv3 and MLDv2 for source-		
	specific multicast		
RFC 4607	Source-specific multicast for IP		
	ortest Path First (OSPF)		
OSPF link-loo	0 0		
OSPF MD5 authentication			

OSPF MD5 authentication		
Out-of-band	LSDB resync	
RFC 1245	OSPF protocol analysis	
RFC 1246	Experience with the OSPF protocol	
RFC 1370	Applicability statement for OSPF	
RFC 1765	OSPF database overflow	
RFC 2328	OSPFv2	
RFC 2370	OSPF opaque LSA option	
RFC 2740	OSPFv3 for IPv6	
RFC 3101	OSPF Not-So-Stubby Area (NSSA) option	
RFC 3509	Alternative implementations of OSPF area	
	border routers	
RFC 3623	Graceful OSPF restart	
RFC 3630	Traffic engineering extensions to OSPF	

x530L Series | Stackable Intelligent Layer-3 Switches

RFC 4552	Authentication/confidentiality for OSPFv3		
RFC 5329	Traffic engineering extensions to OSPFv3		
RFC 5340	OSPFv3 for IPv6 (partial support)		
Quality of Service (QoS) IEEE 802.1p Priority tagging			

1LLL 002.1p	i nonty tagging
RFC 2211	Specification of the controlled-load network
	element service
RFC 2474	DiffServ precedence for eight queues/port
RFC 2475	DiffServ architecture
RFC 2597	DiffServ Assured Forwarding (AF)
RFC 2697	A single-rate three-color marker
RFC 2698	A two-rate three-color marker
RFC 3246	DiffServ Expedited Forwarding (EF)

Resiliency Features

ITU-T G.8023 / Y.1344 Ethernet Ring Protection		
Switching (ERPS)		
IEEE 802.1ag CFM Continuity Check Protocol (CCP)		
IEEE 802.1AXLink aggregation (static and LACP)		
IEEE 802.1D MAC bridges		
IEEE 802.1s Multiple Spanning Tree Protocol (MSTP)		
IEEE 802.1w Rapid Spanning Tree Protocol (RSTP)		
IEEE 802.3adStatic and dynamic link aggregation		
RFC 5798 Virtual Router Redundancy Protocol version 3		
(VRRPv3) for IPv4 and IPv6		

Routing Information Protocol (RIP)

RF	C 1058	Routing Information Protocol (RIP)
RF	C 2080	RIPng for IPv6
RF	C 2081	RIPng protocol applicability statement
RF	C 2082	RIP-2 MD5 authentication
RF	C 2453	RIPv2

Security Features

SSH remote login			
SSLv2 and SSLv3			
TACACS+ Ac	TACACS+ Accounting, Authentication and Authorization		
	(AAA)		
IEEE 802.1X	Authentication protocols (TLS, TTLS, PEAP		
	and MD5)		
IEEE 802.1X	Multi-supplicant authentication		
IEEE 802.1X			
RFC 2560	X.509 Online Certificate Status Protocol		
	(OCSP)		
RFC 2818	HTTP over TLS ("HTTPS")		
RFC 2865	RADIUS authentication		
RFC 2866	RADIUS accounting		
RFC 2868	RADIUS attributes for tunnel protocol support		
RFC 2986	PKCS #10: certification request syntax		
	specification v1.7		
RFC 3546	Transport Layer Security (TLS) extensions		
RFC 3579	RADIUS support for Extensible Authentication		
DE0.0500	Protocol (EAP)		
RFC 3580	IEEE 802.1x RADIUS usage guidelines		
RFC 3748	PPP Extensible Authentication Protocol (EAP)		
RFC 4251 RFC 4252	Secure Shell (SSHv2) protocol architecture		
RFC 4252 RFC 4253	Secure Shell (SSHv2) authentication protocol Secure Shell (SSHv2) transport layer protocol		
RFC 4253 RFC 4254	Secure Shell (SSHv2) connection protocol		
RFC 5246	Transport Layer Security (TLS) v1.2		
RFC 5280	X.509 certificate and Certificate Revocation		
11 0 3200	List (CRL) profile		
RFC 5425	Transport Layer Security (TLS) transport		
111 0 0 420	mapping for Syslog		
RFC 5656	Elliptic curve algorithm integration for SSH		
RFC 6125	Domain-based application service identity		
11 0 0 120	within PKI using X.509 certificates with TLS		
RFC 6614	Transport Layer Security (TLS) encryption for		
	RADIUS		
RFC 6668	SHA-2 data integrity verification for SSH		
	• •		
Services	6		
RFC 854	Telnet protocol specification		
DE0 055			

Telnet option specifications

Telnet terminal-type option

Telnet suppress go ahead option

Trivial File Transfer Protocol (TFTP)

Telnet echo option

RFC 1985	SMTP service extension
RFC 2049	MIME
RFC 2131	DHCPv4 (server, relay and client)
RFC 2132	DHCP options and BootP vendor extensions
RFC 2616	Hypertext Transfer Protocol - HTTP/1.1
RFC 2821	Simple Mail Transfer Protocol (SMTP)
RFC 2822	Internet message format
RFC 3046	DHCP relay agent information option (DHCP
	option 82)
RFC 3315	DHCPv6 (server, relay and client)
RFC 3633	IPv6 prefix options for DHCPv6
RFC 3646	DNS configuration options for DHCPv6
DEC 2002	Subscriber ID subscribes for DHCD relay

RFC 3993 Subscriber-ID suboption for DHCP relay agent option

RFC 4330	Simple Network Time Protocol (SNTP)
	version 4
RFC 5905	Network Time Protocol (NTP) version 4

VLAN Support

Generic VLAN Registration Protocol (GVRP) IEEE 802.1ad Provider bridges (VLAN stacking, Q-in-Q) IEEE 802.1Q Virtual LAN (VLAN) bridges IEEE 802.1v VLAN classification by protocol and port IEEE 802.3acVLAN tagging

Voice over IP (VoIP) LLDP-MED ANSI/TIA-1057

Voice VLAN

Feature Licenses

NAME	DESCRIPTION	INCLUDES	STACK LICENSING
AT-FL-x530L-01	x530L premium license	 OSPFv2 (256 routes) BGP4 (256 routes) PIMv4-SM, DM and SSM v4 VLAN double tagging (Q-in-Q) RIPng (256 routes) OSPFv3 (256 routes) MLDv1/v2 PIM-SMv6/SSMv6 RADIUS-Full UDLD 	One license per stack member
AT-FL-x530-AM20-1YR	AMF Master license	AMF Master 20 nodes for 1 year	One license per stack
AT-FL-x530-AM20-5YR	AMF Master license	AMF Master 20 nodes for 5 years	One license per stack
AT-FL-x530L-8032	ITU-T G.8032 license	G.8032 ring protectionEthernet CFM	 One license per stack member
AT-FL-x530L-CPOE	Continuous PoE license	 Continuous PoE power 	 One license per stack member
AT-FL-x53L-MSTK	Mixed Stacking license	 Stack x530L with x530 Series switches 	 One license per stack member
AT-FL-x530L-0F13-1YR	OpenFlow license	 OpenFlow v1.3 (1250 entries) for 1 year 	 Not supported on a stack
AT-FL-x530L-0F13-5YR	OpenFlow license	 OpenFlow v1.3 (1250 entries) for 5 years 	 Not supported on a stack

Ordering Information



Switches

19 inch rack-mount brackets included

AT-x530L-28GTX-xx 24-port 10/100/1000T stackable switch with 4 SFP+ ports and 2 fixed power supplies

AT-x530L-28GPX-xx 24-port 10/100/1000T PoE+ stackable switch with 4 SFP+ ports and 2 fixed power supplies

AT-x530L-52GTX-xx 48-port 10/100/1000T stackable switch with 4

SFP+ ports and 2 fixed power supplies

AT-x530L-52GPX-xx

48-port 10/100/1000T PoE+ stackable switch with 4 SFP+ ports and 2 fixed power supplies

Where xx = 10 for US power cord 20 for no power cord 30 for UK power cord 40 for Australian power cord 50 for European power cord

RFC 855

RFC 857

RFC 858

RFC 1091

RFC 1350

x530L Series | Stackable Intelligent Layer-3 Switches

10G SFP+ Modules

AT-SP10SR 10GSR 850 nm short-haul, 300 m with MMF

AT-SP10SR/I 10GSR 850 nm short-haul, 300 m with MMF industrial temperature

AT-SP10LRM 10GLRM 1310 nm short-haul, 220 m with MMF

AT-SP10LR 10GLR 1310 nm medium-haul, 10 km with SMF AT-SP10LR/I

10GLR 1310 nm medium-haul, 10 km with SMF industrial temperature

AT-SP10LR20/I 10GER 1310 nm long-haul, 20 km with SMF industrial temperature

AT-SP10ER40/I 10GER 1550 nm long-haul, 40 km with SMF industrial temperature

AT-SP10ZR80/I 10GER 1550 nm long-haul, 80 km with SMF industrial temperature

AT-SP10T^{1, 2} 10GBase-T 20 m copper

AT-SP10BD10/I-12 10G Bi-Di, 1270 nm TX/1330 nm RX, 10km, industrial temperature, TAA³ AT-SP10BD10/I-13 10G Bi-Di, 1330 nm TX/1270 nm RX, 10km, industrial temperature, TAA³

AT-SP10BD20-12 10G Bi-Di, 1270 nm TX/1330 nm RX, 20km, TAA³

AT-SP10BD20-13 10G Bi-Di, 1330 nm TX/1270 nm RX, 20km, TAA³

AT-SP10BD40/I-12 10G Bi-Di, 1270 nm TX/1330 nm RX, 40km, industrial temperature, TAA³

AT-SP10BD40/I-13 10G Bi-Di, 1330 nm TX/1270 nm RX, 40km, industrial temperature, TAA³

AT-SP10TW1 1 meter SFP+ direct attach cable

AT-SP10TW3 3 meter SFP+ direct attach cable

1000Mbps SFP Modules

AT-SPSX 1000SX GbE multi-mode 850 nm fiber up to 550 m

AT-SPSX/I 1000SX GbE multi-mode 850 nm fiber up to 550 m industrial temperature

AT-SPEX 1000X GbE multi-mode 1310 nm fiber up to 2 km AT-SPLX10 1000LX GbE single-mode 1310 nm fiber up to 10 km

AT-SPLX10/I 1000LX GbE single-mode 1310 nm fiber up to 10 km, industrial temperature

AT-SPBD10-13 1000LX (LC) GbE Bi-Di (1310 nm Tx, 1490 nm Rx) fiber up to 10 km

AT-SPBD10-14 1000LX (LC) GbE Bi-Di (1490 nm Tx, 1310 nm Rx) fiber up to 10 km

AT-SPBD40-13/I

1000LX (LC) GbE single-mode Bi-Di (1310 nm Tx, 1490 nm Rx) fiber up to 40 km, industrial temperature

AT-SPBD40-14/I

1000LX (LC) GbE single-mode Bi-Di (1490 nm Tx, 1310 nm Rx) fiber up to 40 km, industrial temperature

AT-SPLX40 1000LX GbE single-mode 1310 nm fiber up to 40 km

¹ Using Cat 6a/7 cabling ² Up to 100 m running at 1G ³ Trade Act Agreement Compliant

