FUJITSU

Data Sheet FUJITSU Server PRIMERGY RX1330 M4 Rack Server

Small in size and low in cost - rich in optional features

FUJITSU Server PRIMERGY will give you the servers you need to power any workload and changing business requirements. As business processes expand so does the need for applications. Each has its own resource footprint, so you need a way to optimize your computing to better serve your users. PRIMERGY systems will help you match your computing capabilities to your business priorities with our complete portfolio of expandable PRIMERGY tower servers for remote and branch offices, versatile rack-mount servers as well as hyper-converged multi-node servers. They convince by business proven quality with a wide range of innovations, highest efficiency cutting operational cost and complexity, provide more agility in daily operations, and integrate seamlessly to let help you concentrate on core business functions.

FUJITSU Server PRIMERGY RX rack systems are versatile rack-optimized servers providing best-inclass performance and energy efficiency, and thus form the "standard" in each data center. PRIMERGY RX servers already deliver 25 years of development and production know-how resulting in extremely low failure rates below market average, and lead to continuous operations and outstanding hardware availability.

PRIMERGY RX1330 M4

The FUJITSU Server PRIMERGY RX1330 M4 is a highly reliable and energy-efficient singlesocket rack server designed to deliver optimal performance and value in a compact 1U. Equipped with the right compute and memory for efficient utilization of resources, it is best suited for small and medium businesses providing a cost-efficient foundation for wide range of workloads like file, web hosting, infrastructure, communication, collaboration, and virtualization. The PRIMERGY

RX1330 M4 refresh gets a performance boost with latest Intel® Xeon® E-2200 processors supporting up to 8 cores and higher memory capacity of 128GB DDR4 memory at speed up to 2,666 MT/s. It also provides versatile storage options with the advantage of high-speed, low latency 4x2.5-inch NVMe PCIe SSDs. 2x M.2 devices and Dual microSD are provided for efficient boot requirements. The FUJITSU Server PRIMERGY RX1330 M4 provides many features to guarantee high reliability and availability, such as the optional Fujitsu Battery Backup Unit, hot-plug redundant fans, hot-plug redundant power supplies, and modular RAID controllers. By delivering high energy efficient PSUs and operation in higher ambient temperature driven by optional Cool-safe® Advanced Thermal Design, the PRIMERGY RX1330 M4 contributes to very low operational costs. It provides a simple design for easy serviceability and comes along with the latest integrated Remote Management Controller (iRMC S5) to simplify server management. ISM Essential which is available free of charge provides essential server management functions. Whether it is used for a start-up or expanding business, the PRIMERGY RX1330 M4 is an ideal choice of entry server for many SMBs across all industries.

Note: Check the product configurator for the server compatible components currently available at launch.













vmware

Features & Benefits

Main Features

Benefits

Performance boost and improved scalability

Wide choice of latest Intel® Xeon® E-2200/E-2100 processor family for servers with upto 8 cores, as well as affordable Intel® Core i3 or Pentium or Intel® Celeron® processors. Supports higher memory capacity of up to 128 GB with up to four 32 GB DDR4 @ 2,666 MT/s, high-speed storage and a wide range of networking technologies.

Improved Scalability by design

It provides great storage options expandable up to 10x2.5-inch or 4x3.5-inch disk drives, with an advantage of 4x2.5-inch NVMe PCle SSDs, 2x M.2 modules (1x SATA; 1x NVMe/SATA) and Dual microSD, USB Gen 3.1 Gen 2 for external connectivity. It also provides 3 x PCle Gen 3 slots, 2x1 Gbit Onboard LAN with advanced 10GbE/25GbE high-speed networking options.

Enterprise-class reliability and operational efficiency

It offers rock-solid reliability with Optional Fujitsu Battery Backup Unit, hot plug redundant fans and modular RAID controllers with up to 8GB cache. Highly efficient 450W (94% efficiency) hot plug power supplies and Fujitsu's Cool-safe® Advanced Thermal Design supports higher ambient temperatures up to 45 degrees in the data center.

Simplifies management and enhances security

Embedded with iRMC S5 for wide remote management functions. In addition FUJITSU Software Infrastructure Manager (ISM) provides converged management across multiple data centers. The new ISM Essential license, available free-of-charge provides essential server management and converged monitoring functions.

- Deliver significant performance gain with latest generation processors, a higher number of cores and larger memory. Accelerate performance for virtualization workloads and wide range of SMB workloads including media streaming, caching, web hosting.
- It also improves storage efficiency by providing high-speed, low latency storage, ideal for workloads that need higher I/O performance. Higher data transfer with the latest USB technology, fast boot devices for efficient installation of operating systems or mirrored boot for VMWare ESXi is also provided. A broad range of networking options and PCIe slots provide flexible expansion options for future scalability.
- Maximize uptime and save energy cost with high energy efficient redundant components. FJBU keeps the server running during short blackouts or voltage fluctuations and enables a graceful shutdown. Higher ambient temperatures reduce system cooling costs.
- Fujitsu offers comprehensive infrastructure management and server management solutions which is key to efficient data center operations. iRMC S5 enhances server administrator productivity and offers a variety of new user-friendly and enhanced security features. ISM helps improve data center efficiency and overall IT Productivity with converged infrastructure management, paving the path to software-defined data center.

Technical details

PRIMERGY RX1330 M4 Base unit	RX1330 M4 LFF	RX1330 M4 LFF	RX1330 M4 SFF	RX1330 M4 SFF	RX1330 M4 SFF	RX1330 M4 SFF
Base unit	KA 1330 M4 LFF	KAT330 M4 LFF	KA1330 M4 SFF	KA I 330 M4 SFF	KX 1330 MI4 SFF	10xSFF
Housing types	Rack					
Storage drive architecture	3.5-inch SAS/SATA	3.5-inch SAS/SATA	2.5-inch SAS/SATA	2.5-inch SAS/SATA	2.5-inch SAS/SATA/ PCIe	2.5-inch SAS/SATA
Power supply	Standard	Hot-plug	Standard	Hot-plug	Hot-plug	Hot-plug
Product Type	Mono Socket Rack	Server				
Mainboard						
Mainboard type	D3675					
Chipset	Intel [®] C246					
Processor quantity and type		1 x Intel® Xeon® E-2200 processor family / Intel® Xeon® E-2100 processor family / Intel® Celeron® processor / Intel® Core™ i3 processor / Intel® Pentium® processor				
Processor	Intel® Xeon® proce	essor E-2288G (8C/1	6T, 3.70 GHz, up to 4	4.7 GHz, 2,666 MHz)		
	·	essor E-2286G (6C/1				
	·	essor E-2278G (8C/1				
	· · ·	essor E-2276G (6C/1	•			
		essor E-2274G (4C/4				
	•	essor E-2246G (6C/1	•			
	I	essor E-2244G (4C/8	· · ·			
	·	essor E-2236 (6C/12	· · · ·			
		essor E-2234 (4C/8T,				
		essor E-2226G (6C/6				
		essor E-2224G (4C/4 ⁻	•			
	I	essor E-2224 (4C/4T,	· •	· · ·		
	I	essor E-2186G (6C/1) essor E-2176G (6C/1)				
	· · · ·	essor E-21760 (6C/1. essor E-2174G (4C/8	•			
	· · · · ·	essor E-2146G (6C/1.				
	·	essor E-2146G (6C/1)				
	•	essor E-2136 (6C/12	•			
	I	essor E-2134 (4C/8T,	· · · ·			
	·	essor E-2126G (6C/6	· •			
		essor E-2124G (4C/4	•			
	· · ·	essor E-2124 (4C/4T,	•			
	· · · ·	rocessor G5420 (2C/	•			
		rocessor G5400 (2C/				
		00 processor (4C/4T,		•		
		00 processor (4C/4T,				
		cessor G4930 (2C/2				
	I	ocessor G4900 (2C/2				
Memory slots	4 (2 banks with 2	4 (2 banks with 2 DIMMs each)				
Memory slot type	DIMM (DDR4)					
Memory capacity (min max.)	4 GB - 128 GB					
Memory protection	ECC					
Memory notes	Dual channel supp per channel has to		el performance, a m	inimum of 2 memor	y modules have to b	e ordered. Capacit

Manage and			11.0		
Memory options	4 GB (1 module(s) 4 GB) DDR4, unbuffered, ECC, 2,666 MT/s, PC4-2666, DIMM, 1Rx8				
	8 GB (1 module(s) 8 GB) DDR4, unbuffered, ECC, 2,666 MT/s, PC4-2666, DIMM, 1Rx8 16 GB (1 module(s) 16 GB) DDR4, unbuffered, ECC, 2,666 MT/s, PC4-2666, DIMM, 2Rx8				
		nbuffered, ECC, 2,666 MT/s, PC4-2666, I			
		IIDUIIEIEU, ELL, 2,000 MII/S, PL4-2000, L	ΠΜΙΜΙ, ΖΚΧΟ		
Interfaces					
USB 2.0 ports	2 Rear: 2x USB 2.0 for all base units. Front (only 10x 2.5" HDD): 1x USB 2.0				
USB 3.0 ports	4 Rear: 2x 3.1 Gen2 for all base units, Front (except 10x 2.5" HDD): 2x USB 3.1 Gen1				
Graphics (15-pin)	1 x VGA (15-pin) / optional 1 x front VGA (not for 10x 2.5" HDD base unit)				
Serial connection	1 x serial RS-232-C Optional				
LAN / Ethernet (RJ-45)	2 x 1 Gbit/s Ethernet				
Management LAN (RJ45)	Management LAN traffic can be swi 1 x dedicated management LAN po	tched to shared onboard Gbit LAN port rt for iRMC S5(10/100/1000 Mbit/s)			
Onboard or integrated Controller					
RAID controller	Integrated RAID 0/1 or RAID 5/6 con All hardware storage controller optic	troller (option) ons are described under Components			
SATA Controller	Intel® C246, 1 port used for accessib 4 port for internal SATA HDD/SSD wi	ole drive or SATA DOM th RAID 0, 1, 10 for Windows and Linux;			
LAN Controller	Intel® i210 onboard 2 x 10/100/1000 Mbit/s Ethernet (T0 iSCSI, PXE-Boot and WoL are suppor				
Remote management controller	Integrated Remote Management Co	ntroller (iRMC S5, 512 MB attached mer	nory incl. graphics controller)		
Trusted Platform Module (TPM)	Infineon / TPM 1.2 or TPM 2.0 modu	le; TCG compliant (option)			
Onboard or integrated Controller (B	ase unit specific)				
RAID controller	4 port SATA with RAID 0/1/10 for HD	Ds			
SATA Controller	4-port SATA 6Gb with RAID 0, 1, 10				
SATA controller type notes	for hot-plug SATA hard disks				
Slots					
PCI-Express 3.0 x4	1 x Low profile				
PCI-Express 3.0 x8	2 x Low profile Length 175mm; PCIe slot#1 supports Modular RAID functions				
Slot Notes	Optional support of 1x full height P	Cle Gen3 x8 card, instead of 1x PCle Gen	2 x4 and 1x PCIe Gen3 x8		
PCI-Express 3.0 x4					
PCI-Express 3.0 x4 (mech. x8)	1 x				
PCI-Express 3.0 x8	2 x				
Drive bays					
Storage drive bays	4/8 x 2.5-inch hot-plug SATA/SAS (Up to 4x NVMe PCIe SSD supported) or 4x 3.5-inch hot-plug or 10 x 2.5-inch hot- plug SATA/SAS				
Accessible drive bays	1 x 5.25/0.4-inch for CD-RW/DVD				
Notes accessible drives	Following limitations applies to 10x 2.5-inch HDD base unit: No CD-RW/DVD, 1x USB 2.0 at the front, no front VGA				
Drive bays (Base unit specific)					
Storage drive bays	Max. 4x 3.5-inch	Max. 8x 2.5-inch	Max. 10x 2.5-inch		
Accessible drive bays	1 x 5.25/0.4-inch for CD-RW/DVD	1 x 5.25/0.4-inch for CD-RW/DVD	Accessible drive bays are not available in case of max. storage drive configuration		
Fan Configuration					
Number of fans	5				
Fan notes	Hot Plug Fans - 4 fans in combination with standard power supply or 5 fans in combination with hot-plug PSU base unit for 4+1 redundancy.				
Operating panel					
Operating buttons	On/off switch				
	NMI button Reset button				

Operating panel		
Status LEDs	System status (orange)	
	Identification (blue)	
	Hard disks access (green)	
	Power (green)	
	At system rear side: System status (orange)	
	Identification (blue)	
	LAN connection (green)	
	LAN speed (green / yellow)	
BIOS		
BIOS features	ROM based setup utility	
	Recovery BIOS	
	BIOS settings save and restore	
	Local BIOS update from USB device Online update tools for main Linux versions	
	Local and remote update via ServerView Update Manager	
	Remote PXE boot support	
	Remote iSCSI boot support	
Operating Systems and Virtualization S	oftware	
Certified or supported operating	Windows Server 2019 Datacenter	
systems and virtualization software	Windows Server 2019 Standard	
	Windows Server 2019 Essentials	
	Windows Server Datacenter, version 1809	
	Windows Server Standard, version 1809	
	Hyper-V Server 2016	
	Windows Server 2016 Datacenter	
	Windows Server 2016 Standard	
	Windows Server 2016 Essentials	
	Windows Storage Server 2016 Standard	
	Windows Server Datacenter, version 1709	
	VMware vSphere™ 6.7	
	VMware vSphere™ 6.5	
	SUSE® Linux Enterprise Server 12	
	Red Hat® Enterprise Linux 8	
	Red Hat® Enterprise Linux 7	
Operating system release link	http://docs.ts.fujitsu.com/dl.aspx?id=d4ebd846-aa0c-478b-8f58-4cfbf3230473	
Operating system notes	RHEL 7.5 and SLES 15 GA are not supported for the new CPUs including the Intel® Xeon® E-2200 product family. VMware ESX hints:	
	- SATA RAID is not supported	
	- Storing virtual machines locally requires a SAS RAID Controller	
	Support of other Linux derivatives on demand	
	Red Hat [®] certification starting with version 5.8 / 6.4.	
	Hardware requirements of Software Defined Storage supported by i.e. Microsoft Storage Spaces or VMWare vSAN please see Systemarchitect or paper configurator or datasheet of PSAS CP400i.	
nfrastructure and Server Management		
DC Infrastructure Management	Infrastructure Manager (ISM)	
	Essential	
	Advanced	
Server Management	Infrastructure Manager (ISM)	
-	Essential	
	Advanced	
	ServerView Suite	
Management notes	For further information regarding ISM and ServerView Suite see dedicated data sheets.	
Manageability link	http://docs.ts.fujitsu.com/dl.aspx?id=9e92297a-16fb-4c69-8559-e38e7b42fee6	

Dimensions / Weight		
Rack (W x D x H)	482.6 mm (Bezel) / 435.4 mm (Body) x 572 x 42.8 mm	
Height Unit Rack	10	
Mounting Cable depth rack	200 mm cable depth	
Weight	up to 13 kg	
Weight notes	Actual weight may vary depending on configuration	
Rack integration kit	Rack integration kit as option	
Environment		
Operating ambient temperature	5 - 45 °C (41 - 113 °F)	
Operating temperature note	Cool-safe® Advanced Thermal Design (above 35 °C or below 10 °C) depending on configuration. For detailed information see relevant system configurator.	
Operating relative humidity	10 - 85 % (non condensing)	
) perating environment	FTS 04230 – Guideline for Data Center (installation specification)	
perating environment link	http://docs.ts.fujitsu.com/dl.aspx?id=e4813edf-4a27-461a-8184-983092c12dbe	
ound pressure (LpAm)	24 / 52 dB(A) (min / max idle), 26 / 40 db(A) (min / max operating)	
ound power (LWAd; 1B = 10dB)	4.2 / 7 B (min / max idle), 4.2 / 5.8 B (min / max operating)	
loise notes	Noise emissions and operation modes depend on system configuration.	
lectrical values		
Power supply configuration	1x standard power supply or1x hot-plug power supply or 2x hot plug power supplies for redundancy depending or model	
lot-plug power supply redundancy	Optional	
ctive power (max. configuration)	264 W	
pparent power (max. configuration)	267 VA	
eat emission (max. configuration)	950.4 kJ/h (900.8 BTU/h)	
ated current max.	4.5 A (100 V) / 2.0 A (240 V)	
ower supply	300W standard, 92% (Gold efficiency), 100-240V, 50 / 60Hz 450W hot-plug, 94% (Platinum efficiency), 100-240V, 50 / 60Hz	
ower supply notes	Power Safeguard adapts system performance in case the power requirements exceeds supply limits.	
attery backup	Fujitsu Battery Unit 380W, 12V (as option)	
ompliance		
Product	PRIMERGY RX1330 M4	
lodel	PR1330	
ilobal	CB RoHS (Substance limitations in accordance with global RoHS regulations) WEEE (Waste electrical and electronical equipment)	
Germany	CS CS	
urope	CE	
ISA/Canada	CSAc/us ULc/us FCC Class A	
apan	VCCI:V3 Class A + JIS 61000-3-2	
ussia	GOST	
outh Korea	KC	
hina		
ustralia/New Zealand	C-Tick	
aiwan	BSMI	
ompliance link	https://sp.ts.fujitsu.com/sites/certificates	
Compliance notes	There is general compliance with the safety requirements of all European countries and North America. National approvals required in order to satisfy statutory regulations or for other reasons can be applied for on request. * Warning: This is a class A product. In a domestic environment this product may cause radio interference in which case the us may be required to take adequate measures.	

Components

Optical drives	Blu-ray Disc™ Triple Writer, (6x BD-RW, 8x DVD, 24x CD), ultraslim, SATA I		
	DVD Super Multi ultra slim , (8x DVD; 24x CD), ultraslim, SATA I		
Hard disk drives	HDD SATA, 6 Gb/s, 500 GB, 7,200 rpm, 512e, hot-plug, 3.5-inch, economic		
	HDD SATA, 6 Gb/s, 14 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical		
	HDD SATA, 6 Gb/s, 12 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical		
	HDD SATA, 6 Gb/s, 8 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical		
	HDD SATA, 6 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical		
	HDD SATA, 6 Gb/s, 4 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical		
	HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical		
	HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical		
	HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical		
	HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, economic		
	HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical		
Hard disk drives	HDD SAS, 12 Gb/s, 900 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise		
	HDD SAS, 12 Gb/s, 900 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise		
	HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise		
	HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise		
	HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise		
	HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise		
	HDD SAS, 12 Gb/s, 600 GB , 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED		
	HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise		
	HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise		
	HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise, SED		
	HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise		
	HDD SAS, 12 Gb/s, 14 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED		
	HDD SAS, 12 Gb/s, 14 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical		
	HDD SAS, 12 Gb/s, 12 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED		
	HDD SAS, 12 Gb/s, 12 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical		
	HDD SAS, 12 Gb/s, 10 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED		
	HDD SAS, 12 Gb/s, 8 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical		
	HDD SAS, 12 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, enterprise, SED		
	HDD SAS, 12 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical		
	HDD SAS, 12 Gb/s, 4 TB, 7,200 rpm, hot-plug, 3.5-inch, business critical		
	HDD SAS, 12 Gb/s, 2.4 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise, SED		
	HDD SAS, 12 Gb/s, 2.4 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise		
	HDD SAS, 12 Gb/s, 2 TB, 7,200 rpm, hot-plug, 3.5-inch, business critical		
	HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise, SED		
	HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot plug, 2.5 inch, enterprise		
	HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, hot-plug, 2.5-inch, enterprise		
	HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise		
	HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512e, h0c-plug, 2.5-inch, enterprise HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise		
	HDD SAS, 12 Gb/s, 1 TB, 7,200 rpm, hot-plug, 3.5-inch, business critical		

Solid-State-Drive	SSD SATA, 6 Gb/s, 960 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 960 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)		
	SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)		
	SSD SATA, 6 Gb/s, 480 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 480 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)		
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)		
	SSD SATA, 6 Gb/s, 240 GB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1.4 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 240 GB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1.4 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)		
	SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3.6 DWPD (Drive Writes Per Day for 5 years)		
	SSD SATA, 6 Gb/s, 7.68 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.5 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 7.68 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.5 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 3.84 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 1.0 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 3.84 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 1.0 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 3.84 TB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)		
	SSD SATA, 6 Gb/s, 3.84 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)		
	SSD SATA, 6 Gb/s, 1.92 TB, Read-Intensive, hot-plug, 3.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years)		
	SSD SATA, 6 Gb/s, 1.92 TB, Read-Intensive, hot-plug, 2.5-inch, enterprise, 0.9 DWPD (Drive Writes Per Day for 5 years		
	SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)		
	SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)		
	SSD M.2 SATA, 6 Gb/s, 480 GB, non hot plug, enterprise, 1.4 DWPD (Drive Writes Per Day for 5 years)		
	SSD M.2 SATA, 6 Gb/s, 240 GB, non hot plug, enterprise, for VMware		
	SSD M.2 SATA, 6 Gb/s, 240 GB, non hot plug, enterprise, 1.4 DWPD (Drive Writes Per Day for 5 years)		
PCIe SSD & SATA DOM SSD	PCle-SSD SFF, 500 GB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 0.7 DWPD (Drive Writes Per Day for 5 years)		
	PCIe-SSD SFF, 4 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 3.0 DWPD (Drive Writes Per Day for 5 years)		
	PCIe-SSD SFF, 4 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 0.6 DWPD (Drive Writes Per Day for 5 years)		
	PCIe-SSD SFF, 2 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 3.0 DWPD (Drive Writes Per Day for 5 years)		
	PCIe-SSD SFF, 1 TB, Read-Intensive, hot-plug, 2.5-inch, Flash drive, 3.0 DWPD (Drive Writes Per Day for 5 years)		
	Dual microSD 64GB Enterprise		
SCSI / SAS Controller	LSI PSAS CP400e LP SAS Ctrl. 12 Gbit/s 8 ports ext. PCle 3.0 x8		
	Fujitsu PSAS CP400i SAS Ctrl. 12 Gbit/s 8 ports int. PCIe 3.0 x8		
RAID Controller	Fujitsu PRAID EP580i LP, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, NVMe-PCIe 8 Gbit/s, 8 Gbit/s 16 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 8 GB, Optional FBU based on LSI SAS3516		
	Fujitsu PRAID EP540i LP, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, NVMe-PCIe 8 Gbit/s, 8 Gbit/s 16 ports int. RAID level: 0, 1 10, 5, 50, 6, 60, 4 GB, Optional FBU based on LSI SAS3516		
	Fujitsu PRAID EP520i LP, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, NVMe-PCIe 8 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50 6, 60, 2 GB, Optional FBU based on LSI SAS3516		
	Fujitsu PRAID EP420i, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3108		
	Fujitsu PRAID EP420i for SafeStore, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3108		
	Fujitsu PRAID EP400i, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 1 GB, Optional FBU based on LSI SAS3108		
	Fujitsu PRAID CP400i, RAID Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 1E, 10, 5, 50, No FBU support		

Fibre Channel controller	Fibre Channel Host Bus Adapter 1 x 32 Gbit/s Cavium QLE2740 MMF LC-style		
	Fibre Channel Host Bus Adapter 2 x 32 Gbit/s Cavium QLE2742 MMF LC-style		
	Fibre Channel Host Bus Adapter 1 x 32 Gbit/s Emulex LPe32000-M6-F MMF LC-style		
	Fibre Channel Host Bus Adapter 2 x 32 Gbit/s Emulex LPe32002-M6-F MMF LC-style		
	Fibre Channel Host Bus Adapter 1 x 16 Gbit/s Qlogic QLE2690 LC-style		
	Fibre Channel Host Bus Adapter 2 x 16 Gbit/s Qlogic QLE2692 LC-style		
	Fibre Channel Host Bus Adapter 1 x 16 Gbit/s Emulex LPe31000-M6-F MMF LC-style		
	Fibre Channel Host Bus Adapter 2 x 16 Gbit/s Emulex LPe31002-M6-F MMF LC-style		
Communication, Network	Converged Network Adapter 2 x 10 Gbit/s / 25 Gbit/s PCIe 3.0 x8 SFP28 (Cavium)		
	Ethernet Ctrl. 2 x 10 Gbit/s ; 1 Gbit/s PCIe 3.0 x8 RJ45 (Cavium)		
	Ethernet Ctrl. 2 x 10 Gbit/s ; 1 Gbit/s PCIe 3.0 x8 RJ45 (Intel®)		
	Ethernet Ctrl. 2 x 10 Gbit/s ; 1 Gbit/s PCIe 3.0 x8 SFP+ (Cavium)		
	Ethernet Ctrl. 2 x 10 Gbit/s / 25 Gbit/s PCIe 3.0 x8 SFP28 (Cavium)		
	Ethernet Ctrl. 2 x 10 Gbit/s / 25 Gbit/s PCIe 3.0 x8 SFP28 (Intel®) Ethernet Ctrl. 2 x 10 Gbit/s / 25 Gbit/s PCIe 3.0 x8 SFP28 (Mellanox) Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 SFP+ (Intel®) Ethernet Ctrl. 2 x 1 Gbit/s PCIe 2.1 x4 RJ45 (Intel®) Ethernet Ctrl. 4 x 10 Gbit/s ; 1 Gbit/s PCIe 3.0 x8 RJ45 (Cavium) Ethernet Ctrl. 4 x 10 Gbit/s ; 1 Gbit/s PCIe 3.0 x8 RJ45 (Intel®)		
	Ethernet Ctrl. 4 x 1 Gbit/s PCIe 2.1 x4 RJ45 (Intel®)		
Graphics	NVIDIA® Quadro® P400 , 2 GB, PCIe x16, 3 x miniDP		
Rack infrastructure	Rackmount kit full extraction (815mm), tool less mounting, length variable 559-914mm		
	Rackmount kit full extraction (815mm), tool less mounting, length variable 559-914mm		
	Rackmount kit tool less mounting		
	Cable Management 1U for PRIMECENTER- and 3rd-party racks		
Warranty			
Warranty period	1 year		
Warranty type	Onsite warranty		
Warranty Terms & Conditions Product Support Services - the per	www.fujitsu.com/support fect extension		
Support Pack Options	Globally available in major business areas: 9x5, Next Business Day Onsite Response Time 9x5, 4h Onsite Response Time (depending on country) 24x7, 4h Onsite Response Time (depending on country)		
Recommended Service	24x7 Onsite Service with 4h Onsite Response Time		
Service Lifecycle	5 years after end of product life		
Service Weblink	http://www.fujitsu.com/emeia/products/product-support-services/		

More information

Fujitsu products, solutions & services

In addition to FUJITSU Server PRIMERGY RX1330 M4, Fujitsu provides a range of platform solutions. They combine reliable Fujitsu products with the best in services, know-how and worldwide partnerships.

Fujitsu Portfolio

Built on industry standards, Fujitsu offers a full portfolio of IT hardware and software products, services, solutions and cloud offering, ranging from clients to datacenter solutions and includes the broad stack of Business Solutions, as well as the full stack of Cloud offerings. This allows customers to select from alternative sourcing and delivery models to increase their business agility and to improve their IT operation's reliability.

Computing Products

www.fujitsu.com/global/products/computing/

Software

www.fujitsu.com/software/

More information

Learn more about FUJITSU Server PRIMERGY RX1330 M4, please contact your Fujitsu sales representative or Fujitsu Business partner, or visit our website. www.fujitsu.com/primergy

Fujitsu green policy innovation

Fujitsu Green Policy Innovation is our worldwide project for reducing burdens on the environment.

Using our global know-how, we aim to contribute to the creation of a sustainable environment for future generations through IT. Please find further information at http://www. fujitsu.com/global/about/environment



Copyrights

All rights reserved, including intellectual property rights. Designations may be trademarks and/or copyrights of the respective owner, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see http:// www.fujitsu.com/emeia/resources/navigation/ terms-of-use.html

Copyright 2020 FUJITSU LIMITED

Disclaimer

Technical data is subject to modification and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective owner, the use of which by third parties for their own purposes may infringe the rights of such owner.

Contact FUJITSU LIMITED

Website: www.fujitsu.com 2020-04-25 WW-EN All rights reserved, including intellectual property rights. Designations may be trademarks and/or copyrights of the respective owner, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see http://www.fujitsu.com/emeia/resources/navigation/terms-of-use.html Copyright 2020 FUJITSU LIMITED