

AR-SFP-10G-ER-C

Arista® Compatible 10Gb/s SFP+ ER Transceiver

Hot Pluggable, Duplex LC, +3.3V, 1550nm, EML SMF 40km DDM

FEATURES

- Supports 9.95 to 11.3Gb/s bit rates
- Hot-Pluggable
- Duplex LC connector
- 1550nm cooled EML transmitter, PIN photo-detector
- SMF links up to 40km
- 2-wire interface for management specifications compliant with SFF 8472 digital diagnostic monitoring interface
- Power Supply: +3.3V
- Power consumption<1.5W
- Temperature Range: 0~ 70°C
- RoHS compliant

APPLICATIONS

- 10GBASE-ER/EW Ethernet
- SONET OC-192 / SDH
- 10G Fibre channel

DESCRIPTION

ATGBICS® Compatible AR-SFP-10G-ER-C is a very compact 10Gb/s optical transceiver module for serial optical communication applications at 10Gb/s. The AR-SFP-10G-ER converts a 10Gb/s serial electrical data stream to 10Gb/s optical output signal and a 10Gb/s optical input signal to 10Gb/s serial electrical data streams. The high speed 10Gb/s electrical interface is fully compliant with SFI specification.

The high performance 1550nm cooled EML transmitter and high sensitivity PIN receiver provide superior performance for Ethernet applications at up to 40km links.

The SFP+ Module compliant with SFF-8431, SFF-8432 and IEEE 802.3ae 10GBASE-ER. Digital diagnostics functions are available via a 2-wire serial interface, as specified in SFF-8472.

The fully SFP compliant form factor provides hot pluggability, easy optical port upgrades and low EMI emission.



Absolute Maximum Ratings

Parameter	Symbol	Min.	Typical	Max.	Unit
Storage Temperature	Ts	-40		+85	°C
Case Operating Temperature	T _A	0		70	°C
Maximum Supply Voltage	Vcc	-0.5		4	V
Relative Humidity	RH	0		85	%

Electrical Characteristics (T_{OP} = 0 to 70 °C, VCC = 3.135 to 3.465 Volts)

Parameter	Symbol	Min.	Typical	Max.	Unit	Notes
Supply Voltage	Vcc	3.135		3.465	V	
Supply Current	lcc			400	mA	
Power Consumption	Р			1.5	W	
Transmitter Section:	'	,				
Input differential impedance	R _{in}		100		Ω	1
Tx Input Single Ended DC Voltage Tolerance (Ref VeeT)	V	-0.3		4	V	
Differential input voltage swing	Vin,pp	180		700	mV	2
Transmit Disable Voltage	V _D	2		Vcc	V	3
Transmit Enable Voltage	V _{EN}	Vee		Vee+0.8	V	
Receiver Section:	'	,				
Single Ended Output Voltage Tolerance	V	-0.3		4	V	
Rx Output Diff Voltage	Vo	300		850	mV	
Rx Output Rise and Fall Time	Tr/Tf	30			ps	4
LOS Fault	V _{LOS} fault	2		Vcc _{ноsт}	V	5
LOS Normal	V _{LOS} norm	Vee		Vee+0.8	V	5

Notes:

- 1. Connected directly to TX data input pins. AC coupling from pins into laser driver IC.
- 2. Per SFF-8431 Rev 3.0
- 3. Into 100 ohms differential termination.
- 4. 20%~80%
- 5. LOS is an open collector output. Should be pulled up with $4.7k 10k\Omega$ on the host board. Normal operation is logic 0; loss of signal is logic 1. Maximum pull-up voltage is 5.5V.



Optical Parameters ($T_{OP} = 0$ to 70° C, VCC = 3.135 to 3.465 Volts)

Parameter	Symbol	Min.	Typical	Max.	Unit	Notes
Transmitter Section:						
Center Wavelength	λt	1530	1550	1565	nm	
spectral width	$\triangle \lambda$			0.3	nm	
Average Optical Power	Pavg	-1		+4	dBm	1
Optical Power OMA	Poma	-2.1			dBm	
Laser Off Power	Poff			-30	dBm	
Extinction Ratio	ER	6			dB	
Transmitter Dispersion Penalty	TDP			3.0	dB	2
Relative Intensity Noise	Rin			-128	dB/Hz	3
Optical Return Loss Tolerance		20			dB	
Receiver Section:						
Center Wavelength	λr	1260		1600	nm	
Receiver Sensitivity	Sen			-16	dBm	4
Stressed Sensitivity (OMA)	Senst			-14	dBm	4
Los Assert	LOSA	-27		-	dBm	
Los Dessert	LOS _D			-17	dBm	
Los Hysteresis	LOS _H	0.5			dB	
Overload	Sat	0			dBm	5
Receiver Reflectance	Rrx			-26	dB	

Notes:

- 1. Average power figures are informative only, per IEEE802.3ae.
- 2. TWDP figure requires the host board to be SFF-8431compliant. TWDP is calculated using the Matlab code provided in clause 68.6.6.2 of IEEE802.3ae.
- 3. 12dB reflection.
- 4. Conditions of stressed receiver tests per IEEE802.3ae. CSRS testing requires the host board to be SFF-8431 compliant.
- 5. Receiver overload specified in OMA and under the worst comprehensive stressed condition.




Timing Characteristics

Parameter	Symbol	Min.	Typical	Max.	Unit
TX Disable Assert Time	t_off			10	us
TX Disable Negate Time	t_on			1	ms
Time to Initialize Include Reset of TX_FAULT	t_int			300	ms
TX_FAULT from Fault to Assertion	t_fault			100	us
TX Disable Time to Start Reset	t_reset	10			us
Receiver Loss of Signal Assert Time	T _A ,RX_LOS			100	us
Receiver Loss of Signal De-assert Time	T _d ,RX_LOS			100	us
Rate-Select Charge Time	t_ratesel			10	us
Serial ID Clock Time	t_serial-clock			100	kHz

Pin Assignment

Diagram of Host Board Connector Block Pin Numbers and Name





Pin Function Definitions

PIN No	Name	Function	Notes
1	VeeT	Module transmitter ground	1
2	Tx Fault	Module transmitter fault	2
3	Tx Disable	Transmitter Disable; Turns off transmitter laser output	3
4	SDL	2 wire serial interface data input/output (SDA)	
5	SCL	2 wire serial interface clock input (SCL)	
6	MOD-ABS	Module Absent, connect to VeeR or VeeT in the module	2
7	RS0	Rate select0, optionally control SFP+ receiver. When high, input data rate >4.5Gb/s; when low, input data rate <=4.5Gb/s	
8	LOS	Receiver Loss of Signal Indication	4
9	RS1	Rate select0, optionally control SFP+ transmitter. When high, input data rate >4.5Gb/s; when low, input data rate <=4.5Gb/s	
10	VeeR	Module receiver ground	1
11	VeeR	Module receiver ground	1
12	RD-	Receiver inverted data out put	
13	RD+	Receiver non-inverted data out put	
14	VeeR	Module receiver ground	1
15	VccR	Module receiver 3.3V supply	
16	VccT	Module transmitter 3.3V supply	
17	VeeT	Module transmitter ground	1
18	TD+	Transmitter inverted data out put	
19	TD-	Transmitter non-inverted data out put	
20	VeeT	Module transmitter ground	1

Notes:


- 1. The module ground pins shall be isolated from the module case.
- 2. This pin is an open collector/drain output pin and shall be pulled up with 4.7K-10Kohms to Host on
- 3. This pin shall be pulled up with 4.7K-10Kohms to VccT in the module.
- 4. This pin is an open collector/drain output pin and shall be pulled up with 4.7K-10Kohms to Host on the host board.



SFP Module EEPROM Information and Management

The SFP modules implement the 2-wire serial communication protocol as defined in the SFP -8472. The serial ID information of the SFP modules and Digital Diagnostic Monitor parameters can be accessed through the I²C interface at address A0h and A2h. The memory is mapped in Table 1. Detailed ID information (A0h) is listed in Table 2. And the DDM specification at address A2h. For more details of the memory map and byte definitions, please refer to the SFF-8472, "Digital Diagnostic Monitoring Interface for Optical Transceivers". The DDM parameters have been internally calibrated.

Table 1 - Digital Diagnostic Memory Map (Specific Data Field Descriptions)








Table 2 - EEPROM Serial ID Memory Contents (A0h)

Description	Data	Length	Name of	Description and Contents
0 1 Identifier Type of Serial transceiver (03h=SFP) 1 1 Reserved Extended identifier of type serial transceiver (04h) 2 1 Connector Code of optical connector type (07=LC) 3-10 8 Transceiver 10G Base-ER 11 1 Encoding 64B/66B 12 1 BR, Nominal Nominal baud rate, unit of 100Mbps 13-14 2 Reserved (0000h) 15 1 Length(9um) Link length supported for 9/125um fiber, units of 10m 16 1 Length(50um) Link length supported for 50/125um fiber, units of 10m 17 1 Length(62.5um) Link length supported for 62.5/125um fiber, units of 10m 18 1 Length(Copper) Link length supported for copper, units of meters 19 1 Reserved 20-35 16 Vendor Name SFP vendor name: ATGBICS 36 1 Reserved 37-39 3 Vendor OUI SFP transceiver vendor OUI ID 40-55 16			Length	
1 1 Reserved Extended identifier of type serial transceiver (04h) 2 1 Connector Code of optical connector type (07=LC) 3-10 8 Transceiver 10G Base-ER 11 1 Encoding 64B/66B 12 1 BR, Nominal Nominal baud rate, unit of 100Mbps 13-14 2 Reserved (0000h) 15 1 Length(9um) Link length supported for 9/125um fiber, units of 100m 16 1 Length(50um) Link length supported for 50/125um fiber, units of 10m 17 1 Length(62.5um) Link length supported for 62.5/125um fiber, units of 10m 18 1 Length(Copper) Link length supported for 62.5/125um fiber, units of 10m 18 1 Length(Copper) Link length supported for 62.5/125um fiber, units of 10m 18 1 Length(62.5um) Link length supported for 62.5/125um fiber, units of 10m 18 1 Length(62.5um) Link length supported for 62.5/125um fiber, units of 10m 20-35 16 Vendor Name SFP vendor name: ATGBICS			Identifier	Type of Serial transceiver (03h=SEP)
2 1 Connector Code of optical connector type (07=LC) 3-10 8 Transceiver 10G Base-ER 11 1 Encoding 64B/66B 12 1 BR, Nominal Nominal baud rate, unit of 100Mbps 13-14 2 Reserved (0000h) 15 1 Length(9um) Link length supported for 9/125um fiber, units of 10m 16 1 Length(50um) Link length supported for 50/125um fiber, units of 10m 17 1 Length(62.5um) Link length supported for 62.5/125um fiber, units of 10m 18 1 Length(Copper) Link length supported for copper, units of meters 19 1 Reserved 20-35 16 Vendor Name SFP vendor name: ATGBICS 36 1 Reserved 37-39 3 Vendor PN Part Number: "AR-SFP-10G-ER-C" (ASCII) 40-55 16 Vendor PN Part Number: "AR-SFP-10G-ER-C" (ASCII) 56-59 4 Vendor rev Revision level for part number 60-62 3 <				
3-10 8 Transceiver 10G Base-ER 11 1 Encoding 64B/66B 12 1 BR, Nominal Nominal baud rate, unit of 100Mbps 13-14 2 Reserved (0000h) 15 1 Length(9um) Link length supported for 9/125um fiber, units of 100m 16 1 Length(50um) Link length supported for 50/125um fiber, units of 10m 17 1 Length(62.5um) Link length supported for 62.5/125um fiber, units of 10m 18 1 Length(Copper) Link length supported for copper, units of meters 19 1 Reserved 20-35 16 Vendor Name SFP vendor name: ATGBICS 36 1 Reserved 37-39 3 Vendor PN Part Number: "AR-SFP-10G-ER-C" (ASCII) 40-55 16 Vendor PN Part Number: "AR-SFP-10G-ER-C" (ASCII) 56-59 4 Vendor rev Revision level for part number 60-62 3 Reserved 63 1 CCID Least significant byte of sum				, ,
11 1 Encoding 64B/66B 12 1 BR, Nominal Nominal baud rate, unit of 100Mbps 13-14 2 Reserved (0000h) 15 1 Length(9um) Link length supported for 9/125um fiber, units of 100m 16 1 Length(50um) Link length supported for 50/125um fiber, units of 10m 17 1 Length(Copper) Link length supported for 62.5/125um fiber, units of 10m 18 1 Length(Copper) Link length supported for copper, units of meters 19 1 Reserved 20-35 16 Vendor Name SFP vendor name: ATGBICS 36 1 Reserved 37-39 3 Vendor OUI SFP transceiver vendor OUI ID 40-55 16 Vendor PN Part Number: "AR-SFP-10G-ER-C" (ASCII) 56-59 4 Vendor rev Revision level for part number 60-62 3 Reserved 63 1 CCID Least significant byte of sum of data in address 0-62 Extended ID Fields <td< th=""><th></th><th>-</th><th></th><th>i i i i i i i i i i i i i i i i i i i</th></td<>		-		i i i i i i i i i i i i i i i i i i i
12 1 BR, Nominal Nominal baud rate, unit of 100Mbps 13-14 2 Reserved (0000h) 15 1 Length(9um) Link length supported for 9/125um fiber, units of 100m 16 1 Length(50um) Link length supported for 50/125um fiber, units of 10m 17 1 Length(62.5um) Link length supported for 62.5/125um fiber, units of 10m 18 1 Length(Copper) Link length supported for copper, units of meters 19 1 Reserved 20-35 16 Vendor Name SFP vendor name: ATGBICS 36 1 Reserved 37-39 3 Vendor OUI SFP transceiver vendor OUI ID 40-55 16 Vendor PN Part Number: "AR-SFP-10G-ER-C" (ASCII) 56-59 4 Vendor rev Revision level for part number 60-62 3 Reserved 63 1 CCID Least significant byte of sum of data in address 0-62 Extended ID Fields Indicates which optical SFP signals are implemented (001Ah = LOS, TX_FAULT, TX_DISABLE all supported) 66 1				
13-14 2 Reserved (0000h) 15 1 Length(9um) Link length supported for 9/125um fiber, units of 100m 16 1 Length(50um) Link length supported for 50/125um fiber, units of 10m 17 1 Length(62.5um) Link length supported for 62.5/125um fiber, units of 10m 18 1 Length(Copper) Link length supported for copper, units of meters 19 1 Reserved 20-35 16 Vendor Name SFP vendor name: ATGBICS 36 1 Reserved 37-39 3 Vendor OUI SFP transceiver vendor OUI ID 40-55 16 Vendor PN Part Number: "AR-SFP-10G-ER-C" (ASCII) 56-59 4 Vendor rev Revision level for part number 60-62 3 Reserved 63 1 CCID Least significant byte of sum of data in address 0-62 Extended ID Fields 64-65 2 Option Indicates which optical SFP signals are implemented (001Ah = LOS, TX_FAULT, TX_DISABLE all supported) 66 1 BR,			J	
15 1 Length(9um) Link length supported for 9/125um fiber, units of 100m 16 1 Length(50um) Link length supported for 50/125um fiber, units of 10m 17 1 Length(62.5um) Link length supported for 62.5/125um fiber, units of 10m 18 1 Length(Copper) Link length supported for copper, units of meters 19 1 Reserved 20-35 16 Vendor Name SFP vendor name: ATGBICS 36 1 Reserved 37-39 3 Vendor OUI SFP transceiver vendor OUI ID 40-55 16 Vendor PN Part Number: "AR-SFP-10G-ER-C" (ASCII) 56-59 4 Vendor rev Revision level for part number 60-62 3 Reserved 63 1 CCID Least significant byte of sum of data in address 0-62 Extended ID Fields 64-65 2 Option Indicates which optical SFP signals are implemented (001Ah = LOS, TX_FAULT, TX_DISABLE all supported) 66 1 BR, max Upper bit rate margin, units of % 67 1 BR, min Lower bit rate margin, units of % 68-83 16 Vendor SN Serial number (ASCII) 84-91 8 Date code .'s Manufacturing date code				·
16				, ,
17 1 Length(62.5um) Link length supported for 62.5/125um fiber, units of 10m 18 1 Length(Copper) Link length supported for copper, units of meters 19 1 Reserved 20-35 16 Vendor Name SFP vendor name: ATGBICS 36 1 Reserved 37-39 3 Vendor OUI SFP transceiver vendor OUI ID 40-55 16 Vendor PN Part Number: "AR-SFP-10G-ER-C" (ASCII) 56-59 4 Vendor rev Revision level for part number 60-62 3 Reserved 63 1 CCID Least significant byte of sum of data in address 0-62 Extended ID Fields 64-65 2 Option Indicates which optical SFP signals are implemented (001Ah = LOS, TX_FAULT, TX_DISABLE all supported) 66 1 BR, max Upper bit rate margin, units of % 67 1 BR, min Lower bit rate margin, units of % 68-83 16 Vendor SN Serial number (ASCII) 84-91 8 Date code .'s Manuf			- , ,	
18			<u> </u>	
19 1 Reserved 20-35 16 Vendor Name SFP vendor name: ATGBICS 36 1 Reserved 37-39 3 Vendor OUI SFP transceiver vendor OUI ID 40-55 16 Vendor PN Part Number: "AR-SFP-10G-ER-C" (ASCII) 56-59 4 Vendor rev Revision level for part number 60-62 3 Reserved 63 1 CCID Least significant byte of sum of data in address 0-62 Extended ID Fields 64-65 2 Option Indicates which optical SFP signals are implemented (001Ah = LOS, TX_FAULT, TX_DISABLE all supported) 66 1 BR, max Upper bit rate margin, units of % 67 1 BR, min Lower bit rate margin, units of % 68-83 16 Vendor SN Serial number (ASCII) 84-91 8 Date code .'s Manufacturing date code 92-94 3 Reserved				
20-35 16 Vendor Name SFP vendor name: ATGBICS 36 1 Reserved 37-39 3 Vendor OUI SFP transceiver vendor OUI ID 40-55 16 Vendor PN Part Number: "AR-SFP-10G-ER-C" (ASCII) 56-59 4 Vendor rev Revision level for part number 60-62 3 Reserved 63 1 CCID Least significant byte of sum of data in address 0-62 Extended ID Fields Extended ID Fields 64-65 2 Option Indicates which optical SFP signals are implemented (001Ah = LOS, TX_FAULT, TX_DISABLE all supported) 66 1 BR, max Upper bit rate margin, units of % 67 1 BR, min Lower bit rate margin, units of % 68-83 16 Vendor SN Serial number (ASCII) 84-91 8 Date code .'s Manufacturing date code 92-94 3 Reserved			• ` ' '	Link length supported for copper, units of meters
36 1 Reserved 37-39 3 Vendor OUI SFP transceiver vendor OUI ID 40-55 16 Vendor PN Part Number: "AR-SFP-10G-ER-C" (ASCII) 56-59 4 Vendor rev Revision level for part number 60-62 3 Reserved 63 1 CCID Least significant byte of sum of data in address 0-62 Extended ID Fields Extended ID Fields 64-65 2 Option Indicates which optical SFP signals are implemented (001Ah = LOS, TX_FAULT, TX_DISABLE all supported) 66 1 BR, max Upper bit rate margin, units of % 67 1 BR, min Lower bit rate margin, units of % 68-83 16 Vendor SN Serial number (ASCII) 84-91 8 Date code .'s Manufacturing date code 92-94 3 Reserved				CED vandar nama: ATCRICS
37-39 3 Vendor OUI SFP transceiver vendor OUI ID 40-55 16 Vendor PN Part Number: "AR-SFP-10G-ER-C" (ASCII) 56-59 4 Vendor rev Revision level for part number 60-62 3 Reserved 63 1 CCID Least significant byte of sum of data in address 0-62 Extended ID Fields 64-65 2 Option Indicates which optical SFP signals are implemented (001Ah = LOS, TX_FAULT, TX_DISABLE all supported) 66 1 BR, max Upper bit rate margin, units of % 67 1 BR, min Lower bit rate margin, units of % 68-83 16 Vendor SN Serial number (ASCII) 84-91 8 Date code .'s Manufacturing date code				SEP vendor name: ATGBICS
40-55 16 Vendor PN Part Number: "AR-SFP-10G-ER-C" (ASCII) 56-59 4 Vendor rev Revision level for part number 60-62 3 Reserved 63 1 CCID Least significant byte of sum of data in address 0-62 Extended ID Fields 64-65 2 Option Indicates which optical SFP signals are implemented (001Ah = LOS, TX_FAULT, TX_DISABLE all supported) 66 1 BR, max Upper bit rate margin, units of % 67 1 BR, min Lower bit rate margin, units of % 68-83 16 Vendor SN Serial number (ASCII) 84-91 8 Date code .'s Manufacturing date code				OFD to the CUILD
56-59 4 Vendor rev Revision level for part number 60-62 3 Reserved 63 1 CCID Least significant byte of sum of data in address 0-62 Extended ID Fields 64-65 2 Option Indicates which optical SFP signals are implemented (001Ah = LOS, TX_FAULT, TX_DISABLE all supported) 66 1 BR, max Upper bit rate margin, units of % 67 1 BR, min Lower bit rate margin, units of % 68-83 16 Vendor SN Serial number (ASCII) 84-91 8 Date code .'s Manufacturing date code 92-94 3 Reserved				
60-62 3 Reserved 63 1 CCID Least significant byte of sum of data in address 0-62 Extended ID Fields 64-65 2 Option Indicates which optical SFP signals are implemented (001Ah = LOS, TX_FAULT, TX_DISABLE all supported) 66 1 BR, max Upper bit rate margin, units of % 67 1 BR, min Lower bit rate margin, units of % 68-83 16 Vendor SN Serial number (ASCII) 84-91 8 Date code .'s Manufacturing date code 92-94 3 Reserved				· /
63 1 CCID Least significant byte of sum of data in address 0-62 Extended ID Fields 64-65 2 Option Indicates which optical SFP signals are implemented (001Ah = LOS, TX_FAULT, TX_DISABLE all supported) 66 1 BR, max Upper bit rate margin, units of % 67 1 BR, min Lower bit rate margin, units of % 68-83 16 Vendor SN Serial number (ASCII) 84-91 8 Date code .'s Manufacturing date code 92-94 3 Reserved				Revision level for part number
Extended ID Fields 64-65 2 Option Indicates which optical SFP signals are implemented (001Ah = LOS, TX_FAULT, TX_DISABLE all supported) 66 1 BR, max Upper bit rate margin, units of % 67 1 BR, min Lower bit rate margin, units of % 68-83 16 Vendor SN Serial number (ASCII) 84-91 8 Date code .'s Manufacturing date code 92-94 3 Reserved				
64-65 2 Option Indicates which optical SFP signals are implemented (001Ah = LOS, TX_FAULT, TX_DISABLE all supported) 66 1 BR, max Upper bit rate margin, units of % 67 1 BR, min Lower bit rate margin, units of % 68-83 16 Vendor SN Serial number (ASCII) 84-91 8 Date code .'s Manufacturing date code 92-94 3 Reserved			CCID	Least significant byte of sum of data in address 0-62
(001Ah = LOS, TX_FAULT, TX_DISABLE all supported) 66				
67 1 BR, min Lower bit rate margin, units of % 68-83 16 Vendor SN Serial number (ASCII) 84-91 8 Date code .'s Manufacturing date code 92-94 3 Reserved	64-65	2	Option	
68-83 16 Vendor SN Serial number (ASCII) 84-91 8 Date code .'s Manufacturing date code 92-94 3 Reserved	66	1	BR, max	Upper bit rate margin, units of %
84-91 8 Date code .'s Manufacturing date code 92-94 3 Reserved	67	1	BR, min	Lower bit rate margin, units of %
92-94 3 Reserved	68-83	16	Vendor SN	Serial number (ASCII)
	84-91	8	Date code	.'s Manufacturing date code
95 1 CCEX Check code for the extended ID Fields (addresses 64 to 94)	92-94	3	Reserved	
	95	1	CCEX	Check code for the extended ID Fields (addresses 64 to 94)
Vendor Specific ID Fields				
96-127 32 Readable . specific date, read only	96-127	32	Readable	. specific date, read only
128-255 128 Reserved Reserved for SFF-8079	128-255	128	Reserved	Reserved for SFF-8079



Digital Diagnostic Monitor Characteristics

Data Address	Parameter	Accuracy	Unit
96-97	Transceiver Internal Temperature	±3.0	°C
98-99	VCC3 Internal Supply Voltage	±3.0	%
100-101	Laser Bias Current	±10	%
102-103	Tx Output Power	±3.0	dBm
104-105	Rx Input Power	±3.0	dBm


Regulatory Compliance

The AR-SFP-10G-ER complies with international Electromagnetic Compatibility (EMC) and international safety requirements and standards (see details in Table following).


Electrostatic Discharge (ESD) to the Electrical Pins	MIL-STD-883E Method 3015.7	Class 1(>1000 V)
Electrostatic Discharge (ESD) to the Duplex LC Receptacle	IEC 61000-4-2 GR-1089-CORE	Compatible with standards
Electromagnetic Interference (EMI)	FCC Part 15 Class B EN55022 Class B (CISPR 22B) VCCI Class B	Compatible with standards
Laser Eye Safety	FDA 21CFR 1040.10 and 1040.11 EN60950, EN (IEC) 60825-1,2	Compatible with Class 1 laser product.



Recommended Circuit



Recommended Host Board Power Supply Circuit



Recommended High-speed Interface Circuit



Mechanical Dimensions

